

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013319

Luminaire Tested: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013319
REPORT IS A COMBINATION OF REPORTS P999274 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5959.0 lumens
Efficiency: N/A
Efficacy: 124.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013319

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013319

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	27	27	26
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22
3	76	67	60	55	67	60	54	50	46	42	39	33	31	29	22	20	19
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	19	18	16
5	64	53	45	40	56	47	41	36	37	32	29	27	24	21	17	16	14
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	13	11
8	50	38	31	26	44	35	28	24	27	22	19	20	17	15	13	11	10
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9
10	43	32	25	21	38	29	23	19	23	18	15	17	14	12	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4718	4718	4718
5°	4719	4579	4579
10°	4679	4434	4381
15°	4615	4254	4148
20°	4530	4049	3882
25°	4426	3827	3622
30°	4323	3602	3331
35°	4209	3373	3045
40°	4075	3127	2752
45°	3948	2882	2462
50°	3804	2616	2168
55°	3649	2342	1864
60°	3477	2051	1564
65°	3311	1719	1275
70°	3074	1367	974
75°	2769	995	682
80°	2316	610	491
85°	1739	351	268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3948 cd/sqm

TEST NUMBER: P1013319

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.4	0.9
10°-20°	151.7	2.5
20°-30°	219.0	3.7
30°-40°	248.2	4.2
40°-50°	239.7	4.0
50°-60°	199.3	3.3
60°-70°	137.5	2.3
70°-80°	69.5	1.2
80°-90°	20.7	0.3
90°-100°	49.5	0.8
100°-110°	326.3	5.5
110°-120°	623.1	10.5
120°-130°	791.0	13.3
130°-140°	846.2	14.2
140°-150°	791.3	13.3
150°-160°	638.1	10.7
160°-170°	411.5	6.9
170°-180°	141.8	2.4
0°-30°	425.2	7.1
0°-40°	673.4	11.3
0°-60°	1112.3	18.7
0°-90°	1340.1	22.5
90°-120°	999.0	16.8
90°-150°	3427.5	57.5
90°-180°	4619.0	77.5
0°-180°	5959.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	579	579	579	579	579	
5°	578	576	571	575	574	55
15°	550	546	535	534	531	155
25°	498	490	471	464	460	229
35°	430	416	394	379	371	269
45°	351	334	308	286	278	271
55°	266	248	219	196	188	238
65°	181	162	133	114	109	179
75°	96	80	59	49	46	101
85°	24	15	14	13	13	26
90°	3	16	25	31	34	5
95°	61	23	25	31	32	76
105°	336	343	348	358	318	352
115°	627	631	630	632	632	618
125°	882	886	884	888	889	788
135°	1094	1093	1098	1100	1102	843
145°	1262	1265	1265	1266	1268	788
155°	1383	1384	1381	1386	1382	638
165°	1459	1454	1454	1462	1452	412
175°	1493	1486	1487	1497	1484	142
180°	1493	1493	1493	1493	1493	

TEST NUMBER: P1013319

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	578.6	578.6	578.6	578.6	578.6
2.5°	580.4	578.6	573.8	578.6	578.2
5°	577.7	576.0	570.7	575.1	574.2
7.5°	573.8	572.0	565.3	568.4	567.1
10°	567.6	565.3	557.4	559.1	557.4
12.5°	559.6	556.9	547.2	548.1	545.4
15°	550.3	546.3	535.2	534.3	531.2
17.5°	539.6	533.9	521.0	518.8	514.4
20°	526.8	521.0	506.0	502.4	496.7
22.5°	512.6	506.0	489.6	483.8	479.4
25°	497.6	489.6	471.4	463.9	459.5
27.5°	482.0	472.3	453.3	444.4	438.2
30°	465.7	454.6	433.8	422.7	415.6
32.5°	448.4	435.5	413.8	400.5	393.9
35°	430.2	416.0	393.9	378.8	370.8
37.5°	411.2	396.5	372.2	355.8	347.8
40°	390.8	376.2	350.9	332.3	324.3
42.5°	371.3	355.8	329.2	310.1	301.7
45°	350.9	334.5	307.9	286.2	278.2
47.5°	330.1	313.2	285.8	263.2	254.3
50°	308.8	291.5	263.2	241.0	232.6
52.5°	287.1	270.3	241.0	218.4	209.6
55°	265.8	248.1	219.3	196.3	187.9
57.5°	245.0	226.4	198.0	174.6	168.4
60°	222.4	204.7	176.3	153.3	146.2
62.5°	202.0	183.4	154.2	133.4	128.0
65°	180.8	161.7	133.4	114.3	109.0
67.5°	158.6	140.4	113.9	97.0	90.8
70°	137.8	119.2	93.9	79.3	74.9
72.5°	115.6	99.2	75.8	63.8	59.8
75°	96.1	79.8	58.9	48.7	46.1
77.5°	75.8	61.6	43.9	36.8	35.9
80°	56.3	43.4	30.1	28.8	28.4
82.5°	39.4	27.9	21.7	20.8	20.4
85°	23.9	15.1	13.7	12.8	12.8
87.5°	10.2	6.6	6.2	5.8	6.2
90°	3.3	15.6	24.6	31.3	33.5
92.5°	16.7	14.5	23.4	30.1	30.1
95°	61.4	23.4	24.6	31.3	32.4
97.5°	117.2	141.8	24.6	30.1	31.3
100°	183.1	203.2	49.1	30.1	31.3
102.5°	256.8	270.2	283.6	32.4	32.4
105°	336.1	342.7	348.3	358.4	318.2
107.5°	408.6	412.0	419.8	425.4	429.8
110°	482.3	485.7	492.4	494.6	497.9

TEST NUMBER: P1013319

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	553.8	560.5	562.7	561.6	566.0
115°	627.4	630.8	629.7	631.9	631.9
117.5°	693.3	697.8	701.1	700.0	700.0
120°	760.3	764.8	763.7	765.9	763.7
122.5°	822.8	825.1	827.3	828.4	826.2
125°	882.0	886.5	884.2	887.6	888.7
127.5°	938.9	940.1	945.6	944.5	943.4
130°	993.6	994.8	998.1	999.2	999.2
132.5°	1043.9	1046.1	1050.6	1051.7	1050.6
135°	1094.1	1093.0	1097.5	1099.7	1101.9
137.5°	1138.8	1138.8	1144.4	1146.6	1145.5
140°	1182.3	1184.6	1186.8	1190.1	1191.3
142.5°	1221.4	1225.9	1227.0	1229.2	1229.2
145°	1261.6	1264.9	1264.9	1266.1	1268.3
147.5°	1292.8	1299.5	1298.4	1299.5	1300.7
150°	1327.5	1331.9	1330.8	1330.8	1331.9
152.5°	1356.5	1359.8	1357.6	1359.8	1358.7
155°	1383.3	1384.4	1381.0	1385.5	1382.2
157.5°	1406.7	1406.7	1402.3	1407.8	1402.3
160°	1426.8	1423.5	1422.4	1429.1	1422.4
162.5°	1444.7	1440.2	1439.1	1445.8	1438.0
165°	1459.2	1453.6	1453.6	1462.5	1452.5
167.5°	1471.5	1465.9	1464.8	1474.8	1463.7
170°	1481.5	1474.8	1475.9	1484.9	1473.7
172.5°	1488.2	1481.5	1482.6	1491.6	1479.3
175°	1492.7	1486.0	1487.1	1497.2	1483.8
177.5°	1496.0	1488.2	1490.5	1499.4	1486.0
180°	1492.7	1492.7	1492.7	1492.7	1492.7

(END OF REPORT)