

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013325

Luminaire Tested: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013325
REPORT IS A COMBINATION OF REPORTS P999311 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_3000K
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2862.0 lumens
Efficiency: N/A
Efficacy: 128.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013325

CATALOG NUMBER: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013325

CATALOG NUMBER: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	98	94	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	41	40
3	82	72	65	59	75	67	61	56	57	52	48	47	44	41	39	36	34
4	75	64	56	50	69	59	53	47	51	45	41	42	38	35	35	32	30
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	51	43	38	58	48	41	35	41	35	31	34	30	27	28	25	23
7	59	46	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20
8	54	42	35	29	50	39	32	28	34	28	25	29	25	21	24	21	18
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17
10	47	35	28	23	44	33	27	22	29	23	20	25	20	18	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4906	4906	4906
5°	4906	4760	4761
10°	4865	4610	4555
15°	4798	4422	4312
20°	4710	4209	4036
25°	4601	3979	3766
30°	4493	3744	3463
35°	4376	3507	3166
40°	4236	3251	2862
45°	4104	2996	2560
50°	3956	2719	2254
55°	3794	2435	1938
60°	3614	2133	1626
65°	3441	1786	1325
70°	3197	1423	1012
75°	2882	1035	708
80°	2406	635	510
85°	1812	366	281

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4104 cd/sqm

TEST NUMBER: P1013325

CATALOG NUMBER: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.6	2.0
10°-20°	157.7	5.5
20°-30°	227.7	8.0
30°-40°	258.1	9.0
40°-50°	249.2	8.7
50°-60°	207.2	7.2
60°-70°	143.0	5.0
70°-80°	72.3	2.5
80°-90°	19.3	0.7
90°-100°	15.8	0.6
100°-110°	103.9	3.6
110°-120°	198.4	6.9
120°-130°	251.9	8.8
130°-140°	269.5	9.4
140°-150°	252.0	8.8
150°-160°	203.2	7.1
160°-170°	131.1	4.6
170°-180°	45.2	1.6
0°-30°	442.0	15.4
0°-40°	700.1	24.5
0°-60°	1156.4	40.4
0°-90°	1391.0	48.6
90°-120°	318.1	11.1
90°-150°	1091.6	38.1
90°-180°	1471.0	51.4
0°-180°	2862.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	602	602	602	602	602	
5°	601	599	593	598	597	57
15°	572	568	556	556	552	161
25°	517	509	490	482	478	238
35°	447	432	410	394	386	280
45°	365	348	320	298	289	281
55°	276	258	228	204	195	247
65°	188	168	139	119	113	186
75°	100	83	61	51	48	105
85°	25	16	14	13	13	27
90°	1	5	8	10	11	2
95°	20	8	8	10	10	24
105°	107	109	111	114	101	112
115°	200	201	200	201	201	197
125°	281	282	282	283	283	251
135°	348	348	350	350	351	269
145°	402	403	403	403	404	251
155°	440	441	440	441	440	203
165°	465	463	463	466	463	131
175°	475	473	474	477	472	45
180°	475	475	475	475	475	

TEST NUMBER: P1013325

CATALOG NUMBER: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	601.6	601.6	601.6	601.6	601.6
2.5°	603.4	601.6	596.5	601.6	601.1
5°	600.7	598.8	593.3	597.9	597.0
7.5°	596.5	594.7	587.8	591.0	589.6
10°	590.1	587.8	579.5	581.3	579.5
12.5°	581.8	579.0	568.9	569.8	567.0
15°	572.1	567.9	556.4	555.5	552.3
17.5°	561.0	555.1	541.7	539.4	534.8
20°	547.7	541.7	526.0	522.3	516.4
22.5°	532.9	526.0	509.0	503.0	498.4
25°	517.3	509.0	490.1	482.3	477.7
27.5°	501.2	491.0	471.2	462.0	455.6
30°	484.1	472.6	450.9	439.4	432.1
32.5°	466.2	452.8	430.2	416.4	409.5
35°	447.3	432.5	409.5	393.8	385.5
37.5°	427.5	412.3	386.9	369.9	361.6
40°	406.3	391.1	364.8	345.5	337.2
42.5°	386.0	369.9	342.2	322.4	313.7
45°	364.8	347.8	320.1	297.6	289.3
47.5°	343.2	325.7	297.1	273.6	264.4
50°	321.1	303.1	273.6	250.6	241.8
52.5°	298.5	281.0	250.6	227.1	217.9
55°	276.4	257.9	228.0	204.1	195.3
57.5°	254.7	235.4	205.9	181.5	175.0
60°	231.2	212.8	183.3	159.4	152.0
62.5°	210.0	190.7	160.3	138.6	133.1
65°	187.9	168.1	138.6	118.8	113.3
67.5°	164.9	146.0	118.4	100.9	94.4
70°	143.3	123.9	97.7	82.5	77.8
72.5°	120.2	103.2	78.8	66.3	62.2
75°	100.0	82.9	61.3	50.7	47.9
77.5°	78.8	64.0	45.6	38.2	37.3
80°	58.5	45.1	31.3	29.9	29.5
82.5°	41.0	29.0	22.6	21.6	21.2
85°	24.9	15.7	14.3	13.4	13.4
87.5°	10.6	6.9	6.4	6.0	6.4
90°	1.1	5.0	7.8	10.0	10.7
92.5°	5.3	4.6	7.5	9.6	9.6
95°	19.6	7.5	7.8	10.0	10.3
97.5°	37.3	45.2	7.8	9.6	10.0
100°	58.3	64.7	15.6	9.6	10.0
102.5°	81.8	86.0	90.3	10.3	10.3
105°	107.0	109.2	110.9	114.1	101.3
107.5°	130.1	131.2	133.7	135.5	136.9
110°	153.6	154.7	156.8	157.5	158.6



TEST NUMBER: P1013325

CATALOG NUMBER: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	176.4	178.5	179.2	178.8	180.3
115°	199.8	200.9	200.5	201.2	201.2
117.5°	220.8	222.2	223.3	222.9	222.9
120°	242.1	243.6	243.2	243.9	243.2
122.5°	262.1	262.8	263.5	263.8	263.1
125°	280.9	282.3	281.6	282.7	283.0
127.5°	299.0	299.4	301.2	300.8	300.5
130°	316.5	316.8	317.9	318.2	318.2
132.5°	332.5	333.2	334.6	334.9	334.6
135°	348.5	348.1	349.5	350.2	350.9
137.5°	362.7	362.7	364.5	365.2	364.8
140°	376.5	377.3	378.0	379.0	379.4
142.5°	389.0	390.4	390.8	391.5	391.5
145°	401.8	402.9	402.9	403.2	403.9
147.5°	411.7	413.9	413.5	413.9	414.2
150°	422.8	424.2	423.8	423.8	424.2
152.5°	432.0	433.1	432.4	433.1	432.7
155°	440.5	440.9	439.8	441.3	440.2
157.5°	448.0	448.0	446.6	448.4	446.6
160°	454.4	453.3	453.0	455.1	453.0
162.5°	460.1	458.7	458.3	460.5	458.0
165°	464.7	462.9	462.9	465.8	462.6
167.5°	468.6	466.9	466.5	469.7	466.1
170°	471.8	469.7	470.1	472.9	469.3
172.5°	474.0	471.8	472.2	475.0	471.1
175°	475.4	473.3	473.6	476.8	472.5
177.5°	476.5	474.0	474.7	477.5	473.3
180°	475.4	475.4	475.4	475.4	475.4

(END OF REPORT)