

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025945

Luminaire Tested: S124RDIP-B1020D1035UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025945
REPORT IS A COMBINATION OF REPORTS P998845 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1020D1035UB35-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7728.0 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025945

CATALOG NUMBER: S124RDIP-B1020D1035UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1025945

CATALOG NUMBER: S124RDIP-B1020D1035UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51
2	90	83	77	72	84	77	72	68	66	63	59	56	54	51	47	45	43
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	39	37
4	76	65	57	51	70	61	54	48	52	47	43	45	41	38	38	35	32
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28
6	64	52	44	38	59	49	42	36	43	37	33	37	32	29	31	28	25
7	59	47	39	34	55	44	37	32	39	33	29	33	29	26	28	25	22
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14699	14699	14699
5°	14700	14262	14264
10°	14576	13812	13648
15°	14375	13252	12922
20°	14113	12613	12093
25°	13785	11923	11284
30°	13464	11220	10375
35°	13112	10508	9487
40°	12692	9740	8574
45°	12298	8979	7671
50°	11851	8148	6753
55°	11367	7296	5807
60°	10831	6391	4872
65°	10312	5353	3970
70°	9575	4261	3035
75°	8631	3101	2122
80°	7210	1904	1525
85°	5421	1097	838

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12298 cd/sqm

TEST NUMBER: P1025945

CATALOG NUMBER: S124RDIP-B1020D1035UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.5	2.2
10°-20°	472.6	6.1
20°-30°	682.3	8.8
30°-40°	773.3	10.0
40°-50°	746.6	9.7
50°-60°	620.7	8.0
60°-70°	428.4	5.5
70°-80°	216.5	2.8
80°-90°	57.7	0.7
90°-100°	83.6	1.1
100°-110°	250.5	3.2
110°-120°	425.6	5.5
120°-130°	561.3	7.3
130°-140°	630.4	8.2
140°-150°	619.6	8.0
150°-160°	521.1	6.7
160°-170°	346.7	4.5
170°-180°	121.4	1.6
0°-30°	1324.4	17.1
0°-40°	2097.7	27.1
0°-60°	3465.1	44.8
0°-90°	4167.7	53.9
90°-120°	759.7	9.8
90°-150°	2571.0	33.3
90°-180°	3560.0	46.1
0°-180°	7728.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1803	1803	1803	1803	1803	
5°	1800	1794	1778	1792	1789	171
15°	1714	1702	1667	1664	1655	483
25°	1550	1525	1468	1445	1431	714
35°	1340	1296	1227	1180	1155	838
45°	1093	1042	959	892	867	843
55°	828	773	683	611	585	741
65°	563	504	415	356	340	556
75°	300	248	184	152	144	316
85°	74	47	43	40	40	82
90°	3	14	22	28	30	9
95°	60	68	75	78	78	64
105°	231	232	236	239	242	245
115°	433	433	431	430	429	427
125°	630	630	629	627	625	562
135°	813	819	819	817	814	629
145°	987	991	992	991	988	618
155°	1131	1131	1130	1134	1130	521
165°	1232	1229	1227	1232	1229	347
175°	1281	1276	1275	1282	1275	122
180°	1283	1283	1283	1283	1283	

TEST NUMBER: P1025945

CATALOG NUMBER: S124RDIP-B1020D1035UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1802.6	1802.6	1802.6	1802.6	1802.6
2.5°	1808.1	1802.6	1787.4	1802.6	1801.2
5°	1799.8	1794.3	1777.7	1791.5	1788.8
7.5°	1787.4	1781.9	1761.2	1770.8	1766.7
10°	1768.1	1761.2	1736.3	1741.8	1736.3
12.5°	1743.2	1734.9	1704.6	1707.3	1699.0
15°	1714.2	1701.8	1667.3	1664.5	1654.9
17.5°	1681.1	1663.2	1623.1	1616.2	1602.4
20°	1641.1	1623.1	1576.2	1565.2	1547.2
22.5°	1596.9	1576.2	1525.1	1507.2	1493.4
25°	1550.0	1525.1	1468.5	1445.1	1431.3
27.5°	1501.7	1471.3	1412.0	1384.4	1365.0
30°	1450.6	1416.1	1351.2	1316.7	1294.6
32.5°	1396.8	1356.7	1289.1	1247.7	1227.0
35°	1340.2	1296.0	1227.0	1180.1	1155.2
37.5°	1280.8	1235.3	1159.4	1108.3	1083.5
40°	1217.3	1171.8	1093.1	1035.2	1010.3
42.5°	1156.6	1108.3	1025.5	966.1	939.9
45°	1093.1	1042.1	959.2	891.6	866.8
47.5°	1028.3	975.8	890.2	819.8	792.2
50°	962.0	908.2	819.8	750.8	724.6
52.5°	894.4	841.9	750.8	680.4	652.8
55°	828.1	772.9	683.2	611.4	585.2
57.5°	763.3	705.3	617.0	543.8	524.5
60°	692.9	637.7	549.3	477.6	455.5
62.5°	629.4	571.4	480.3	415.4	398.9
65°	563.1	503.8	415.4	356.1	339.5
67.5°	494.1	437.5	354.7	302.3	282.9
70°	429.2	371.3	292.6	247.1	233.3
72.5°	360.2	309.2	236.0	198.8	186.3
75°	299.5	248.4	183.6	151.8	143.5
77.5°	236.0	191.8	136.6	114.6	111.8
80°	175.3	135.3	93.9	89.7	88.3
82.5°	122.8	87.0	67.6	64.9	63.5
85°	74.5	46.9	42.8	40.0	40.0
87.5°	31.7	20.7	19.3	17.9	19.3
90°	3.0	13.9	21.8	27.8	29.8
92.5°	25.8	38.7	43.7	46.6	47.6
95°	59.5	68.5	75.4	78.4	78.4
97.5°	95.3	103.2	111.1	115.1	115.1
100°	138.9	142.9	151.8	153.8	153.8
102.5°	184.6	185.6	193.5	196.5	197.5
105°	231.2	232.2	236.2	239.2	242.1
107.5°	279.9	280.8	281.8	285.8	284.8
110°	329.5	331.5	330.5	328.5	331.5

TEST NUMBER: P1025945

CATALOG NUMBER: S124RDIP-B1020D1035UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	381.1	381.1	379.1	379.1	379.1
115°	432.7	432.7	430.7	429.7	428.7
117.5°	481.3	481.3	480.3	477.3	474.4
120°	529.9	533.9	530.9	526.0	527.9
122.5°	580.5	581.5	580.5	577.6	572.6
125°	630.2	630.2	629.2	627.2	625.2
127.5°	674.8	677.8	675.8	673.8	672.8
130°	722.5	725.4	725.4	723.4	719.5
132.5°	771.1	773.1	772.1	770.1	769.1
135°	812.8	818.7	818.7	816.7	813.8
137.5°	859.4	862.4	864.4	861.4	862.4
140°	906.0	908.0	908.0	907.0	906.0
142.5°	948.7	950.7	949.7	949.7	949.7
145°	987.4	991.4	992.4	991.4	988.4
147.5°	1027.1	1032.1	1031.1	1030.1	1029.1
150°	1062.8	1066.8	1066.8	1066.8	1065.8
152.5°	1096.6	1098.6	1099.6	1102.5	1099.6
155°	1131.3	1131.3	1130.3	1134.3	1130.3
157.5°	1161.1	1159.1	1159.1	1162.1	1159.1
160°	1186.9	1185.9	1184.9	1187.9	1182.9
162.5°	1210.7	1207.7	1206.7	1212.7	1207.7
165°	1231.5	1228.6	1226.6	1232.5	1228.6
167.5°	1248.4	1244.4	1244.4	1250.4	1244.4
170°	1262.3	1257.3	1258.3	1264.3	1257.3
172.5°	1272.2	1268.3	1268.3	1275.2	1268.3
175°	1281.2	1276.2	1275.2	1282.2	1275.2
177.5°	1285.1	1280.2	1280.2	1287.1	1279.2
180°	1283.1	1283.1	1283.1	1283.1	1283.1

(END OF REPORT)