

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013326

Luminaire Tested: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013326
REPORT IS A COMBINATION OF REPORTS P999312 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2874.0 lumens
Efficiency: N/A
Efficacy: 128.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013326

CATALOG NUMBER: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1013326

CATALOG NUMBER: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	98	94	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	41	40
3	82	72	65	59	75	67	61	56	57	52	48	47	44	41	39	36	34
4	75	64	56	50	69	59	53	47	51	45	41	42	38	35	35	32	30
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	51	43	38	58	48	41	35	41	35	31	34	30	27	28	25	23
7	59	46	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20
8	54	42	35	29	50	39	32	28	34	28	25	29	25	21	24	21	18
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17
10	47	35	28	24	44	33	27	22	29	23	20	25	20	18	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4927	4927	4927
5°	4927	4780	4781
10°	4885	4630	4575
15°	4819	4441	4331
20°	4730	4228	4053
25°	4620	3996	3782
30°	4513	3761	3477
35°	4395	3522	3180
40°	4254	3265	2874
45°	4122	3010	2571
50°	3972	2731	2264
55°	3811	2446	1946
60°	3630	2142	1633
65°	3456	1794	1331
70°	3210	1429	1017
75°	2893	1039	711
80°	2418	639	511
85°	1819	366	281

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4122 cd/sqm

TEST NUMBER: P1013326

CATALOG NUMBER: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.8	2.0
10°-20°	158.4	5.5
20°-30°	228.7	8.0
30°-40°	259.2	9.0
40°-50°	250.3	8.7
50°-60°	208.1	7.2
60°-70°	143.6	5.0
70°-80°	72.6	2.5
80°-90°	19.4	0.7
90°-100°	15.8	0.6
100°-110°	104.3	3.6
110°-120°	199.2	6.9
120°-130°	252.9	8.8
130°-140°	270.6	9.4
140°-150°	253.0	8.8
150°-160°	204.0	7.1
160°-170°	131.6	4.6
170°-180°	45.4	1.6
0°-30°	443.9	15.4
0°-40°	703.1	24.5
0°-60°	1161.4	40.4
0°-90°	1397.0	48.6
90°-120°	319.4	11.1
90°-150°	1096.0	38.1
90°-180°	1477.0	51.4
0°-180°	2874.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	604	604	604	604	604	
5°	603	601	596	600	600	57
15°	575	570	559	558	555	162
25°	520	511	492	484	480	239
35°	449	434	411	396	387	281
45°	366	349	322	299	290	283
55°	278	259	229	205	196	248
65°	189	169	139	119	114	186
75°	100	83	62	51	48	106
85°	25	16	14	13	13	27
90°	1	5	8	10	11	2
95°	20	8	8	10	10	24
105°	108	110	111	115	102	112
115°	201	202	201	202	202	197
125°	282	284	283	284	284	252
135°	350	350	351	352	352	270
145°	403	404	404	405	406	252
155°	442	443	442	443	442	204
165°	467	465	465	468	464	132
175°	477	475	476	479	474	45
180°	477	477	477	477	477	

TEST NUMBER: P1013326

CATALOG NUMBER: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	604.2	604.2	604.2	604.2	604.2
2.5°	606.0	604.2	599.1	604.2	603.7
5°	603.2	601.4	595.8	600.5	599.5
7.5°	599.1	597.2	590.3	593.5	592.1
10°	592.6	590.3	582.0	583.8	582.0
12.5°	584.3	581.5	571.3	572.3	569.5
15°	574.6	570.4	558.8	557.9	554.7
17.5°	563.5	557.4	544.0	541.7	537.1
20°	550.0	544.0	528.3	524.6	518.6
22.5°	535.2	528.3	511.2	505.2	500.5
25°	519.5	511.2	492.2	484.4	479.7
27.5°	503.3	493.1	473.3	464.0	457.5
30°	486.2	474.6	452.9	441.3	433.9
32.5°	468.2	454.7	432.1	418.2	411.3
35°	449.2	434.4	411.3	395.5	387.2
37.5°	429.3	414.0	388.6	371.5	363.1
40°	408.0	392.8	366.4	347.0	338.6
42.5°	387.7	371.5	343.7	323.8	315.0
45°	366.4	349.3	321.5	298.8	290.5
47.5°	344.6	327.1	298.4	274.8	265.5
50°	322.4	304.4	274.8	251.7	242.9
52.5°	299.8	282.2	251.7	228.1	218.8
55°	277.6	259.1	229.0	204.9	196.1
57.5°	255.8	236.4	206.8	182.3	175.8
60°	232.2	213.7	184.1	160.1	152.7
62.5°	211.0	191.5	161.0	139.2	133.7
65°	188.7	168.9	139.2	119.4	113.8
67.5°	165.6	146.6	118.9	101.3	94.8
70°	143.9	124.4	98.1	82.8	78.2
72.5°	120.7	103.6	79.1	66.6	62.5
75°	100.4	83.3	61.5	50.9	48.1
77.5°	79.1	64.3	45.8	38.4	37.5
80°	58.8	45.3	31.5	30.1	29.6
82.5°	41.2	29.1	22.7	21.7	21.3
85°	25.0	15.7	14.3	13.4	13.4
87.5°	10.6	6.9	6.5	6.0	6.5
90°	1.1	5.0	7.9	10.0	10.7
92.5°	5.4	4.6	7.5	9.6	9.6
95°	19.6	7.5	7.9	10.0	10.4
97.5°	37.5	45.3	7.9	9.6	10.0
100°	58.6	65.0	15.7	9.6	10.0
102.5°	82.1	86.4	90.7	10.4	10.4
105°	107.5	109.6	111.4	114.6	101.7
107.5°	130.7	131.7	134.2	136.0	137.4
110°	154.2	155.3	157.4	158.2	159.2



TEST NUMBER: P1013326

CATALOG NUMBER: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	177.1	179.2	179.9	179.6	181.0
115°	200.6	201.7	201.4	202.1	202.1
117.5°	221.7	223.1	224.2	223.8	223.8
120°	243.1	244.6	244.2	244.9	244.2
122.5°	263.1	263.8	264.5	264.9	264.2
125°	282.0	283.5	282.8	283.8	284.2
127.5°	300.2	300.6	302.4	302.0	301.7
130°	317.7	318.1	319.2	319.5	319.5
132.5°	333.8	334.5	335.9	336.3	335.9
135°	349.9	349.5	350.9	351.7	352.4
137.5°	364.2	364.2	365.9	366.7	366.3
140°	378.1	378.8	379.5	380.6	380.9
142.5°	390.6	392.0	392.4	393.1	393.1
145°	403.4	404.5	404.5	404.9	405.6
147.5°	413.4	415.6	415.2	415.6	415.9
150°	424.5	425.9	425.6	425.6	425.9
152.5°	433.8	434.8	434.1	434.8	434.5
155°	442.3	442.7	441.6	443.1	442.0
157.5°	449.8	449.8	448.4	450.2	448.4
160°	456.3	455.2	454.8	457.0	454.8
162.5°	462.0	460.5	460.2	462.3	459.8
165°	466.6	464.8	464.8	467.7	464.5
167.5°	470.5	468.8	468.4	471.6	468.0
170°	473.8	471.6	472.0	474.8	471.3
172.5°	475.9	473.8	474.1	477.0	473.0
175°	477.3	475.2	475.5	478.8	474.5
177.5°	478.4	475.9	476.6	479.5	475.2
180°	477.3	477.3	477.3	477.3	477.3

(END OF REPORT)