

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013327

Luminaire Tested: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013327
REPORT IS A COMBINATION OF REPORTS P999313 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_4000K
Description: Define 4 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2847.0 lumens
Efficiency: N/A
Efficacy: 127.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013327

CATALOG NUMBER: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013327

CATALOG NUMBER: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55			49
1	98	94	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47			41
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	41	40			35
3	82	72	65	59	75	67	61	56	57	52	48	47	44	41	39	36	34			30
4	75	64	56	50	69	59	53	47	51	45	41	42	38	35	35	32	30			26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26			23
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23			20
7	59	46	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20			18
8	54	42	35	29	50	39	32	28	34	28	25	29	25	21	24	21	18			16
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17			15
10	47	35	28	24	44	33	27	22	29	23	20	25	20	18	21	17	15			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4880	4880	4880
5°	4881	4736	4737
10°	4840	4586	4531
15°	4773	4400	4291
20°	4686	4188	4016
25°	4578	3959	3747
30°	4471	3726	3445
35°	4354	3489	3150
40°	4214	3235	2847
45°	4084	2981	2547
50°	3935	2705	2242
55°	3775	2423	1928
60°	3597	2122	1617
65°	3425	1777	1318
70°	3179	1415	1008
75°	2867	1030	705
80°	2394	633	506
85°	1797	364	279

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4084 cd/sqm

TEST NUMBER: P1013327

CATALOG NUMBER: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.3	2.0
10°-20°	156.9	5.5
20°-30°	226.6	8.0
30°-40°	256.8	9.0
40°-50°	247.9	8.7
50°-60°	206.1	7.2
60°-70°	142.3	5.0
70°-80°	71.9	2.5
80°-90°	19.2	0.7
90°-100°	15.7	0.6
100°-110°	103.4	3.6
110°-120°	197.4	6.9
120°-130°	250.5	8.8
130°-140°	268.0	9.4
140°-150°	250.6	8.8
150°-160°	202.1	7.1
160°-170°	130.3	4.6
170°-180°	44.9	1.6
0°-30°	439.8	15.4
0°-40°	696.6	24.5
0°-60°	1150.6	40.4
0°-90°	1384.0	48.6
90°-120°	316.4	11.1
90°-150°	1085.6	38.1
90°-180°	1463.0	51.4
0°-180°	2847.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	598	598	598	598	598	
5°	598	596	590	595	594	57
15°	569	565	554	553	550	160
25°	515	506	488	480	475	237
35°	445	430	407	392	384	278
45°	363	346	318	296	288	280
55°	275	257	227	203	194	246
65°	187	167	138	118	113	185
75°	100	82	61	50	48	105
85°	25	16	14	13	13	27
90°	1	5	8	10	11	2
95°	19	7	8	10	10	24
105°	106	109	110	114	101	111
115°	199	200	199	200	200	196
125°	279	281	280	281	282	249
135°	347	346	348	348	349	267
145°	400	401	401	401	402	250
155°	438	438	437	439	438	202
165°	462	460	460	463	460	131
175°	473	471	471	474	470	45
180°	473	473	473	473	473	

TEST NUMBER: P1013327

CATALOG NUMBER: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	598.5	598.5	598.5	598.5	598.5
2.5°	600.4	598.5	593.5	598.5	598.1
5°	597.6	595.8	590.3	594.9	594.0
7.5°	593.5	591.7	584.8	588.0	586.6
10°	587.1	584.8	576.5	578.4	576.5
12.5°	578.8	576.1	566.0	566.9	564.2
15°	569.2	565.1	553.6	552.7	549.5
17.5°	558.2	552.3	539.0	536.7	532.1
20°	544.9	539.0	523.4	519.7	513.8
22.5°	530.3	523.4	506.4	500.5	495.9
25°	514.7	506.4	487.6	479.8	475.3
27.5°	498.6	488.6	468.8	459.7	453.3
30°	481.7	470.2	448.7	437.2	429.9
32.5°	463.8	450.5	428.1	414.3	407.4
35°	445.0	430.3	407.4	391.8	383.6
37.5°	425.3	410.2	385.0	368.0	359.8
40°	404.2	389.1	363.0	343.7	335.5
42.5°	384.1	368.0	340.5	320.8	312.1
45°	363.0	346.0	318.5	296.1	287.8
47.5°	341.4	324.0	295.6	272.2	263.1
50°	319.4	301.6	272.2	249.3	240.6
52.5°	297.0	279.6	249.3	225.9	216.8
55°	275.0	256.6	226.9	203.0	194.3
57.5°	253.4	234.2	204.9	180.6	174.2
60°	230.1	211.7	182.4	158.6	151.2
62.5°	209.0	189.7	159.5	137.9	132.4
65°	187.0	167.3	137.9	118.2	112.7
67.5°	164.1	145.3	117.8	100.4	94.0
70°	142.5	123.3	97.2	82.0	77.5
72.5°	119.6	102.7	78.4	66.0	61.9
75°	99.5	82.5	61.0	50.4	47.7
77.5°	78.4	63.7	45.4	38.0	37.1
80°	58.2	44.9	31.2	29.8	29.3
82.5°	40.8	28.9	22.5	21.5	21.1
85°	24.7	15.6	14.2	13.3	13.3
87.5°	10.5	6.9	6.4	6.0	6.4
90°	1.1	5.0	7.8	9.9	10.6
92.5°	5.3	4.6	7.4	9.5	9.5
95°	19.4	7.4	7.8	9.9	10.3
97.5°	37.1	44.9	7.8	9.5	9.9
100°	58.0	64.4	15.6	9.5	9.9
102.5°	81.3	85.6	89.8	10.3	10.3
105°	106.4	108.6	110.3	113.5	100.8
107.5°	129.4	130.5	133.0	134.7	136.1
110°	152.8	153.8	156.0	156.7	157.7

TEST NUMBER: P1013327

CATALOG NUMBER: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	175.4	177.5	178.2	177.9	179.3
115°	198.7	199.8	199.4	200.2	200.2
117.5°	219.6	221.0	222.1	221.7	221.7
120°	240.8	242.2	241.9	242.6	241.9
122.5°	260.6	261.3	262.0	262.4	261.7
125°	279.4	280.8	280.1	281.1	281.5
127.5°	297.4	297.8	299.5	299.2	298.8
130°	314.7	315.1	316.1	316.5	316.5
132.5°	330.6	331.4	332.8	333.1	332.8
135°	346.6	346.2	347.6	348.3	349.0
137.5°	360.7	360.7	362.5	363.2	362.8
140°	374.5	375.2	375.9	377.0	377.3
142.5°	386.9	388.3	388.6	389.3	389.3
145°	399.6	400.7	400.7	401.0	401.7
147.5°	409.5	411.6	411.3	411.6	412.0
150°	420.5	421.9	421.5	421.5	421.9
152.5°	429.7	430.7	430.0	430.7	430.4
155°	438.1	438.5	437.4	438.9	437.8
157.5°	445.6	445.6	444.2	445.9	444.2
160°	451.9	450.9	450.5	452.6	450.5
162.5°	457.6	456.2	455.8	458.0	455.5
165°	462.2	460.4	460.4	463.3	460.1
167.5°	466.1	464.3	464.0	467.1	463.6
170°	469.3	467.1	467.5	470.3	466.8
172.5°	471.4	469.3	469.6	472.5	468.6
175°	472.8	470.7	471.0	474.2	470.0
177.5°	473.9	471.4	472.1	474.9	470.7
180°	472.8	472.8	472.8	472.8	472.8

(END OF REPORT)