

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013343

Luminaire Tested: S124RDIP-B350D810UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013343
REPORT IS A COMBINATION OF REPORTS P999390 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D810UB2750-4F0-XX-W2A-F_2700K
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4512.0 lumens
Efficiency: N/A
Efficacy: 132.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013343

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1013343

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38
1	94	89	86	82	84	81	77	75	64	62	60	48	47	46	34	33	33
2	85	78	72	68	76	71	66	61	56	53	50	43	40	38	30	29	28
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24
4	71	61	53	48	64	55	49	44	44	39	36	34	31	28	24	22	21
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	20	18
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	18	16
7	56	44	36	31	50	40	33	28	32	27	24	25	21	19	18	16	14
8	51	40	32	27	46	36	30	25	29	24	21	23	19	17	17	14	13
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4863	4863	4863
5°	4864	4719	4719
10°	4823	4570	4516
15°	4757	4384	4275
20°	4670	4173	4001
25°	4561	3945	3733
30°	4454	3713	3432
35°	4338	3477	3139
40°	4200	3223	2837
45°	4069	2971	2538
50°	3921	2695	2234
55°	3761	2414	1921
60°	3583	2114	1612
65°	3412	1772	1313
70°	3168	1410	1004
75°	2856	1025	702
80°	2385	631	504
85°	1797	364	277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4069 cd/sqm

TEST NUMBER: P1013343

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.1	1.2
10°-20°	156.4	3.5
20°-30°	225.7	5.0
30°-40°	255.9	5.7
40°-50°	247.0	5.5
50°-60°	205.4	4.6
60°-70°	141.8	3.1
70°-80°	71.6	1.6
80°-90°	20.3	0.4
90°-100°	33.6	0.7
100°-110°	221.3	4.9
110°-120°	422.5	9.4
120°-130°	536.4	11.9
130°-140°	573.8	12.7
140°-150°	536.5	11.9
150°-160°	432.7	9.6
160°-170°	279.0	6.2
170°-180°	96.2	2.1
0°-30°	438.2	9.7
0°-40°	694.0	15.4
0°-60°	1146.4	25.4
0°-90°	1380.1	30.6
90°-120°	677.4	15.0
90°-150°	2324.0	51.5
90°-180°	3132.0	69.4
0°-180°	4512.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	596	596	596	596	596	
5°	596	594	588	593	592	57
15°	567	563	552	551	548	160
25°	513	505	486	478	474	236
35°	443	429	406	390	382	277
45°	362	345	317	295	287	279
55°	274	256	226	202	194	245
65°	186	167	138	118	112	184
75°	99	82	61	50	48	105
85°	25	16	14	13	13	27
90°	2	11	17	21	23	4
95°	42	16	17	21	22	51
105°	228	232	236	243	216	238
115°	425	428	427	428	428	419
125°	598	601	600	602	603	534
135°	742	741	744	746	747	572
145°	855	858	858	858	860	535
155°	938	939	936	940	937	432
165°	989	986	986	992	985	280
175°	1012	1008	1008	1015	1006	96
180°	1012	1012	1012	1012	1012	

TEST NUMBER: P1013343

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	596.4	596.4	596.4	596.4	596.4
2.5°	598.2	596.4	591.4	596.4	595.9
5°	595.5	593.6	588.2	592.7	591.8
7.5°	591.4	589.5	582.7	585.9	584.5
10°	585.0	582.7	574.5	576.3	574.5
12.5°	576.7	574.0	564.0	564.9	562.1
15°	567.2	563.0	551.6	550.7	547.5
17.5°	556.2	550.3	537.0	534.7	530.2
20°	543.0	537.0	521.5	517.8	511.9
22.5°	528.3	521.5	504.6	498.7	494.1
25°	512.8	504.6	485.9	478.1	473.5
27.5°	496.8	486.8	467.1	458.0	451.6
30°	479.9	468.5	447.1	435.6	428.3
32.5°	462.1	448.9	426.5	412.8	406.0
35°	443.4	428.8	406.0	390.4	382.2
37.5°	423.8	408.7	383.6	366.7	358.5
40°	402.8	387.7	361.7	342.5	334.3
42.5°	382.7	366.7	339.3	319.7	311.0
45°	361.7	344.8	317.4	295.0	286.8
47.5°	340.2	322.8	294.5	271.2	262.1
50°	318.3	300.5	271.2	248.4	239.7
52.5°	295.9	278.6	248.4	225.1	216.0
55°	274.0	255.7	226.0	202.3	193.6
57.5°	252.5	233.3	204.1	179.9	173.5
60°	229.2	211.0	181.7	158.0	150.7
62.5°	208.2	189.1	158.9	137.5	132.0
65°	186.3	166.7	137.5	117.8	112.3
67.5°	163.5	144.8	117.4	100.0	93.6
70°	142.0	122.8	96.8	81.7	77.2
72.5°	119.2	102.3	78.1	65.8	61.6
75°	99.1	82.2	60.7	50.2	47.5
77.5°	78.1	63.5	45.2	37.9	37.0
80°	58.0	44.8	31.1	29.7	29.2
82.5°	40.6	28.8	22.4	21.5	21.0
85°	24.7	15.5	14.2	13.2	13.2
87.5°	10.5	6.8	6.4	5.9	6.4
90°	2.3	10.6	16.7	21.2	22.7
92.5°	11.4	9.8	15.9	20.4	20.4
95°	41.6	15.9	16.7	21.2	22.0
97.5°	79.5	96.1	16.7	20.4	21.2
100°	124.2	137.8	33.3	20.4	21.2
102.5°	174.1	183.2	192.3	22.0	22.0
105°	227.9	232.4	236.2	243.0	215.8
107.5°	277.1	279.3	284.6	288.4	291.5
110°	327.0	329.3	333.8	335.4	337.6

TEST NUMBER: P1013343

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.5	380.0	381.5	380.8	383.8
115°	425.4	427.7	427.0	428.5	428.5
117.5°	470.1	473.1	475.4	474.7	474.7
120°	515.5	518.6	517.8	519.3	517.8
122.5°	557.9	559.4	561.0	561.7	560.2
125°	598.0	601.1	599.6	601.8	602.6
127.5°	636.7	637.4	641.2	640.4	639.7
130°	673.7	674.5	676.8	677.5	677.5
132.5°	707.8	709.3	712.4	713.1	712.4
135°	741.9	741.1	744.2	745.7	747.2
137.5°	772.2	772.2	775.9	777.5	776.7
140°	801.7	803.2	804.7	807.0	807.7
142.5°	828.2	831.2	832.0	833.5	833.5
145°	855.4	857.7	857.7	858.5	860.0
147.5°	876.6	881.2	880.4	881.2	881.9
150°	900.1	903.1	902.4	902.4	903.1
152.5°	919.8	922.1	920.5	922.1	921.3
155°	937.9	938.7	936.4	939.5	937.2
157.5°	953.8	953.8	950.8	954.6	950.8
160°	967.5	965.2	964.4	969.0	964.4
162.5°	979.6	976.6	975.8	980.3	975.0
165°	989.4	985.6	985.6	991.7	984.9
167.5°	997.8	994.0	993.2	1000.0	992.5
170°	1004.6	1000.0	1000.8	1006.8	999.3
172.5°	1009.1	1004.6	1005.3	1011.4	1003.1
175°	1012.1	1007.6	1008.4	1015.2	1006.1
177.5°	1014.4	1009.1	1010.6	1016.7	1007.6
180°	1012.1	1012.1	1012.1	1012.1	1012.1

(END OF REPORT)