

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013357

Luminaire Tested: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013357
REPORT IS A COMBINATION OF REPORTS P999434 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6183.0 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013357

CATALOG NUMBER: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013357

CATALOG NUMBER: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	91	87	84	86	82	79	76	67	64	63	52	51	49	39	38	37
2	87	79	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32
3	79	70	63	57	71	64	58	53	52	47	44	41	38	35	31	29	27
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	27	25	23
5	66	55	47	42	60	50	44	38	41	36	32	33	29	26	25	22	21
6	61	49	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18
7	57	45	37	32	51	41	34	29	34	29	25	27	23	20	21	18	16
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	16	15
9	49	37	30	25	44	34	27	23	28	23	20	23	19	16	18	15	13
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7937	7937	7937
5°	7937	7701	7702
10°	7870	7459	7370
15°	7762	7156	6977
20°	7620	6811	6530
25°	7444	6439	6093
30°	7271	6059	5603
35°	7080	5674	5123
40°	6853	5260	4630
45°	6641	4849	4142
50°	6400	4400	3647
55°	6139	3940	3136
60°	5848	3451	2630
65°	5569	2890	2144
70°	5171	2301	1639
75°	4660	1674	1146
80°	3895	1028	824
85°	2925	592	453

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6641 cd/sqm

TEST NUMBER: P1013357

CATALOG NUMBER: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	1.5
10°-20°	255.2	4.1
20°-30°	368.4	6.0
30°-40°	417.6	6.8
40°-50°	403.2	6.5
50°-60°	335.2	5.4
60°-70°	231.3	3.7
70°-80°	116.9	1.9
80°-90°	32.3	0.5
90°-100°	42.2	0.7
100°-110°	277.7	4.5
110°-120°	530.3	8.6
120°-130°	673.3	10.9
130°-140°	720.3	11.6
140°-150°	673.5	10.9
150°-160°	543.1	8.8
160°-170°	350.3	5.7
170°-180°	120.7	2.0
0°-30°	715.2	11.6
0°-40°	1132.7	18.3
0°-60°	1871.1	30.3
0°-90°	2251.6	36.4
90°-120°	850.3	13.8
90°-150°	2917.3	47.2
90°-180°	3931.0	63.6
0°-180°	6183.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	973	973	973	973	973	
5°	972	969	960	967	966	92
15°	926	919	900	899	894	261
25°	837	824	793	780	773	386
35°	724	700	663	637	624	452
45°	590	563	518	482	468	455
55°	447	417	369	330	316	400
65°	304	272	224	192	183	300
75°	162	134	99	82	78	171
85°	40	25	23	22	22	44
90°	3	13	21	27	28	5
95°	52	20	21	27	28	64
105°	286	292	296	305	271	299
115°	534	537	536	538	538	526
125°	751	754	753	756	756	670
135°	931	930	934	936	938	718
145°	1074	1077	1077	1078	1080	671
155°	1177	1178	1176	1179	1176	543
165°	1242	1237	1237	1245	1236	351
175°	1270	1265	1266	1274	1263	121
180°	1270	1270	1270	1270	1270	

TEST NUMBER: P1013357

CATALOG NUMBER: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	973.3	973.3	973.3	973.3	973.3
2.5°	976.3	973.3	965.1	973.3	972.6
5°	971.8	968.9	959.9	967.4	965.9
7.5°	965.1	962.2	951.0	956.2	954.0
10°	954.7	951.0	937.6	940.5	937.6
12.5°	941.3	936.8	920.4	921.9	917.4
15°	925.6	918.9	900.3	898.8	893.6
17.5°	907.8	898.1	876.5	872.7	865.3
20°	886.1	876.5	851.1	845.1	835.5
22.5°	862.3	851.1	823.5	813.8	806.4
25°	837.0	823.5	793.0	780.3	772.9
27.5°	810.9	794.5	762.4	747.5	737.1
30°	783.3	764.7	729.6	711.0	699.1
32.5°	754.2	732.6	696.1	673.7	662.6
35°	723.7	699.8	662.6	637.2	623.8
37.5°	691.6	667.0	626.0	598.5	585.0
40°	657.3	632.7	590.3	559.0	545.5
42.5°	624.5	598.5	553.7	521.7	507.5
45°	590.3	562.7	518.0	481.5	468.0
47.5°	555.2	526.9	480.7	442.7	427.8
50°	519.5	490.4	442.7	405.4	391.3
52.5°	482.9	454.6	405.4	367.4	352.5
55°	447.2	417.4	368.9	330.2	316.0
57.5°	412.1	380.8	333.1	293.6	283.2
60°	374.1	344.3	296.6	257.9	245.9
62.5°	339.8	308.5	259.4	224.3	215.4
65°	304.1	272.0	224.3	192.3	183.3
67.5°	266.8	236.3	191.5	163.2	152.8
70°	231.8	200.5	158.0	133.4	126.0
72.5°	194.5	166.9	127.4	107.3	100.6
75°	161.7	134.2	99.1	82.0	77.5
77.5°	127.4	103.6	73.8	61.9	60.4
80°	94.7	73.0	50.7	48.4	47.7
82.5°	66.3	47.0	36.5	35.0	34.3
85°	40.2	25.3	23.1	21.6	21.6
87.5°	17.1	11.2	10.4	9.7	10.4
90°	2.9	13.3	20.9	26.6	28.5
92.5°	14.3	12.4	20.0	25.7	25.7
95°	52.3	20.0	20.9	26.6	27.6
97.5°	99.8	120.7	20.9	25.7	26.6
100°	155.8	172.9	41.8	25.7	26.6
102.5°	218.6	230.0	241.4	27.6	27.6
105°	286.0	291.7	296.5	305.0	270.8
107.5°	347.8	350.6	357.3	362.0	365.9
110°	410.5	413.4	419.1	421.0	423.8

TEST NUMBER: P1013357

CATALOG NUMBER: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	471.3	477.0	478.9	478.0	481.8
115°	534.0	536.9	535.9	537.8	537.8
117.5°	590.1	593.9	596.8	595.8	595.8
120°	647.1	650.9	650.0	651.9	650.0
122.5°	700.3	702.2	704.1	705.1	703.2
125°	750.7	754.5	752.6	755.5	756.4
127.5°	799.2	800.1	804.9	803.9	803.0
130°	845.7	846.7	849.5	850.5	850.5
132.5°	888.5	890.4	894.2	895.1	894.2
135°	931.3	930.3	934.1	936.0	937.9
137.5°	969.3	969.3	974.0	975.9	975.0
140°	1006.3	1008.2	1010.1	1013.0	1013.9
142.5°	1039.6	1043.4	1044.3	1046.2	1046.2
145°	1073.8	1076.6	1076.6	1077.6	1079.5
147.5°	1100.4	1106.1	1105.2	1106.1	1107.1
150°	1129.9	1133.7	1132.7	1132.7	1133.7
152.5°	1154.6	1157.4	1155.5	1157.4	1156.5
155°	1177.4	1178.3	1175.5	1179.3	1176.4
157.5°	1197.3	1197.3	1193.5	1198.3	1193.5
160°	1214.4	1211.6	1210.6	1216.3	1210.6
162.5°	1229.6	1225.8	1224.9	1230.6	1223.9
165°	1242.0	1237.2	1237.2	1244.8	1236.3
167.5°	1252.4	1247.7	1246.7	1255.3	1245.8
170°	1261.0	1255.3	1256.2	1263.8	1254.3
172.5°	1266.7	1261.0	1261.9	1269.6	1259.1
175°	1270.5	1264.8	1265.7	1274.3	1262.9
177.5°	1273.4	1266.7	1268.6	1276.2	1264.8
180°	1270.5	1270.5	1270.5	1270.5	1270.5

(END OF REPORT)