

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013367

Luminaire Tested: S124RDIP-B575D1205UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013367
REPORT IS A COMBINATION OF REPORTS P999474 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D1205UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6871.0 lumens
Efficiency: N/A
Efficacy: 116.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013367

CATALOG NUMBER: S124RDIP-B575D1205UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013367

CATALOG NUMBER: S124RDIP-B575D1205UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	30	29
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	28	27	25
4	72	61	54	48	64	56	49	44	45	40	36	35	31	29	25	23	22
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19
6	61	49	41	36	54	44	38	33	36	31	27	28	25	22	21	18	17
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	17	15	13
9	48	36	29	24	43	33	27	23	27	22	19	21	18	15	16	14	12
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7937	7937	7937
5°	7937	7701	7702
10°	7870	7459	7370
15°	7762	7156	6977
20°	7620	6811	6530
25°	7444	6439	6093
30°	7271	6059	5603
35°	7080	5674	5123
40°	6853	5260	4630
45°	6641	4849	4142
50°	6400	4400	3647
55°	6139	3940	3136
60°	5848	3451	2630
65°	5569	2890	2144
70°	5171	2301	1639
75°	4660	1674	1146
80°	3895	1028	824
85°	2925	592	453

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6641 cd/sqm

TEST NUMBER: P1013367

CATALOG NUMBER: S124RDIP-B575D1205UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	1.3
10°-20°	255.2	3.7
20°-30°	368.4	5.4
30°-40°	417.6	6.1
40°-50°	403.2	5.9
50°-60°	335.2	4.9
60°-70°	231.3	3.4
70°-80°	116.9	1.7
80°-90°	32.8	0.5
90°-100°	49.5	0.7
100°-110°	326.3	4.7
110°-120°	623.1	9.1
120°-130°	791.0	11.5
130°-140°	846.2	12.3
140°-150°	791.3	11.5
150°-160°	638.1	9.3
160°-170°	411.5	6.0
170°-180°	141.8	2.1
0°-30°	715.2	10.4
0°-40°	1132.7	16.5
0°-60°	1871.1	27.2
0°-90°	2252.0	32.8
90°-120°	999.0	14.5
90°-150°	3427.5	49.9
90°-180°	4619.0	67.2
0°-180°	6871.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	973	973	973	973	973	
5°	972	969	960	967	966	92
15°	926	919	900	899	894	261
25°	837	824	793	780	773	386
35°	724	700	663	637	624	452
45°	590	563	518	482	468	455
55°	447	417	369	330	316	400
65°	304	272	224	192	183	300
75°	162	134	99	82	78	171
85°	40	25	23	22	22	44
90°	3	16	25	31	34	6
95°	61	23	25	31	32	76
105°	336	343	348	358	318	352
115°	627	631	630	632	632	618
125°	882	886	884	888	889	788
135°	1094	1093	1098	1100	1102	843
145°	1262	1265	1265	1266	1268	788
155°	1383	1384	1381	1386	1382	638
165°	1459	1454	1454	1462	1452	412
175°	1493	1486	1487	1497	1484	142
180°	1493	1493	1493	1493	1493	

TEST NUMBER: P1013367

CATALOG NUMBER: S124RDIP-B575D1205UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	973.3	973.3	973.3	973.3	973.3
2.5°	976.3	973.3	965.1	973.3	972.6
5°	971.8	968.9	959.9	967.4	965.9
7.5°	965.1	962.2	951.0	956.2	954.0
10°	954.7	951.0	937.6	940.5	937.6
12.5°	941.3	936.8	920.4	921.9	917.4
15°	925.6	918.9	900.3	898.8	893.6
17.5°	907.8	898.1	876.5	872.7	865.3
20°	886.1	876.5	851.1	845.1	835.5
22.5°	862.3	851.1	823.5	813.8	806.4
25°	837.0	823.5	793.0	780.3	772.9
27.5°	810.9	794.5	762.4	747.5	737.1
30°	783.3	764.7	729.6	711.0	699.1
32.5°	754.2	732.6	696.1	673.7	662.6
35°	723.7	699.8	662.6	637.2	623.8
37.5°	691.6	667.0	626.0	598.5	585.0
40°	657.3	632.7	590.3	559.0	545.5
42.5°	624.5	598.5	553.7	521.7	507.5
45°	590.3	562.7	518.0	481.5	468.0
47.5°	555.2	526.9	480.7	442.7	427.8
50°	519.5	490.4	442.7	405.4	391.3
52.5°	482.9	454.6	405.4	367.4	352.5
55°	447.2	417.4	368.9	330.2	316.0
57.5°	412.1	380.8	333.1	293.6	283.2
60°	374.1	344.3	296.6	257.9	245.9
62.5°	339.8	308.5	259.4	224.3	215.4
65°	304.1	272.0	224.3	192.3	183.3
67.5°	266.8	236.3	191.5	163.2	152.8
70°	231.8	200.5	158.0	133.4	126.0
72.5°	194.5	166.9	127.4	107.3	100.6
75°	161.7	134.2	99.1	82.0	77.5
77.5°	127.4	103.6	73.8	61.9	60.4
80°	94.7	73.0	50.7	48.4	47.7
82.5°	66.3	47.0	36.5	35.0	34.3
85°	40.2	25.3	23.1	21.6	21.6
87.5°	17.1	11.2	10.4	9.7	10.4
90°	3.3	15.6	24.6	31.3	33.5
92.5°	16.7	14.5	23.4	30.1	30.1
95°	61.4	23.4	24.6	31.3	32.4
97.5°	117.2	141.8	24.6	30.1	31.3
100°	183.1	203.2	49.1	30.1	31.3
102.5°	256.8	270.2	283.6	32.4	32.4
105°	336.1	342.7	348.3	358.4	318.2
107.5°	408.6	412.0	419.8	425.4	429.8
110°	482.3	485.7	492.4	494.6	497.9

TEST NUMBER: P1013367

CATALOG NUMBER: S124RDIP-B575D1205UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	553.8	560.5	562.7	561.6	566.0
115°	627.4	630.8	629.7	631.9	631.9
117.5°	693.3	697.8	701.1	700.0	700.0
120°	760.3	764.8	763.7	765.9	763.7
122.5°	822.8	825.1	827.3	828.4	826.2
125°	882.0	886.5	884.2	887.6	888.7
127.5°	938.9	940.1	945.6	944.5	943.4
130°	993.6	994.8	998.1	999.2	999.2
132.5°	1043.9	1046.1	1050.6	1051.7	1050.6
135°	1094.1	1093.0	1097.5	1099.7	1101.9
137.5°	1138.8	1138.8	1144.4	1146.6	1145.5
140°	1182.3	1184.6	1186.8	1190.1	1191.3
142.5°	1221.4	1225.9	1227.0	1229.2	1229.2
145°	1261.6	1264.9	1264.9	1266.1	1268.3
147.5°	1292.8	1299.5	1298.4	1299.5	1300.7
150°	1327.5	1331.9	1330.8	1330.8	1331.9
152.5°	1356.5	1359.8	1357.6	1359.8	1358.7
155°	1383.3	1384.4	1381.0	1385.5	1382.2
157.5°	1406.7	1406.7	1402.3	1407.8	1402.3
160°	1426.8	1423.5	1422.4	1429.1	1422.4
162.5°	1444.7	1440.2	1439.1	1445.8	1438.0
165°	1459.2	1453.6	1453.6	1462.5	1452.5
167.5°	1471.5	1465.9	1464.8	1474.8	1463.7
170°	1481.5	1474.8	1475.9	1484.9	1473.7
172.5°	1488.2	1481.5	1482.6	1491.6	1479.3
175°	1492.7	1486.0	1487.1	1497.2	1483.8
177.5°	1496.0	1488.2	1490.5	1499.4	1486.0
180°	1492.7	1492.7	1492.7	1492.7	1492.7

(END OF REPORT)