

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013372

Luminaire Tested: S124RDIP-B575D365UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013372
REPORT IS A COMBINATION OF REPORTS P999510 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D365UB2750-4F0-XX-W2A-F_2700K
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3777.0 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013372

CATALOG NUMBER: S124RDIP-B575D365UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1013372

CATALOG NUMBER: S124RDIP-B575D365UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	61	61	61
1	101	96	93	89	94	90	87	84	79	77	74	69	67	65	59	58	57	52	52	52
2	92	85	79	73	86	79	74	70	70	66	62	61	58	55	53	50	48	44	44	44
3	84	75	67	62	78	70	64	59	62	57	53	54	50	47	47	44	42	38	38	38
4	77	66	58	52	72	62	55	50	55	50	45	48	44	41	42	39	36	33	33	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	35	38	35	32	29	29	29
6	65	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28	25	25	25
7	61	48	40	35	57	46	38	33	41	35	31	36	31	28	32	28	25	23	23	23
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	23	20	20	20
9	53	40	33	28	49	38	31	27	34	29	25	31	26	22	27	23	20	18	18	18
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	25	21	19	17	17	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8181	8181	8181
5°	8182	7938	7938
10°	8112	7687	7595
15°	8000	7375	7191
20°	7854	7020	6730
25°	7672	6636	6280
30°	7493	6245	5774
35°	7298	5848	5280
40°	7064	5421	4772
45°	6845	4998	4269
50°	6596	4535	3759
55°	6327	4060	3232
60°	6028	3557	2711
65°	5739	2979	2210
70°	5330	2371	1689
75°	4804	1726	1181
80°	4014	1059	850
85°	3020	610	467

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6845 cd/sqm

TEST NUMBER: P1013372

CATALOG NUMBER: S124RDIP-B575D365UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.3	2.5
10°-20°	263.0	7.0
20°-30°	379.7	10.1
30°-40°	430.4	11.4
40°-50°	415.5	11.0
50°-60°	345.5	9.1
60°-70°	238.4	6.3
70°-80°	120.5	3.2
80°-90°	31.6	0.8
90°-100°	15.7	0.4
100°-110°	103.0	2.7
110°-120°	196.7	5.2
120°-130°	249.7	6.6
130°-140°	267.1	7.1
140°-150°	249.8	6.6
150°-160°	201.4	5.3
160°-170°	129.9	3.4
170°-180°	44.8	1.2
0°-30°	737.1	19.5
0°-40°	1167.5	30.9
0°-60°	1928.5	51.1
0°-90°	2319.0	61.4
90°-120°	315.4	8.3
90°-150°	1081.9	28.6
90°-180°	1458.0	38.6
0°-180°	3777.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1003	1003	1003	1003	1003	
5°	1002	999	989	997	996	95
15°	954	947	928	926	921	269
25°	863	849	817	804	797	397
35°	746	721	683	657	643	466
45°	608	580	534	496	482	469
55°	461	430	380	340	326	412
65°	313	280	231	198	189	309
75°	167	138	102	84	80	176
85°	42	26	24	22	22	46
90°	1	5	8	10	11	3
95°	19	7	8	10	10	24
105°	106	108	110	113	100	111
115°	198	199	199	200	200	195
125°	278	280	279	280	280	249
135°	345	345	346	347	348	266
145°	398	399	399	400	400	249
155°	437	437	436	437	436	201
165°	461	459	459	462	458	130
175°	471	469	469	473	468	45
180°	471	471	471	471	471	

TEST NUMBER: P1013372

CATALOG NUMBER: S124RDIP-B575D365UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1003.2	1003.2	1003.2	1003.2	1003.2
2.5°	1006.3	1003.2	994.8	1003.2	1002.4
5°	1001.7	998.6	989.4	997.1	995.5
7.5°	994.8	991.7	980.2	985.5	983.2
10°	984.0	980.2	966.3	969.4	966.3
12.5°	970.2	965.6	948.7	950.2	945.6
15°	954.0	947.1	927.9	926.4	921.0
17.5°	935.6	925.6	903.3	899.5	891.8
20°	913.3	903.3	877.2	871.1	861.1
22.5°	888.7	877.2	848.8	838.8	831.1
25°	862.6	848.8	817.3	804.2	796.6
27.5°	835.7	818.8	785.8	770.5	759.7
30°	807.3	788.1	752.0	732.8	720.5
32.5°	777.4	755.1	717.4	694.4	682.9
35°	745.9	721.3	682.9	656.8	642.9
37.5°	712.8	687.5	645.2	616.8	603.0
40°	677.5	652.2	608.4	576.1	562.3
42.5°	643.7	616.8	570.7	537.7	523.1
45°	608.4	580.0	533.9	496.2	482.4
47.5°	572.3	543.1	495.5	456.3	440.9
50°	535.4	505.4	456.3	417.9	403.3
52.5°	497.8	468.6	417.9	378.7	363.3
55°	460.9	430.2	380.2	340.3	325.7
57.5°	424.8	392.5	343.4	302.6	291.9
60°	385.6	354.9	305.7	265.8	253.5
62.5°	350.3	318.0	267.3	231.2	222.0
65°	313.4	280.4	231.2	198.2	189.0
67.5°	275.0	243.5	197.4	168.2	157.5
70°	238.9	206.6	162.8	137.5	129.8
72.5°	200.5	172.1	131.4	110.6	103.7
75°	166.7	138.3	102.2	84.5	79.9
77.5°	131.4	106.8	76.0	63.8	62.2
80°	97.6	75.3	52.2	49.9	49.2
82.5°	68.4	48.4	37.6	36.1	35.3
85°	41.5	26.1	23.8	22.3	22.3
87.5°	17.7	11.5	10.8	10.0	10.8
90°	1.1	4.9	7.8	9.9	10.6
92.5°	5.3	4.6	7.4	9.5	9.5
95°	19.4	7.4	7.8	9.9	10.2
97.5°	37.0	44.8	7.8	9.5	9.9
100°	57.8	64.1	15.5	9.5	9.9
102.5°	81.1	85.3	89.5	10.2	10.2
105°	106.1	108.2	110.0	113.1	100.4
107.5°	129.0	130.0	132.5	134.3	135.7
110°	152.2	153.3	155.4	156.1	157.2



TEST NUMBER: P1013372

CATALOG NUMBER: S124RDIP-B575D365UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.8	176.9	177.6	177.3	178.7
115°	198.1	199.1	198.8	199.5	199.5
117.5°	218.9	220.3	221.3	221.0	221.0
120°	240.0	241.4	241.1	241.8	241.1
122.5°	259.7	260.4	261.1	261.5	260.8
125°	278.4	279.8	279.1	280.2	280.5
127.5°	296.4	296.7	298.5	298.1	297.8
130°	313.7	314.0	315.1	315.4	315.4
132.5°	329.5	330.2	331.6	332.0	331.6
135°	345.4	345.0	346.4	347.1	347.8
137.5°	359.5	359.5	361.2	361.9	361.6
140°	373.2	373.9	374.6	375.7	376.0
142.5°	385.6	387.0	387.3	388.0	388.0
145°	398.2	399.3	399.3	399.6	400.4
147.5°	408.1	410.2	409.9	410.2	410.6
150°	419.0	420.4	420.1	420.1	420.4
152.5°	428.2	429.3	428.5	429.3	428.9
155°	436.7	437.0	435.9	437.4	436.3
157.5°	444.1	444.1	442.6	444.4	442.6
160°	450.4	449.3	449.0	451.1	449.0
162.5°	456.0	454.6	454.3	456.4	453.9
165°	460.6	458.9	458.9	461.7	458.5
167.5°	464.5	462.7	462.4	465.6	462.0
170°	467.7	465.6	465.9	468.7	465.2
172.5°	469.8	467.7	468.0	470.8	467.0
175°	471.2	469.1	469.4	472.6	468.4
177.5°	472.2	469.8	470.5	473.3	469.1
180°	471.2	471.2	471.2	471.2	471.2

(END OF REPORT)