

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013385

Luminaire Tested: S124RDIP-B575D590UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013385
REPORT IS A COMBINATION OF REPORTS P999554 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D590UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4524.0 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013385

CATALOG NUMBER: S124RDIP-B575D590UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013385

CATALOG NUMBER: S124RDIP-B575D590UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	90	87	90	87	83	81	73	71	69	61	59	58	50	49	48
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	44	42	41
3	82	72	65	60	75	67	61	56	57	52	49	48	44	42	39	37	35
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	33	30
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	26
6	63	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23
7	59	47	39	33	54	43	36	31	37	32	28	32	28	24	27	23	21
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	23	19	17
10	47	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7937	7937	7937
5°	7937	7701	7702
10°	7870	7459	7370
15°	7762	7156	6977
20°	7620	6811	6530
25°	7444	6439	6093
30°	7271	6059	5603
35°	7080	5674	5123
40°	6853	5260	4630
45°	6641	4849	4142
50°	6400	4400	3647
55°	6139	3940	3136
60°	5848	3451	2630
65°	5569	2890	2144
70°	5171	2301	1639
75°	4660	1674	1146
80°	3895	1028	824
85°	2925	592	453

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6641 cd/sqm

TEST NUMBER: P1013385

CATALOG NUMBER: S124RDIP-B575D590UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	2.0
10°-20°	255.2	5.6
20°-30°	368.4	8.1
30°-40°	417.6	9.2
40°-50°	403.2	8.9
50°-60°	335.2	7.4
60°-70°	231.3	5.1
70°-80°	116.9	2.6
80°-90°	31.2	0.7
90°-100°	24.4	0.5
100°-110°	160.6	3.6
110°-120°	306.7	6.8
120°-130°	389.4	8.6
130°-140°	416.5	9.2
140°-150°	389.5	8.6
150°-160°	314.1	6.9
160°-170°	202.6	4.5
170°-180°	69.8	1.5
0°-30°	715.2	15.8
0°-40°	1132.7	25.0
0°-60°	1871.1	41.4
0°-90°	2250.5	49.7
90°-120°	491.7	10.9
90°-150°	1687.0	37.3
90°-180°	2273.0	50.2
0°-180°	4524.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	973	973	973	973	973	
5°	972	969	960	967	966	92
15°	926	919	900	899	894	261
25°	837	824	793	780	773	386
35°	724	700	663	637	624	452
45°	590	563	518	482	468	455
55°	447	417	369	330	316	400
65°	304	272	224	192	183	300
75°	162	134	99	82	78	171
85°	40	25	23	22	22	44
90°	2	8	12	15	16	4
95°	30	12	12	15	16	37
105°	165	169	172	176	157	173
115°	309	310	310	311	311	304
125°	434	436	435	437	437	388
135°	538	538	540	541	542	415
145°	621	623	623	623	624	388
155°	681	681	680	682	680	314
165°	718	716	716	720	715	203
175°	735	731	732	737	730	70
180°	735	735	735	735	735	

TEST NUMBER: P1013385

CATALOG NUMBER: S124RDIP-B575D590UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	973.3	973.3	973.3	973.3	973.3
2.5°	976.3	973.3	965.1	973.3	972.6
5°	971.8	968.9	959.9	967.4	965.9
7.5°	965.1	962.2	951.0	956.2	954.0
10°	954.7	951.0	937.6	940.5	937.6
12.5°	941.3	936.8	920.4	921.9	917.4
15°	925.6	918.9	900.3	898.8	893.6
17.5°	907.8	898.1	876.5	872.7	865.3
20°	886.1	876.5	851.1	845.1	835.5
22.5°	862.3	851.1	823.5	813.8	806.4
25°	837.0	823.5	793.0	780.3	772.9
27.5°	810.9	794.5	762.4	747.5	737.1
30°	783.3	764.7	729.6	711.0	699.1
32.5°	754.2	732.6	696.1	673.7	662.6
35°	723.7	699.8	662.6	637.2	623.8
37.5°	691.6	667.0	626.0	598.5	585.0
40°	657.3	632.7	590.3	559.0	545.5
42.5°	624.5	598.5	553.7	521.7	507.5
45°	590.3	562.7	518.0	481.5	468.0
47.5°	555.2	526.9	480.7	442.7	427.8
50°	519.5	490.4	442.7	405.4	391.3
52.5°	482.9	454.6	405.4	367.4	352.5
55°	447.2	417.4	368.9	330.2	316.0
57.5°	412.1	380.8	333.1	293.6	283.2
60°	374.1	344.3	296.6	257.9	245.9
62.5°	339.8	308.5	259.4	224.3	215.4
65°	304.1	272.0	224.3	192.3	183.3
67.5°	266.8	236.3	191.5	163.2	152.8
70°	231.8	200.5	158.0	133.4	126.0
72.5°	194.5	166.9	127.4	107.3	100.6
75°	161.7	134.2	99.1	82.0	77.5
77.5°	127.4	103.6	73.8	61.9	60.4
80°	94.7	73.0	50.7	48.4	47.7
82.5°	66.3	47.0	36.5	35.0	34.3
85°	40.2	25.3	23.1	21.6	21.6
87.5°	17.1	11.2	10.4	9.7	10.4
90°	1.6	7.7	12.1	15.4	16.5
92.5°	8.2	7.1	11.5	14.8	14.8
95°	30.2	11.5	12.1	15.4	15.9
97.5°	57.7	69.8	12.1	14.8	15.4
100°	90.1	100.0	24.2	14.8	15.4
102.5°	126.4	133.0	139.6	15.9	15.9
105°	165.4	168.7	171.5	176.4	156.6
107.5°	201.1	202.8	206.6	209.4	211.6
110°	237.4	239.0	242.3	243.4	245.1

TEST NUMBER: P1013385

CATALOG NUMBER: S124RDIP-B575D590UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	272.6	275.9	277.0	276.4	278.6
115°	308.8	310.5	309.9	311.0	311.0
117.5°	341.3	343.5	345.1	344.6	344.6
120°	374.2	376.4	375.9	377.0	375.9
122.5°	405.0	406.1	407.2	407.8	406.7
125°	434.1	436.3	435.2	436.9	437.4
127.5°	462.2	462.7	465.5	464.9	464.4
130°	489.1	489.6	491.3	491.8	491.8
132.5°	513.8	514.9	517.1	517.7	517.1
135°	538.5	538.0	540.2	541.3	542.4
137.5°	560.5	560.5	563.3	564.4	563.8
140°	582.0	583.1	584.1	585.8	586.3
142.5°	601.2	603.4	603.9	605.0	605.0
145°	621.0	622.6	622.6	623.2	624.3
147.5°	636.4	639.7	639.1	639.7	640.2
150°	653.4	655.6	655.0	655.0	655.6
152.5°	667.7	669.3	668.2	669.3	668.8
155°	680.9	681.4	679.8	682.0	680.3
157.5°	692.4	692.4	690.2	693.0	690.2
160°	702.3	700.6	700.1	703.4	700.1
162.5°	711.1	708.9	708.3	711.6	707.8
165°	718.2	715.5	715.5	719.9	714.9
167.5°	724.3	721.5	721.0	725.9	720.4
170°	729.2	725.9	726.5	730.9	725.4
172.5°	732.5	729.2	729.8	734.2	728.1
175°	734.7	731.4	732.0	736.9	730.3
177.5°	736.4	732.5	733.6	738.0	731.4
180°	734.7	734.7	734.7	734.7	734.7

(END OF REPORT)