

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013394

Luminaire Tested: S124RDIP-B575D810UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013394
REPORT IS A COMBINATION OF REPORTS P999593 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D810UB2750-4F0-XX-W2A-F_4000K
Description: Define 4 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5468.0 lumens
Efficiency: N/A
Efficacy: 121.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013394

CATALOG NUMBER: S124RDIP-B575D810UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013394

CATALOG NUMBER: S124RDIP-B575D810UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31
4	74	63	55	49	67	58	51	46	48	43	39	39	36	33	31	29	27
5	68	56	48	42	61	52	45	40	43	38	34	35	32	29	28	25	23
6	62	50	43	37	57	46	40	34	39	34	30	32	28	25	26	23	21
7	58	46	38	32	52	42	35	30	35	30	26	29	25	22	23	21	18
8	53	41	34	29	49	38	31	27	32	27	23	27	23	20	21	19	16
9	50	38	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15
10	46	35	28	23	42	32	26	21	27	22	19	23	19	16	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8205	8205	8205
5°	8206	7962	7962
10°	8137	7710	7618
15°	8025	7397	7213
20°	7878	7041	6750
25°	7695	6656	6299
30°	7517	6264	5792
35°	7319	5865	5296
40°	7086	5437	4787
45°	6865	5013	4283
50°	6615	4549	3770
55°	6346	4073	3242
60°	6046	3567	2720
65°	5758	2988	2216
70°	5345	2378	1694
75°	4818	1731	1184
80°	4022	1063	852
85°	3027	612	467

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6865 cd/sqm

TEST NUMBER: P1013394

CATALOG NUMBER: S124RDIP-B575D810UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	1.7
10°-20°	263.8	4.8
20°-30°	380.9	7.0
30°-40°	431.7	7.9
40°-50°	416.8	7.6
50°-60°	346.5	6.3
60°-70°	239.2	4.4
70°-80°	120.8	2.2
80°-90°	32.8	0.6
90°-100°	33.7	0.6
100°-110°	221.9	4.1
110°-120°	423.7	7.7
120°-130°	537.9	9.8
130°-140°	575.4	10.5
140°-150°	538.1	9.8
150°-160°	433.9	7.9
160°-170°	279.8	5.1
170°-180°	96.4	1.8
0°-30°	739.3	13.5
0°-40°	1171.0	21.4
0°-60°	1934.3	35.4
0°-90°	2327.1	42.6
90°-120°	679.3	12.4
90°-150°	2330.7	42.6
90°-180°	3141.0	57.4
0°-180°	5468.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1005	1002	992	1000	998	95
15°	957	950	931	929	924	270
25°	865	851	820	807	799	399
35°	748	724	685	659	645	468
45°	610	582	536	498	484	471
55°	462	432	381	341	327	414
65°	314	281	232	199	190	310
75°	167	139	102	85	80	176
85°	42	26	24	22	22	46
90°	2	11	17	21	23	5
95°	42	16	17	21	22	51
105°	228	233	237	244	216	239
115°	427	429	428	430	430	420
125°	600	603	601	604	604	536
135°	744	743	746	748	749	573
145°	858	860	860	861	862	536
155°	941	941	939	942	940	434
165°	992	988	988	994	988	280
175°	1015	1010	1011	1018	1009	97
180°	1015	1015	1015	1015	1015	

TEST NUMBER: P1013394

CATALOG NUMBER: S124RDIP-B575D810UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1006.2	1006.2	1006.2	1006.2	1006.2
2.5°	1009.3	1006.2	997.8	1006.2	1005.5
5°	1004.7	1001.6	992.4	1000.1	998.5
7.5°	997.8	994.7	983.1	988.5	986.2
10°	987.0	983.1	969.2	972.3	969.2
12.5°	973.1	968.5	951.5	953.1	948.4
15°	956.9	950.0	930.7	929.2	923.8
17.5°	938.4	928.4	906.1	902.2	894.5
20°	916.1	906.1	879.9	873.7	863.7
22.5°	891.4	879.9	851.4	841.3	833.6
25°	865.2	851.4	819.8	806.7	799.0
27.5°	838.3	821.3	788.2	772.8	762.0
30°	809.8	790.5	754.3	735.0	722.7
32.5°	779.7	757.4	719.6	696.5	684.9
35°	748.1	723.5	684.9	658.7	644.9
37.5°	715.0	689.6	647.2	618.7	604.8
40°	679.6	654.1	610.2	577.8	564.0
42.5°	645.7	618.7	572.5	539.3	524.7
45°	610.2	581.7	535.5	497.7	483.9
47.5°	574.0	544.7	497.0	457.7	442.2
50°	537.0	507.0	457.7	419.1	404.5
52.5°	499.3	470.0	419.1	379.8	364.4
55°	462.3	431.5	381.4	341.3	326.7
57.5°	426.1	393.7	344.4	303.6	292.8
60°	386.8	356.0	306.6	266.6	254.3
62.5°	351.3	319.0	268.1	231.9	222.7
65°	314.4	281.2	231.9	198.8	189.5
67.5°	275.8	244.2	198.0	168.7	157.9
70°	239.6	207.3	163.3	137.9	130.2
72.5°	201.1	172.6	131.7	110.9	104.0
75°	167.2	138.7	102.5	84.8	80.1
77.5°	131.7	107.1	76.3	63.9	62.4
80°	97.8	75.5	52.4	50.1	49.3
82.5°	68.6	48.5	37.8	36.2	35.4
85°	41.6	26.2	23.9	22.3	22.3
87.5°	17.7	11.6	10.8	10.0	10.8
90°	2.3	10.6	16.7	21.3	22.8
92.5°	11.4	9.9	15.9	20.5	20.5
95°	41.8	15.9	16.7	21.3	22.0
97.5°	79.7	96.4	16.7	20.5	21.3
100°	124.5	138.2	33.4	20.5	21.3
102.5°	174.6	183.7	192.8	22.0	22.0
105°	228.5	233.1	236.9	243.7	216.4
107.5°	277.9	280.1	285.5	289.3	292.3
110°	328.0	330.2	334.8	336.3	338.6

TEST NUMBER: P1013394

CATALOG NUMBER: S124RDIP-B575D810UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.6	381.1	382.6	381.9	384.9
115°	426.7	428.9	428.2	429.7	429.7
117.5°	471.5	474.5	476.8	476.0	476.0
120°	517.0	520.0	519.3	520.8	519.3
122.5°	559.5	561.0	562.6	563.3	561.8
125°	599.8	602.8	601.3	603.6	604.3
127.5°	638.5	639.2	643.0	642.3	641.5
130°	675.7	676.4	678.7	679.5	679.5
132.5°	709.8	711.4	714.4	715.2	714.4
135°	744.0	743.3	746.3	747.8	749.3
137.5°	774.4	774.4	778.2	779.7	778.9
140°	804.0	805.5	807.0	809.3	810.1
142.5°	830.6	833.6	834.4	835.9	835.9
145°	857.9	860.2	860.2	860.9	862.4
147.5°	879.1	883.7	882.9	883.7	884.5
150°	902.7	905.7	905.0	905.0	905.7
152.5°	922.4	924.7	923.2	924.7	923.9
155°	940.6	941.4	939.1	942.2	939.9
157.5°	956.6	956.6	953.5	957.3	953.5
160°	970.3	968.0	967.2	971.8	967.2
162.5°	982.4	979.4	978.6	983.2	977.8
165°	992.3	988.5	988.5	994.5	987.7
167.5°	1000.6	996.8	996.1	1002.9	995.3
170°	1007.5	1002.9	1003.7	1009.7	1002.1
172.5°	1012.0	1007.5	1008.2	1014.3	1005.9
175°	1015.0	1010.5	1011.2	1018.1	1009.0
177.5°	1017.3	1012.0	1013.5	1019.6	1010.5
180°	1015.0	1015.0	1015.0	1015.0	1015.0

(END OF REPORT)