

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026082

Luminaire Tested: S124RDIP-B1195D1035UB27-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026082
REPORT IS A COMBINATION OF REPORTS P999022 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D1035UB27-4F0-XX-W2A-F
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8844.0 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026082

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1026082

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	47	45	44
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	32
5	70	58	50	44	64	54	47	42	47	42	37	40	36	33	34	31	28
6	64	52	44	38	59	49	42	36	43	37	33	37	32	29	31	28	25
7	59	47	39	34	55	44	37	32	39	33	29	33	29	26	29	25	22
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16898	16898	16898
5°	16899	16395	16397
10°	16756	15878	15689
15°	16525	15234	14854
20°	16223	14500	13902
25°	15847	13707	12972
30°	15479	12899	11927
35°	15073	12079	10906
40°	14590	11197	9857
45°	14138	10322	8818
50°	13624	9367	7764
55°	13068	8387	6675
60°	12451	7347	5600
65°	11856	6154	4565
70°	11010	4899	3488
75°	9922	3563	2440
80°	8287	2188	1753
85°	6236	1261	964

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14138 cd/sqm

TEST NUMBER: P1026082

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.9	2.2
10°-20°	543.3	6.1
20°-30°	784.4	8.9
30°-40°	889.0	10.1
40°-50°	858.3	9.7
50°-60°	713.6	8.1
60°-70°	492.5	5.6
70°-80°	248.9	2.8
80°-90°	65.9	0.7
90°-100°	43.5	0.5
100°-110°	286.4	3.2
110°-120°	546.8	6.2
120°-130°	694.2	7.8
130°-140°	742.6	8.4
140°-150°	694.4	7.9
150°-160°	560.0	6.3
160°-170°	361.1	4.1
170°-180°	124.5	1.4
0°-30°	1522.5	17.2
0°-40°	2411.5	27.3
0°-60°	3983.4	45.0
0°-90°	4790.7	54.2
90°-120°	876.6	9.9
90°-150°	3007.8	34.0
90°-180°	4053.0	45.8
0°-180°	8844.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2072	2072	2072	2072	2072	
5°	2069	2063	2044	2060	2056	196
15°	1971	1956	1917	1914	1902	555
25°	1782	1753	1688	1661	1645	821
35°	1541	1490	1410	1357	1328	963
45°	1257	1198	1103	1025	996	969
55°	952	888	785	703	673	852
65°	647	579	478	409	390	639
75°	344	286	211	174	165	363
85°	86	54	49	46	46	94
90°	3	14	22	27	29	8
95°	54	21	22	27	28	66
105°	295	301	306	314	279	309
115°	551	554	553	554	554	542
125°	774	778	776	779	780	691
135°	960	959	963	965	967	740
145°	1107	1110	1110	1111	1113	692
155°	1214	1215	1212	1216	1213	560
165°	1280	1276	1276	1283	1275	362
175°	1310	1304	1305	1314	1302	125
180°	1310	1310	1310	1310	1310	

TEST NUMBER: P1026082

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2072.2	2072.2	2072.2	2072.2	2072.2
2.5°	2078.5	2072.2	2054.7	2072.2	2070.6
5°	2069.0	2062.7	2043.6	2059.5	2056.3
7.5°	2054.7	2048.4	2024.6	2035.7	2030.9
10°	2032.5	2024.6	1996.0	2002.4	1996.0
12.5°	2004.0	1994.4	1959.5	1962.7	1953.2
15°	1970.6	1956.4	1916.7	1913.5	1902.4
17.5°	1932.6	1911.9	1865.9	1858.0	1842.1
20°	1886.5	1865.9	1812.0	1799.3	1778.7
22.5°	1835.8	1812.0	1753.3	1732.6	1716.8
25°	1781.8	1753.3	1688.2	1661.2	1645.4
27.5°	1726.3	1691.4	1623.2	1591.4	1569.2
30°	1667.6	1627.9	1553.3	1513.7	1488.3
32.5°	1605.7	1559.7	1481.9	1434.3	1410.5
35°	1540.7	1489.9	1410.5	1356.6	1328.0
37.5°	1472.4	1420.1	1332.8	1274.1	1245.5
40°	1399.4	1347.1	1256.6	1190.0	1161.4
42.5°	1329.6	1274.1	1178.9	1110.7	1080.5
45°	1256.6	1197.9	1102.7	1025.0	996.4
47.5°	1182.1	1121.8	1023.4	942.5	910.7
50°	1105.9	1044.0	942.5	863.1	833.0
52.5°	1028.2	967.9	863.1	782.2	750.5
55°	952.0	888.5	785.4	702.9	672.7
57.5°	877.4	810.8	709.2	625.1	602.9
60°	796.5	733.0	631.5	549.0	523.6
62.5°	723.5	656.9	552.2	477.6	458.5
65°	647.4	579.1	477.6	409.4	390.3
67.5°	568.0	503.0	407.8	347.5	325.3
70°	493.5	426.8	336.4	284.0	268.1
72.5°	414.1	355.4	271.3	228.5	214.2
75°	344.3	285.6	211.0	174.5	165.0
77.5°	271.3	220.5	157.1	131.7	128.5
80°	201.5	155.5	107.9	103.1	101.5
82.5°	141.2	100.0	77.7	74.6	73.0
85°	85.7	53.9	49.2	46.0	46.0
87.5°	36.5	23.8	22.2	20.6	22.2
90°	2.9	13.7	21.6	27.4	29.4
92.5°	14.7	12.7	20.6	26.5	26.5
95°	53.9	20.6	21.6	27.4	28.4
97.5°	102.9	124.4	21.6	26.5	27.4
100°	160.7	178.3	43.1	26.5	27.4
102.5°	225.3	237.1	248.9	28.4	28.4
105°	294.9	300.8	305.7	314.5	279.2
107.5°	358.6	361.5	368.4	373.3	377.2
110°	423.2	426.2	432.1	434.0	437.0

TEST NUMBER: P1026082

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	485.9	491.8	493.8	492.8	496.7
115°	550.6	553.5	552.6	554.5	554.5
117.5°	608.4	612.3	615.3	614.3	614.3
120°	667.2	671.1	670.1	672.1	670.1
122.5°	722.1	724.0	726.0	727.0	725.0
125°	774.0	777.9	775.9	778.9	779.9
127.5°	824.0	824.9	829.8	828.9	827.9
130°	872.0	872.9	875.9	876.9	876.9
132.5°	916.0	918.0	921.9	922.9	921.9
135°	960.1	959.2	963.1	965.0	967.0
137.5°	999.3	999.3	1004.2	1006.2	1005.2
140°	1037.5	1039.5	1041.5	1044.4	1045.4
142.5°	1071.8	1075.7	1076.7	1078.7	1078.7
145°	1107.1	1110.0	1110.0	1111.0	1113.0
147.5°	1134.5	1140.4	1139.4	1140.4	1141.4
150°	1164.9	1168.8	1167.8	1167.8	1168.8
152.5°	1190.4	1193.3	1191.4	1193.3	1192.3
155°	1213.9	1214.9	1211.9	1215.8	1212.9
157.5°	1234.5	1234.5	1230.5	1235.4	1230.5
160°	1252.1	1249.2	1248.2	1254.1	1248.2
162.5°	1267.8	1263.9	1262.9	1268.8	1261.9
165°	1280.5	1275.6	1275.6	1283.4	1274.6
167.5°	1291.3	1286.4	1285.4	1294.2	1284.4
170°	1300.1	1294.2	1295.2	1303.0	1293.2
172.5°	1306.0	1300.1	1301.1	1308.9	1298.1
175°	1309.9	1304.0	1305.0	1313.8	1302.1
177.5°	1312.8	1306.0	1307.9	1315.8	1304.0
180°	1309.9	1309.9	1309.9	1309.9	1309.9

(END OF REPORT)