

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013409

Luminaire Tested: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013409
REPORT IS A COMBINATION OF REPORTS P999668 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K
Description: Define 4 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8115.0 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013409

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013409

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41
2	88	81	75	70	80	74	69	65	61	58	54	49	47	45	38	37	35
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26
5	68	56	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21
7	58	46	38	33	53	42	35	31	35	30	26	29	25	22	23	20	18
8	54	42	34	29	49	38	32	27	32	27	24	27	23	20	21	19	17
9	50	38	31	26	45	35	29	24	30	25	21	25	21	18	20	17	15
10	47	35	28	23	42	32	26	22	27	22	19	23	19	16	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10758	10758	10758	10758
5°	10759	12157	10776	9291
10°	10701	14013	10692	8080
15°	10573	15772	10573	6765
20°	10440	17099	10386	5957
25°	10278	17173	10231	5380
30°	10104	14602	10025	4984
35°	9860	11018	9735	4688
40°	9588	7985	9399	4457
45°	9138	6069	8911	4253
50°	8604	4904	8368	3954
55°	8026	4061	7764	3555
60°	7446	3434	7113	2956
65°	6717	2797	6503	2350
70°	6048	2268	5763	1909
75°	5300	1635	4934	1399
80°	4372	1083	3977	1028
85°	3173	558	2627	558

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 13468 cd/sqm

TEST NUMBER: P1013409

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.7	1.6
10°-20°	385.8	4.8
20°-30°	604.3	7.4
30°-40°	671.0	8.3
40°-50°	594.6	7.3
50°-60°	463.4	5.7
60°-70°	303.1	3.7
70°-80°	148.7	1.8
80°-90°	39.4	0.5
90°-100°	51.2	0.6
100°-110°	337.5	4.2
110°-120°	644.4	7.9
120°-130°	818.1	10.1
130°-140°	875.1	10.8
140°-150°	818.3	10.1
150°-160°	659.9	8.1
160°-170°	425.6	5.2
170°-180°	146.7	1.8
0°-30°	1117.8	13.8
0°-40°	1788.9	22.0
0°-60°	2846.9	35.1
0°-90°	3338.2	41.1
90°-120°	1033.1	12.7
90°-150°	3544.6	43.7
90°-180°	4777.0	58.9
0°-180°	8115.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1319	1319	1319	1319	1319	
5°	1317	1524	1319	1165	1317	125
15°	1261	2020	1261	866	1261	356
25°	1156	2178	1150	682	1156	533
35°	1008	1342	995	571	1008	630
45°	812	686	792	480	812	626
55°	585	409	566	358	585	523
65°	367	239	355	201	367	366
75°	184	111	171	95	184	195
85°	44	27	36	27	44	49
90°	4	35	4	35	4	6
95°	64	34	64	34	64	78
105°	348	329	348	329	348	364
115°	649	654	649	654	649	639
125°	912	919	912	919	912	815
135°	1132	1140	1132	1140	1132	872
145°	1305	1312	1305	1312	1305	815
155°	1431	1429	1431	1429	1431	660
165°	1509	1502	1509	1502	1509	426
175°	1544	1534	1544	1534	1544	147
180°	1544	1544	1544	1544	1544	

TEST NUMBER: P1013409

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1321.4	1333.1	1339.5	1344.8	1355.4	1359.7	1368.2	1370.3	1378.8	1377.8	1374.6
5°	1317.2	1337.4	1352.2	1368.2	1387.3	1398.0	1409.6	1426.7	1435.2	1446.9	1454.3
7.5°	1309.7	1337.4	1361.8	1386.3	1417.1	1434.1	1449.0	1475.6	1497.9	1517.0	1538.3
10°	1298.0	1333.1	1369.3	1402.2	1444.7	1464.9	1487.3	1526.6	1557.4	1584.0	1618.0
12.5°	1280.0	1328.9	1369.3	1413.9	1468.1	1495.8	1525.5	1572.3	1608.4	1652.0	1694.6
15°	1260.8	1315.0	1368.2	1426.7	1488.3	1520.2	1550.0	1612.7	1668.0	1717.9	1764.7
17.5°	1239.6	1299.1	1357.6	1422.4	1496.8	1536.2	1571.2	1646.7	1707.3	1772.2	1818.9
20°	1214.0	1278.9	1345.9	1418.2	1502.1	1545.7	1585.1	1671.2	1738.1	1808.3	1866.8
22.5°	1186.4	1256.6	1329.9	1408.6	1495.8	1543.6	1589.3	1681.8	1759.4	1824.3	1902.9
25°	1155.6	1230.0	1305.5	1388.4	1486.2	1538.3	1585.1	1676.5	1759.4	1844.4	1921.0
27.5°	1123.7	1200.2	1278.9	1366.1	1466.0	1517.0	1570.2	1658.4	1755.1	1847.6	1925.2
30°	1088.6	1163.0	1245.9	1328.9	1435.2	1486.2	1540.4	1636.1	1741.3	1833.8	1917.8
32.5°	1050.3	1126.9	1205.5	1291.6	1395.8	1451.1	1501.1	1609.5	1716.9	1808.3	1887.0
35°	1007.8	1080.1	1154.5	1242.7	1345.9	1395.8	1455.4	1568.0	1676.5	1773.2	1824.3
37.5°	962.1	1031.2	1100.3	1187.5	1286.3	1346.9	1405.4	1519.1	1634.0	1698.8	1725.4
40°	919.6	980.2	1040.8	1124.7	1224.7	1287.4	1346.9	1464.9	1565.9	1615.9	1595.7
42.5°	865.3	928.1	982.3	1059.9	1160.9	1219.4	1280.0	1402.2	1484.1	1504.3	1454.3
45°	812.2	864.3	916.4	991.9	1098.2	1148.1	1213.0	1326.7	1394.8	1376.7	1303.3
47.5°	760.1	802.6	851.5	924.9	1020.6	1080.1	1140.7	1239.6	1287.4	1261.9	1159.8
50°	698.4	741.0	792.0	855.8	948.3	1005.7	1053.5	1144.9	1181.1	1118.4	995.0
52.5°	640.0	677.2	720.8	780.3	868.5	920.6	972.7	1051.4	1063.1	990.8	861.1
55°	584.7	614.5	660.2	708.0	788.8	844.1	880.2	947.2	944.0	853.7	742.0
57.5°	527.3	554.9	585.8	635.7	712.3	753.7	793.1	851.5	820.7	744.2	633.6
60°	476.3	492.2	523.0	570.9	635.7	671.9	702.7	734.6	708.0	625.1	540.0
62.5°	419.9	438.0	460.3	498.6	556.0	590.0	612.3	626.2	598.5	534.7	457.1
65°	366.8	382.7	406.1	440.1	483.7	509.2	520.9	530.5	515.6	443.3	381.6
67.5°	318.9	329.6	350.8	373.1	419.9	426.3	442.2	446.5	416.7	361.4	312.5
70°	271.1	281.7	291.3	317.9	339.1	350.8	354.0	354.0	324.2	288.1	247.7
72.5°	226.4	232.8	242.4	260.5	272.1	280.7	284.9	279.6	252.0	222.2	192.4
75°	183.9	187.1	195.6	207.3	216.9	213.7	212.6	206.2	186.0	164.8	147.8
77.5°	141.4	143.5	153.1	156.3	156.3	159.5	155.2	148.8	131.8	115.9	108.4
80°	106.3	109.5	110.6	112.7	110.6	110.6	107.4	96.7	88.2	80.8	75.5
82.5°	73.4	75.5	76.5	73.4	75.5	72.3	67.0	59.5	54.2	53.2	51.0
85°	43.6	44.6	43.6	43.6	40.4	39.3	35.1	34.0	31.9	31.9	30.8
87.5°	21.3	20.2	18.1	15.9	15.9	14.9	15.9	13.8	15.9	14.9	13.8
90°	3.5	6.3	9.1	12.0	14.8	16.2	17.2	19.3	21.3	23.4	25.4
92.5°	17.3	16.8	16.3	15.8	15.3	15.0	16.0	18.1	20.1	22.2	24.2
95°	63.5	54.8	46.0	37.3	28.6	24.2	24.3	24.6	24.9	25.1	25.4
97.5°	121.2	126.8	132.5	138.1	143.8	146.6	133.1	106.2	79.3	52.3	25.4
100°	189.4	194.0	198.6	203.2	207.8	210.1	192.4	157.0	121.6	86.2	50.8
102.5°	265.6	268.7	271.7	274.8	277.9	279.4	280.9	284.0	287.1	290.2	293.3
105°	347.5	349.1	350.6	352.2	353.7	354.5	355.1	356.4	357.7	358.9	360.2
107.5°	422.6	423.4	424.2	424.9	425.7	426.1	427.0	428.8	430.5	432.3	434.1
110°	498.8	499.6	500.4	501.1	501.9	502.3	503.1	504.6	506.1	507.7	509.2

TEST NUMBER: P1013409

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	572.7	574.2	575.8	577.3	578.8	579.6	579.9	580.4	580.9	581.4	581.9
115°	648.9	649.7	650.5	651.2	652.0	652.4	652.3	652.0	651.7	651.5	651.2
117.5°	717.0	718.0	719.0	720.1	721.1	721.6	722.0	722.8	723.5	724.3	725.1
120°	786.3	787.3	788.3	789.4	790.4	790.9	790.8	790.5	790.3	790.0	789.8
122.5°	851.0	851.5	852.0	852.5	853.0	853.3	853.6	854.1	854.6	855.1	855.6
125°	912.1	913.1	914.2	915.2	916.3	916.8	916.5	916.0	915.5	915.0	914.5
127.5°	971.0	971.3	971.5	971.8	972.1	972.2	972.8	974.1	975.4	976.7	978.0
130°	1027.6	1027.9	1028.1	1028.4	1028.7	1028.8	1029.2	1029.9	1030.7	1031.4	1032.2
132.5°	1079.6	1080.1	1080.6	1081.1	1081.6	1081.9	1082.4	1083.4	1084.5	1085.5	1086.5
135°	1131.5	1131.3	1131.0	1130.8	1130.5	1130.4	1130.9	1131.9	1133.0	1134.0	1135.0
137.5°	1177.7	1177.7	1177.7	1177.7	1177.7	1177.7	1178.3	1179.6	1180.9	1182.2	1183.5
140°	1222.7	1223.2	1223.7	1224.2	1224.7	1225.0	1225.3	1225.8	1226.3	1226.9	1227.4
142.5°	1263.1	1264.1	1265.2	1266.2	1267.3	1267.8	1267.9	1268.2	1268.4	1268.7	1268.9
145°	1304.7	1305.5	1306.3	1307.0	1307.8	1308.2	1308.2	1308.2	1308.2	1308.2	1308.2
147.5°	1337.0	1338.6	1340.1	1341.7	1343.2	1344.0	1343.9	1343.6	1343.3	1343.1	1342.8
150°	1372.8	1373.8	1374.9	1375.9	1377.0	1377.5	1377.4	1377.1	1376.8	1376.6	1376.3
152.5°	1402.9	1403.7	1404.4	1405.2	1405.9	1406.3	1406.0	1405.5	1405.0	1404.5	1404.0
155°	1430.6	1430.8	1431.1	1431.3	1431.6	1431.7	1431.3	1430.6	1429.8	1429.1	1428.3
157.5°	1454.8	1454.8	1454.8	1454.8	1454.8	1454.8	1454.3	1453.3	1452.2	1451.2	1450.2
160°	1475.6	1474.8	1474.0	1473.3	1472.5	1472.1	1472.0	1471.7	1471.5	1471.2	1471.0
162.5°	1494.1	1493.1	1492.1	1491.0	1490.0	1489.5	1489.4	1489.1	1488.8	1488.6	1488.3
165°	1509.1	1507.8	1506.5	1505.2	1503.9	1503.3	1503.3	1503.3	1503.3	1503.3	1503.3
167.5°	1521.8	1520.5	1519.2	1517.9	1516.6	1516.0	1515.9	1515.6	1515.4	1515.1	1514.9
170°	1532.2	1530.6	1529.1	1527.5	1526.0	1525.2	1525.3	1525.6	1525.9	1526.1	1526.4
172.5°	1539.1	1537.6	1536.0	1534.5	1533.0	1532.2	1532.3	1532.6	1532.8	1533.1	1533.3
175°	1543.7	1542.2	1540.6	1539.1	1537.6	1536.8	1536.9	1537.2	1537.4	1537.7	1537.9
177.5°	1547.2	1545.4	1543.6	1541.8	1540.0	1539.1	1539.4	1539.9	1540.4	1540.9	1541.4
180°	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7

TEST NUMBER: P1013409

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1383.1	1394.8	1395.8	1406.5	1403.3	1398.0	1407.5	1401.1	1413.9	1409.6	1415.0
5°	1463.9	1479.8	1493.6	1502.1	1517.0	1513.8	1529.8	1524.5	1536.2	1524.5	1539.3
7.5°	1558.5	1585.1	1598.9	1621.2	1627.6	1628.6	1647.8	1652.0	1659.5	1652.0	1660.5
10°	1651.0	1682.9	1714.8	1732.8	1744.5	1760.5	1777.5	1784.9	1790.2	1782.8	1788.1
12.5°	1735.0	1784.9	1820.0	1856.1	1864.6	1878.5	1896.5	1894.4	1915.7	1911.4	1921.0
15°	1812.6	1867.8	1910.4	1939.1	1962.5	1974.1	2008.2	2010.3	2009.2	2019.9	2013.5
17.5°	1881.7	1928.4	1989.0	2026.2	2054.9	2054.9	2074.1	2113.4	2110.2	2109.2	2115.5
20°	1938.0	1991.2	2047.5	2110.2	2133.6	2137.9	2164.4	2184.6	2187.8	2187.8	2187.8
22.5°	1980.5	2043.2	2103.8	2148.5	2166.6	2181.4	2204.8	2217.6	2221.8	2219.7	2221.8
25°	2001.8	2061.3	2123.0	2163.4	2174.0	2182.5	2184.6	2192.1	2191.0	2178.3	2185.7
27.5°	2006.0	2063.4	2103.8	2114.5	2109.2	2103.8	2069.8	2073.0	2063.4	2044.3	2051.8
30°	1986.9	2017.7	2016.7	1983.7	1974.1	1951.8	1921.0	1875.3	1838.1	1822.1	1827.4
32.5°	1917.8	1917.8	1879.5	1805.1	1772.2	1731.8	1676.5	1635.0	1586.1	1575.5	1595.7
35°	1822.1	1767.9	1697.7	1599.9	1550.0	1520.2	1424.5	1394.8	1353.3	1341.6	1351.2
37.5°	1673.3	1582.9	1480.9	1389.4	1346.9	1293.8	1209.8	1167.3	1137.5	1117.3	1126.9
40°	1506.4	1396.9	1290.6	1177.9	1131.1	1087.5	1024.8	986.5	938.7	940.8	944.0
42.5°	1346.9	1218.3	1099.2	995.0	950.4	914.3	870.7	823.9	806.9	801.6	796.2
45°	1177.9	1040.8	929.1	851.5	811.1	777.1	736.7	710.1	689.9	685.7	691.0
47.5°	1018.4	902.6	796.2	724.0	691.0	674.0	642.1	617.7	604.9	594.3	600.6
50°	873.9	765.4	680.4	619.8	596.4	584.7	554.9	542.2	529.4	526.2	525.2
52.5°	754.8	662.3	588.9	540.0	522.0	515.6	493.3	475.2	464.6	467.8	469.9
55°	646.4	567.7	510.3	470.9	456.1	448.6	432.7	419.9	412.5	409.3	411.4
57.5°	550.7	482.6	441.2	409.3	397.6	394.4	377.4	373.1	367.8	364.6	364.6
60°	463.5	415.7	377.4	359.3	346.6	343.4	330.6	325.3	324.2	321.1	318.9
62.5°	390.2	350.8	324.2	305.1	299.8	298.7	290.2	283.8	280.7	278.5	278.5
65°	326.4	297.7	275.3	261.5	257.3	255.1	245.6	243.4	241.3	239.2	238.1
67.5°	272.1	246.6	230.7	221.1	215.8	216.9	211.6	207.3	207.3	206.2	205.2
70°	220.1	204.1	190.3	185.0	182.9	180.7	178.6	175.4	174.3	174.3	174.3
72.5°	173.3	162.7	155.2	152.0	149.9	147.8	145.6	145.6	145.6	144.6	144.6
75°	132.9	128.6	123.3	120.1	120.1	122.3	119.1	115.9	112.7	110.6	111.6
77.5°	99.9	97.8	94.6	89.3	90.4	88.2	88.2	86.1	87.2	87.2	85.0
80°	73.4	70.2	69.1	65.9	67.0	65.9	64.8	64.8	62.7	62.7	62.7
82.5°	51.0	47.8	47.8	46.8	45.7	45.7	44.6	44.6	45.7	43.6	43.6
85°	30.8	29.8	29.8	27.6	27.6	27.6	27.6	28.7	27.6	26.6	26.6
87.5°	13.8	14.9	13.8	12.8	12.8	12.8	11.7	11.7	10.6	11.7	11.7
90°	26.9	28.5	30.0	31.5	32.3	32.6	33.1	33.6	34.1	34.6	34.1
92.5°	25.8	27.3	28.9	30.4	31.2	31.2	31.2	31.2	31.2	31.2	31.2
95°	26.9	28.5	30.0	31.5	32.3	32.4	32.7	33.0	33.2	33.5	33.2
97.5°	26.7	28.0	29.3	30.6	31.2	31.3	31.6	31.8	32.1	32.3	32.1
100°	46.4	42.1	37.7	33.4	31.2	31.3	31.6	31.8	32.1	32.3	32.1
102.5°	235.6	177.8	120.1	62.4	33.5	33.5	33.5	33.5	33.5	33.5	33.5
105°	362.5	364.8	367.1	369.4	370.6	366.0	356.8	347.5	338.3	329.1	338.3
107.5°	435.4	436.7	438.0	439.3	439.9	440.4	441.4	442.5	443.5	444.5	443.5
110°	509.7	510.2	510.7	511.2	511.5	511.9	512.7	513.4	514.2	515.0	514.2

TEST NUMBER: P1013409

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	581.7	581.4	581.2	580.9	580.8	581.3	582.3	583.4	584.4	585.4	584.4
115°	651.7	652.2	652.7	653.2	653.5	653.5	653.5	653.5	653.5	653.5	653.5
117.5°	724.8	724.6	724.3	724.0	723.9	723.9	723.9	723.9	723.9	723.9	723.9
120°	790.3	790.8	791.3	791.8	792.1	791.8	791.3	790.8	790.3	789.8	790.3
122.5°	855.8	856.1	856.3	856.6	856.7	856.4	855.9	855.4	854.9	854.4	854.9
125°	915.3	916.0	916.8	917.5	917.9	918.0	918.3	918.6	918.8	919.1	918.8
127.5°	977.7	977.5	977.2	976.9	976.8	976.7	976.4	976.1	975.9	975.6	975.9
130°	1032.5	1032.7	1033.0	1033.3	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4
132.5°	1086.7	1087.0	1087.2	1087.5	1087.6	1087.5	1087.2	1087.0	1086.7	1086.5	1086.7
135°	1135.5	1136.0	1136.5	1137.0	1137.3	1137.6	1138.1	1138.6	1139.1	1139.6	1139.1
137.5°	1184.0	1184.5	1185.0	1185.5	1185.8	1185.7	1185.4	1185.1	1184.9	1184.6	1184.9
140°	1228.2	1228.9	1229.7	1230.4	1230.8	1230.9	1231.2	1231.5	1231.7	1232.0	1231.7
142.5°	1269.4	1269.9	1270.4	1270.9	1271.2	1271.2	1271.2	1271.2	1271.2	1271.2	1271.2
145°	1308.4	1308.7	1308.9	1309.2	1309.3	1309.6	1310.1	1310.6	1311.1	1311.6	1311.1
147.5°	1343.1	1343.3	1343.6	1343.9	1344.0	1344.1	1344.4	1344.6	1344.9	1345.1	1344.9
150°	1376.3	1376.3	1376.3	1376.3	1376.3	1376.4	1376.7	1377.0	1377.2	1377.5	1377.2
152.5°	1404.5	1405.0	1405.5	1406.0	1406.3	1406.2	1405.9	1405.7	1405.4	1405.2	1405.4
155°	1429.3	1430.3	1431.4	1432.4	1432.9	1432.5	1431.7	1431.0	1430.2	1429.4	1430.2
157.5°	1451.5	1452.8	1454.1	1455.4	1456.0	1455.4	1454.1	1452.8	1451.5	1450.2	1451.5
160°	1472.5	1474.1	1475.6	1477.1	1477.9	1477.1	1475.6	1474.1	1472.5	1471.0	1472.5
162.5°	1489.8	1491.4	1492.9	1494.4	1495.2	1494.3	1492.5	1490.7	1488.9	1487.1	1488.9
165°	1505.3	1507.4	1509.4	1511.5	1512.5	1511.4	1509.1	1506.8	1504.5	1502.2	1504.5
167.5°	1517.2	1519.5	1521.8	1524.1	1525.2	1523.9	1521.4	1518.8	1516.3	1513.7	1516.3
170°	1528.4	1530.5	1532.5	1534.6	1535.6	1534.3	1531.8	1529.2	1526.7	1524.1	1526.7
172.5°	1535.4	1537.4	1539.5	1541.6	1542.6	1541.2	1538.4	1535.5	1532.7	1529.9	1532.7
175°	1540.2	1542.5	1544.8	1547.1	1548.3	1546.8	1543.7	1540.6	1537.6	1534.5	1537.6
177.5°	1543.4	1545.5	1547.5	1549.6	1550.6	1549.1	1546.0	1542.9	1539.9	1536.8	1539.9
180°	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7

TEST NUMBER: P1013409

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1418.2	1410.7	1409.6	1409.6	1398.0	1404.3	1391.6	1377.8	1371.4	1371.4	1359.7
5°	1536.2	1528.7	1521.3	1509.6	1509.6	1503.2	1483.0	1462.8	1447.9	1435.2	1421.3
7.5°	1657.3	1649.9	1628.6	1616.9	1623.3	1610.6	1584.0	1550.0	1524.5	1504.3	1475.6
10°	1789.2	1769.0	1758.3	1752.0	1729.6	1715.8	1685.0	1635.0	1603.1	1576.6	1539.3
12.5°	1896.5	1902.9	1862.5	1865.7	1843.4	1824.3	1776.4	1728.6	1680.7	1643.5	1588.2
15°	2012.4	1993.3	1968.8	1949.7	1942.3	1918.9	1878.5	1814.7	1762.6	1704.1	1641.4
17.5°	2103.8	2089.0	2065.6	2047.5	2031.6	1975.2	1941.2	1884.8	1813.6	1756.2	1679.7
20°	2181.4	2167.6	2134.7	2123.0	2094.3	2053.9	2005.0	1917.8	1854.0	1791.3	1716.9
22.5°	2214.4	2200.6	2171.9	2157.0	2138.9	2099.6	2052.8	1969.9	1891.2	1812.6	1733.9
25°	2186.8	2186.8	2172.9	2167.6	2151.7	2116.6	2068.8	1998.6	1914.6	1829.6	1736.0
27.5°	2052.8	2079.4	2089.0	2094.3	2094.3	2095.3	2062.4	1994.3	1912.5	1829.6	1731.8
30°	1859.3	1904.0	1943.3	1955.0	1975.2	1997.5	2011.4	1978.4	1905.0	1817.9	1720.1
32.5°	1615.9	1673.3	1746.6	1764.7	1792.4	1859.3	1896.5	1910.4	1870.0	1793.4	1689.2
35°	1373.5	1445.8	1490.4	1545.7	1571.2	1670.1	1753.0	1803.0	1793.4	1747.7	1653.1
37.5°	1161.9	1203.4	1257.6	1316.1	1367.1	1461.7	1564.9	1661.6	1700.9	1678.6	1607.4
40°	958.9	1007.8	1072.7	1120.5	1155.6	1250.2	1377.8	1483.0	1569.1	1582.9	1539.3
42.5°	815.4	864.3	903.6	955.7	983.4	1074.8	1187.5	1319.3	1421.3	1475.6	1456.4
45°	704.8	734.6	766.5	796.2	830.3	911.1	1015.2	1159.8	1274.6	1351.2	1358.6
47.5°	608.1	634.7	662.3	689.9	709.1	771.8	867.5	985.5	1110.9	1216.2	1257.6
50°	540.0	552.8	573.0	588.9	611.3	665.5	742.0	844.1	977.0	1090.7	1144.9
52.5°	473.1	489.0	505.0	518.8	533.7	571.9	642.1	730.3	845.2	962.1	1029.1
55°	416.7	429.5	444.4	453.9	462.4	496.5	549.6	617.7	716.5	827.1	910.0
57.5°	371.0	376.3	389.1	394.4	404.0	431.6	469.9	530.5	610.2	717.6	785.6
60°	321.1	331.7	341.2	345.5	352.9	372.1	398.7	455.0	524.1	602.8	680.4
62.5°	280.7	284.9	292.3	297.7	303.0	323.2	345.5	388.0	440.1	506.0	577.3
65°	243.4	245.6	249.8	257.3	260.5	275.3	288.1	318.9	367.8	417.8	489.0
67.5°	205.2	207.3	212.6	216.9	220.1	229.6	243.4	265.8	292.3	347.6	387.0
70°	175.4	175.4	178.6	180.7	183.9	188.2	195.6	212.6	237.1	272.1	308.3
72.5°	146.7	146.7	146.7	149.9	149.9	153.1	157.3	169.0	186.0	213.7	237.1
75°	113.7	114.8	116.9	116.9	118.0	122.3	125.4	128.6	137.1	155.2	176.5
77.5°	86.1	88.2	89.3	87.2	89.3	89.3	93.6	97.8	102.1	107.4	123.3
80°	63.8	64.8	62.7	63.8	63.8	65.9	68.0	67.0	69.1	75.5	79.7
82.5°	42.5	43.6	43.6	43.6	43.6	46.8	46.8	45.7	46.8	47.8	48.9
85°	26.6	25.5	25.5	26.6	25.5	25.5	26.6	27.6	26.6	27.6	28.7
87.5°	11.7	11.7	11.7	11.7	10.6	10.6	11.7	10.6	11.7	10.6	9.6
90°	33.6	33.1	32.6	32.3	31.5	30.0	28.5	26.9	25.4	23.4	21.3
92.5°	31.2	31.2	31.2	31.2	30.4	28.9	27.3	25.8	24.2	22.2	20.1
95°	33.0	32.7	32.4	32.3	31.5	30.0	28.5	26.9	25.4	25.1	24.9
97.5°	31.8	31.6	31.3	31.2	30.6	29.3	28.0	26.7	25.4	52.3	79.3
100°	31.8	31.6	31.3	31.2	33.4	37.7	42.1	46.4	50.8	86.2	121.6
102.5°	33.5	33.5	33.5	33.5	62.4	120.1	177.8	235.6	293.3	290.2	287.1
105°	347.5	356.8	366.0	370.6	369.4	367.1	364.8	362.5	360.2	358.9	357.7
107.5°	442.5	441.4	440.4	439.9	439.3	438.0	436.7	435.4	434.1	432.3	430.5
110°	513.4	512.7	511.9	511.5	511.2	510.7	510.2	509.7	509.2	507.7	506.1

TEST NUMBER: P1013409

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	583.4	582.3	581.3	580.8	580.9	581.2	581.4	581.7	581.9	581.4	580.9
115°	653.5	653.5	653.5	653.5	653.2	652.7	652.2	651.7	651.2	651.5	651.7
117.5°	723.9	723.9	723.9	723.9	724.0	724.3	724.6	724.8	725.1	724.3	723.5
120°	790.8	791.3	791.8	792.1	791.8	791.3	790.8	790.3	789.8	790.0	790.3
122.5°	855.4	855.9	856.4	856.7	856.6	856.3	856.1	855.8	855.6	855.1	854.6
125°	918.6	918.3	918.0	917.9	917.5	916.8	916.0	915.3	914.5	915.0	915.5
127.5°	976.1	976.4	976.7	976.8	976.9	977.2	977.5	977.7	978.0	976.7	975.4
130°	1033.4	1033.4	1033.4	1033.4	1033.3	1033.0	1032.7	1032.5	1032.2	1031.4	1030.7
132.5°	1087.0	1087.2	1087.5	1087.6	1087.5	1087.2	1087.0	1086.7	1086.5	1085.5	1084.5
135°	1138.6	1138.1	1137.6	1137.3	1137.0	1136.5	1136.0	1135.5	1135.0	1134.0	1133.0
137.5°	1185.1	1185.4	1185.7	1185.8	1185.5	1185.0	1184.5	1184.0	1183.5	1182.2	1180.9
140°	1231.5	1231.2	1230.9	1230.8	1230.4	1229.7	1228.9	1228.2	1227.4	1226.9	1226.3
142.5°	1271.2	1271.2	1271.2	1271.2	1270.9	1270.4	1269.9	1269.4	1268.9	1268.7	1268.4
145°	1310.6	1310.1	1309.6	1309.3	1309.2	1308.9	1308.7	1308.4	1308.2	1308.2	1308.2
147.5°	1344.6	1344.4	1344.1	1344.0	1343.9	1343.6	1343.3	1343.1	1342.8	1343.1	1343.3
150°	1377.0	1376.7	1376.4	1376.3	1376.3	1376.3	1376.3	1376.3	1376.3	1376.6	1376.8
152.5°	1405.7	1405.9	1406.2	1406.3	1406.0	1405.5	1405.0	1404.5	1404.0	1404.5	1405.0
155°	1431.0	1431.7	1432.5	1432.9	1432.4	1431.4	1430.3	1429.3	1428.3	1429.1	1429.8
157.5°	1452.8	1454.1	1455.4	1456.0	1455.4	1454.1	1452.8	1451.5	1450.2	1451.2	1452.2
160°	1474.1	1475.6	1477.1	1477.9	1477.1	1475.6	1474.1	1472.5	1471.0	1471.2	1471.5
162.5°	1490.7	1492.5	1494.3	1495.2	1494.4	1492.9	1491.4	1489.8	1488.3	1488.6	1488.8
165°	1506.8	1509.1	1511.4	1512.5	1511.5	1509.4	1507.4	1505.3	1503.3	1503.3	1503.3
167.5°	1518.8	1521.4	1523.9	1525.2	1524.1	1521.8	1519.5	1517.2	1514.9	1515.1	1515.4
170°	1529.2	1531.8	1534.3	1535.6	1534.6	1532.5	1530.5	1528.4	1526.4	1526.1	1525.9
172.5°	1535.5	1538.4	1541.2	1542.6	1541.6	1539.5	1537.4	1535.4	1533.3	1533.1	1532.8
175°	1540.6	1543.7	1546.8	1548.3	1547.1	1544.8	1542.5	1540.2	1537.9	1537.7	1537.4
177.5°	1542.9	1546.0	1549.1	1550.6	1549.6	1547.5	1545.5	1543.4	1541.4	1540.9	1540.4
180°	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7

TEST NUMBER: P1013409

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1353.3	1348.0	1344.8	1343.7	1334.2	1328.9	1325.7	1323.5	1320.3	1311.8	1304.4
5°	1404.3	1389.4	1382.0	1373.5	1358.6	1341.6	1327.8	1319.3	1308.7	1291.6	1275.7
7.5°	1452.2	1429.8	1415.0	1403.3	1377.8	1350.1	1327.8	1309.7	1289.5	1266.1	1243.8
10°	1502.1	1466.0	1446.9	1428.8	1391.6	1355.4	1323.5	1297.0	1268.3	1237.4	1213.0
12.5°	1541.5	1493.6	1472.4	1446.9	1401.1	1358.6	1318.2	1282.1	1244.9	1211.9	1176.8
15°	1587.2	1527.7	1503.2	1470.2	1407.5	1352.2	1300.2	1260.8	1222.5	1173.6	1136.4
17.5°	1613.8	1544.7	1509.6	1480.9	1412.8	1345.9	1285.3	1236.4	1191.7	1142.8	1103.5
20°	1640.3	1561.7	1522.3	1481.9	1401.1	1329.9	1266.1	1207.7	1160.9	1107.7	1067.3
22.5°	1648.8	1557.4	1516.0	1478.7	1393.7	1314.0	1240.6	1181.1	1126.9	1073.7	1028.0
25°	1648.8	1556.4	1507.5	1459.6	1370.3	1288.5	1215.1	1150.3	1089.7	1036.5	990.8
27.5°	1631.8	1535.1	1484.1	1440.5	1348.0	1259.8	1184.3	1113.0	1054.6	1001.4	949.3
30°	1610.6	1504.3	1453.2	1401.1	1311.8	1227.9	1146.0	1080.1	1018.4	957.8	911.1
32.5°	1584.0	1471.3	1415.0	1361.8	1267.2	1180.0	1104.5	1039.7	981.2	918.5	866.4
35°	1545.7	1422.4	1359.7	1312.9	1221.5	1131.1	1058.8	995.0	938.7	873.9	817.5
37.5°	1496.8	1377.8	1314.0	1256.6	1161.9	1079.0	1011.0	949.3	894.1	834.5	771.8
40°	1439.4	1315.0	1259.8	1199.2	1099.2	1020.6	956.8	901.5	846.2	789.9	729.3
42.5°	1374.6	1251.2	1189.6	1131.1	1035.4	957.8	898.3	848.3	797.3	745.2	680.4
45°	1297.0	1181.1	1121.6	1066.3	973.8	894.1	839.8	792.0	748.4	695.3	637.8
47.5°	1209.8	1108.8	1048.2	988.7	898.3	829.2	776.1	735.7	698.4	645.3	593.2
50°	1124.7	1024.8	975.9	915.3	832.4	767.5	713.3	679.3	650.6	598.5	551.7
52.5°	1017.4	941.9	895.1	843.0	763.3	697.4	654.9	625.1	591.1	550.7	509.2
55°	922.8	852.6	815.4	766.5	687.8	629.3	593.2	565.6	539.0	502.8	469.9
57.5°	815.4	771.8	734.6	692.1	614.5	564.5	532.6	509.2	484.8	455.0	428.4
60°	702.7	682.5	646.4	612.3	546.4	502.8	476.3	455.0	431.6	407.2	384.8
62.5°	602.8	591.1	569.8	543.2	481.6	444.4	417.8	401.8	384.8	362.5	341.2
65°	508.2	502.8	482.6	463.5	421.0	388.0	364.6	355.1	335.9	318.9	299.8
67.5°	424.2	417.8	406.1	397.6	361.4	330.6	318.9	306.2	290.2	277.5	261.5
70°	339.1	338.1	330.6	320.0	300.9	278.5	266.8	258.3	242.4	232.8	221.1
72.5°	263.6	269.0	262.6	258.3	245.6	229.6	219.0	213.7	200.9	193.5	185.0
75°	196.7	200.9	204.1	196.7	193.5	186.0	176.5	171.2	164.8	154.1	151.0
77.5°	133.9	143.5	143.5	145.6	146.7	142.5	135.0	130.8	123.3	121.2	116.9
80°	88.2	96.7	97.8	99.9	103.1	103.1	97.8	96.7	89.3	88.2	85.0
82.5°	51.0	58.5	62.7	65.9	64.8	69.1	64.8	63.8	59.5	59.5	57.4
85°	27.6	28.7	30.8	33.0	35.1	37.2	37.2	36.1	35.1	34.0	31.9
87.5°	10.6	10.6	11.7	10.6	11.7	13.8	14.9	14.9	13.8	12.8	10.6
90°	19.3	17.2	16.2	14.8	12.0	9.1	6.3	3.5	6.3	9.1	12.0
92.5°	18.1	16.0	15.0	15.3	15.8	16.3	16.8	17.3	16.8	16.3	15.8
95°	24.6	24.3	24.2	28.6	37.3	46.0	54.8	63.5	54.8	46.0	37.3
97.5°	106.2	133.1	146.6	143.8	138.1	132.5	126.8	121.2	126.8	132.5	138.1
100°	157.0	192.4	210.1	207.8	203.2	198.6	194.0	189.4	194.0	198.6	203.2
102.5°	284.0	280.9	279.4	277.9	274.8	271.7	268.7	265.6	268.7	271.7	274.8
105°	356.4	355.1	354.5	353.7	352.2	350.6	349.1	347.5	349.1	350.6	352.2
107.5°	428.8	427.0	426.1	425.7	424.9	424.2	423.4	422.6	423.4	424.2	424.9
110°	504.6	503.1	502.3	501.9	501.1	500.4	499.6	498.8	499.6	500.4	501.1

TEST NUMBER: P1013409

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	580.4	579.9	579.6	578.8	577.3	575.8	574.2	572.7	574.2	575.8	577.3
115°	652.0	652.3	652.4	652.0	651.2	650.5	649.7	648.9	649.7	650.5	651.2
117.5°	722.8	722.0	721.6	721.1	720.1	719.0	718.0	717.0	718.0	719.0	720.1
120°	790.5	790.8	790.9	790.4	789.4	788.3	787.3	786.3	787.3	788.3	789.4
122.5°	854.1	853.6	853.3	853.0	852.5	852.0	851.5	851.0	851.5	852.0	852.5
125°	916.0	916.5	916.8	916.3	915.2	914.2	913.1	912.1	913.1	914.2	915.2
127.5°	974.1	972.8	972.2	972.1	971.8	971.5	971.3	971.0	971.3	971.5	971.8
130°	1029.9	1029.2	1028.8	1028.7	1028.4	1028.1	1027.9	1027.6	1027.9	1028.1	1028.4
132.5°	1083.4	1082.4	1081.9	1081.6	1081.1	1080.6	1080.1	1079.6	1080.1	1080.6	1081.1
135°	1131.9	1130.9	1130.4	1130.5	1130.8	1131.0	1131.3	1131.5	1131.3	1131.0	1130.8
137.5°	1179.6	1178.3	1177.7	1177.7	1177.7	1177.7	1177.7	1177.7	1177.7	1177.7	1177.7
140°	1225.8	1225.3	1225.0	1224.7	1224.2	1223.7	1223.2	1222.7	1223.2	1223.7	1224.2
142.5°	1268.2	1267.9	1267.8	1267.3	1266.2	1265.2	1264.1	1263.1	1264.1	1265.2	1266.2
145°	1308.2	1308.2	1308.2	1307.8	1307.0	1306.3	1305.5	1304.7	1305.5	1306.3	1307.0
147.5°	1343.6	1343.9	1344.0	1343.2	1341.7	1340.1	1338.6	1337.0	1338.6	1340.1	1341.7
150°	1377.1	1377.4	1377.5	1377.0	1375.9	1374.9	1373.8	1372.8	1373.8	1374.9	1375.9
152.5°	1405.5	1406.0	1406.3	1405.9	1405.2	1404.4	1403.7	1402.9	1403.7	1404.4	1405.2
155°	1430.6	1431.3	1431.7	1431.6	1431.3	1431.1	1430.8	1430.6	1430.8	1431.1	1431.3
157.5°	1453.3	1454.3	1454.8	1454.8	1454.8	1454.8	1454.8	1454.8	1454.8	1454.8	1454.8
160°	1471.7	1472.0	1472.1	1472.5	1473.3	1474.0	1474.8	1475.6	1474.8	1474.0	1473.3
162.5°	1489.1	1489.4	1489.5	1490.0	1491.0	1492.1	1493.1	1494.1	1493.1	1492.1	1491.0
165°	1503.3	1503.3	1503.3	1503.9	1505.2	1506.5	1507.8	1509.1	1507.8	1506.5	1505.2
167.5°	1515.6	1515.9	1516.0	1516.6	1517.9	1519.2	1520.5	1521.8	1520.5	1519.2	1517.9
170°	1525.6	1525.3	1525.2	1526.0	1527.5	1529.1	1530.6	1532.2	1530.6	1529.1	1527.5
172.5°	1532.6	1532.3	1532.2	1533.0	1534.5	1536.0	1537.6	1539.1	1537.6	1536.0	1534.5
175°	1537.2	1536.9	1536.8	1537.6	1539.1	1540.6	1542.2	1543.7	1542.2	1540.6	1539.1
177.5°	1539.9	1539.4	1539.1	1540.0	1541.8	1543.6	1545.4	1547.2	1545.4	1543.6	1541.8
180°	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7

TEST NUMBER: P1013409

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1298.0	1295.9	1293.8	1285.3	1277.8	1265.1	1254.4	1250.2	1249.1	1250.2	1247.0
5°	1260.8	1259.8	1252.3	1237.4	1223.6	1208.7	1198.1	1187.5	1181.1	1181.1	1173.6
7.5°	1225.7	1218.3	1211.9	1192.8	1176.8	1156.6	1140.7	1131.1	1125.8	1114.1	1114.1
10°	1188.5	1177.9	1169.4	1151.3	1127.9	1107.7	1087.5	1075.8	1066.3	1057.8	1054.6
12.5°	1151.3	1142.8	1126.9	1107.7	1084.3	1058.8	1037.6	1029.1	1006.7	988.7	989.7
15°	1116.2	1097.1	1089.7	1062.0	1034.4	1009.9	979.1	954.6	936.6	924.9	910.0
17.5°	1076.9	1057.8	1043.9	1020.6	984.4	946.1	916.4	883.4	865.3	845.2	835.6
20°	1033.3	1017.4	1006.7	969.5	925.9	880.2	847.3	827.1	806.9	792.0	783.5
22.5°	996.1	975.9	963.2	913.2	865.3	819.6	794.1	777.1	760.1	747.3	743.1
25°	948.3	936.6	905.7	862.2	803.7	772.9	750.5	728.2	718.6	710.1	700.6
27.5°	908.9	880.2	859.0	801.6	765.4	730.3	708.0	691.0	679.3	670.8	663.4
30°	860.0	833.5	803.7	755.9	722.9	689.9	669.7	655.9	643.2	637.8	631.5
32.5°	809.0	784.6	755.9	717.6	677.2	651.7	635.7	620.8	612.3	607.0	599.6
35°	763.3	732.5	713.3	677.2	644.2	615.5	600.6	587.9	578.3	576.2	575.1
37.5°	714.4	691.0	672.9	635.7	608.1	583.6	569.8	556.0	550.7	549.6	545.4
40°	671.9	651.7	634.7	599.6	569.8	547.5	536.9	528.4	523.0	523.0	522.0
42.5°	634.7	613.4	596.4	564.5	537.9	517.7	506.0	497.5	495.4	496.5	495.4
45°	593.2	575.1	558.1	525.2	502.8	488.0	475.2	470.9	467.8	468.8	469.9
47.5°	553.9	539.0	522.0	495.4	469.9	453.9	446.5	442.2	442.2	442.2	444.4
50°	518.8	501.8	486.9	459.3	435.9	423.1	416.7	411.4	412.5	413.5	414.6
52.5°	477.3	462.4	451.8	424.2	407.2	391.2	383.8	384.8	383.8	383.8	385.9
55°	441.2	426.3	415.7	390.2	373.1	362.5	356.1	352.9	354.0	351.9	356.1
57.5°	400.8	388.0	380.6	356.1	341.2	331.7	326.4	321.1	323.2	322.1	321.1
60°	365.7	350.8	339.1	322.1	309.4	297.7	294.5	289.2	291.3	289.2	288.1
62.5°	325.3	313.6	305.1	288.1	277.5	267.9	260.5	257.3	256.2	253.0	249.8
65°	284.9	278.5	270.0	253.0	242.4	234.9	230.7	227.5	226.4	217.9	208.4
67.5°	247.7	243.4	234.9	222.2	212.6	205.2	198.8	193.5	187.1	180.7	175.4
70°	212.6	206.2	200.9	189.2	180.7	173.3	166.9	160.5	157.3	151.0	148.8
72.5°	178.6	172.2	166.9	156.3	148.8	141.4	139.3	131.8	128.6	127.6	127.6
75°	143.5	138.2	135.0	125.4	119.1	113.7	110.6	108.4	106.3	104.2	101.0
77.5°	109.5	106.3	104.2	97.8	92.5	89.3	88.2	80.8	78.7	76.5	74.4
80°	79.7	78.7	76.5	71.2	69.1	61.7	61.7	59.5	58.5	58.5	58.5
82.5°	54.2	52.1	51.0	45.7	44.6	43.6	42.5	41.5	42.5	41.5	42.5
85°	28.7	27.6	26.6	26.6	26.6	26.6	26.6	26.6	26.6	25.5	26.6
87.5°	10.6	10.6	10.6	10.6	9.6	10.6	10.6	9.6	10.6	10.6	10.6
90°	14.8	16.2	17.2	19.3	21.3	23.4	25.4	26.9	28.5	30.0	31.5
92.5°	15.3	15.0	16.0	18.1	20.1	22.2	24.2	25.8	27.3	28.9	30.4
95°	28.6	24.2	24.3	24.6	24.9	25.1	25.4	26.9	28.5	30.0	31.5
97.5°	143.8	146.6	133.1	106.2	79.3	52.3	25.4	26.7	28.0	29.3	30.6
100°	207.8	210.1	192.4	157.0	121.6	86.2	50.8	46.4	42.1	37.7	33.4
102.5°	277.9	279.4	280.9	284.0	287.1	290.2	293.3	235.6	177.8	120.1	62.4
105°	353.7	354.5	355.1	356.4	357.7	358.9	360.2	362.5	364.8	367.1	369.4
107.5°	425.7	426.1	427.0	428.8	430.5	432.3	434.1	435.4	436.7	438.0	439.3
110°	501.9	502.3	503.1	504.6	506.1	507.7	509.2	509.7	510.2	510.7	511.2

TEST NUMBER: P1013409

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	578.8	579.6	579.9	580.4	580.9	581.4	581.9	581.7	581.4	581.2	580.9
115°	652.0	652.4	652.3	652.0	651.7	651.5	651.2	651.7	652.2	652.7	653.2
117.5°	721.1	721.6	722.0	722.8	723.5	724.3	725.1	724.8	724.6	724.3	724.0
120°	790.4	790.9	790.8	790.5	790.3	790.0	789.8	790.3	790.8	791.3	791.8
122.5°	853.0	853.3	853.6	854.1	854.6	855.1	855.6	855.8	856.1	856.3	856.6
125°	916.3	916.8	916.5	916.0	915.5	915.0	914.5	915.3	916.0	916.8	917.5
127.5°	972.1	972.2	972.8	974.1	975.4	976.7	978.0	977.7	977.5	977.2	976.9
130°	1028.7	1028.8	1029.2	1029.9	1030.7	1031.4	1032.2	1032.5	1032.7	1033.0	1033.3
132.5°	1081.6	1081.9	1082.4	1083.4	1084.5	1085.5	1086.5	1086.7	1087.0	1087.2	1087.5
135°	1130.5	1130.4	1130.9	1131.9	1133.0	1134.0	1135.0	1135.5	1136.0	1136.5	1137.0
137.5°	1177.7	1177.7	1178.3	1179.6	1180.9	1182.2	1183.5	1184.0	1184.5	1185.0	1185.5
140°	1224.7	1225.0	1225.3	1225.8	1226.3	1226.9	1227.4	1228.2	1228.9	1229.7	1230.4
142.5°	1267.3	1267.8	1267.9	1268.2	1268.4	1268.7	1268.9	1269.4	1269.9	1270.4	1270.9
145°	1307.8	1308.2	1308.2	1308.2	1308.2	1308.2	1308.2	1308.4	1308.7	1308.9	1309.2
147.5°	1343.2	1344.0	1343.9	1343.6	1343.3	1343.1	1342.8	1343.1	1343.3	1343.6	1343.9
150°	1377.0	1377.5	1377.4	1377.1	1376.8	1376.6	1376.3	1376.3	1376.3	1376.3	1376.3
152.5°	1405.9	1406.3	1406.0	1405.5	1405.0	1404.5	1404.0	1404.5	1405.0	1405.5	1406.0
155°	1431.6	1431.7	1431.3	1430.6	1429.8	1429.1	1428.3	1429.3	1430.3	1431.4	1432.4
157.5°	1454.8	1454.8	1454.3	1453.3	1452.2	1451.2	1450.2	1451.5	1452.8	1454.1	1455.4
160°	1472.5	1472.1	1472.0	1471.7	1471.5	1471.2	1471.0	1472.5	1474.1	1475.6	1477.1
162.5°	1490.0	1489.5	1489.4	1489.1	1488.8	1488.6	1488.3	1489.8	1491.4	1492.9	1494.4
165°	1503.9	1503.3	1503.3	1503.3	1503.3	1503.3	1503.3	1505.3	1507.4	1509.4	1511.5
167.5°	1516.6	1516.0	1515.9	1515.6	1515.4	1515.1	1514.9	1517.2	1519.5	1521.8	1524.1
170°	1526.0	1525.2	1525.3	1525.6	1525.9	1526.1	1526.4	1528.4	1530.5	1532.5	1534.6
172.5°	1533.0	1532.2	1532.3	1532.6	1532.8	1533.1	1533.3	1535.4	1537.4	1539.5	1541.6
175°	1537.6	1536.8	1536.9	1537.2	1537.4	1537.7	1537.9	1540.2	1542.5	1544.8	1547.1
177.5°	1540.0	1539.1	1539.4	1539.9	1540.4	1540.9	1541.4	1543.4	1545.5	1547.5	1549.6
180°	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7

TEST NUMBER: P1013409

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1247.0	1251.2	1245.9	1249.1	1241.7	1240.6	1241.7	1241.7	1242.7	1243.8	1244.9
5°	1176.8	1175.8	1169.4	1165.1	1161.9	1165.1	1167.3	1169.4	1167.3	1169.4	1170.5
7.5°	1110.9	1107.7	1104.5	1097.1	1099.2	1097.1	1103.5	1100.3	1100.3	1105.6	1109.9
10°	1052.5	1046.1	1043.9	1035.4	1029.1	1028.0	1035.4	1038.6	1041.8	1043.9	1052.5
12.5°	977.0	967.4	960.0	963.2	945.1	952.5	954.6	950.4	963.2	978.0	969.5
15°	896.2	897.2	882.4	877.0	862.2	866.4	867.5	878.1	888.7	887.7	900.4
17.5°	836.6	830.3	817.5	816.4	810.1	813.3	812.2	820.7	817.5	822.8	833.5
20°	781.4	777.1	766.5	762.2	764.4	762.2	763.3	764.4	767.5	779.2	777.1
22.5°	737.8	732.5	732.5	727.1	720.8	718.6	724.0	727.1	731.4	733.5	738.8
25°	699.5	695.3	689.9	686.8	681.4	682.5	685.7	689.9	693.1	697.4	701.6
27.5°	660.2	660.2	654.9	653.8	651.7	650.6	654.9	657.0	657.0	660.2	664.4
30°	629.3	629.3	624.0	623.0	621.9	621.9	625.1	626.2	627.2	630.4	632.5
32.5°	599.6	598.5	596.4	597.5	596.4	597.5	597.5	598.5	600.6	601.7	606.0
35°	571.9	573.0	570.9	570.9	569.8	570.9	573.0	574.1	575.1	577.3	577.3
37.5°	545.4	547.5	546.4	549.6	549.6	549.6	549.6	551.7	551.7	551.7	550.7
40°	522.0	522.0	520.9	523.0	525.2	525.2	526.2	526.2	527.3	527.3	526.2
42.5°	495.4	497.5	500.7	501.8	503.9	502.8	506.0	505.0	506.0	503.9	501.8
45°	470.9	470.9	475.2	479.5	480.5	480.5	480.5	482.6	480.5	477.3	476.3
47.5°	444.4	446.5	448.6	453.9	455.0	455.0	455.0	455.0	452.9	452.9	452.9
50°	417.8	418.9	419.9	422.0	425.2	424.2	424.2	424.2	428.4	424.2	425.2
52.5°	385.9	387.0	388.0	392.3	391.2	391.2	392.3	392.3	395.5	394.4	392.3
55°	354.0	354.0	356.1	356.1	356.1	358.3	359.3	361.4	360.4	361.4	362.5
57.5°	322.1	320.0	318.9	318.9	322.1	321.1	322.1	322.1	326.4	328.5	329.6
60°	284.9	284.9	283.8	277.5	277.5	276.4	279.6	281.7	283.8	293.4	292.3
62.5°	246.6	242.4	238.1	239.2	232.8	236.0	233.9	236.0	242.4	249.8	250.9
65°	208.4	205.2	200.9	199.9	197.7	200.9	199.9	200.9	204.1	208.4	213.7
67.5°	174.3	173.3	171.2	170.1	170.1	170.1	172.2	172.2	173.3	176.5	179.7
70°	148.8	147.8	148.8	146.7	147.8	146.7	147.8	148.8	149.9	151.0	154.1
72.5°	125.4	125.4	125.4	123.3	125.4	124.4	124.4	125.4	126.5	127.6	129.7
75°	99.9	97.8	95.7	93.6	92.5	94.6	95.7	94.6	97.8	102.1	102.1
77.5°	75.5	74.4	74.4	74.4	75.5	74.4	76.5	75.5	76.5	76.5	78.7
80°	58.5	57.4	58.5	58.5	57.4	59.5	58.5	58.5	59.5	60.6	59.5
82.5°	42.5	43.6	42.5	42.5	42.5	44.6	42.5	42.5	42.5	43.6	43.6
85°	26.6	26.6	26.6	26.6	27.6	26.6	27.6	26.6	28.7	27.6	27.6
87.5°	9.6	10.6	11.7	11.7	11.7	11.7	10.6	11.7	12.8	11.7	12.8
90°	32.3	32.6	33.1	33.6	34.1	34.6	34.1	33.6	33.1	32.6	32.3
92.5°	31.2	31.2	31.2	31.2	31.2	31.2	31.2	31.2	31.2	31.2	31.2
95°	32.3	32.4	32.7	33.0	33.2	33.5	33.2	33.0	32.7	32.4	32.3
97.5°	31.2	31.3	31.6	31.8	32.1	32.3	32.1	31.8	31.6	31.3	31.2
100°	31.2	31.3	31.6	31.8	32.1	32.3	32.1	31.8	31.6	31.3	31.2
102.5°	33.5	33.5	33.5	33.5	33.5	33.5	33.5	33.5	33.5	33.5	33.5
105°	370.6	366.0	356.8	347.5	338.3	329.1	338.3	347.5	356.8	366.0	370.6
107.5°	439.9	440.4	441.4	442.5	443.5	444.5	443.5	442.5	441.4	440.4	439.9
110°	511.5	511.9	512.7	513.4	514.2	515.0	514.2	513.4	512.7	511.9	511.5

TEST NUMBER: P1013409

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	580.8	581.3	582.3	583.4	584.4	585.4	584.4	583.4	582.3	581.3	580.8
115°	653.5	653.5	653.5	653.5	653.5	653.5	653.5	653.5	653.5	653.5	653.5
117.5°	723.9	723.9	723.9	723.9	723.9	723.9	723.9	723.9	723.9	723.9	723.9
120°	792.1	791.8	791.3	790.8	790.3	789.8	790.3	790.8	791.3	791.8	792.1
122.5°	856.7	856.4	855.9	855.4	854.9	854.4	854.9	855.4	855.9	856.4	856.7
125°	917.9	918.0	918.3	918.6	918.8	919.1	918.8	918.6	918.3	918.0	917.9
127.5°	976.8	976.7	976.4	976.1	975.9	975.6	975.9	976.1	976.4	976.7	976.8
130°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4
132.5°	1087.6	1087.5	1087.2	1087.0	1086.7	1086.5	1086.7	1087.0	1087.2	1087.5	1087.6
135°	1137.3	1137.6	1138.1	1138.6	1139.1	1139.6	1139.1	1138.6	1138.1	1137.6	1137.3
137.5°	1185.8	1185.7	1185.4	1185.1	1184.9	1184.6	1184.9	1185.1	1185.4	1185.7	1185.8
140°	1230.8	1230.9	1231.2	1231.5	1231.7	1232.0	1231.7	1231.5	1231.2	1230.9	1230.8
142.5°	1271.2	1271.2	1271.2	1271.2	1271.2	1271.2	1271.2	1271.2	1271.2	1271.2	1271.2
145°	1309.3	1309.6	1310.1	1310.6	1311.1	1311.6	1311.1	1310.6	1310.1	1309.6	1309.3
147.5°	1344.0	1344.1	1344.4	1344.6	1344.9	1345.1	1344.9	1344.6	1344.4	1344.1	1344.0
150°	1376.3	1376.4	1376.7	1377.0	1377.2	1377.5	1377.2	1377.0	1376.7	1376.4	1376.3
152.5°	1406.3	1406.2	1405.9	1405.7	1405.4	1405.2	1405.4	1405.7	1405.9	1406.2	1406.3
155°	1432.9	1432.5	1431.7	1431.0	1430.2	1429.4	1430.2	1431.0	1431.7	1432.5	1432.9
157.5°	1456.0	1455.4	1454.1	1452.8	1451.5	1450.2	1451.5	1452.8	1454.1	1455.4	1456.0
160°	1477.9	1477.1	1475.6	1474.1	1472.5	1471.0	1472.5	1474.1	1475.6	1477.1	1477.9
162.5°	1495.2	1494.3	1492.5	1490.7	1488.9	1487.1	1488.9	1490.7	1492.5	1494.3	1495.2
165°	1512.5	1511.4	1509.1	1506.8	1504.5	1502.2	1504.5	1506.8	1509.1	1511.4	1512.5
167.5°	1525.2	1523.9	1521.4	1518.8	1516.3	1513.7	1516.3	1518.8	1521.4	1523.9	1525.2
170°	1535.6	1534.3	1531.8	1529.2	1526.7	1524.1	1526.7	1529.2	1531.8	1534.3	1535.6
172.5°	1542.6	1541.2	1538.4	1535.5	1532.7	1529.9	1532.7	1535.5	1538.4	1541.2	1542.6
175°	1548.3	1546.8	1543.7	1540.6	1537.6	1534.5	1537.6	1540.6	1543.7	1546.8	1548.3
177.5°	1550.6	1549.1	1546.0	1542.9	1539.9	1536.8	1539.9	1542.9	1546.0	1549.1	1550.6
180°	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7

TEST NUMBER: P1013409

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1249.1	1254.4	1252.3	1244.9	1248.1	1254.4	1260.8	1269.3	1274.6	1278.9	1281.0
5°	1175.8	1185.3	1183.2	1183.2	1187.5	1198.1	1208.7	1226.8	1233.2	1240.6	1251.2
7.5°	1110.9	1118.4	1124.7	1126.9	1133.2	1147.1	1160.9	1181.1	1197.0	1205.5	1211.9
10°	1053.5	1058.8	1068.4	1073.7	1080.1	1097.1	1117.3	1138.6	1154.5	1169.4	1177.9
12.5°	980.2	1001.4	1014.2	1022.7	1031.2	1056.7	1072.7	1096.0	1115.2	1129.0	1141.8
15°	898.3	923.8	931.3	964.2	985.5	1005.7	1030.1	1057.8	1075.8	1091.8	1108.8
17.5°	829.2	847.3	855.8	890.9	908.9	940.8	975.9	1011.0	1038.6	1050.3	1067.3
20°	785.6	795.2	812.2	823.9	843.0	880.2	918.5	961.0	1002.5	1014.2	1031.2
22.5°	741.0	753.7	765.4	781.4	796.2	821.8	860.0	906.8	951.5	972.7	992.9
25°	700.6	713.3	720.8	737.8	751.6	777.1	803.7	851.5	904.7	922.8	954.6
27.5°	668.7	676.1	688.9	696.3	712.3	735.7	760.1	796.2	848.3	879.2	910.0
30°	636.8	642.1	652.7	663.4	675.1	691.0	718.6	753.7	801.6	828.1	859.0
32.5°	604.9	613.4	619.8	627.2	640.0	659.1	678.2	712.3	750.5	780.3	811.1
35°	578.3	581.5	590.0	598.5	607.0	624.0	644.2	677.2	711.2	734.6	762.2
37.5°	549.6	554.9	561.3	564.5	578.3	588.9	610.2	635.7	676.1	691.0	718.6
40°	527.3	526.2	532.6	537.9	544.3	561.3	574.1	601.7	633.6	657.0	674.0
42.5°	499.6	499.6	501.8	508.2	516.7	527.3	542.2	565.6	598.5	615.5	635.7
45°	477.3	474.1	475.2	479.5	484.8	495.4	510.3	530.5	563.4	577.3	598.5
47.5°	450.7	447.6	447.6	451.8	456.1	463.5	475.2	498.6	525.2	543.2	559.2
50°	421.0	422.0	421.0	424.2	426.3	433.7	446.5	465.6	490.1	505.0	523.0
52.5°	393.3	391.2	390.2	392.3	396.5	401.8	415.7	432.7	456.1	470.9	486.9
55°	359.3	361.4	361.4	361.4	367.8	370.0	380.6	397.6	421.0	432.7	447.6
57.5°	328.5	327.4	329.6	328.5	333.8	341.2	349.8	362.5	385.9	397.6	411.4
60°	294.5	295.5	296.6	296.6	300.9	308.3	317.9	329.6	348.7	360.4	373.1
62.5°	253.0	258.3	263.6	265.8	272.1	277.5	283.8	296.6	313.6	322.1	333.8
65°	213.7	221.1	228.6	233.9	238.1	243.4	252.0	263.6	277.5	286.0	297.7
67.5°	179.7	185.0	194.5	199.9	208.4	214.7	220.1	229.6	246.6	249.8	259.4
70°	155.2	157.3	161.6	165.8	175.4	180.7	187.1	196.7	209.4	216.9	222.2
72.5°	130.8	131.8	133.9	138.2	142.5	148.8	156.3	164.8	176.5	179.7	187.1
75°	104.2	110.6	110.6	113.7	116.9	120.1	126.5	135.0	142.5	147.8	152.0
77.5°	77.6	80.8	82.9	88.2	92.5	95.7	99.9	106.3	110.6	114.8	118.0
80°	60.6	61.7	62.7	62.7	64.8	69.1	73.4	77.6	82.9	85.0	88.2
82.5°	44.6	44.6	44.6	46.8	47.8	48.9	48.9	51.0	56.3	58.5	61.7
85°	28.7	28.7	28.7	28.7	29.8	30.8	31.9	33.0	33.0	33.0	35.1
87.5°	11.7	13.8	12.8	13.8	13.8	13.8	13.8	14.9	14.9	15.9	15.9
90°	31.5	30.0	28.5	26.9	25.4	23.4	21.3	19.3	17.2	16.2	14.8
92.5°	30.4	28.9	27.3	25.8	24.2	22.2	20.1	18.1	16.0	15.0	15.3
95°	31.5	30.0	28.5	26.9	25.4	25.1	24.9	24.6	24.3	24.2	28.6
97.5°	30.6	29.3	28.0	26.7	25.4	52.3	79.3	106.2	133.1	146.6	143.8
100°	33.4	37.7	42.1	46.4	50.8	86.2	121.6	157.0	192.4	210.1	207.8
102.5°	62.4	120.1	177.8	235.6	293.3	290.2	287.1	284.0	280.9	279.4	277.9
105°	369.4	367.1	364.8	362.5	360.2	358.9	357.7	356.4	355.1	354.5	353.7
107.5°	439.3	438.0	436.7	435.4	434.1	432.3	430.5	428.8	427.0	426.1	425.7
110°	511.2	510.7	510.2	509.7	509.2	507.7	506.1	504.6	503.1	502.3	501.9

TEST NUMBER: P1013409

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	580.9	581.2	581.4	581.7	581.9	581.4	580.9	580.4	579.9	579.6	578.8
115°	653.2	652.7	652.2	651.7	651.2	651.5	651.7	652.0	652.3	652.4	652.0
117.5°	724.0	724.3	724.6	724.8	725.1	724.3	723.5	722.8	722.0	721.6	721.1
120°	791.8	791.3	790.8	790.3	789.8	790.0	790.3	790.5	790.8	790.9	790.4
122.5°	856.6	856.3	856.1	855.8	855.6	855.1	854.6	854.1	853.6	853.3	853.0
125°	917.5	916.8	916.0	915.3	914.5	915.0	915.5	916.0	916.5	916.8	916.3
127.5°	976.9	977.2	977.5	977.7	978.0	976.7	975.4	974.1	972.8	972.2	972.1
130°	1033.3	1033.0	1032.7	1032.5	1032.2	1031.4	1030.7	1029.9	1029.2	1028.8	1028.7
132.5°	1087.5	1087.2	1087.0	1086.7	1086.5	1085.5	1084.5	1083.4	1082.4	1081.9	1081.6
135°	1137.0	1136.5	1136.0	1135.5	1135.0	1134.0	1133.0	1131.9	1130.9	1130.4	1130.5
137.5°	1185.5	1185.0	1184.5	1184.0	1183.5	1182.2	1180.9	1179.6	1178.3	1177.7	1177.7
140°	1230.4	1229.7	1228.9	1228.2	1227.4	1226.9	1226.3	1225.8	1225.3	1225.0	1224.7
142.5°	1270.9	1270.4	1269.9	1269.4	1268.9	1268.7	1268.4	1268.2	1267.9	1267.8	1267.3
145°	1309.2	1308.9	1308.7	1308.4	1308.2	1308.2	1308.2	1308.2	1308.2	1308.2	1307.8
147.5°	1343.9	1343.6	1343.3	1343.1	1342.8	1343.1	1343.3	1343.6	1343.9	1344.0	1343.2
150°	1376.3	1376.3	1376.3	1376.3	1376.3	1376.6	1376.8	1377.1	1377.4	1377.5	1377.0
152.5°	1406.0	1405.5	1405.0	1404.5	1404.0	1404.5	1405.0	1405.5	1406.0	1406.3	1405.9
155°	1432.4	1431.4	1430.3	1429.3	1428.3	1429.1	1429.8	1430.6	1431.3	1431.7	1431.6
157.5°	1455.4	1454.1	1452.8	1451.5	1450.2	1451.2	1452.2	1453.3	1454.3	1454.8	1454.8
160°	1477.1	1475.6	1474.1	1472.5	1471.0	1471.2	1471.5	1471.7	1472.0	1472.1	1472.5
162.5°	1494.4	1492.9	1491.4	1489.8	1488.3	1488.6	1488.8	1489.1	1489.4	1489.5	1490.0
165°	1511.5	1509.4	1507.4	1505.3	1503.3	1503.3	1503.3	1503.3	1503.3	1503.3	1503.9
167.5°	1524.1	1521.8	1519.5	1517.2	1514.9	1515.1	1515.4	1515.6	1515.9	1516.0	1516.6
170°	1534.6	1532.5	1530.5	1528.4	1526.4	1526.1	1525.9	1525.6	1525.3	1525.2	1526.0
172.5°	1541.6	1539.5	1537.4	1535.4	1533.3	1533.1	1532.8	1532.6	1532.3	1532.2	1533.0
175°	1547.1	1544.8	1542.5	1540.2	1537.9	1537.7	1537.4	1537.2	1536.9	1536.8	1537.6
177.5°	1549.6	1547.5	1545.5	1543.4	1541.4	1540.9	1540.4	1539.9	1539.4	1539.1	1540.0
180°	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7	1543.7

TEST NUMBER: P1013409

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1319.3	1319.3	1319.3	1319.3
2.5°	1289.5	1295.9	1306.5	1321.4
5°	1259.8	1277.8	1294.8	1317.2
7.5°	1233.2	1254.4	1277.8	1309.7
10°	1202.3	1228.9	1258.7	1298.0
12.5°	1166.2	1203.4	1237.4	1280.0
15°	1139.6	1167.3	1210.9	1260.8
17.5°	1102.4	1139.6	1183.2	1239.6
20°	1067.3	1106.7	1155.6	1214.0
22.5°	1030.1	1074.8	1123.7	1186.4
25°	991.9	1039.7	1088.6	1155.6
27.5°	956.8	1000.4	1055.6	1123.7
30°	914.3	964.2	1017.4	1088.6
32.5°	872.8	924.9	979.1	1050.3
35°	828.1	880.2	939.8	1007.8
37.5°	784.6	842.0	896.2	962.1
40°	736.7	796.2	852.6	919.6
42.5°	689.9	751.6	807.9	865.3
45°	646.4	707.0	758.0	812.2
47.5°	604.9	659.1	711.2	760.1
50°	564.5	610.2	658.0	698.4
52.5°	522.0	565.6	603.8	640.0
55°	483.7	517.7	551.7	584.7
57.5°	438.0	472.0	501.8	527.3
60°	399.7	421.0	449.7	476.3
62.5°	356.1	380.6	402.9	419.9
65°	313.6	334.9	351.9	366.8
67.5°	277.5	290.2	303.0	318.9
70°	233.9	244.5	259.4	271.1
72.5°	196.7	205.2	212.6	226.4
75°	159.5	166.9	171.2	183.9
77.5°	123.3	130.8	133.9	141.4
80°	94.6	95.7	99.9	106.3
82.5°	64.8	67.0	68.0	73.4
85°	37.2	42.5	41.5	43.6
87.5°	15.9	17.0	19.1	21.3
90°	12.0	9.1	6.3	3.5
92.5°	15.8	16.3	16.8	17.3
95°	37.3	46.0	54.8	63.5
97.5°	138.1	132.5	126.8	121.2
100°	203.2	198.6	194.0	189.4
102.5°	274.8	271.7	268.7	265.6
105°	352.2	350.6	349.1	347.5
107.5°	424.9	424.2	423.4	422.6
110°	501.1	500.4	499.6	498.8

TEST NUMBER: P1013409

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	577.3	575.8	574.2	572.7
115°	651.2	650.5	649.7	648.9
117.5°	720.1	719.0	718.0	717.0
120°	789.4	788.3	787.3	786.3
122.5°	852.5	852.0	851.5	851.0
125°	915.2	914.2	913.1	912.1
127.5°	971.8	971.5	971.3	971.0
130°	1028.4	1028.1	1027.9	1027.6
132.5°	1081.1	1080.6	1080.1	1079.6
135°	1130.8	1131.0	1131.3	1131.5
137.5°	1177.7	1177.7	1177.7	1177.7
140°	1224.2	1223.7	1223.2	1222.7
142.5°	1266.2	1265.2	1264.1	1263.1
145°	1307.0	1306.3	1305.5	1304.7
147.5°	1341.7	1340.1	1338.6	1337.0
150°	1375.9	1374.9	1373.8	1372.8
152.5°	1405.2	1404.4	1403.7	1402.9
155°	1431.3	1431.1	1430.8	1430.6
157.5°	1454.8	1454.8	1454.8	1454.8
160°	1473.3	1474.0	1474.8	1475.6
162.5°	1491.0	1492.1	1493.1	1494.1
165°	1505.2	1506.5	1507.8	1509.1
167.5°	1517.9	1519.2	1520.5	1521.8
170°	1527.5	1529.1	1530.6	1532.2
172.5°	1534.5	1536.0	1537.6	1539.1
175°	1539.1	1540.6	1542.2	1543.7
177.5°	1541.8	1543.6	1545.4	1547.2
180°	1543.7	1543.7	1543.7	1543.7

(END OF REPORT)