

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026084

Luminaire Tested: S124RDIP-B1195D1035UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026084
REPORT IS A COMBINATION OF REPORTS P999024 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D1035UB27-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8429.2 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026084

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026084

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	95	92	88	93	89	86	83	77	75	72	66	64	63	56	54	53
2	91	84	78	73	84	78	73	68	68	64	60	58	55	53	49	47	45
3	83	74	67	61	77	69	63	57	60	55	51	52	48	45	44	41	39
4	76	66	58	52	71	61	54	49	54	48	44	46	42	39	39	36	34
5	70	59	50	44	65	55	48	42	48	42	38	42	37	34	36	32	30
6	65	53	45	39	60	49	42	37	43	38	33	38	33	30	32	29	26
7	60	48	40	34	56	45	38	33	39	34	29	34	30	26	30	26	23
8	56	43	36	30	52	41	34	29	36	30	26	32	27	24	27	24	21
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	25	22	19
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16898	16898	16898
5°	16899	16395	16397
10°	16756	15878	15689
15°	16525	15234	14854
20°	16223	14500	13902
25°	15847	13707	12972
30°	15479	12899	11927
35°	15073	12079	10906
40°	14590	11197	9857
45°	14138	10322	8818
50°	13624	9367	7764
55°	13068	8387	6675
60°	12451	7347	5600
65°	11856	6154	4565
70°	11010	4899	3488
75°	9922	3563	2440
80°	8287	2188	1753
85°	6236	1261	964

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14138 cd/sqm

TEST NUMBER: P1026084

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.9	2.3
10°-20°	543.3	6.4
20°-30°	784.4	9.3
30°-40°	889.0	10.5
40°-50°	858.3	10.2
50°-60°	713.6	8.5
60°-70°	492.5	5.8
70°-80°	248.9	3.0
80°-90°	65.1	0.8
90°-100°	370.4	4.4
100°-110°	753.4	8.9
110°-120°	671.5	8.0
120°-130°	564.1	6.7
130°-140°	470.7	5.6
140°-150°	359.5	4.3
150°-160°	252.7	3.0
160°-170°	148.6	1.8
170°-180°	48.3	0.6
0°-30°	1522.5	18.1
0°-40°	2411.5	28.6
0°-60°	3983.4	47.3
0°-90°	4789.9	56.8
90°-120°	1795.4	21.3
90°-150°	3189.7	37.8
90°-180°	3639.0	43.2
0°-180°	8429.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2072	2072	2072	2072	2072	
5°	2069	2063	2044	2060	2056	196
15°	1971	1956	1917	1914	1902	555
25°	1782	1753	1688	1661	1645	821
35°	1541	1490	1410	1357	1328	963
45°	1257	1198	1103	1025	996	969
55°	952	888	785	703	673	852
65°	647	579	478	409	390	639
75°	344	286	211	174	165	363
85°	86	54	49	46	46	94
90°	1	8	18	20	21	7
95°	32	102	798	395	239	35
105°	115	166	643	1384	1378	122
115°	202	253	573	1101	1324	200
125°	281	334	570	937	1056	251
135°	334	398	565	832	944	258
145°	385	441	562	702	771	242
155°	438	473	547	619	646	202
165°	477	492	524	555	563	135
175°	498	499	503	510	508	47
180°	499	499	499	499	499	

TEST NUMBER: P1026084

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2072.2	2072.2	2072.2	2072.2	2072.2
2.5°	2078.5	2072.2	2054.7	2072.2	2070.6
5°	2069.0	2062.7	2043.6	2059.5	2056.3
7.5°	2054.7	2048.4	2024.6	2035.7	2030.9
10°	2032.5	2024.6	1996.0	2002.4	1996.0
12.5°	2004.0	1994.4	1959.5	1962.7	1953.2
15°	1970.6	1956.4	1916.7	1913.5	1902.4
17.5°	1932.6	1911.9	1865.9	1858.0	1842.1
20°	1886.5	1865.9	1812.0	1799.3	1778.7
22.5°	1835.8	1812.0	1753.3	1732.6	1716.8
25°	1781.8	1753.3	1688.2	1661.2	1645.4
27.5°	1726.3	1691.4	1623.2	1591.4	1569.2
30°	1667.6	1627.9	1553.3	1513.7	1488.3
32.5°	1605.7	1559.7	1481.9	1434.3	1410.5
35°	1540.7	1489.9	1410.5	1356.6	1328.0
37.5°	1472.4	1420.1	1332.8	1274.1	1245.5
40°	1399.4	1347.1	1256.6	1190.0	1161.4
42.5°	1329.6	1274.1	1178.9	1110.7	1080.5
45°	1256.6	1197.9	1102.7	1025.0	996.4
47.5°	1182.1	1121.8	1023.4	942.5	910.7
50°	1105.9	1044.0	942.5	863.1	833.0
52.5°	1028.2	967.9	863.1	782.2	750.5
55°	952.0	888.5	785.4	702.9	672.7
57.5°	877.4	810.8	709.2	625.1	602.9
60°	796.5	733.0	631.5	549.0	523.6
62.5°	723.5	656.9	552.2	477.6	458.5
65°	647.4	579.1	477.6	409.4	390.3
67.5°	568.0	503.0	407.8	347.5	325.3
70°	493.5	426.8	336.4	284.0	268.1
72.5°	414.1	355.4	271.3	228.5	214.2
75°	344.3	285.6	211.0	174.5	165.0
77.5°	271.3	220.5	157.1	131.7	128.5
80°	201.5	155.5	107.9	103.1	101.5
82.5°	141.2	100.0	77.7	74.6	73.0
85°	85.7	53.9	49.2	46.0	46.0
87.5°	36.5	23.8	22.2	20.6	22.2
90°	1.0	7.8	17.6	19.6	20.6
92.5°	13.7	75.4	384.1	126.8	89.2
95°	32.3	101.9	798.5	395.3	239.1
97.5°	53.9	112.6	854.3	807.3	574.1
100°	74.5	127.4	787.7	1116.8	898.4
102.5°	94.1	145.0	704.4	1310.9	1180.6
105°	114.6	166.1	642.7	1383.9	1378.5
107.5°	137.2	187.6	602.5	1361.8	1472.5
110°	159.7	209.2	583.9	1283.4	1474.5

TEST NUMBER: P1026084

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	181.3	230.8	575.1	1187.4	1416.7
115°	201.8	253.2	573.1	1101.2	1323.6
117.5°	223.4	274.3	572.2	1033.6	1232.5
120°	244.9	294.9	572.2	988.0	1158.0
122.5°	264.5	315.0	571.2	958.2	1099.3
125°	281.2	334.1	570.2	937.2	1056.2
127.5°	296.9	351.7	568.2	917.0	1028.7
130°	309.6	368.9	567.3	893.0	1005.2
132.5°	322.3	383.6	566.3	864.6	978.8
135°	334.1	397.8	565.3	831.8	944.5
137.5°	345.8	410.0	565.3	796.6	904.3
140°	358.6	421.2	564.3	762.2	860.2
142.5°	372.3	431.6	564.3	730.4	813.2
145°	385.0	440.9	562.4	701.5	771.0
147.5°	399.7	449.7	559.4	677.5	731.9
150°	413.4	458.0	556.5	655.4	699.5
152.5°	426.2	465.8	551.6	636.8	670.1
155°	437.9	472.8	546.7	619.2	645.6
157.5°	449.7	479.1	541.8	602.5	623.1
160°	460.5	484.5	535.9	585.9	602.5
162.5°	470.3	488.9	530.0	569.7	582.9
165°	477.1	491.8	524.2	555.0	563.3
167.5°	485.0	494.2	518.3	542.3	547.7
170°	489.9	496.2	512.4	529.6	533.0
172.5°	494.8	497.7	506.5	518.3	518.3
175°	497.7	498.7	502.6	509.5	507.5
177.5°	499.7	498.7	499.7	503.1	499.7
180°	498.7	498.7	498.7	498.7	498.7

(END OF REPORT)