

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026100

Luminaire Tested: S124RDIP-B1195D1035UB40-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026100
REPORT IS A COMBINATION OF REPORTS P999050 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D1035UB40-4F0-XX-W2A-F
Description: Define 4 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8870.0 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026100

CATALOG NUMBER: S124RDIP-B1195D1035UB40-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1026100

CATALOG NUMBER: S124RDIP-B1195D1035UB40-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	47	45	44
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	32
5	70	58	50	44	64	54	47	42	47	42	37	40	36	33	34	31	28
6	64	52	44	38	59	49	42	36	43	37	33	37	32	29	31	28	25
7	59	47	39	34	55	44	37	32	39	33	29	33	29	26	29	25	22
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16947	16947	16947
5°	16949	16444	16445
10°	16805	15925	15736
15°	16574	15279	14898
20°	16271	14542	13943
25°	15893	13747	13009
30°	15524	12937	11962
35°	15117	12115	10938
40°	14633	11230	9886
45°	14180	10353	8844
50°	13663	9394	7786
55°	13106	8412	6695
60°	12487	7368	5616
65°	11891	6172	4579
70°	11041	4913	3498
75°	9951	3573	2447
80°	8312	2194	1758
85°	6251	1263	966

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14180 cd/sqm

TEST NUMBER: P1026100

CATALOG NUMBER: S124RDIP-B1195D1035UB40-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.4	2.2
10°-20°	544.9	6.1
20°-30°	786.7	8.9
30°-40°	891.6	10.1
40°-50°	860.8	9.7
50°-60°	715.7	8.1
60°-70°	494.0	5.6
70°-80°	249.6	2.8
80°-90°	66.1	0.7
90°-100°	43.6	0.5
100°-110°	287.2	3.2
110°-120°	548.4	6.2
120°-130°	696.2	7.8
130°-140°	744.8	8.4
140°-150°	696.4	7.9
150°-160°	561.6	6.3
160°-170°	362.2	4.1
170°-180°	124.8	1.4
0°-30°	1527.0	17.2
0°-40°	2418.5	27.3
0°-60°	3995.0	45.0
0°-90°	4804.7	54.2
90°-120°	879.2	9.9
90°-150°	3016.6	34.0
90°-180°	4065.0	45.8
0°-180°	8870.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2078	2078	2078	2078	2078	
5°	2075	2069	2050	2066	2062	197
15°	1976	1962	1922	1919	1908	557
25°	1787	1758	1693	1666	1650	823
35°	1545	1494	1415	1361	1332	966
45°	1260	1201	1106	1028	999	972
55°	955	891	788	705	675	854
65°	649	581	479	411	392	641
75°	345	286	212	175	166	364
85°	86	54	49	46	46	94
90°	3	14	22	28	30	8
95°	54	21	22	28	28	67
105°	296	302	307	315	280	310
115°	552	555	554	556	556	544
125°	776	780	778	781	782	693
135°	963	962	966	968	970	742
145°	1110	1113	1113	1114	1116	694
155°	1218	1218	1216	1219	1216	561
165°	1284	1279	1279	1287	1278	363
175°	1314	1308	1309	1318	1306	125
180°	1314	1314	1314	1314	1314	

TEST NUMBER: P1026100

CATALOG NUMBER: S124RDIP-B1195D1035UB40-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2078.2	2078.2	2078.2	2078.2	2078.2
2.5°	2084.6	2078.2	2060.7	2078.2	2076.7
5°	2075.1	2068.7	2049.6	2065.5	2062.3
7.5°	2060.7	2054.4	2030.5	2041.6	2036.9
10°	2038.5	2030.5	2001.9	2008.2	2001.9
12.5°	2009.8	2000.3	1965.3	1968.4	1958.9
15°	1976.4	1962.1	1922.3	1919.1	1908.0
17.5°	1938.2	1917.5	1871.4	1863.4	1847.5
20°	1892.1	1871.4	1817.3	1804.5	1783.9
22.5°	1841.1	1817.3	1758.4	1737.7	1721.8
25°	1787.0	1758.4	1693.1	1666.1	1650.2
27.5°	1731.3	1696.3	1627.9	1596.1	1573.8
30°	1672.5	1632.7	1557.9	1518.1	1492.6
32.5°	1610.4	1564.3	1486.3	1438.5	1414.7
35°	1545.2	1494.2	1414.7	1360.6	1331.9
37.5°	1476.7	1424.2	1336.7	1277.8	1249.2
40°	1403.5	1351.0	1260.3	1193.5	1164.8
42.5°	1333.5	1277.8	1182.3	1113.9	1083.7
45°	1260.3	1201.4	1106.0	1028.0	999.3
47.5°	1185.5	1125.1	1026.4	945.2	913.4
50°	1109.1	1047.1	945.2	865.7	835.4
52.5°	1031.2	970.7	865.7	784.5	752.7
55°	954.8	891.1	787.7	704.9	674.7
57.5°	880.0	813.2	711.3	627.0	604.7
60°	798.8	735.2	633.3	550.6	525.1
62.5°	725.6	658.8	553.8	479.0	459.9
65°	649.3	580.8	479.0	410.6	391.5
67.5°	569.7	504.4	409.0	348.5	326.2
70°	494.9	428.1	337.4	284.8	268.9
72.5°	415.3	356.5	272.1	229.1	214.8
75°	345.3	286.4	211.6	175.0	165.5
77.5°	272.1	221.2	157.5	132.1	128.9
80°	202.1	155.9	108.2	103.4	101.8
82.5°	141.6	100.3	78.0	74.8	73.2
85°	85.9	54.1	49.3	46.1	46.1
87.5°	36.6	23.9	22.3	20.7	22.3
90°	2.9	13.8	21.6	27.5	29.5
92.5°	14.7	12.8	20.6	26.5	26.5
95°	54.0	20.6	21.6	27.5	28.5
97.5°	103.2	124.8	21.6	26.5	27.5
100°	161.2	178.8	43.2	26.5	27.5
102.5°	226.0	237.8	249.6	28.5	28.5
105°	295.8	301.7	306.6	315.4	280.0
107.5°	359.6	362.6	369.5	374.4	378.3
110°	424.5	427.4	433.3	435.3	438.3

TEST NUMBER: P1026100

CATALOG NUMBER: S124RDIP-B1195D1035UB40-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	487.4	493.3	495.2	494.3	498.2
115°	552.2	555.2	554.2	556.2	556.2
117.5°	610.2	614.1	617.1	616.1	616.1
120°	669.2	673.1	672.1	674.1	672.1
122.5°	724.2	726.2	728.1	729.1	727.1
125°	776.3	780.2	778.2	781.2	782.2
127.5°	826.4	827.4	832.3	831.3	830.3
130°	874.5	875.5	878.5	879.5	879.5
132.5°	918.8	920.7	924.7	925.6	924.7
135°	963.0	962.0	965.9	967.9	969.9
137.5°	1002.3	1002.3	1007.2	1009.2	1008.2
140°	1040.6	1042.6	1044.5	1047.5	1048.5
142.5°	1075.0	1078.9	1079.9	1081.9	1081.9
145°	1110.4	1113.3	1113.3	1114.3	1116.3
147.5°	1137.9	1143.8	1142.8	1143.8	1144.8
150°	1168.3	1172.3	1171.3	1171.3	1172.3
152.5°	1193.9	1196.8	1194.9	1196.8	1195.9
155°	1217.5	1218.5	1215.5	1219.4	1216.5
157.5°	1238.1	1238.1	1234.2	1239.1	1234.2
160°	1255.8	1252.9	1251.9	1257.8	1251.9
162.5°	1271.5	1267.6	1266.6	1272.5	1265.6
165°	1284.3	1279.4	1279.4	1287.2	1278.4
167.5°	1295.1	1290.2	1289.2	1298.1	1288.2
170°	1303.9	1298.1	1299.0	1306.9	1297.1
172.5°	1309.8	1303.9	1304.9	1312.8	1302.0
175°	1313.8	1307.9	1308.9	1317.7	1305.9
177.5°	1316.7	1309.8	1311.8	1319.7	1307.9
180°	1313.8	1313.8	1313.8	1313.8	1313.8

(END OF REPORT)