

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013423

Luminaire Tested: S124RDIP-B795D365UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013423
REPORT IS A COMBINATION OF REPORTS P999713 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D365UB2750-4F0-XX-W2A-F_4000K
Description: Define 4 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4672.0 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013423

CATALOG NUMBER: S124RDIP-B795D365UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013423

CATALOG NUMBER: S124RDIP-B795D365UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73			69
1	102	98	94	91	97	93	89	86	83	80	78	74	72	70	65	64	63			59
2	94	86	80	75	88	82	76	71	73	69	65	65	62	59	58	56	53			50
3	86	76	69	63	81	72	66	60	65	60	55	58	54	50	52	49	46			42
4	79	68	60	53	74	64	57	51	58	52	47	52	47	44	46	43	40			37
5	72	60	52	46	68	58	50	45	52	46	41	47	42	38	42	38	35			32
6	67	55	46	40	63	52	44	39	47	41	36	43	37	34	38	34	31			28
7	62	49	41	36	58	47	40	34	43	37	32	39	34	30	35	31	28			25
8	58	45	37	32	54	43	36	31	39	33	29	36	31	27	32	28	25			23
9	54	41	34	29	51	40	32	28	36	30	26	33	28	24	30	26	23			21
10	50	38	31	26	48	36	30	25	33	28	24	30	26	22	28	24	21			19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11322	11322	11322
5°	11323	10985	10986
10°	11227	10639	10512
15°	11072	10207	9952
20°	10870	9715	9314
25°	10617	9184	8691
30°	10371	8643	7991
35°	10099	8094	7307
40°	9776	7503	6605
45°	9473	6916	5908
50°	9128	6276	5202
55°	8755	5619	4472
60°	8343	4923	3752
65°	7942	4123	3058
70°	7376	3282	2338
75°	6648	2388	1635
80°	5552	1466	1175
85°	4177	846	646

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9473 cd/sqm

TEST NUMBER: P1013423

CATALOG NUMBER: S124RDIP-B795D365UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.6	2.8
10°-20°	364.0	7.8
20°-30°	525.5	11.2
30°-40°	595.6	12.7
40°-50°	575.1	12.3
50°-60°	478.1	10.2
60°-70°	330.0	7.1
70°-80°	166.8	3.6
80°-90°	43.3	0.9
90°-100°	15.7	0.3
100°-110°	103.4	2.2
110°-120°	197.4	4.2
120°-130°	250.5	5.4
130°-140°	268.0	5.7
140°-150°	250.6	5.4
150°-160°	202.1	4.3
160°-170°	130.3	2.8
170°-180°	44.9	1.0
0°-30°	1020.1	21.8
0°-40°	1615.7	34.6
0°-60°	2668.9	57.1
0°-90°	3209.0	68.7
90°-120°	316.4	6.8
90°-150°	1085.6	23.2
90°-180°	1463.0	31.3
0°-180°	4672.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1388	1388	1388	1388	1388	
5°	1386	1382	1369	1380	1378	132
15°	1320	1311	1284	1282	1275	372
25°	1194	1175	1131	1113	1102	550
35°	1032	998	945	909	890	645
45°	842	803	739	687	668	649
55°	638	595	526	471	451	571
65°	434	388	320	274	262	428
75°	231	191	141	117	111	243
85°	57	36	33	31	31	63
90°	1	5	8	10	11	4
95°	19	7	8	10	10	24
105°	106	109	110	114	101	111
115°	199	200	199	200	200	196
125°	279	281	280	281	282	249
135°	347	346	348	348	349	267
145°	400	401	401	401	402	250
155°	438	438	437	439	438	202
165°	462	460	460	463	460	131
175°	473	471	471	474	470	45
180°	473	473	473	473	473	

TEST NUMBER: P1013423

CATALOG NUMBER: S124RDIP-B795D365UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1388.4	1388.4	1388.4	1388.4	1388.4
2.5°	1392.6	1388.4	1376.7	1388.4	1387.3
5°	1386.3	1382.0	1369.2	1379.9	1377.7
7.5°	1376.7	1372.4	1356.5	1363.9	1360.7
10°	1361.8	1356.5	1337.4	1341.6	1337.4
12.5°	1342.7	1336.3	1312.9	1315.0	1308.6
15°	1320.3	1310.8	1284.2	1282.1	1274.6
17.5°	1294.8	1281.0	1250.2	1244.9	1234.2
20°	1264.0	1250.2	1214.0	1205.5	1191.7
22.5°	1230.0	1214.0	1174.7	1160.9	1150.3
25°	1193.8	1174.7	1131.1	1113.0	1102.4
27.5°	1156.6	1133.2	1087.5	1066.3	1051.4
30°	1117.3	1090.7	1040.8	1014.2	997.2
32.5°	1075.8	1045.0	992.9	961.0	945.1
35°	1032.2	998.2	945.1	908.9	889.8
37.5°	986.5	951.5	893.0	853.7	834.5
40°	937.6	902.6	842.0	797.3	778.2
42.5°	890.9	853.7	789.9	744.2	724.0
45°	842.0	802.6	738.8	686.7	667.6
47.5°	792.0	751.6	685.7	631.5	610.2
50°	741.0	699.5	631.5	578.3	558.1
52.5°	688.9	648.5	578.3	524.1	502.8
55°	637.8	595.3	526.2	470.9	450.7
57.5°	587.9	543.2	475.2	418.9	404.0
60°	533.7	491.1	423.1	367.8	350.8
62.5°	484.8	440.1	370.0	320.0	307.2
65°	433.7	388.0	320.0	274.3	261.5
67.5°	380.6	337.0	273.2	232.8	217.9
70°	330.6	286.0	225.4	190.3	179.7
72.5°	277.5	238.1	181.8	153.1	143.5
75°	230.7	191.4	141.4	116.9	110.6
77.5°	181.8	147.8	105.2	88.2	86.1
80°	135.0	104.2	72.3	69.1	68.0
82.5°	94.6	67.0	52.1	50.0	48.9
85°	57.4	36.1	33.0	30.8	30.8
87.5°	24.5	15.9	14.9	13.8	14.9
90°	1.1	5.0	7.8	9.9	10.6
92.5°	5.3	4.6	7.4	9.5	9.5
95°	19.4	7.4	7.8	9.9	10.3
97.5°	37.1	44.9	7.8	9.5	9.9
100°	58.0	64.4	15.6	9.5	9.9
102.5°	81.3	85.6	89.8	10.3	10.3
105°	106.4	108.6	110.3	113.5	100.8
107.5°	129.4	130.5	133.0	134.7	136.1
110°	152.8	153.8	156.0	156.7	157.7



TEST NUMBER: P1013423

CATALOG NUMBER: S124RDIP-B795D365UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	175.4	177.5	178.2	177.9	179.3
115°	198.7	199.8	199.4	200.2	200.2
117.5°	219.6	221.0	222.1	221.7	221.7
120°	240.8	242.2	241.9	242.6	241.9
122.5°	260.6	261.3	262.0	262.4	261.7
125°	279.4	280.8	280.1	281.1	281.5
127.5°	297.4	297.8	299.5	299.2	298.8
130°	314.7	315.1	316.1	316.5	316.5
132.5°	330.6	331.4	332.8	333.1	332.8
135°	346.6	346.2	347.6	348.3	349.0
137.5°	360.7	360.7	362.5	363.2	362.8
140°	374.5	375.2	375.9	377.0	377.3
142.5°	386.9	388.3	388.6	389.3	389.3
145°	399.6	400.7	400.7	401.0	401.7
147.5°	409.5	411.6	411.3	411.6	412.0
150°	420.5	421.9	421.5	421.5	421.9
152.5°	429.7	430.7	430.0	430.7	430.4
155°	438.1	438.5	437.4	438.9	437.8
157.5°	445.6	445.6	444.2	445.9	444.2
160°	451.9	450.9	450.5	452.6	450.5
162.5°	457.6	456.2	455.8	458.0	455.5
165°	462.2	460.4	460.4	463.3	460.1
167.5°	466.1	464.3	464.0	467.1	463.6
170°	469.3	467.1	467.5	470.3	466.8
172.5°	471.4	469.3	469.6	472.5	468.6
175°	472.8	470.7	471.0	474.2	470.0
177.5°	473.9	471.4	472.1	474.9	470.7
180°	472.8	472.8	472.8	472.8	472.8

(END OF REPORT)