

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026122

Luminaire Tested: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026122
REPORT IS A COMBINATION OF REPORTS P999082 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9229.0 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026122

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1026122

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	54	53	52
2	91	84	78	73	84	78	73	68	67	63	60	57	55	52	48	46	45
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	38
4	76	66	58	52	71	62	55	49	53	48	44	46	42	39	39	36	34
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	39	60	50	43	37	43	38	34	38	33	30	32	29	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	24	21
9	52	40	33	28	48	38	31	26	33	28	24	29	25	21	25	22	19
10	49	37	30	25	45	35	28	24	31	25	22	27	23	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16265	16265	16265	16265
5°	16264	18378	16291	14047
10°	16178	21186	16165	12216
15°	15985	23844	15985	10228
20°	15784	25851	15701	9007
25°	15537	25962	15466	8134
30°	15276	22077	15157	7535
35°	14906	16657	14718	7088
40°	14495	12072	14210	6739
45°	13815	9175	13472	6430
50°	13008	7415	12652	5977
55°	12134	6140	11736	5374
60°	11255	5192	10753	4470
65°	10155	4229	9831	3553
70°	9143	3429	8714	2886
75°	8011	2472	7458	2114
80°	6609	1638	6017	1555
85°	4795	843	3973	843

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 20362 cd/sqm

TEST NUMBER: P1026122

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.1	2.1
10°-20°	583.2	6.3
20°-30°	913.6	9.9
30°-40°	1014.5	11.0
40°-50°	899.0	9.7
50°-60°	700.6	7.6
60°-70°	458.3	5.0
70°-80°	224.9	2.4
80°-90°	58.0	0.6
90°-100°	98.3	1.1
100°-110°	294.4	3.2
110°-120°	500.1	5.4
120°-130°	659.6	7.1
130°-140°	740.8	8.0
140°-150°	728.1	7.9
150°-160°	612.4	6.6
160°-170°	407.5	4.4
170°-180°	142.7	1.5
0°-30°	1690.0	18.3
0°-40°	2704.5	29.3
0°-60°	4304.1	46.6
0°-90°	5045.2	54.7
90°-120°	892.8	9.7
90°-150°	3021.3	32.7
90°-180°	4184.0	45.3
0°-180°	9229.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1995	1995	1995	1995	1995	
5°	1991	2305	1995	1762	1991	189
15°	1906	3054	1906	1310	1906	538
25°	1747	3293	1739	1032	1747	805
35°	1524	2028	1504	863	1524	952
45°	1228	1037	1197	726	1228	947
55°	884	619	855	542	884	790
65°	554	362	537	304	554	553
75°	278	167	259	143	278	295
85°	66	40	55	40	66	74
90°	4	35	4	35	4	10
95°	70	92	70	92	70	76
105°	272	284	272	284	272	288
115°	508	504	508	504	508	501
125°	740	735	740	735	740	660
135°	955	956	955	956	955	739
145°	1160	1162	1160	1162	1160	726
155°	1329	1328	1329	1328	1329	612
165°	1447	1444	1447	1444	1447	408
175°	1506	1498	1506	1498	1506	143
180°	1508	1508	1508	1508	1508	

TEST NUMBER: P1026122

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6
2.5°	1997.8	2015.4	2025.1	2033.1	2049.2	2055.6	2068.5	2071.7	2084.6	2083.0	2078.1
5°	1991.3	2021.9	2044.4	2068.5	2097.4	2113.5	2131.2	2156.9	2169.7	2187.4	2198.7
7.5°	1980.1	2021.9	2058.8	2095.8	2142.4	2168.1	2190.6	2230.8	2264.6	2293.5	2325.6
10°	1962.4	2015.4	2070.1	2119.9	2184.2	2214.7	2248.5	2308.0	2354.6	2394.8	2446.2
12.5°	1935.1	2009.0	2070.1	2137.6	2219.6	2261.4	2306.4	2377.1	2431.7	2497.6	2561.9
15°	1906.2	1988.1	2068.5	2156.9	2250.1	2298.3	2343.3	2438.1	2521.7	2597.3	2668.0
17.5°	1874.0	1964.0	2052.4	2150.5	2263.0	2322.4	2375.5	2489.6	2581.2	2679.2	2749.9
20°	1835.4	1933.5	2034.7	2144.0	2271.0	2336.9	2396.4	2526.5	2627.8	2733.9	2822.3
22.5°	1793.7	1899.7	2010.6	2129.6	2261.4	2333.7	2402.8	2542.6	2659.9	2758.0	2876.9
25°	1747.0	1859.5	1973.7	2099.0	2246.9	2325.6	2396.4	2534.6	2659.9	2788.5	2904.2
27.5°	1698.8	1814.5	1933.5	2065.3	2216.4	2293.5	2373.9	2507.3	2653.5	2793.3	2910.7
30°	1645.8	1758.3	1883.7	2009.0	2169.7	2246.9	2328.9	2473.5	2632.6	2772.4	2899.4
32.5°	1587.9	1703.6	1822.6	1952.8	2110.3	2193.8	2269.4	2433.3	2595.7	2733.9	2852.8
35°	1523.6	1632.9	1745.4	1878.8	2034.7	2110.3	2200.3	2370.6	2534.6	2680.8	2758.0
37.5°	1454.5	1559.0	1663.5	1795.3	1944.7	2036.3	2124.7	2296.7	2470.3	2568.3	2608.5
40°	1390.2	1481.9	1573.5	1700.4	1851.5	1946.3	2036.3	2214.7	2367.4	2443.0	2412.4
42.5°	1308.3	1403.1	1485.1	1602.4	1755.1	1843.5	1935.1	2119.9	2243.7	2274.2	2198.7
45°	1227.9	1306.7	1385.4	1499.5	1660.3	1735.8	1833.8	2005.8	2108.7	2081.3	1970.4
47.5°	1149.2	1213.4	1287.4	1398.3	1542.9	1632.9	1724.5	1874.0	1946.3	1907.8	1753.5
50°	1055.9	1120.2	1197.4	1293.8	1433.6	1520.4	1592.8	1731.0	1785.6	1690.8	1504.4
52.5°	967.5	1023.8	1089.7	1179.7	1313.1	1391.8	1470.6	1589.5	1607.2	1497.9	1301.8
55°	884.0	929.0	998.1	1070.4	1192.6	1276.1	1330.8	1432.0	1427.2	1290.6	1121.8
57.5°	797.2	839.0	885.6	961.1	1076.8	1139.5	1199.0	1287.4	1240.8	1125.1	957.9
60°	720.0	744.1	790.8	863.1	961.1	1015.8	1062.4	1110.6	1070.4	945.0	816.5
62.5°	634.9	662.2	695.9	753.8	840.6	892.0	925.8	946.6	904.9	808.4	691.1
65°	554.5	578.6	614.0	665.4	731.3	769.9	787.5	802.0	779.5	670.2	577.0
67.5°	482.2	498.2	530.4	564.1	634.9	644.5	668.6	675.0	630.0	546.5	472.5
70°	409.8	425.9	440.4	480.6	512.7	530.4	535.2	535.2	490.2	435.6	374.5
72.5°	342.3	352.0	366.4	393.8	411.4	424.3	430.7	422.7	380.9	335.9	290.9
75°	278.0	282.9	295.7	313.4	327.9	323.1	321.4	311.8	281.3	249.1	223.4
77.5°	213.8	217.0	231.4	236.3	236.3	241.1	234.7	225.0	199.3	175.2	163.9
80°	160.7	165.5	167.2	170.4	167.2	167.2	162.3	146.3	133.4	122.1	114.1
82.5°	110.9	114.1	115.7	110.9	114.1	109.3	101.3	90.0	82.0	80.4	77.1
85°	65.9	67.5	65.9	65.9	61.1	59.5	53.0	51.4	48.2	48.2	46.6
87.5°	32.1	30.5	27.3	24.1	24.1	22.5	24.1	20.9	24.1	22.5	20.9
90°	3.5	6.3	9.2	12.0	14.9	16.3	17.3	19.4	21.5	23.6	25.7
92.5°	30.3	33.7	37.1	40.4	43.8	45.5	46.1	47.4	48.7	50.0	51.3
95°	70.0	72.3	74.7	77.0	79.3	80.5	81.4	83.2	85.0	86.8	88.6
97.5°	112.0	114.1	116.1	118.2	120.3	121.3	122.3	124.4	126.5	128.5	130.6
100°	163.3	164.3	165.3	166.4	167.4	167.9	169.1	171.4	173.7	176.1	178.4
102.5°	216.9	217.2	217.4	217.7	218.0	218.1	219.1	221.2	223.3	225.3	227.4
105°	271.7	272.0	272.2	272.5	272.8	272.9	273.4	274.5	275.5	276.6	277.6
107.5°	328.9	329.1	329.4	329.6	329.9	330.0	330.1	330.4	330.7	330.9	331.2
110°	387.2	387.7	388.2	388.7	389.2	389.5	389.4	389.1	388.8	388.6	388.3

TEST NUMBER: P1026122

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	447.8	447.8	447.8	447.8	447.8	447.8	447.5	447.0	446.5	446.0	445.5
115°	508.5	508.5	508.5	508.5	508.5	508.5	508.2	507.7	507.2	506.6	506.1
117.5°	565.6	565.6	565.6	565.6	565.6	565.6	565.5	565.2	564.9	564.7	564.4
120°	622.7	623.7	624.8	625.8	626.9	627.4	627.0	626.2	625.5	624.7	623.9
122.5°	682.2	682.5	682.7	683.0	683.3	683.4	683.3	683.0	682.7	682.5	682.2
125°	740.5	740.5	740.5	740.5	740.5	740.5	740.4	740.1	739.9	739.6	739.4
127.5°	793.0	793.8	794.6	795.3	796.1	796.5	796.2	795.7	795.2	794.7	794.2
130°	849.0	849.8	850.6	851.3	852.1	852.5	852.5	852.5	852.5	852.5	852.5
132.5°	906.1	906.6	907.2	907.7	908.2	908.5	908.4	908.1	907.8	907.6	907.3
135°	955.1	956.7	958.2	959.8	961.3	962.1	962.1	962.1	962.1	962.1	962.1
137.5°	1009.9	1010.7	1011.5	1012.2	1013.0	1013.4	1013.7	1014.2	1014.7	1015.2	1015.7
140°	1064.7	1065.2	1065.8	1066.3	1066.8	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1
142.5°	1114.9	1115.4	1115.9	1116.4	1116.9	1117.2	1117.1	1116.8	1116.5	1116.3	1116.0
145°	1160.3	1161.3	1162.4	1163.4	1164.5	1165.0	1165.1	1165.4	1165.7	1165.9	1166.2
147.5°	1207.0	1208.3	1209.6	1210.9	1212.2	1212.8	1212.7	1212.4	1212.2	1211.9	1211.7
150°	1249.0	1250.0	1251.0	1252.1	1253.1	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6
152.5°	1288.6	1289.1	1289.7	1290.2	1290.7	1291.0	1291.1	1291.4	1291.6	1291.9	1292.1
155°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.3	1329.0	1328.8	1328.5	1328.3
157.5°	1364.4	1363.9	1363.4	1362.9	1362.4	1362.1	1362.1	1362.1	1362.1	1362.1	1362.1
160°	1394.7	1394.5	1394.2	1394.0	1393.7	1393.6	1393.5	1393.2	1392.9	1392.7	1392.4
162.5°	1422.7	1421.9	1421.1	1420.4	1419.6	1419.2	1419.1	1418.8	1418.6	1418.3	1418.1
165°	1447.2	1446.4	1445.6	1444.9	1444.1	1443.7	1443.4	1442.9	1442.4	1441.9	1441.4
167.5°	1467.1	1466.1	1465.0	1464.0	1462.9	1462.4	1462.4	1462.4	1462.4	1462.4	1462.4
170°	1483.4	1482.1	1480.8	1479.5	1478.2	1477.5	1477.6	1477.9	1478.2	1478.4	1478.7
172.5°	1495.0	1494.0	1493.0	1491.9	1490.9	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
175°	1505.5	1504.2	1502.9	1501.6	1500.3	1499.7	1499.6	1499.3	1499.0	1498.8	1498.5
177.5°	1510.2	1508.9	1507.6	1506.3	1505.0	1504.4	1504.4	1504.4	1504.4	1504.4	1504.4
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9

TEST NUMBER: P1026122

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6
2.5°	2091.0	2108.7	2110.3	2126.3	2121.5	2113.5	2128.0	2118.3	2137.6	2131.2	2139.2
5°	2213.1	2237.2	2258.1	2271.0	2293.5	2288.7	2312.8	2304.7	2322.4	2304.7	2327.2
7.5°	2356.2	2396.4	2417.3	2451.0	2460.6	2462.3	2491.2	2497.6	2508.9	2497.6	2510.5
10°	2496.0	2544.2	2592.4	2619.8	2637.4	2661.5	2687.3	2698.5	2706.6	2695.3	2703.3
12.5°	2623.0	2698.5	2751.6	2806.2	2819.1	2839.9	2867.3	2864.1	2896.2	2889.8	2904.2
15°	2740.3	2823.9	2888.2	2931.6	2966.9	2984.6	3036.0	3039.2	3037.6	3053.7	3044.1
17.5°	2844.8	2915.5	3007.1	3063.4	3106.7	3106.7	3135.7	3195.1	3190.3	3188.7	3198.4
20°	2930.0	3010.3	3095.5	3190.3	3225.7	3232.1	3272.3	3302.8	3307.6	3307.6	3307.6
22.5°	2994.2	3089.1	3180.7	3248.2	3275.5	3298.0	3333.4	3352.7	3359.1	3355.9	3359.1
25°	3026.4	3116.4	3209.6	3270.7	3286.8	3299.6	3302.8	3314.1	3312.5	3293.2	3304.4
27.5°	3032.8	3119.6	3180.7	3196.8	3188.7	3180.7	3129.2	3134.1	3119.6	3090.7	3101.9
30°	3003.9	3050.5	3048.9	2999.1	2984.6	2950.8	2904.2	2835.1	2778.9	2754.8	2762.8
32.5°	2899.4	2899.4	2841.6	2729.1	2679.2	2618.2	2534.6	2471.9	2398.0	2381.9	2412.4
35°	2754.8	2672.8	2566.7	2418.9	2343.3	2298.3	2153.7	2108.7	2046.0	2028.3	2042.8
37.5°	2529.8	2393.1	2238.9	2100.6	2036.3	1956.0	1829.0	1764.7	1719.7	1689.2	1703.6
40°	2277.4	2111.9	1951.2	1780.8	1710.1	1644.2	1549.4	1491.5	1419.2	1422.4	1427.2
42.5°	2036.3	1841.9	1661.9	1504.4	1436.9	1382.2	1316.3	1245.6	1219.9	1211.8	1203.8
45°	1780.8	1573.5	1404.7	1287.4	1226.3	1174.9	1113.8	1073.6	1043.1	1036.7	1044.7
47.5°	1539.7	1364.5	1203.8	1094.5	1044.7	1019.0	970.8	933.8	914.5	898.4	908.1
50°	1321.1	1157.2	1028.6	937.0	901.6	884.0	839.0	819.7	800.4	795.6	794.0
52.5°	1141.1	1001.3	890.4	816.5	789.1	779.5	745.7	718.4	702.4	707.2	710.4
55°	977.2	858.3	771.5	712.0	689.5	678.2	654.1	634.9	623.6	618.8	622.0
57.5°	832.5	729.7	667.0	618.8	601.1	596.3	570.6	564.1	556.1	551.3	551.3
60°	700.7	628.4	570.6	543.2	524.0	519.1	499.8	491.8	490.2	485.4	482.2
62.5°	589.8	530.4	490.2	461.3	453.2	451.6	438.8	429.1	424.3	421.1	421.1
65°	493.4	450.0	416.3	395.4	388.9	385.7	371.3	368.1	364.8	361.6	360.0
67.5°	411.4	372.9	348.8	334.3	326.3	327.9	319.8	313.4	313.4	311.8	310.2
70°	332.7	308.6	287.7	279.7	276.4	273.2	270.0	265.2	263.6	263.6	263.6
72.5°	262.0	245.9	234.7	229.8	226.6	223.4	220.2	220.2	220.2	218.6	218.6
75°	200.9	194.5	186.4	181.6	181.6	184.8	180.0	175.2	170.4	167.2	168.8
77.5°	151.1	147.9	143.0	135.0	136.6	133.4	133.4	130.2	131.8	131.8	128.6
80°	110.9	106.1	104.5	99.6	101.3	99.6	98.0	98.0	94.8	94.8	94.8
82.5°	77.1	72.3	72.3	70.7	69.1	69.1	67.5	67.5	69.1	65.9	65.9
85°	46.6	45.0	45.0	41.8	41.8	41.8	41.8	43.4	41.8	40.2	40.2
87.5°	20.9	22.5	20.9	19.3	19.3	19.3	17.7	17.7	16.1	17.7	17.7
90°	27.3	28.8	30.4	31.9	32.7	33.0	33.5	34.0	34.5	35.0	34.5
92.5°	52.1	52.9	53.6	54.4	54.8	54.9	55.2	55.5	55.7	56.0	55.7
95°	89.4	90.2	90.9	91.7	92.1	92.1	92.1	92.1	92.1	92.1	92.1
97.5°	131.6	132.7	133.7	134.8	135.3	135.3	135.3	135.3	135.3	135.3	135.3
100°	178.9	179.5	180.0	180.5	180.8	180.8	180.8	180.8	180.8	180.8	180.8
102.5°	228.2	229.0	229.7	230.5	230.9	231.0	231.3	231.6	231.8	232.1	231.8
105°	278.4	279.1	279.9	280.6	281.0	281.4	282.2	282.9	283.7	284.5	283.7
107.5°	332.2	333.3	334.3	335.4	335.9	335.8	335.5	335.2	335.0	334.7	335.0
110°	387.8	387.3	386.8	386.3	386.0	386.4	387.2	387.9	388.7	389.5	388.7

TEST NUMBER: P1026122

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5
115°	505.9	505.6	505.4	505.1	505.0	504.9	504.6	504.3	504.1	503.8	504.1
117.5°	563.6	562.8	562.1	561.3	560.9	560.5	559.7	559.0	558.2	557.4	558.2
120°	622.6	621.3	620.0	618.7	618.1	618.4	618.9	619.4	619.9	620.4	619.9
122.5°	681.4	680.6	679.9	679.1	678.7	678.1	676.8	675.5	674.2	672.9	674.2
125°	738.9	738.3	737.8	737.3	737.0	736.7	736.2	735.7	735.2	734.7	735.2
127.5°	793.7	793.1	792.6	792.1	791.8	791.7	791.4	791.2	790.9	790.7	790.9
130°	852.0	851.4	850.9	850.4	850.1	849.6	848.6	847.5	846.5	845.5	846.5
132.5°	906.8	906.3	905.8	905.3	905.0	904.9	904.6	904.3	904.1	903.8	904.1
135°	961.6	961.1	960.6	960.1	959.8	959.4	958.6	957.9	957.1	956.3	957.1
137.5°	1014.9	1014.1	1013.4	1012.6	1012.2	1012.3	1012.6	1012.9	1013.1	1013.4	1013.1
140°	1066.8	1066.6	1066.3	1066.0	1065.9	1065.8	1065.5	1065.2	1065.0	1064.7	1065.0
142.5°	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0
145°	1165.9	1165.7	1165.4	1165.1	1165.0	1164.6	1163.8	1163.1	1162.3	1161.5	1162.3
147.5°	1211.4	1211.2	1210.9	1210.6	1210.5	1210.4	1210.1	1209.8	1209.6	1209.3	1209.6
150°	1253.6	1253.6	1253.6	1253.6	1253.6	1253.5	1253.2	1253.0	1252.7	1252.5	1252.7
152.5°	1292.9	1293.7	1294.4	1295.2	1295.6	1295.2	1294.4	1293.7	1292.9	1292.1	1292.9
155°	1329.3	1330.3	1331.4	1332.4	1332.9	1332.4	1331.4	1330.3	1329.3	1328.3	1329.3
157.5°	1362.9	1363.7	1364.4	1365.2	1365.6	1365.2	1364.4	1363.7	1362.9	1362.1	1362.9
160°	1393.2	1394.0	1394.7	1395.5	1395.9	1395.3	1394.0	1392.7	1391.4	1390.1	1391.4
162.5°	1419.7	1421.2	1422.8	1424.3	1425.1	1424.4	1423.1	1421.8	1420.5	1419.2	1420.5
165°	1443.0	1444.5	1446.1	1447.6	1448.4	1447.9	1446.8	1445.8	1444.7	1443.7	1444.7
167.5°	1464.0	1465.5	1467.1	1468.6	1469.4	1468.6	1467.1	1465.5	1464.0	1462.4	1464.0
170°	1480.3	1481.8	1483.4	1484.9	1485.7	1484.8	1483.0	1481.1	1479.3	1477.5	1479.3
172.5°	1492.2	1494.0	1495.8	1497.6	1498.5	1497.6	1495.8	1494.0	1492.2	1490.4	1492.2
175°	1500.3	1502.1	1504.0	1505.8	1506.7	1505.8	1504.0	1502.1	1500.3	1498.5	1500.3
177.5°	1506.2	1508.0	1509.8	1511.6	1512.5	1511.5	1509.4	1507.3	1505.3	1503.2	1505.3
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9

TEST NUMBER: P1026122

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6
2.5°	2144.0	2132.8	2131.2	2131.2	2113.5	2123.1	2103.8	2083.0	2073.3	2073.3	2055.6
5°	2322.4	2311.2	2299.9	2282.2	2282.2	2272.6	2242.1	2211.5	2189.0	2169.7	2148.8
7.5°	2505.6	2494.4	2462.3	2444.6	2454.2	2434.9	2394.8	2343.3	2304.7	2274.2	2230.8
10°	2704.9	2674.4	2658.3	2648.7	2614.9	2594.0	2547.4	2471.9	2423.7	2383.5	2327.2
12.5°	2867.3	2876.9	2815.8	2820.7	2786.9	2758.0	2685.7	2613.3	2541.0	2484.8	2401.2
15°	3042.5	3013.5	2976.6	2947.6	2936.4	2901.0	2839.9	2743.5	2664.8	2576.4	2481.5
17.5°	3180.7	3158.2	3122.8	3095.5	3071.4	2986.2	2934.8	2849.6	2741.9	2655.1	2539.4
20°	3298.0	3277.1	3227.3	3209.6	3166.2	3105.1	3031.2	2899.4	2803.0	2708.2	2595.7
22.5°	3347.8	3326.9	3283.5	3261.0	3233.7	3174.3	3103.5	2978.2	2859.2	2740.3	2621.4
25°	3306.0	3306.0	3285.1	3277.1	3253.0	3200.0	3127.6	3021.6	2894.6	2766.0	2624.6
27.5°	3103.5	3143.7	3158.2	3166.2	3166.2	3167.8	3118.0	3015.1	2891.4	2766.0	2618.2
30°	2811.0	2878.5	2938.0	2955.7	2986.2	3020.0	3040.9	2991.0	2880.1	2748.3	2600.5
32.5°	2443.0	2529.8	2640.7	2668.0	2709.8	2811.0	2867.3	2888.2	2827.1	2711.4	2553.9
35°	2076.5	2185.8	2253.3	2336.9	2375.5	2524.9	2650.3	2725.8	2711.4	2642.3	2499.2
37.5°	1756.7	1819.4	1901.3	1989.7	2066.9	2209.9	2365.8	2512.1	2571.5	2537.8	2430.1
40°	1449.7	1523.6	1621.7	1694.0	1747.0	1890.1	2083.0	2242.1	2372.3	2393.1	2327.2
42.5°	1232.7	1306.7	1366.1	1444.9	1486.7	1624.9	1795.3	1994.6	2148.8	2230.8	2201.9
45°	1065.6	1110.6	1158.8	1203.8	1255.2	1377.4	1534.9	1753.5	1927.1	2042.8	2054.0
47.5°	919.3	959.5	1001.3	1043.1	1072.0	1166.8	1311.5	1489.9	1679.5	1838.7	1901.3
50°	816.5	835.8	866.3	890.4	924.1	1006.1	1121.8	1276.1	1477.0	1649.0	1731.0
52.5°	715.2	739.3	763.4	784.3	806.8	864.7	970.8	1104.2	1277.7	1454.5	1555.8
55°	630.0	649.3	671.8	686.3	699.1	750.6	830.9	933.8	1083.3	1250.4	1375.8
57.5°	560.9	569.0	588.2	596.3	610.7	652.5	710.4	802.0	922.5	1084.9	1187.7
60°	485.4	501.5	515.9	522.3	533.6	562.5	602.7	687.9	792.4	911.3	1028.6
62.5°	424.3	430.7	442.0	450.0	458.1	488.6	522.3	586.6	665.4	765.0	872.7
65°	368.1	371.3	377.7	388.9	393.8	416.3	435.6	482.2	556.1	631.6	739.3
67.5°	310.2	313.4	321.4	327.9	332.7	347.2	368.1	401.8	442.0	525.6	585.0
70°	265.2	265.2	270.0	273.2	278.0	284.5	295.7	321.4	358.4	411.4	466.1
72.5°	221.8	221.8	221.8	226.6	226.6	231.4	237.9	255.5	281.3	323.1	358.4
75°	172.0	173.6	176.8	176.8	178.4	184.8	189.7	194.5	207.3	234.7	266.8
77.5°	130.2	133.4	135.0	131.8	135.0	135.0	141.4	147.9	154.3	162.3	186.4
80°	96.4	98.0	94.8	96.4	96.4	99.6	102.9	101.3	104.5	114.1	120.5
82.5°	64.3	65.9	65.9	65.9	65.9	70.7	70.7	69.1	70.7	72.3	73.9
85°	40.2	38.6	38.6	40.2	38.6	38.6	40.2	41.8	40.2	41.8	43.4
87.5°	17.7	17.7	17.7	17.7	16.1	16.1	17.7	16.1	17.7	16.1	14.5
90°	34.0	33.5	33.0	32.7	31.9	30.4	28.8	27.3	25.7	23.6	21.5
92.5°	55.5	55.2	54.9	54.8	54.4	53.6	52.9	52.1	51.3	50.0	48.7
95°	92.1	92.1	92.1	92.1	91.7	90.9	90.2	89.4	88.6	86.8	85.0
97.5°	135.3	135.3	135.3	135.3	134.8	133.7	132.7	131.6	130.6	128.5	126.5
100°	180.8	180.8	180.8	180.8	180.5	180.0	179.5	178.9	178.4	176.1	173.7
102.5°	231.6	231.3	231.0	230.9	230.5	229.7	229.0	228.2	227.4	225.3	223.3
105°	282.9	282.2	281.4	281.0	280.6	279.9	279.1	278.4	277.6	276.6	275.5
107.5°	335.2	335.5	335.8	335.9	335.4	334.3	333.3	332.2	331.2	330.9	330.7
110°	387.9	387.2	386.4	386.0	386.3	386.8	387.3	387.8	388.3	388.6	388.8

TEST NUMBER: P1026122

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	446.0	446.5
115°	504.3	504.6	504.9	505.0	505.1	505.4	505.6	505.9	506.1	506.6	507.2
117.5°	559.0	559.7	560.5	560.9	561.3	562.1	562.8	563.6	564.4	564.7	564.9
120°	619.4	618.9	618.4	618.1	618.7	620.0	621.3	622.6	623.9	624.7	625.5
122.5°	675.5	676.8	678.1	678.7	679.1	679.9	680.6	681.4	682.2	682.5	682.7
125°	735.7	736.2	736.7	737.0	737.3	737.8	738.3	738.9	739.4	739.6	739.9
127.5°	791.2	791.4	791.7	791.8	792.1	792.6	793.1	793.7	794.2	794.7	795.2
130°	847.5	848.6	849.6	850.1	850.4	850.9	851.4	852.0	852.5	852.5	852.5
132.5°	904.3	904.6	904.9	905.0	905.3	905.8	906.3	906.8	907.3	907.6	907.8
135°	957.9	958.6	959.4	959.8	960.1	960.6	961.1	961.6	962.1	962.1	962.1
137.5°	1012.9	1012.6	1012.3	1012.2	1012.6	1013.4	1014.1	1014.9	1015.7	1015.2	1014.7
140°	1065.2	1065.5	1065.8	1065.9	1066.0	1066.3	1066.6	1066.8	1067.1	1067.1	1067.1
142.5°	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.3	1116.5
145°	1163.1	1163.8	1164.6	1165.0	1165.1	1165.4	1165.7	1165.9	1166.2	1165.9	1165.7
147.5°	1209.8	1210.1	1210.4	1210.5	1210.6	1210.9	1211.2	1211.4	1211.7	1211.9	1212.2
150°	1253.0	1253.2	1253.5	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6
152.5°	1293.7	1294.4	1295.2	1295.6	1295.2	1294.4	1293.7	1292.9	1292.1	1291.9	1291.6
155°	1330.3	1331.4	1332.4	1332.9	1332.4	1331.4	1330.3	1329.3	1328.3	1328.5	1328.8
157.5°	1363.7	1364.4	1365.2	1365.6	1365.2	1364.4	1363.7	1362.9	1362.1	1362.1	1362.1
160°	1392.7	1394.0	1395.3	1395.9	1395.5	1394.7	1394.0	1393.2	1392.4	1392.7	1392.9
162.5°	1421.8	1423.1	1424.4	1425.1	1424.3	1422.8	1421.2	1419.7	1418.1	1418.3	1418.6
165°	1445.8	1446.8	1447.9	1448.4	1447.6	1446.1	1444.5	1443.0	1441.4	1441.9	1442.4
167.5°	1465.5	1467.1	1468.6	1469.4	1468.6	1467.1	1465.5	1464.0	1462.4	1462.4	1462.4
170°	1481.1	1483.0	1484.8	1485.7	1484.9	1483.4	1481.8	1480.3	1478.7	1478.4	1478.2
172.5°	1494.0	1495.8	1497.6	1498.5	1497.6	1495.8	1494.0	1492.2	1490.4	1490.4	1490.4
175°	1502.1	1504.0	1505.8	1506.7	1505.8	1504.0	1502.1	1500.3	1498.5	1498.8	1499.0
177.5°	1507.3	1509.4	1511.5	1512.5	1511.6	1509.8	1508.0	1506.2	1504.4	1504.4	1504.4
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9

TEST NUMBER: P1026122

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6
2.5°	2046.0	2037.9	2033.1	2031.5	2017.1	2009.0	2004.2	2001.0	1996.2	1983.3	1972.1
5°	2123.1	2100.6	2089.4	2076.5	2054.0	2028.3	2007.4	1994.6	1978.5	1952.8	1928.7
7.5°	2195.5	2161.7	2139.2	2121.5	2083.0	2041.2	2007.4	1980.1	1949.6	1914.2	1880.4
10°	2271.0	2216.4	2187.4	2160.1	2103.8	2049.2	2001.0	1960.8	1917.4	1870.8	1833.8
12.5°	2330.5	2258.1	2226.0	2187.4	2118.3	2054.0	1992.9	1938.3	1882.0	1832.2	1779.2
15°	2399.6	2309.6	2272.6	2222.8	2128.0	2044.4	1965.6	1906.2	1848.3	1774.4	1718.1
17.5°	2439.8	2335.3	2282.2	2238.9	2136.0	2034.7	1943.1	1869.2	1801.7	1727.8	1668.3
20°	2479.9	2361.0	2301.5	2240.5	2118.3	2010.6	1914.2	1825.8	1755.1	1674.7	1613.6
22.5°	2492.8	2354.6	2291.9	2235.6	2107.1	1986.5	1875.6	1785.6	1703.6	1623.3	1554.2
25°	2492.8	2353.0	2279.0	2206.7	2071.7	1947.9	1837.0	1739.0	1647.4	1567.0	1497.9
27.5°	2467.1	2320.8	2243.7	2177.8	2037.9	1904.6	1790.4	1682.8	1594.4	1514.0	1435.2
30°	2434.9	2274.2	2197.1	2118.3	1983.3	1856.3	1732.6	1632.9	1539.7	1448.1	1377.4
32.5°	2394.8	2224.4	2139.2	2058.8	1915.8	1784.0	1669.9	1571.9	1483.5	1388.6	1309.9
35°	2336.9	2150.5	2055.6	1984.9	1846.7	1710.1	1600.8	1504.4	1419.2	1321.1	1235.9
37.5°	2263.0	2083.0	1986.5	1899.7	1756.7	1631.3	1528.5	1435.2	1351.7	1261.7	1166.8
40°	2176.2	1988.1	1904.6	1812.9	1661.9	1542.9	1446.5	1362.9	1279.3	1194.2	1102.5
42.5°	2078.1	1891.7	1798.5	1710.1	1565.4	1448.1	1358.1	1282.6	1205.4	1126.7	1028.6
45°	1960.8	1785.6	1695.6	1612.0	1472.2	1351.7	1269.7	1197.4	1131.5	1051.1	964.3
47.5°	1829.0	1676.3	1584.7	1494.7	1358.1	1253.6	1173.3	1112.2	1055.9	975.6	896.8
50°	1700.4	1549.4	1475.4	1383.8	1258.4	1160.4	1078.4	1027.0	983.6	904.9	834.1
52.5°	1538.1	1424.0	1353.3	1274.5	1154.0	1054.3	990.0	945.0	893.6	832.5	769.9
55°	1395.1	1289.0	1232.7	1158.8	1039.9	951.5	896.8	855.0	814.9	760.2	710.4
57.5°	1232.7	1166.8	1110.6	1046.3	929.0	853.4	805.2	769.9	732.9	687.9	647.7
60°	1062.4	1031.8	977.2	925.8	826.1	760.2	720.0	687.9	652.5	615.6	581.8
62.5°	911.3	893.6	861.5	821.3	728.1	671.8	631.6	607.5	581.8	548.1	515.9
65°	768.2	760.2	729.7	700.7	636.5	586.6	551.3	536.8	507.9	482.2	453.2
67.5°	641.3	631.6	614.0	601.1	546.5	499.8	482.2	462.9	438.8	419.5	395.4
70°	512.7	511.1	499.8	483.8	454.8	421.1	403.4	390.6	366.4	352.0	334.3
72.5°	398.6	406.6	397.0	390.6	371.3	347.2	331.1	323.1	303.8	292.5	279.7
75°	297.3	303.8	308.6	297.3	292.5	281.3	266.8	258.8	249.1	233.0	228.2
77.5°	202.5	217.0	217.0	220.2	221.8	215.4	204.1	197.7	186.4	183.2	176.8
80°	133.4	146.3	147.9	151.1	155.9	155.9	147.9	146.3	135.0	133.4	128.6
82.5°	77.1	88.4	94.8	99.6	98.0	104.5	98.0	96.4	90.0	90.0	86.8
85°	41.8	43.4	46.6	49.8	53.0	56.3	56.3	54.6	53.0	51.4	48.2
87.5°	16.1	16.1	17.7	16.1	17.7	20.9	22.5	22.5	20.9	19.3	16.1
90°	19.4	17.3	16.3	14.9	12.0	9.2	6.3	3.5	6.3	9.2	12.0
92.5°	47.4	46.1	45.5	43.8	40.4	37.1	33.7	30.3	33.7	37.1	40.4
95°	83.2	81.4	80.5	79.3	77.0	74.7	72.3	70.0	72.3	74.7	77.0
97.5°	124.4	122.3	121.3	120.3	118.2	116.1	114.1	112.0	114.1	116.1	118.2
100°	171.4	169.1	167.9	167.4	166.4	165.3	164.3	163.3	164.3	165.3	166.4
102.5°	221.2	219.1	218.1	218.0	217.7	217.4	217.2	216.9	217.2	217.4	217.7
105°	274.5	273.4	272.9	272.8	272.5	272.2	272.0	271.7	272.0	272.2	272.5
107.5°	330.4	330.1	330.0	329.9	329.6	329.4	329.1	328.9	329.1	329.4	329.6
110°	389.1	389.4	389.5	389.2	388.7	388.2	387.7	387.2	387.7	388.2	388.7

TEST NUMBER: P1026122

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	447.0	447.5	447.8	447.8	447.8	447.8	447.8	447.8	447.8	447.8	447.8
115°	507.7	508.2	508.5	508.5	508.5	508.5	508.5	508.5	508.5	508.5	508.5
117.5°	565.2	565.5	565.6	565.6	565.6	565.6	565.6	565.6	565.6	565.6	565.6
120°	626.2	627.0	627.4	626.9	625.8	624.8	623.7	622.7	623.7	624.8	625.8
122.5°	683.0	683.3	683.4	683.3	683.0	682.7	682.5	682.2	682.5	682.7	683.0
125°	740.1	740.4	740.5	740.5	740.5	740.5	740.5	740.5	740.5	740.5	740.5
127.5°	795.7	796.2	796.5	796.1	795.3	794.6	793.8	793.0	793.8	794.6	795.3
130°	852.5	852.5	852.5	852.1	851.3	850.6	849.8	849.0	849.8	850.6	851.3
132.5°	908.1	908.4	908.5	908.2	907.7	907.2	906.6	906.1	906.6	907.2	907.7
135°	962.1	962.1	962.1	961.3	959.8	958.2	956.7	955.1	956.7	958.2	959.8
137.5°	1014.2	1013.7	1013.4	1013.0	1012.2	1011.5	1010.7	1009.9	1010.7	1011.5	1012.2
140°	1067.1	1067.1	1067.1	1066.8	1066.3	1065.8	1065.2	1064.7	1065.2	1065.8	1066.3
142.5°	1116.8	1117.1	1117.2	1116.9	1116.4	1115.9	1115.4	1114.9	1115.4	1115.9	1116.4
145°	1165.4	1165.1	1165.0	1164.5	1163.4	1162.4	1161.3	1160.3	1161.3	1162.4	1163.4
147.5°	1212.4	1212.7	1212.8	1212.2	1210.9	1209.6	1208.3	1207.0	1208.3	1209.6	1210.9
150°	1253.6	1253.6	1253.6	1253.1	1252.1	1251.0	1250.0	1249.0	1250.0	1251.0	1252.1
152.5°	1291.4	1291.1	1291.0	1290.7	1290.2	1289.7	1289.1	1288.6	1289.1	1289.7	1290.2
155°	1329.0	1329.3	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
157.5°	1362.1	1362.1	1362.1	1362.4	1362.9	1363.4	1363.9	1364.4	1363.9	1363.4	1362.9
160°	1393.2	1393.5	1393.6	1393.7	1394.0	1394.2	1394.5	1394.7	1394.5	1394.2	1394.0
162.5°	1418.8	1419.1	1419.2	1419.6	1420.4	1421.1	1421.9	1422.7	1421.9	1421.1	1420.4
165°	1442.9	1443.4	1443.7	1444.1	1444.9	1445.6	1446.4	1447.2	1446.4	1445.6	1444.9
167.5°	1462.4	1462.4	1462.4	1462.9	1464.0	1465.0	1466.1	1467.1	1466.1	1465.0	1464.0
170°	1477.9	1477.6	1477.5	1478.2	1479.5	1480.8	1482.1	1483.4	1482.1	1480.8	1479.5
172.5°	1490.4	1490.4	1490.4	1490.9	1491.9	1493.0	1494.0	1495.0	1494.0	1493.0	1491.9
175°	1499.3	1499.6	1499.7	1500.3	1501.6	1502.9	1504.2	1505.5	1504.2	1502.9	1501.6
177.5°	1504.4	1504.4	1504.4	1505.0	1506.3	1507.6	1508.9	1510.2	1508.9	1507.6	1506.3
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9

TEST NUMBER: P1026122

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6
2.5°	1962.4	1959.2	1956.0	1943.1	1931.9	1912.6	1896.5	1890.1	1888.5	1890.1	1885.3
5°	1906.2	1904.6	1893.3	1870.8	1849.9	1827.4	1811.3	1795.3	1785.6	1785.6	1774.4
7.5°	1853.1	1841.9	1832.2	1803.3	1779.2	1748.7	1724.5	1710.1	1702.0	1684.4	1684.4
10°	1796.9	1780.8	1767.9	1740.6	1705.3	1674.7	1644.2	1626.5	1612.0	1599.2	1594.4
12.5°	1740.6	1727.8	1703.6	1674.7	1639.4	1600.8	1568.6	1555.8	1522.0	1494.7	1496.3
15°	1687.6	1658.6	1647.4	1605.6	1563.8	1526.9	1480.2	1443.3	1416.0	1398.3	1375.8
17.5°	1628.1	1599.2	1578.3	1542.9	1488.3	1430.4	1385.4	1335.6	1308.3	1277.7	1263.3
20°	1562.2	1538.1	1522.0	1465.8	1399.9	1330.8	1281.0	1250.4	1219.9	1197.4	1184.5
22.5°	1506.0	1475.4	1456.1	1380.6	1308.3	1239.2	1200.6	1174.9	1149.2	1129.9	1123.4
25°	1433.6	1416.0	1369.3	1303.5	1215.1	1168.4	1134.7	1100.9	1086.5	1073.6	1059.2
27.5°	1374.2	1330.8	1298.6	1211.8	1157.2	1104.2	1070.4	1044.7	1027.0	1014.2	1002.9
30°	1300.2	1260.1	1215.1	1142.7	1092.9	1043.1	1012.5	991.7	972.4	964.3	954.7
32.5°	1223.1	1186.1	1142.7	1084.9	1023.8	985.2	961.1	938.6	925.8	917.7	906.5
35°	1154.0	1107.4	1078.4	1023.8	974.0	930.6	908.1	888.8	874.3	871.1	869.5
37.5°	1080.0	1044.7	1017.4	961.1	919.3	882.4	861.5	840.6	832.5	830.9	824.5
40°	1015.8	985.2	959.5	906.5	861.5	827.7	811.6	798.8	790.8	790.8	789.1
42.5°	959.5	927.4	901.6	853.4	813.3	782.7	765.0	752.2	749.0	750.6	749.0
45°	896.8	869.5	843.8	794.0	760.2	737.7	718.4	712.0	707.2	708.8	710.4
47.5°	837.4	814.9	789.1	749.0	710.4	686.3	675.0	668.6	668.6	668.6	671.8
50°	784.3	758.6	736.1	694.3	659.0	639.7	630.0	622.0	623.6	625.2	626.8
52.5°	721.6	699.1	683.1	641.3	615.6	591.5	580.2	581.8	580.2	580.2	583.4
55°	667.0	644.5	628.4	589.8	564.1	548.1	538.4	533.6	535.2	532.0	538.4
57.5°	605.9	586.6	575.4	538.4	515.9	501.5	493.4	485.4	488.6	487.0	485.4
60°	552.9	530.4	512.7	487.0	467.7	450.0	445.2	437.2	440.4	437.2	435.6
62.5°	491.8	474.1	461.3	435.6	419.5	405.0	393.8	388.9	387.3	382.5	377.7
65°	430.7	421.1	408.2	382.5	366.4	355.2	348.8	343.9	342.3	329.5	315.0
67.5°	374.5	368.1	355.2	335.9	321.4	310.2	300.5	292.5	282.9	273.2	265.2
70°	321.4	311.8	303.8	286.1	273.2	262.0	252.3	242.7	237.9	228.2	225.0
72.5°	270.0	260.4	252.3	236.3	225.0	213.8	210.5	199.3	194.5	192.9	192.9
75°	217.0	208.9	204.1	189.7	180.0	172.0	167.2	163.9	160.7	157.5	152.7
77.5°	165.5	160.7	157.5	147.9	139.8	135.0	133.4	122.1	118.9	115.7	112.5
80°	120.5	118.9	115.7	107.7	104.5	93.2	93.2	90.0	88.4	88.4	88.4
82.5°	82.0	78.8	77.1	69.1	67.5	65.9	64.3	62.7	64.3	62.7	64.3
85°	43.4	41.8	40.2	40.2	40.2	40.2	40.2	40.2	40.2	38.6	40.2
87.5°	16.1	16.1	16.1	16.1	14.5	16.1	16.1	14.5	16.1	16.1	16.1
90°	14.9	16.3	17.3	19.4	21.5	23.6	25.7	27.3	28.8	30.4	31.9
92.5°	43.8	45.5	46.1	47.4	48.7	50.0	51.3	52.1	52.9	53.6	54.4
95°	79.3	80.5	81.4	83.2	85.0	86.8	88.6	89.4	90.2	90.9	91.7
97.5°	120.3	121.3	122.3	124.4	126.5	128.5	130.6	131.6	132.7	133.7	134.8
100°	167.4	167.9	169.1	171.4	173.7	176.1	178.4	178.9	179.5	180.0	180.5
102.5°	218.0	218.1	219.1	221.2	223.3	225.3	227.4	228.2	229.0	229.7	230.5
105°	272.8	272.9	273.4	274.5	275.5	276.6	277.6	278.4	279.1	279.9	280.6
107.5°	329.9	330.0	330.1	330.4	330.7	330.9	331.2	332.2	333.3	334.3	335.4
110°	389.2	389.5	389.4	389.1	388.8	388.6	388.3	387.8	387.3	386.8	386.3

TEST NUMBER: P1026122

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	447.8	447.8	447.5	447.0	446.5	446.0	445.5	445.5	445.5	445.5	445.5
115°	508.5	508.5	508.2	507.7	507.2	506.6	506.1	505.9	505.6	505.4	505.1
117.5°	565.6	565.6	565.5	565.2	564.9	564.7	564.4	563.6	562.8	562.1	561.3
120°	626.9	627.4	627.0	626.2	625.5	624.7	623.9	622.6	621.3	620.0	618.7
122.5°	683.3	683.4	683.3	683.0	682.7	682.5	682.2	681.4	680.6	679.9	679.1
125°	740.5	740.5	740.4	740.1	739.9	739.6	739.4	738.9	738.3	737.8	737.3
127.5°	796.1	796.5	796.2	795.7	795.2	794.7	794.2	793.7	793.1	792.6	792.1
130°	852.1	852.5	852.5	852.5	852.5	852.5	852.5	852.0	851.4	850.9	850.4
132.5°	908.2	908.5	908.4	908.1	907.8	907.6	907.3	906.8	906.3	905.8	905.3
135°	961.3	962.1	962.1	962.1	962.1	962.1	962.1	961.6	961.1	960.6	960.1
137.5°	1013.0	1013.4	1013.7	1014.2	1014.7	1015.2	1015.7	1014.9	1014.1	1013.4	1012.6
140°	1066.8	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1	1066.8	1066.6	1066.3	1066.0
142.5°	1116.9	1117.2	1117.1	1116.8	1116.5	1116.3	1116.0	1116.0	1116.0	1116.0	1116.0
145°	1164.5	1165.0	1165.1	1165.4	1165.7	1165.9	1166.2	1165.9	1165.7	1165.4	1165.1
147.5°	1212.2	1212.8	1212.7	1212.4	1212.2	1211.9	1211.7	1211.4	1211.2	1210.9	1210.6
150°	1253.1	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6
152.5°	1290.7	1291.0	1291.1	1291.4	1291.6	1291.9	1292.1	1292.9	1293.7	1294.4	1295.2
155°	1329.4	1329.4	1329.3	1329.0	1328.8	1328.5	1328.3	1329.3	1330.3	1331.4	1332.4
157.5°	1362.4	1362.1	1362.1	1362.1	1362.1	1362.1	1362.1	1362.9	1363.7	1364.4	1365.2
160°	1393.7	1393.6	1393.5	1393.2	1392.9	1392.7	1392.4	1393.2	1394.0	1394.7	1395.5
162.5°	1419.6	1419.2	1419.1	1418.8	1418.6	1418.3	1418.1	1419.7	1421.2	1422.8	1424.3
165°	1444.1	1443.7	1443.4	1442.9	1442.4	1441.9	1441.4	1443.0	1444.5	1446.1	1447.6
167.5°	1462.9	1462.4	1462.4	1462.4	1462.4	1462.4	1462.4	1464.0	1465.5	1467.1	1468.6
170°	1478.2	1477.5	1477.6	1477.9	1478.2	1478.4	1478.7	1480.3	1481.8	1483.4	1484.9
172.5°	1490.9	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1492.2	1494.0	1495.8	1497.6
175°	1500.3	1499.7	1499.6	1499.3	1499.0	1498.8	1498.5	1500.3	1502.1	1504.0	1505.8
177.5°	1505.0	1504.4	1504.4	1504.4	1504.4	1504.4	1504.4	1506.2	1508.0	1509.8	1511.6
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9

TEST NUMBER: P1026122

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6
2.5°	1885.3	1891.7	1883.7	1888.5	1877.2	1875.6	1877.2	1877.2	1878.8	1880.4	1882.0
5°	1779.2	1777.6	1767.9	1761.5	1756.7	1761.5	1764.7	1767.9	1764.7	1767.9	1769.5
7.5°	1679.5	1674.7	1669.9	1658.6	1661.9	1658.6	1668.3	1663.5	1663.5	1671.5	1677.9
10°	1591.1	1581.5	1578.3	1565.4	1555.8	1554.2	1565.4	1570.2	1575.1	1578.3	1591.1
12.5°	1477.0	1462.6	1451.3	1456.1	1428.8	1440.1	1443.3	1436.9	1456.1	1478.6	1465.8
15°	1354.9	1356.5	1334.0	1326.0	1303.5	1309.9	1311.5	1327.6	1343.6	1342.0	1361.3
17.5°	1264.9	1255.2	1235.9	1234.3	1224.7	1229.5	1227.9	1240.8	1235.9	1244.0	1260.1
20°	1181.3	1174.9	1158.8	1152.4	1155.6	1152.4	1154.0	1155.6	1160.4	1178.1	1174.9
22.5°	1115.4	1107.4	1107.4	1099.3	1089.7	1086.5	1094.5	1099.3	1105.8	1109.0	1117.0
25°	1057.5	1051.1	1043.1	1038.3	1030.2	1031.8	1036.7	1043.1	1047.9	1054.3	1060.8
27.5°	998.1	998.1	990.0	988.4	985.2	983.6	990.0	993.3	993.3	998.1	1004.5
30°	951.5	951.5	943.4	941.8	940.2	940.2	945.0	946.6	948.3	953.1	956.3
32.5°	906.5	904.9	901.6	903.3	901.6	903.3	903.3	904.9	908.1	909.7	916.1
35°	864.7	866.3	863.1	863.1	861.5	863.1	866.3	867.9	869.5	872.7	872.7
37.5°	824.5	827.7	826.1	830.9	830.9	830.9	830.9	834.1	834.1	834.1	832.5
40°	789.1	789.1	787.5	790.8	794.0	794.0	795.6	795.6	797.2	797.2	795.6
42.5°	749.0	752.2	757.0	758.6	761.8	760.2	765.0	763.4	765.0	761.8	758.6
45°	712.0	712.0	718.4	724.9	726.5	726.5	726.5	729.7	726.5	721.6	720.0
47.5°	671.8	675.0	678.2	686.3	687.9	687.9	687.9	687.9	684.7	684.7	684.7
50°	631.6	633.2	634.9	638.1	642.9	641.3	641.3	641.3	647.7	641.3	642.9
52.5°	583.4	585.0	586.6	593.1	591.5	591.5	593.1	593.1	597.9	596.3	593.1
55°	535.2	535.2	538.4	538.4	538.4	541.6	543.2	546.5	544.8	546.5	548.1
57.5°	487.0	483.8	482.2	482.2	487.0	485.4	487.0	487.0	493.4	496.6	498.2
60°	430.7	430.7	429.1	419.5	419.5	417.9	422.7	425.9	429.1	443.6	442.0
62.5°	372.9	366.4	360.0	361.6	352.0	356.8	353.6	356.8	366.4	377.7	379.3
65°	315.0	310.2	303.8	302.2	298.9	303.8	302.2	303.8	308.6	315.0	323.1
67.5°	263.6	262.0	258.8	257.2	257.2	257.2	260.4	260.4	262.0	266.8	271.6
70°	225.0	223.4	225.0	221.8	223.4	221.8	223.4	225.0	226.6	228.2	233.0
72.5°	189.7	189.7	189.7	186.4	189.7	188.0	188.0	189.7	191.3	192.9	196.1
75°	151.1	147.9	144.6	141.4	139.8	143.0	144.6	143.0	147.9	154.3	154.3
77.5°	114.1	112.5	112.5	112.5	114.1	112.5	115.7	114.1	115.7	115.7	118.9
80°	88.4	86.8	88.4	88.4	86.8	90.0	88.4	88.4	90.0	91.6	90.0
82.5°	64.3	65.9	64.3	64.3	64.3	67.5	64.3	64.3	64.3	65.9	65.9
85°	40.2	40.2	40.2	40.2	41.8	40.2	41.8	40.2	43.4	41.8	41.8
87.5°	14.5	16.1	17.7	17.7	17.7	17.7	16.1	17.7	19.3	17.7	19.3
90°	32.7	33.0	33.5	34.0	34.5	35.0	34.5	34.0	33.5	33.0	32.7
92.5°	54.8	54.9	55.2	55.5	55.7	56.0	55.7	55.5	55.2	54.9	54.8
95°	92.1	92.1	92.1	92.1	92.1	92.1	92.1	92.1	92.1	92.1	92.1
97.5°	135.3	135.3	135.3	135.3	135.3	135.3	135.3	135.3	135.3	135.3	135.3
100°	180.8	180.8	180.8	180.8	180.8	180.8	180.8	180.8	180.8	180.8	180.8
102.5°	230.9	231.0	231.3	231.6	231.8	232.1	231.8	231.6	231.3	231.0	230.9
105°	281.0	281.4	282.2	282.9	283.7	284.5	283.7	282.9	282.2	281.4	281.0
107.5°	335.9	335.8	335.5	335.2	335.0	334.7	335.0	335.2	335.5	335.8	335.9
110°	386.0	386.4	387.2	387.9	388.7	389.5	388.7	387.9	387.2	386.4	386.0

TEST NUMBER: P1026122

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5
115°	505.0	504.9	504.6	504.3	504.1	503.8	504.1	504.3	504.6	504.9	505.0
117.5°	560.9	560.5	559.7	559.0	558.2	557.4	558.2	559.0	559.7	560.5	560.9
120°	618.1	618.4	618.9	619.4	619.9	620.4	619.9	619.4	618.9	618.4	618.1
122.5°	678.7	678.1	676.8	675.5	674.2	672.9	674.2	675.5	676.8	678.1	678.7
125°	737.0	736.7	736.2	735.7	735.2	734.7	735.2	735.7	736.2	736.7	737.0
127.5°	791.8	791.7	791.4	791.2	790.9	790.7	790.9	791.2	791.4	791.7	791.8
130°	850.1	849.6	848.6	847.5	846.5	845.5	846.5	847.5	848.6	849.6	850.1
132.5°	905.0	904.9	904.6	904.3	904.1	903.8	904.1	904.3	904.6	904.9	905.0
135°	959.8	959.4	958.6	957.9	957.1	956.3	957.1	957.9	958.6	959.4	959.8
137.5°	1012.2	1012.3	1012.6	1012.9	1013.1	1013.4	1013.1	1012.9	1012.6	1012.3	1012.2
140°	1065.9	1065.8	1065.5	1065.2	1065.0	1064.7	1065.0	1065.2	1065.5	1065.8	1065.9
142.5°	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0
145°	1165.0	1164.6	1163.8	1163.1	1162.3	1161.5	1162.3	1163.1	1163.8	1164.6	1165.0
147.5°	1210.5	1210.4	1210.1	1209.8	1209.6	1209.3	1209.6	1209.8	1210.1	1210.4	1210.5
150°	1253.6	1253.5	1253.2	1253.0	1252.7	1252.5	1252.7	1253.0	1253.2	1253.5	1253.6
152.5°	1295.6	1295.2	1294.4	1293.7	1292.9	1292.1	1292.9	1293.7	1294.4	1295.2	1295.6
155°	1332.9	1332.4	1331.4	1330.3	1329.3	1328.3	1329.3	1330.3	1331.4	1332.4	1332.9
157.5°	1365.6	1365.2	1364.4	1363.7	1362.9	1362.1	1362.9	1363.7	1364.4	1365.2	1365.6
160°	1395.9	1395.3	1394.0	1392.7	1391.4	1390.1	1391.4	1392.7	1394.0	1395.3	1395.9
162.5°	1425.1	1424.4	1423.1	1421.8	1420.5	1419.2	1420.5	1421.8	1423.1	1424.4	1425.1
165°	1448.4	1447.9	1446.8	1445.8	1444.7	1443.7	1444.7	1445.8	1446.8	1447.9	1448.4
167.5°	1469.4	1468.6	1467.1	1465.5	1464.0	1462.4	1464.0	1465.5	1467.1	1468.6	1469.4
170°	1485.7	1484.8	1483.0	1481.1	1479.3	1477.5	1479.3	1481.1	1483.0	1484.8	1485.7
172.5°	1498.5	1497.6	1495.8	1494.0	1492.2	1490.4	1492.2	1494.0	1495.8	1497.6	1498.5
175°	1506.7	1505.8	1504.0	1502.1	1500.3	1498.5	1500.3	1502.1	1504.0	1505.8	1506.7
177.5°	1512.5	1511.5	1509.4	1507.3	1505.3	1503.2	1505.3	1507.3	1509.4	1511.5	1512.5
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9

TEST NUMBER: P1026122

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6
2.5°	1888.5	1896.5	1893.3	1882.0	1886.9	1896.5	1906.2	1919.0	1927.1	1933.5	1936.7
5°	1777.6	1792.0	1788.8	1788.8	1795.3	1811.3	1827.4	1854.7	1864.4	1875.6	1891.7
7.5°	1679.5	1690.8	1700.4	1703.6	1713.3	1734.2	1755.1	1785.6	1809.7	1822.6	1832.2
10°	1592.8	1600.8	1615.3	1623.3	1632.9	1658.6	1689.2	1721.3	1745.4	1767.9	1780.8
12.5°	1481.9	1514.0	1533.3	1546.1	1559.0	1597.6	1621.7	1657.0	1686.0	1706.9	1726.1
15°	1358.1	1396.7	1407.9	1457.7	1489.9	1520.4	1557.4	1599.2	1626.5	1650.6	1676.3
17.5°	1253.6	1281.0	1293.8	1346.8	1374.2	1422.4	1475.4	1528.5	1570.2	1587.9	1613.6
20°	1187.7	1202.2	1227.9	1245.6	1274.5	1330.8	1388.6	1452.9	1515.6	1533.3	1559.0
22.5°	1120.2	1139.5	1157.2	1181.3	1203.8	1242.4	1300.2	1371.0	1438.5	1470.6	1501.1
25°	1059.2	1078.4	1089.7	1115.4	1136.3	1174.9	1215.1	1287.4	1367.7	1395.1	1443.3
27.5°	1010.9	1022.2	1041.5	1052.7	1076.8	1112.2	1149.2	1203.8	1282.6	1329.2	1375.8
30°	962.7	970.8	986.8	1002.9	1020.6	1044.7	1086.5	1139.5	1211.8	1252.0	1298.6
32.5°	914.5	927.4	937.0	948.3	967.5	996.5	1025.4	1076.8	1134.7	1179.7	1226.3
35°	874.3	879.1	892.0	904.9	917.7	943.4	974.0	1023.8	1075.2	1110.6	1152.4
37.5°	830.9	839.0	848.6	853.4	874.3	890.4	922.5	961.1	1022.2	1044.7	1086.5
40°	797.2	795.6	805.2	813.3	822.9	848.6	867.9	909.7	957.9	993.3	1019.0
42.5°	755.4	755.4	758.6	768.2	781.1	797.2	819.7	855.0	904.9	930.6	961.1
45°	721.6	716.8	718.4	724.9	732.9	749.0	771.5	802.0	851.8	872.7	904.9
47.5°	681.5	676.6	676.6	683.1	689.5	700.7	718.4	753.8	794.0	821.3	845.4
50°	636.5	638.1	636.5	641.3	644.5	655.7	675.0	704.0	740.9	763.4	790.8
52.5°	594.7	591.5	589.8	593.1	599.5	607.5	628.4	654.1	689.5	712.0	736.1
55°	543.2	546.5	546.5	546.5	556.1	559.3	575.4	601.1	636.5	654.1	676.6
57.5°	496.6	495.0	498.2	496.6	504.7	515.9	528.8	548.1	583.4	601.1	622.0
60°	445.2	446.8	448.4	448.4	454.8	466.1	480.6	498.2	527.2	544.8	564.1
62.5°	382.5	390.6	398.6	401.8	411.4	419.5	429.1	448.4	474.1	487.0	504.7
65°	323.1	334.3	345.6	353.6	360.0	368.1	380.9	398.6	419.5	432.3	450.0
67.5°	271.6	279.7	294.1	302.2	315.0	324.7	332.7	347.2	372.9	377.7	392.2
70°	234.7	237.9	244.3	250.7	265.2	273.2	282.9	297.3	316.6	327.9	335.9
72.5°	197.7	199.3	202.5	208.9	215.4	225.0	236.3	249.1	266.8	271.6	282.9
75°	157.5	167.2	167.2	172.0	176.8	181.6	191.3	204.1	215.4	223.4	229.8
77.5°	117.3	122.1	125.4	133.4	139.8	144.6	151.1	160.7	167.2	173.6	178.4
80°	91.6	93.2	94.8	94.8	98.0	104.5	110.9	117.3	125.4	128.6	133.4
82.5°	67.5	67.5	67.5	70.7	72.3	73.9	73.9	77.1	85.2	88.4	93.2
85°	43.4	43.4	43.4	43.4	45.0	46.6	48.2	49.8	49.8	49.8	53.0
87.5°	17.7	20.9	19.3	20.9	20.9	20.9	20.9	22.5	22.5	24.1	24.1
90°	31.9	30.4	28.8	27.3	25.7	23.6	21.5	19.4	17.3	16.3	14.9
92.5°	54.4	53.6	52.9	52.1	51.3	50.0	48.7	47.4	46.1	45.5	43.8
95°	91.7	90.9	90.2	89.4	88.6	86.8	85.0	83.2	81.4	80.5	79.3
97.5°	134.8	133.7	132.7	131.6	130.6	128.5	126.5	124.4	122.3	121.3	120.3
100°	180.5	180.0	179.5	178.9	178.4	176.1	173.7	171.4	169.1	167.9	167.4
102.5°	230.5	229.7	229.0	228.2	227.4	225.3	223.3	221.2	219.1	218.1	218.0
105°	280.6	279.9	279.1	278.4	277.6	276.6	275.5	274.5	273.4	272.9	272.8
107.5°	335.4	334.3	333.3	332.2	331.2	330.9	330.7	330.4	330.1	330.0	329.9
110°	386.3	386.8	387.3	387.8	388.3	388.6	388.8	389.1	389.4	389.5	389.2

TEST NUMBER: P1026122

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	445.5	445.5	445.5	445.5	445.5	446.0	446.5	447.0	447.5	447.8	447.8
115°	505.1	505.4	505.6	505.9	506.1	506.6	507.2	507.7	508.2	508.5	508.5
117.5°	561.3	562.1	562.8	563.6	564.4	564.7	564.9	565.2	565.5	565.6	565.6
120°	618.7	620.0	621.3	622.6	623.9	624.7	625.5	626.2	627.0	627.4	626.9
122.5°	679.1	679.9	680.6	681.4	682.2	682.5	682.7	683.0	683.3	683.4	683.3
125°	737.3	737.8	738.3	738.9	739.4	739.6	739.9	740.1	740.4	740.5	740.5
127.5°	792.1	792.6	793.1	793.7	794.2	794.7	795.2	795.7	796.2	796.5	796.1
130°	850.4	850.9	851.4	852.0	852.5	852.5	852.5	852.5	852.5	852.5	852.1
132.5°	905.3	905.8	906.3	906.8	907.3	907.6	907.8	908.1	908.4	908.5	908.2
135°	960.1	960.6	961.1	961.6	962.1	962.1	962.1	962.1	962.1	962.1	961.3
137.5°	1012.6	1013.4	1014.1	1014.9	1015.7	1015.2	1014.7	1014.2	1013.7	1013.4	1013.0
140°	1066.0	1066.3	1066.6	1066.8	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1	1066.8
142.5°	1116.0	1116.0	1116.0	1116.0	1116.0	1116.3	1116.5	1116.8	1117.1	1117.2	1116.9
145°	1165.1	1165.4	1165.7	1165.9	1166.2	1165.9	1165.7	1165.4	1165.1	1165.0	1164.5
147.5°	1210.6	1210.9	1211.2	1211.4	1211.7	1211.9	1212.2	1212.4	1212.7	1212.8	1212.2
150°	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.1
152.5°	1295.2	1294.4	1293.7	1292.9	1292.1	1291.9	1291.6	1291.4	1291.1	1291.0	1290.7
155°	1332.4	1331.4	1330.3	1329.3	1328.3	1328.5	1328.8	1329.0	1329.3	1329.4	1329.4
157.5°	1365.2	1364.4	1363.7	1362.9	1362.1	1362.1	1362.1	1362.1	1362.1	1362.1	1362.4
160°	1395.5	1394.7	1394.0	1393.2	1392.4	1392.7	1392.9	1393.2	1393.5	1393.6	1393.7
162.5°	1424.3	1422.8	1421.2	1419.7	1418.1	1418.3	1418.6	1418.8	1419.1	1419.2	1419.6
165°	1447.6	1446.1	1444.5	1443.0	1441.4	1441.9	1442.4	1442.9	1443.4	1443.7	1444.1
167.5°	1468.6	1467.1	1465.5	1464.0	1462.4	1462.4	1462.4	1462.4	1462.4	1462.4	1462.9
170°	1484.9	1483.4	1481.8	1480.3	1478.7	1478.4	1478.2	1477.9	1477.6	1477.5	1478.2
172.5°	1497.6	1495.8	1494.0	1492.2	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.9
175°	1505.8	1504.0	1502.1	1500.3	1498.5	1498.8	1499.0	1499.3	1499.6	1499.7	1500.3
177.5°	1511.6	1509.8	1508.0	1506.2	1504.4	1504.4	1504.4	1504.4	1504.4	1504.4	1505.0
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9

TEST NUMBER: P1026122

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1994.6	1994.6	1994.6	1994.6
2.5°	1949.6	1959.2	1975.3	1997.8
5°	1904.6	1931.9	1957.6	1991.3
7.5°	1864.4	1896.5	1931.9	1980.1
10°	1817.8	1857.9	1902.9	1962.4
12.5°	1763.1	1819.4	1870.8	1935.1
15°	1722.9	1764.7	1830.6	1906.2
17.5°	1666.7	1722.9	1788.8	1874.0
20°	1613.6	1673.1	1747.0	1835.4
22.5°	1557.4	1624.9	1698.8	1793.7
25°	1499.5	1571.9	1645.8	1747.0
27.5°	1446.5	1512.4	1596.0	1698.8
30°	1382.2	1457.7	1538.1	1645.8
32.5°	1319.5	1398.3	1480.2	1587.9
35°	1252.0	1330.8	1420.8	1523.6
37.5°	1186.1	1272.9	1354.9	1454.5
40°	1113.8	1203.8	1289.0	1390.2
42.5°	1043.1	1136.3	1221.5	1308.3
45°	977.2	1068.8	1145.9	1227.9
47.5°	914.5	996.5	1075.2	1149.2
50°	853.4	922.5	994.9	1055.9
52.5°	789.1	855.0	912.9	967.5
55°	731.3	782.7	834.1	884.0
57.5°	662.2	713.6	758.6	797.2
60°	604.3	636.5	679.9	720.0
62.5°	538.4	575.4	609.1	634.9
65°	474.1	506.3	532.0	554.5
67.5°	419.5	438.8	458.1	482.2
70°	353.6	369.7	392.2	409.8
72.5°	297.3	310.2	321.4	342.3
75°	241.1	252.3	258.8	278.0
77.5°	186.4	197.7	202.5	213.8
80°	143.0	144.6	151.1	160.7
82.5°	98.0	101.3	102.9	110.9
85°	56.3	64.3	62.7	65.9
87.5°	24.1	25.7	28.9	32.1
90°	12.0	9.2	6.3	3.5
92.5°	40.4	37.1	33.7	30.3
95°	77.0	74.7	72.3	70.0
97.5°	118.2	116.1	114.1	112.0
100°	166.4	165.3	164.3	163.3
102.5°	217.7	217.4	217.2	216.9
105°	272.5	272.2	272.0	271.7
107.5°	329.6	329.4	329.1	328.9
110°	388.7	388.2	387.7	387.2



TEST NUMBER: P1026122

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	447.8	447.8	447.8	447.8
115°	508.5	508.5	508.5	508.5
117.5°	565.6	565.6	565.6	565.6
120°	625.8	624.8	623.7	622.7
122.5°	683.0	682.7	682.5	682.2
125°	740.5	740.5	740.5	740.5
127.5°	795.3	794.6	793.8	793.0
130°	851.3	850.6	849.8	849.0
132.5°	907.7	907.2	906.6	906.1
135°	959.8	958.2	956.7	955.1
137.5°	1012.2	1011.5	1010.7	1009.9
140°	1066.3	1065.8	1065.2	1064.7
142.5°	1116.4	1115.9	1115.4	1114.9
145°	1163.4	1162.4	1161.3	1160.3
147.5°	1210.9	1209.6	1208.3	1207.0
150°	1252.1	1251.0	1250.0	1249.0
152.5°	1290.2	1289.7	1289.1	1288.6
155°	1329.4	1329.4	1329.4	1329.4
157.5°	1362.9	1363.4	1363.9	1364.4
160°	1394.0	1394.2	1394.5	1394.7
162.5°	1420.4	1421.1	1421.9	1422.7
165°	1444.9	1445.6	1446.4	1447.2
167.5°	1464.0	1465.0	1466.1	1467.1
170°	1479.5	1480.8	1482.1	1483.4
172.5°	1491.9	1493.0	1494.0	1495.0
175°	1501.6	1502.9	1504.2	1505.5
177.5°	1506.3	1507.6	1508.9	1510.2
180°	1507.9	1507.9	1507.9	1507.9

(END OF REPORT)