

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026124

Luminaire Tested: S124RDIP-B1195D1205UB35-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026124
REPORT IS A COMBINATION OF REPORTS P999084 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D1205UB35-4F0-XX-W2A-F
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9678.0 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026124

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1026124

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	48	48	43
2	90	82	76	71	82	76	71	67	65	61	58	54	51	49	44	43	41	41	41	36
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	35	35	31
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	30	30	30	27
5	69	57	49	44	63	53	46	41	46	40	36	39	35	31	32	29	27	27	27	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	24	24	24	21
7	59	47	39	33	54	44	36	31	38	32	28	32	28	24	27	24	21	21	21	18
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	19	19	17
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	23	20	17	17	17	15
10	48	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17116	17116	17116
5°	17118	16608	16610
10°	16973	16084	15893
15°	16740	15431	15046
20°	16434	14687	14082
25°	16052	13885	13139
30°	15679	13066	12082
35°	15268	12236	11047
40°	14780	11342	9985
45°	14321	10456	8933
50°	13800	9489	7864
55°	13237	8496	6762
60°	12612	7443	5673
65°	12008	6234	4624
70°	11150	4961	3534
75°	10052	3611	2471
80°	8394	2217	1777
85°	6316	1276	977

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14321 cd/sqm

TEST NUMBER: P1026124

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.4	2.0
10°-20°	550.3	5.7
20°-30°	794.5	8.2
30°-40°	900.5	9.3
40°-50°	869.4	9.0
50°-60°	722.8	7.5
60°-70°	498.9	5.2
70°-80°	252.1	2.6
80°-90°	67.2	0.7
90°-100°	51.8	0.5
100°-110°	340.8	3.5
110°-120°	650.9	6.7
120°-130°	826.3	8.5
130°-140°	883.9	9.1
140°-150°	826.5	8.5
150°-160°	666.5	6.9
160°-170°	429.9	4.4
170°-180°	148.2	1.5
0°-30°	1542.2	15.9
0°-40°	2442.7	25.2
0°-60°	4035.0	41.7
0°-90°	4853.2	50.1
90°-120°	1043.5	10.8
90°-150°	3580.2	37.0
90°-180°	4825.0	49.9
0°-180°	9678.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2099	2099	2099	2099	2099	
5°	2096	2089	2070	2086	2083	199
15°	1996	1982	1942	1938	1927	563
25°	1805	1776	1710	1683	1667	832
35°	1561	1509	1429	1374	1345	975
45°	1273	1213	1117	1038	1009	982
55°	964	900	796	712	682	863
65°	656	587	484	415	395	648
75°	349	289	214	177	167	368
85°	87	55	50	47	47	95
90°	4	16	26	33	35	8
95°	64	24	26	33	34	79
105°	351	358	364	374	332	367
115°	655	659	658	660	660	645
125°	921	926	924	927	928	823
135°	1143	1142	1146	1149	1151	881
145°	1318	1321	1321	1322	1325	823
155°	1445	1446	1443	1447	1444	666
165°	1524	1518	1518	1528	1517	431
175°	1559	1552	1553	1564	1550	148
180°	1559	1559	1559	1559	1559	

TEST NUMBER: P1026124

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2099.0	2099.0	2099.0	2099.0	2099.0
2.5°	2105.4	2099.0	2081.3	2099.0	2097.4
5°	2095.8	2089.4	2070.1	2086.2	2082.9
7.5°	2081.3	2074.9	2050.8	2062.1	2057.2
10°	2058.8	2050.8	2021.9	2028.3	2021.9
12.5°	2029.9	2020.3	1984.9	1988.1	1978.5
15°	1996.2	1981.7	1941.5	1938.3	1927.0
17.5°	1957.6	1936.7	1890.1	1882.0	1866.0
20°	1911.0	1890.1	1835.4	1822.6	1801.7
22.5°	1859.5	1835.4	1776.0	1755.1	1739.0
25°	1804.9	1776.0	1710.1	1682.7	1666.7
27.5°	1748.6	1713.3	1644.2	1612.0	1589.5
30°	1689.2	1649.0	1573.5	1533.3	1507.6
32.5°	1626.5	1579.9	1501.1	1452.9	1428.8
35°	1560.6	1509.2	1428.8	1374.2	1345.2
37.5°	1491.5	1438.5	1350.1	1290.6	1261.7
40°	1417.6	1364.5	1272.9	1205.4	1176.5
42.5°	1346.8	1290.6	1194.2	1125.0	1094.5
45°	1272.9	1213.4	1117.0	1038.3	1009.3
47.5°	1197.4	1136.3	1036.7	954.7	922.5
50°	1120.2	1057.5	954.7	874.3	843.8
52.5°	1041.5	980.4	874.3	792.4	760.2
55°	964.3	900.0	795.6	712.0	681.5
57.5°	888.8	821.3	718.4	633.2	610.7
60°	806.8	742.5	639.7	556.1	530.4
62.5°	732.9	665.4	559.3	483.8	464.5
65°	655.7	586.6	483.8	414.7	395.4
67.5°	575.4	509.5	413.1	352.0	329.5
70°	499.8	432.3	340.7	287.7	271.6
72.5°	419.5	360.0	274.8	231.4	217.0
75°	348.8	289.3	213.8	176.8	167.1
77.5°	274.8	223.4	159.1	133.4	130.2
80°	204.1	157.5	109.3	104.5	102.9
82.5°	143.0	101.3	78.8	75.5	73.9
85°	86.8	54.6	49.8	46.6	46.6
87.5°	37.0	24.1	22.5	20.9	22.5
90°	3.5	16.3	25.7	32.7	35.0
92.5°	17.5	15.2	24.5	31.5	31.5
95°	64.1	24.5	25.7	32.7	33.8
97.5°	122.5	148.1	25.7	31.5	32.7
100°	191.3	212.2	51.3	31.5	32.7
102.5°	268.2	282.2	296.2	33.8	33.8
105°	351.0	358.0	363.9	374.4	332.4
107.5°	426.8	430.3	438.5	444.3	449.0
110°	503.8	507.3	514.3	516.6	520.1

TEST NUMBER: P1026124

CATALOG NUMBER: S124RDIP-B1195D1205UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	578.4	585.4	587.8	586.6	591.3
115°	655.4	658.9	657.7	660.1	660.1
117.5°	724.2	728.9	732.4	731.2	731.2
120°	794.2	798.9	797.7	800.0	797.7
122.5°	859.5	861.8	864.2	865.3	863.0
125°	921.3	926.0	923.6	927.1	928.3
127.5°	980.8	981.9	987.8	986.6	985.4
130°	1037.9	1039.1	1042.6	1043.8	1043.8
132.5°	1090.4	1092.7	1097.4	1098.6	1097.4
135°	1142.9	1141.7	1146.4	1148.7	1151.0
137.5°	1189.5	1189.5	1195.4	1197.7	1196.5
140°	1235.0	1237.3	1239.7	1243.2	1244.3
142.5°	1275.8	1280.5	1281.7	1284.0	1284.0
145°	1317.8	1321.3	1321.3	1322.5	1324.8
147.5°	1350.5	1357.5	1356.3	1357.5	1358.6
150°	1386.6	1391.3	1390.1	1390.1	1391.3
152.5°	1416.9	1420.4	1418.1	1420.4	1419.3
155°	1444.9	1446.1	1442.6	1447.3	1443.8
157.5°	1469.4	1469.4	1464.8	1470.6	1464.8
160°	1490.4	1486.9	1485.7	1492.7	1485.7
162.5°	1509.1	1504.4	1503.2	1510.2	1502.1
165°	1524.2	1518.4	1518.4	1527.7	1517.2
167.5°	1537.1	1531.2	1530.1	1540.6	1528.9
170°	1547.6	1540.6	1541.7	1551.1	1539.4
172.5°	1554.6	1547.6	1548.7	1558.1	1545.2
175°	1559.2	1552.2	1553.4	1563.9	1549.9
177.5°	1562.7	1554.6	1556.9	1566.2	1552.2
180°	1559.2	1559.2	1559.2	1559.2	1559.2

(END OF REPORT)