

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026155

Luminaire Tested: S124RDIP-B1195D365UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026155
REPORT IS A COMBINATION OF REPORTS P999125 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D365UB35-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6132.0 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026155

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026155

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	79			
1	105	100	97	93	100	96	93	90	88	85	83	81	79	77	74	72	71	68			
2	96	88	82	77	91	85	79	74	78	73	69	71	68	65	66	63	60	57			
3	88	78	70	65	84	75	68	63	69	63	59	64	59	55	59	55	52	49			
4	81	69	61	55	77	67	59	54	62	56	51	57	52	48	53	48	45	42			
5	74	62	54	48	71	60	52	46	55	49	44	51	46	42	48	43	40	37			
6	69	56	48	42	65	54	46	41	50	44	39	47	41	37	43	39	35	33			
7	64	51	43	37	61	49	42	36	46	39	35	43	37	33	40	35	31	29			
8	59	47	39	33	57	45	38	32	42	36	31	39	34	30	37	32	28	26			
9	55	43	35	30	53	41	34	29	39	32	28	36	31	27	34	29	26	24			
10	52	39	32	27	50	38	31	26	36	30	25	34	28	24	31	27	23	22			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17116	17116	17116
5°	17118	16608	16610
10°	16973	16084	15893
15°	16740	15431	15046
20°	16434	14687	14082
25°	16052	13885	13139
30°	15679	13066	12082
35°	15268	12236	11047
40°	14780	11342	9985
45°	14321	10456	8933
50°	13800	9489	7864
55°	13237	8496	6762
60°	12612	7443	5673
65°	12008	6234	4624
70°	11150	4961	3534
75°	10052	3611	2471
80°	8394	2217	1777
85°	6316	1276	977

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14321 cd/sqm

TEST NUMBER: P1026155

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.4	3.2
10°-20°	550.3	9.0
20°-30°	794.5	13.0
30°-40°	900.5	14.7
40°-50°	869.4	14.2
50°-60°	722.8	11.8
60°-70°	498.9	8.1
70°-80°	252.1	4.1
80°-90°	65.0	1.1
90°-100°	30.1	0.5
100°-110°	90.1	1.5
110°-120°	153.1	2.5
120°-130°	201.9	3.3
130°-140°	226.8	3.7
140°-150°	222.9	3.6
150°-160°	187.5	3.1
160°-170°	124.8	2.0
170°-180°	43.7	0.7
0°-30°	1542.2	25.2
0°-40°	2442.7	39.8
0°-60°	4035.0	65.8
0°-90°	4851.0	79.1
90°-120°	273.3	4.5
90°-150°	925.1	15.1
90°-180°	1281.0	20.9
0°-180°	6132.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2099	2099	2099	2099	2099	
5°	2096	2089	2070	2086	2083	199
15°	1996	1982	1942	1938	1927	563
25°	1805	1776	1710	1683	1667	832
35°	1561	1509	1429	1374	1345	975
45°	1273	1213	1117	1038	1009	982
55°	964	900	796	712	682	863
65°	656	587	484	415	395	648
75°	349	289	214	177	167	368
85°	87	55	50	47	47	95
90°	1	5	8	10	11	7
95°	21	25	27	28	28	23
105°	83	84	85	86	87	88
115°	156	156	155	155	154	154
125°	227	227	226	226	225	202
135°	292	295	295	294	293	226
145°	355	357	357	357	356	222
155°	407	407	407	408	407	187
165°	443	442	441	444	442	125
175°	461	459	459	461	459	44
180°	462	462	462	462	462	

TEST NUMBER: P1026155

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2099.0	2099.0	2099.0	2099.0	2099.0
2.5°	2105.4	2099.0	2081.3	2099.0	2097.4
5°	2095.8	2089.4	2070.1	2086.2	2082.9
7.5°	2081.3	2074.9	2050.8	2062.1	2057.2
10°	2058.8	2050.8	2021.9	2028.3	2021.9
12.5°	2029.9	2020.3	1984.9	1988.1	1978.5
15°	1996.2	1981.7	1941.5	1938.3	1927.0
17.5°	1957.6	1936.7	1890.1	1882.0	1866.0
20°	1911.0	1890.1	1835.4	1822.6	1801.7
22.5°	1859.5	1835.4	1776.0	1755.1	1739.0
25°	1804.9	1776.0	1710.1	1682.7	1666.7
27.5°	1748.6	1713.3	1644.2	1612.0	1589.5
30°	1689.2	1649.0	1573.5	1533.3	1507.6
32.5°	1626.5	1579.9	1501.1	1452.9	1428.8
35°	1560.6	1509.2	1428.8	1374.2	1345.2
37.5°	1491.5	1438.5	1350.1	1290.6	1261.7
40°	1417.6	1364.5	1272.9	1205.4	1176.5
42.5°	1346.8	1290.6	1194.2	1125.0	1094.5
45°	1272.9	1213.4	1117.0	1038.3	1009.3
47.5°	1197.4	1136.3	1036.7	954.7	922.5
50°	1120.2	1057.5	954.7	874.3	843.8
52.5°	1041.5	980.4	874.3	792.4	760.2
55°	964.3	900.0	795.6	712.0	681.5
57.5°	888.8	821.3	718.4	633.2	610.7
60°	806.8	742.5	639.7	556.1	530.4
62.5°	732.9	665.4	559.3	483.8	464.5
65°	655.7	586.6	483.8	414.7	395.4
67.5°	575.4	509.5	413.1	352.0	329.5
70°	499.8	432.3	340.7	287.7	271.6
72.5°	419.5	360.0	274.8	231.4	217.0
75°	348.8	289.3	213.8	176.8	167.1
77.5°	274.8	223.4	159.1	133.4	130.2
80°	204.1	157.5	109.3	104.5	102.9
82.5°	143.0	101.3	78.8	75.5	73.9
85°	86.8	54.6	49.8	46.6	46.6
87.5°	37.0	24.1	22.5	20.9	22.5
90°	1.1	5.0	7.9	10.0	10.7
92.5°	9.3	13.9	15.7	16.8	17.1
95°	21.4	24.6	27.1	28.2	28.2
97.5°	34.3	37.1	40.0	41.4	41.4
100°	50.0	51.4	54.6	55.3	55.3
102.5°	66.4	66.8	69.6	70.7	71.1
105°	83.2	83.6	85.0	86.1	87.1
107.5°	100.7	101.0	101.4	102.8	102.5
110°	118.5	119.3	118.9	118.2	119.3

TEST NUMBER: P1026155

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	137.1	137.1	136.4	136.4	136.4
115°	155.7	155.7	155.0	154.6	154.3
117.5°	173.2	173.2	172.8	171.7	170.7
120°	190.7	192.1	191.0	189.2	190.0
122.5°	208.9	209.2	208.9	207.8	206.0
125°	226.7	226.7	226.4	225.7	225.0
127.5°	242.8	243.9	243.2	242.4	242.1
130°	259.9	261.0	261.0	260.3	258.9
132.5°	277.4	278.2	277.8	277.1	276.7
135°	292.4	294.6	294.6	293.9	292.8
137.5°	309.2	310.3	311.0	309.9	310.3
140°	326.0	326.7	326.7	326.4	326.0
142.5°	341.4	342.1	341.7	341.7	341.7
145°	355.3	356.7	357.1	356.7	355.6
147.5°	369.6	371.3	371.0	370.6	370.3
150°	382.4	383.8	383.8	383.8	383.5
152.5°	394.6	395.3	395.6	396.7	395.6
155°	407.1	407.1	406.7	408.1	406.7
157.5°	417.8	417.1	417.1	418.1	417.1
160°	427.1	426.7	426.3	427.4	425.6
162.5°	435.6	434.6	434.2	436.3	434.6
165°	443.1	442.0	441.3	443.5	442.0
167.5°	449.2	447.8	447.8	449.9	447.8
170°	454.2	452.4	452.8	454.9	452.4
172.5°	457.8	456.3	456.3	458.8	456.3
175°	461.0	459.2	458.8	461.3	458.8
177.5°	462.4	460.6	460.6	463.1	460.3
180°	461.7	461.7	461.7	461.7	461.7

(END OF REPORT)