

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026168

Luminaire Tested: S124RDIP-B1195D365UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026168
REPORT IS A COMBINATION OF REPORTS P999138 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D365UB50-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5914.5 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026168

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026168

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82
1	105	100	96	93	100	96	93	89	88	85	83	80	78	76	74	72	70
2	96	88	82	77	91	84	79	74	78	73	69	71	68	64	65	62	60
3	88	78	70	64	83	75	68	62	69	63	59	63	59	55	58	55	52
4	80	69	61	55	77	67	59	53	61	55	50	57	52	48	52	48	45
5	74	62	54	48	71	60	52	46	55	49	44	51	46	42	47	43	39
6	68	56	48	42	65	54	46	41	50	44	39	46	41	37	43	38	35
7	64	51	43	37	61	49	41	36	46	39	34	42	37	33	39	35	31
8	59	46	38	33	56	45	37	32	42	35	31	39	33	29	36	32	28
9	55	43	35	30	53	41	34	29	39	32	28	36	31	27	34	29	25
10	52	39	32	27	50	38	31	26	36	30	25	33	28	24	31	27	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16390	16390	16390
5°	16391	15903	15905
10°	16252	15401	15218
15°	16029	14776	14408
20°	15735	14064	13484
25°	15370	13295	12581
30°	15013	12511	11568
35°	14620	11716	10578
40°	14151	10860	9561
45°	13713	10012	8554
50°	13213	9085	7530
55°	12675	8135	6475
60°	12077	7126	5432
65°	11499	5969	4428
70°	10677	4752	3384
75°	9625	3457	2367
80°	8037	2121	1701
85°	6047	1222	935

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13713 cd/sqm

TEST NUMBER: P1026168

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	3.2
10°-20°	527.0	8.9
20°-30°	760.8	12.9
30°-40°	862.2	14.6
40°-50°	832.5	14.1
50°-60°	692.1	11.7
60°-70°	477.7	8.1
70°-80°	241.4	4.1
80°-90°	62.0	1.0
90°-100°	129.3	2.2
100°-110°	262.9	4.4
110°-120°	234.3	4.0
120°-130°	196.8	3.3
130°-140°	164.2	2.8
140°-150°	125.4	2.1
150°-160°	88.2	1.5
160°-170°	51.9	0.9
170°-180°	16.9	0.3
0°-30°	1476.7	25.0
0°-40°	2339.0	39.5
0°-60°	3863.6	65.3
0°-90°	4644.7	78.5
90°-120°	626.5	10.6
90°-150°	1113.0	18.8
90°-180°	1270.0	21.5
0°-180°	5914.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2010	2010	2010	2010	2010	
5°	2007	2001	1982	1998	1994	190
15°	1911	1898	1859	1856	1845	539
25°	1728	1700	1637	1611	1596	796
35°	1494	1445	1368	1316	1288	934
45°	1219	1162	1070	994	966	940
55°	923	862	762	682	652	826
65°	628	562	463	397	379	620
75°	334	277	205	169	160	352
85°	83	52	48	45	45	91
90°	0	3	6	7	7	6
95°	11	36	279	138	83	12
105°	40	58	224	483	481	43
115°	70	88	200	384	462	70
125°	98	117	199	327	368	87
135°	117	139	197	290	330	90
145°	134	154	196	245	269	84
155°	153	165	191	216	225	70
165°	166	172	183	194	197	47
175°	174	174	175	178	177	16
180°	174	174	174	174	174	

TEST NUMBER: P1026168

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2009.9	2009.9	2009.9	2009.9	2009.9
2.5°	2016.0	2009.9	1992.9	2009.9	2008.3
5°	2006.8	2000.6	1982.2	1997.6	1994.5
7.5°	1992.9	1986.8	1963.7	1974.5	1969.8
10°	1971.4	1963.7	1936.0	1942.1	1936.0
12.5°	1943.7	1934.5	1900.6	1903.7	1894.4
15°	1911.4	1897.5	1859.0	1856.0	1845.2
17.5°	1874.4	1854.4	1809.8	1802.1	1786.7
20°	1829.8	1809.8	1757.5	1745.2	1725.2
22.5°	1780.6	1757.5	1700.5	1680.5	1665.1
25°	1728.2	1700.5	1637.4	1611.3	1595.9
27.5°	1674.4	1640.5	1574.3	1543.6	1522.0
30°	1617.4	1579.0	1506.6	1468.2	1443.5
32.5°	1557.4	1512.8	1437.4	1391.2	1368.1
35°	1494.3	1445.1	1368.1	1315.8	1288.1
37.5°	1428.1	1377.4	1292.7	1235.8	1208.1
40°	1357.3	1306.6	1218.8	1154.2	1126.5
42.5°	1289.6	1235.8	1143.4	1077.3	1048.0
45°	1218.8	1161.9	1069.6	994.2	966.5
47.5°	1146.5	1088.0	992.6	914.1	883.4
50°	1072.6	1012.6	914.1	837.2	807.9
52.5°	997.2	938.8	837.2	758.7	727.9
55°	923.4	861.8	761.8	681.8	652.5
57.5°	851.0	786.4	687.9	606.3	584.8
60°	772.6	711.0	612.5	532.5	507.9
62.5°	701.8	637.1	535.6	463.2	444.8
65°	627.9	561.7	463.2	397.0	378.6
67.5°	550.9	487.8	395.5	337.0	315.5
70°	478.6	414.0	326.3	275.5	260.1
72.5°	401.7	344.7	263.2	221.6	207.8
75°	334.0	277.0	204.7	169.3	160.1
77.5°	263.2	213.9	152.4	127.7	124.7
80°	195.4	150.8	104.6	100.0	98.5
82.5°	137.0	97.0	75.4	72.3	70.8
85°	83.1	52.3	47.7	44.6	44.6
87.5°	35.4	23.1	21.5	20.0	21.5
90°	0.3	2.7	6.2	6.8	7.2
92.5°	4.8	26.4	134.0	44.2	31.1
95°	11.3	35.6	278.6	138.0	83.4
97.5°	18.8	39.4	298.1	281.6	200.3
100°	26.0	44.4	274.9	389.8	313.5
102.5°	32.8	50.6	245.8	457.4	411.9
105°	40.0	58.0	224.3	482.9	481.0
107.5°	47.9	65.4	210.2	475.2	513.8
110°	55.7	73.0	203.7	447.8	514.5



TEST NUMBER: P1026168

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	63.2	80.5	200.7	414.3	494.3
115°	70.4	88.4	200.0	384.2	461.8
117.5°	77.9	95.7	199.6	360.6	430.1
120°	85.5	102.9	199.6	344.8	404.1
122.5°	92.3	109.9	199.3	334.4	383.6
125°	98.1	116.6	199.0	327.0	368.5
127.5°	103.6	122.7	198.3	320.0	358.9
130°	108.0	128.8	197.9	311.6	350.7
132.5°	112.5	133.8	197.6	301.6	341.5
135°	116.6	138.8	197.3	290.2	329.5
137.5°	120.7	143.0	197.3	278.0	315.5
140°	125.1	147.0	196.9	266.0	300.1
142.5°	129.9	150.6	196.9	254.8	283.7
145°	134.3	153.8	196.2	244.8	269.0
147.5°	139.5	156.9	195.2	236.4	255.4
150°	144.3	159.8	194.2	228.7	244.1
152.5°	148.7	162.6	192.5	222.2	233.8
155°	152.8	165.0	190.8	216.0	225.3
157.5°	156.9	167.1	189.0	210.2	217.4
160°	160.7	169.0	187.0	204.4	210.2
162.5°	164.1	170.6	184.9	198.8	203.4
165°	166.5	171.6	182.9	193.6	196.6
167.5°	169.2	172.4	180.8	189.2	191.1
170°	170.9	173.1	178.8	184.8	186.0
172.5°	172.6	173.6	176.7	180.8	180.8
175°	173.7	174.0	175.4	177.8	177.1
177.5°	174.3	174.0	174.3	175.6	174.3
180°	174.0	174.0	174.0	174.0	174.0

(END OF REPORT)