

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025031

Luminaire Tested: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025031
REPORT IS A COMBINATION OF REPORTS P995421 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8918.0 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025031

CATALOG NUMBER: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1025031

CATALOG NUMBER: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65
1	100	96	92	89	93	90	86	83	78	76	73	67	66	64	58	56	55
2	91	84	78	73	85	79	73	69	69	65	61	60	56	54	51	49	47
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	45	43	40
4	77	66	58	52	71	62	55	49	54	49	44	47	43	40	41	38	35
5	70	59	51	45	66	55	48	43	49	43	38	43	38	34	37	33	31
6	65	53	45	39	61	50	43	37	44	38	34	39	34	30	34	30	27
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	31	27	24
8	56	44	36	30	52	41	34	29	37	31	27	32	28	24	28	24	22
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20
10	49	37	29	25	46	35	28	24	31	25	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15615	15615	15615	15615
5°	15576	17914	15667	13460
10°	15459	20900	15577	11809
15°	15273	24094	15380	10567
20°	15076	26126	15185	9474
25°	14787	25827	14928	8667
30°	14505	21347	14681	8251
35°	14109	15908	14264	8000
40°	13647	11984	13778	7877
45°	12941	9618	13102	7709
50°	12097	8103	12274	7630
55°	11106	7052	11281	7540
60°	10144	6211	10441	7415
65°	9239	5343	9327	7106
70°	8177	4396	8353	6543
75°	7132	3378	7086	5559
80°	5610	2220	5548	4220
85°	3697	998	3464	2461

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 20191 cd/sqm

TEST NUMBER: P1025031

CATALOG NUMBER: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.4	2.1
10°-20°	575.2	6.5
20°-30°	913.8	10.2
30°-40°	1015.4	11.4
40°-50°	923.4	10.4
50°-60°	754.6	8.5
60°-70°	538.6	6.0
70°-80°	296.4	3.3
80°-90°	82.1	0.9
90°-100°	361.4	4.1
100°-110°	754.6	8.5
110°-120°	670.7	7.5
120°-130°	564.6	6.3
130°-140°	471.1	5.3
140°-150°	359.7	4.0
150°-160°	252.9	2.8
160°-170°	148.7	1.7
170°-180°	48.4	0.5
0°-30°	1675.4	18.8
0°-40°	2690.8	30.2
0°-60°	4368.8	49.0
0°-90°	5286.0	59.3
90°-120°	1786.7	20.0
90°-150°	3182.1	35.7
90°-180°	3632.0	40.7
0°-180°	8918.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1915	1915	1915	1915	1915	
5°	1907	2246	1918	1688	1907	181
15°	1821	3086	1834	1353	1821	514
25°	1663	3276	1678	1099	1663	766
35°	1442	1937	1458	974	1442	901
45°	1150	1087	1164	871	1150	887
55°	809	711	822	760	809	728
65°	504	457	509	608	504	498
75°	248	228	246	376	248	260
85°	51	48	48	117	51	59
90°	1	21	1	21	1	5
95°	32	239	32	239	32	35
105°	115	1378	115	1378	115	122
115°	202	1324	202	1324	202	200
125°	281	1056	281	1056	281	251
135°	334	944	334	944	334	258
145°	385	771	385	771	385	242
155°	438	646	438	646	438	202
165°	477	563	477	563	477	135
175°	498	508	498	508	498	47
180°	499	499	499	499	499	

TEST NUMBER: P1025031

CATALOG NUMBER: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	1914.9	1933.9	1941.9	1948.2	1968.8	1975.2	1976.8	1986.3	1994.2	1995.8	1995.8
5°	1907.0	1937.1	1960.9	1983.1	2016.4	2030.7	2048.2	2067.2	2092.6	2108.4	2116.4
7.5°	1894.3	1938.7	1975.2	2013.3	2059.3	2087.8	2103.7	2154.4	2189.4	2217.9	2252.8
10°	1875.2	1932.3	1984.7	2040.2	2105.3	2140.2	2175.1	2236.9	2286.1	2341.7	2386.1
12.5°	1846.7	1921.2	1984.7	2062.4	2143.3	2184.6	2225.8	2333.7	2390.8	2440.0	2519.3
15°	1821.3	1895.9	1986.3	2065.6	2165.6	2227.4	2287.7	2357.5	2447.9	2554.2	2630.4
17.5°	1792.7	1886.3	1970.4	2081.5	2192.5	2251.2	2300.4	2408.3	2535.2	2639.9	2709.7
20°	1753.1	1848.3	1959.3	2076.7	2208.4	2254.4	2319.4	2463.8	2578.0	2681.2	2795.4
22.5°	1707.1	1818.1	1935.5	2048.2	2184.6	2281.4	2352.8	2479.7	2617.7	2736.7	2865.2
25°	1662.6	1783.2	1886.3	2040.2	2184.6	2249.6	2330.5	2481.3	2632.0	2776.4	2908.0
27.5°	1615.0	1727.7	1867.3	1989.5	2152.9	2224.3	2311.5	2476.5	2636.7	2781.1	2922.3
30°	1562.7	1683.3	1799.1	1943.4	2102.1	2194.1	2275.0	2454.3	2617.7	2768.4	2900.1
32.5°	1504.0	1618.2	1742.0	1878.4	2045.0	2138.6	2240.1	2424.2	2598.7	2728.8	2830.3
35°	1442.1	1557.9	1665.8	1805.4	1976.8	2070.4	2168.7	2371.8	2544.7	2651.0	2709.7
37.5°	1373.9	1483.4	1589.7	1727.7	1899.0	1999.0	2098.9	2295.6	2459.1	2547.9	2532.0
40°	1308.9	1407.2	1505.6	1635.7	1814.9	1921.2	2008.5	2206.8	2349.6	2387.7	2335.3
42.5°	1234.3	1318.4	1413.6	1546.8	1721.3	1821.3	1930.8	2111.6	2217.9	2202.0	2113.2
45°	1150.2	1224.8	1320.0	1445.3	1623.0	1726.1	1818.1	1989.5	2067.2	2027.5	1865.7
47.5°	1069.3	1142.3	1220.0	1345.3	1518.3	1605.5	1699.1	1853.0	1897.4	1813.4	1651.5
50°	982.0	1042.3	1123.2	1242.2	1404.0	1496.1	1573.8	1697.5	1713.4	1610.3	1442.1
52.5°	898.0	948.7	1026.5	1143.9	1294.6	1367.6	1443.7	1553.2	1540.5	1434.2	1272.4
55°	809.1	856.7	928.1	1036.0	1169.2	1239.0	1304.1	1400.9	1373.9	1264.4	1123.2
57.5°	734.5	767.9	837.7	937.6	1047.1	1123.2	1178.8	1254.9	1213.7	1104.2	972.5
60°	648.9	690.1	748.8	829.7	937.6	988.4	1037.6	1088.3	1059.8	955.1	837.7
62.5°	571.1	602.9	653.6	731.4	815.5	861.5	913.8	945.5	917.0	820.2	721.9
65°	504.5	529.9	569.5	633.0	713.9	752.0	782.1	812.3	788.5	698.1	626.7
67.5°	431.5	453.7	487.1	537.8	606.0	633.0	661.6	682.2	655.2	594.9	525.1
70°	366.5	382.3	414.1	452.1	499.7	525.1	548.9	569.5	545.8	495.0	442.6
72.5°	299.8	312.5	341.1	368.1	410.9	428.4	445.8	461.7	453.7	406.1	363.3
75°	247.5	252.3	271.3	293.5	320.5	339.5	352.2	361.7	355.4	317.3	290.3
77.5°	187.2	193.6	207.8	225.3	249.1	260.2	268.1	277.6	269.7	239.6	220.5
80°	136.4	138.0	146.0	161.8	177.7	179.3	187.2	199.9	195.1	174.5	160.2
82.5°	87.3	92.0	95.2	104.7	115.8	119.0	123.7	126.9	125.3	112.6	107.9
85°	50.8	50.8	53.9	60.3	63.5	68.2	69.8	71.4	74.6	66.6	61.9
87.5°	22.2	23.8	23.8	25.4	28.6	28.6	30.1	31.7	33.3	31.7	27.0
90°	1.0	2.9	5.9	6.9	7.8	7.8	7.8	13.7	13.7	15.7	17.6
92.5°	13.7	19.6	30.4	45.1	62.7	75.4	88.2	148.9	244.0	336.0	384.1
95°	32.3	35.3	45.1	57.8	81.3	101.9	122.5	207.7	368.4	602.5	798.5
97.5°	53.9	53.9	62.7	74.5	95.0	112.6	130.3	197.9	336.0	577.1	854.3
100°	74.5	74.5	81.3	93.1	111.7	127.4	143.0	200.8	311.6	511.4	787.7
102.5°	94.1	96.0	101.9	112.7	130.3	145.0	159.7	210.6	304.7	467.3	704.4
105°	114.6	117.6	122.5	134.2	151.9	166.1	180.3	227.3	308.6	445.8	642.7
107.5°	137.2	139.1	144.0	156.8	173.4	187.6	201.8	244.9	320.4	439.9	602.5
110°	159.7	161.7	166.6	178.3	195.9	209.2	222.4	265.5	334.1	441.9	583.9

TEST NUMBER: P1025031

CATALOG NUMBER: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	181.3	183.2	189.1	199.9	217.5	230.8	244.0	285.1	348.8	447.7	575.1
115°	201.8	204.8	211.6	221.4	240.0	253.2	266.5	305.7	364.5	455.6	573.1
117.5°	223.4	226.3	232.2	243.0	260.6	274.3	288.0	325.3	380.1	463.4	572.2
120°	244.9	246.9	253.8	264.5	281.2	294.9	308.6	345.8	396.8	472.2	572.2
122.5°	264.5	266.5	273.3	283.1	301.8	315.0	328.2	365.4	412.5	481.0	571.2
125°	281.2	285.1	291.0	301.8	320.4	334.1	347.8	383.1	428.1	489.9	570.2
127.5°	296.9	299.8	306.7	318.4	338.0	351.7	365.4	399.7	441.9	496.7	568.2
130°	309.6	313.5	321.4	336.0	354.7	368.9	383.1	416.4	454.6	504.6	567.3
132.5°	322.3	325.3	336.0	349.8	370.3	383.6	396.8	430.1	467.3	511.4	566.3
135°	334.1	338.0	347.8	364.5	385.0	397.8	410.5	442.8	478.1	518.3	565.3
137.5°	345.8	349.8	360.5	376.2	397.8	410.0	422.3	452.6	485.9	522.2	565.3
140°	358.6	361.5	372.3	389.0	409.5	421.2	433.0	462.4	493.8	527.1	564.3
142.5°	372.3	375.2	385.0	400.7	420.3	431.6	442.8	471.3	499.7	531.0	564.3
145°	385.0	388.0	397.8	411.5	430.1	440.9	451.7	477.1	503.6	532.0	562.4
147.5°	399.7	400.7	409.5	424.2	439.9	449.7	459.5	484.0	507.5	533.0	559.4
150°	413.4	414.4	422.3	434.0	448.7	458.0	467.3	488.9	510.4	533.0	556.5
152.5°	426.2	426.2	434.0	444.8	457.5	465.8	474.2	492.8	512.4	531.0	551.6
155°	437.9	438.9	444.8	454.6	465.4	472.8	480.1	496.7	513.4	529.1	546.7
157.5°	449.7	449.7	455.6	463.4	473.2	479.1	485.0	499.7	513.4	527.1	541.8
160°	460.5	460.5	464.4	471.3	479.1	484.5	489.9	501.6	513.4	524.2	535.9
162.5°	470.3	469.3	472.2	478.1	485.0	488.9	492.8	503.6	513.4	521.2	530.0
165°	477.1	477.1	479.1	484.0	488.9	491.8	494.8	503.6	511.4	517.3	524.2
167.5°	485.0	484.0	485.0	488.9	491.8	494.2	496.7	503.6	509.5	513.4	518.3
170°	489.9	488.9	489.9	492.8	494.8	496.2	497.7	502.6	507.5	509.5	512.4
172.5°	494.8	493.8	493.8	495.7	496.7	497.7	498.7	501.6	505.5	505.5	506.5
175°	497.7	496.7	496.7	497.7	498.7	498.7	498.7	500.6	503.6	502.6	502.6
177.5°	499.7	498.7	497.7	498.7	498.7	498.7	498.7	499.7	501.6	499.7	499.7
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1025031

CATALOG NUMBER: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	2000.6	2029.1	2041.8	2045.0	2062.4	2051.3	2056.1	2054.5	2067.2	2068.8	2068.8
5°	2146.5	2179.8	2190.9	2206.8	2230.6	2236.9	2232.2	2241.7	2259.2	2246.5	2265.5
7.5°	2300.4	2336.9	2362.3	2397.2	2405.1	2425.7	2438.4	2449.5	2452.7	2454.3	2457.5
10°	2443.2	2489.2	2524.1	2582.8	2595.5	2606.6	2662.1	2639.9	2668.5	2659.0	2662.1
12.5°	2559.0	2649.4	2678.0	2776.4	2785.9	2823.9	2820.8	2855.7	2862.0	2874.7	2862.0
15°	2711.3	2816.0	2862.0	2917.5	2949.3	2993.7	3001.6	3049.2	3068.3	3085.7	3068.3
17.5°	2850.9	2906.4	3023.8	3068.3	3088.9	3112.7	3173.0	3190.4	3219.0	3207.9	3239.6
20°	2920.7	3000.0	3123.8	3199.9	3231.7	3253.9	3304.7	3331.6	3342.7	3342.7	3345.9
22.5°	2982.6	3096.8	3188.8	3276.1	3304.7	3320.5	3350.7	3371.3	3376.0	3379.2	3382.4
25°	3038.1	3141.2	3215.8	3265.0	3276.1	3276.1	3293.5	3280.9	3260.2	3276.1	3285.6
27.5°	3038.1	3111.1	3144.4	3161.9	3161.9	3119.0	3093.6	3041.3	2996.9	2984.2	3012.7
30°	2987.4	3020.7	2974.7	2931.8	2898.5	2870.0	2770.0	2690.7	2674.8	2663.7	2706.5
32.5°	2870.0	2827.1	2736.7	2612.9	2563.8	2498.7	2421.0	2360.7	2324.2	2311.5	2302.0
35°	2662.1	2551.1	2433.7	2267.1	2232.2	2149.7	2043.4	1999.0	1938.7	1937.1	1957.7
37.5°	2435.3	2263.9	2137.0	1978.3	1929.2	1841.9	1742.0	1696.0	1654.7	1623.0	1661.1
40°	2170.3	2021.2	1827.6	1697.5	1627.7	1581.7	1497.6	1446.9	1427.8	1412.0	1435.8
42.5°	1922.8	1759.4	1608.7	1475.4	1418.3	1366.0	1310.4	1261.3	1247.0	1245.4	1262.8
45°	1676.9	1516.7	1377.1	1262.8	1226.4	1194.6	1140.7	1126.4	1102.6	1086.7	1094.7
47.5°	1480.2	1315.2	1199.4	1112.1	1080.4	1053.4	1018.5	994.7	974.1	967.8	977.3
50°	1286.6	1175.6	1056.6	983.6	959.8	934.4	907.5	885.3	875.7	869.4	875.7
52.5°	1131.2	1012.2	931.3	872.6	848.8	829.7	810.7	801.2	788.5	791.7	798.0
55°	991.6	886.8	818.6	775.8	761.5	753.6	729.8	718.7	713.9	710.7	713.9
57.5°	859.9	783.7	733.0	696.5	677.4	672.7	653.6	653.6	648.9	644.1	645.7
60°	755.2	690.1	640.9	612.4	609.2	601.3	588.6	587.0	575.9	580.7	582.2
62.5°	648.9	596.5	563.2	545.8	534.6	531.5	523.5	522.0	517.2	518.8	515.6
65°	564.8	522.0	488.6	474.4	469.6	468.0	461.7	456.9	453.7	456.9	453.7
67.5°	480.7	452.1	426.8	412.5	406.1	404.6	399.8	396.6	398.2	393.4	396.6
70°	401.4	372.8	357.0	349.0	345.9	341.1	341.1	341.1	341.1	337.9	336.3
72.5°	337.9	309.4	298.3	293.5	290.3	288.7	284.0	285.6	284.0	282.4	288.7
75°	268.1	250.7	239.6	234.8	238.0	233.2	228.5	231.6	226.9	228.5	234.8
77.5°	203.1	195.1	188.8	185.6	182.4	179.3	179.3	176.1	176.1	176.1	176.1
80°	147.5	146.0	134.9	133.3	133.3	130.1	130.1	130.1	130.1	128.5	130.1
82.5°	98.4	96.8	93.6	92.0	88.8	90.4	90.4	87.3	87.3	85.7	87.3
85°	57.1	57.1	53.9	52.4	50.8	52.4	49.2	47.6	49.2	47.6	49.2
87.5°	27.0	23.8	25.4	23.8	20.6	22.2	19.0	20.6	19.0	17.5	20.6
90°	16.7	17.6	18.6	19.6	19.6	19.6	20.6	21.6	20.6	20.6	20.6
92.5°	319.4	236.1	176.4	139.1	126.8	114.6	99.9	93.1	89.2	89.2	89.2
95°	821.0	726.0	574.1	442.8	395.3	347.8	299.8	269.4	251.8	239.1	251.8
97.5°	1029.7	1045.4	969.9	862.2	807.3	752.4	685.8	627.0	597.6	574.1	597.6
100°	1038.5	1181.6	1201.2	1153.1	1116.8	1080.6	995.4	935.6	906.3	898.4	906.3
102.5°	965.0	1174.7	1291.3	1320.7	1310.9	1301.1	1257.0	1217.8	1186.5	1180.6	1186.5
105°	872.9	1097.3	1266.8	1363.8	1383.9	1404.0	1405.9	1398.1	1384.4	1378.5	1384.4
107.5°	797.5	1002.3	1185.5	1320.7	1361.8	1403.0	1446.1	1463.7	1471.6	1472.5	1471.6
110°	743.6	918.0	1087.5	1229.6	1283.4	1337.3	1406.9	1448.0	1465.7	1474.5	1465.7

TEST NUMBER: P1025031

CATALOG NUMBER: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	713.2	856.3	1001.3	1133.5	1187.4	1241.3	1322.6	1374.6	1401.0	1416.7	1401.0
115°	696.6	819.1	939.6	1054.2	1101.2	1148.2	1225.6	1284.4	1315.8	1323.6	1315.8
117.5°	687.8	797.5	899.4	992.5	1033.6	1074.8	1143.3	1194.3	1227.6	1232.5	1227.6
120°	680.9	783.8	874.9	953.3	988.0	1022.8	1078.7	1121.8	1147.3	1158.0	1147.3
122.5°	673.1	772.0	859.2	928.8	958.2	987.6	1032.6	1067.9	1088.5	1099.3	1088.5
125°	664.3	758.3	842.6	910.2	937.2	964.1	1003.2	1031.7	1050.3	1056.2	1050.3
127.5°	652.5	742.6	824.0	891.6	917.0	942.5	981.7	1007.2	1022.8	1028.7	1022.8
130°	641.7	723.0	800.4	867.1	893.0	919.0	959.2	983.7	999.3	1005.2	999.3
132.5°	631.9	702.5	774.0	838.7	864.6	890.6	929.8	958.2	972.9	978.8	972.9
135°	622.1	683.9	747.5	807.3	831.8	856.3	895.5	922.9	938.6	944.5	938.6
137.5°	613.3	666.2	722.1	774.0	796.6	819.1	856.3	884.7	897.4	904.3	897.4
140°	606.5	651.5	697.6	741.7	762.2	782.8	817.1	838.7	852.4	860.2	852.4
142.5°	600.6	637.8	677.0	713.2	730.4	747.5	776.9	796.5	808.3	813.2	808.3
145°	593.7	625.1	658.4	687.8	701.5	715.2	739.7	756.4	766.2	771.0	766.2
147.5°	587.8	614.3	641.7	666.2	677.5	688.8	707.4	722.1	729.9	731.9	729.9
150°	581.0	604.5	627.0	646.6	655.4	664.3	679.9	692.7	698.5	699.5	698.5
152.5°	573.1	593.7	612.3	630.0	636.8	643.7	656.4	666.2	669.2	670.1	669.2
155°	565.3	582.9	598.6	613.3	619.2	625.1	634.9	642.7	645.6	645.6	645.6
157.5°	557.5	571.2	584.9	597.6	602.5	607.4	615.3	621.1	623.1	623.1	623.1
160°	548.6	560.4	571.2	582.0	585.9	589.8	595.7	601.6	602.5	602.5	602.5
162.5°	540.8	549.6	558.4	566.3	569.7	573.1	577.1	582.9	583.9	582.9	583.9
165°	532.0	539.8	545.7	552.6	555.0	557.5	561.4	565.3	564.3	563.3	564.3
167.5°	524.2	530.0	534.9	540.8	542.3	543.8	545.7	548.6	548.6	547.7	548.6
170°	516.3	521.2	524.2	528.1	529.6	531.0	533.0	534.0	533.0	533.0	533.0
172.5°	509.5	513.4	515.3	517.3	518.3	519.3	520.2	521.2	520.2	518.3	520.2
175°	504.6	506.5	507.5	509.5	509.5	509.5	509.5	511.4	509.5	507.5	509.5
177.5°	500.6	501.6	502.6	502.6	503.1	503.6	502.6	503.6	501.6	499.7	501.6
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1025031

CATALOG NUMBER: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	2065.6	2060.8	2054.5	2054.5	2046.6	2046.6	2033.9	2011.7	1992.6	1986.3	1989.5
5°	2241.7	2243.3	2233.8	2225.8	2211.6	2200.5	2179.8	2140.2	2127.5	2102.1	2084.6
7.5°	2443.2	2436.8	2419.4	2406.7	2403.5	2378.1	2333.7	2286.1	2248.1	2222.7	2186.2
10°	2670.1	2644.7	2619.3	2611.4	2592.3	2549.5	2498.7	2446.4	2394.0	2338.5	2276.6
12.5°	2860.4	2811.3	2809.7	2790.6	2754.1	2730.3	2670.1	2595.5	2505.1	2443.2	2373.4
15°	3065.1	3019.1	2981.0	2946.1	2928.7	2858.8	2808.1	2714.5	2606.6	2540.0	2492.4
17.5°	3211.0	3190.4	3125.4	3109.5	3085.7	3004.8	2923.9	2831.9	2738.3	2644.7	2516.2
20°	3328.4	3315.8	3272.9	3250.7	3212.6	3149.2	3050.8	2944.5	2836.6	2703.4	2582.8
22.5°	3379.2	3363.4	3328.4	3309.4	3285.6	3231.7	3147.6	3027.0	2885.8	2766.8	2638.3
25°	3279.3	3307.8	3298.3	3290.4	3280.9	3249.1	3185.7	3079.4	2941.3	2806.5	2646.3
27.5°	3054.0	3103.2	3150.8	3157.1	3173.0	3185.7	3160.3	3084.1	2968.3	2825.5	2649.4
30°	2751.0	2773.2	2870.0	2898.5	2920.7	3001.6	3049.2	3030.2	2941.3	2812.8	2651.0
32.5°	2362.3	2421.0	2519.3	2587.6	2647.8	2738.3	2862.0	2911.2	2879.5	2774.8	2614.5
35°	1994.2	2064.0	2178.2	2265.5	2325.8	2454.3	2600.3	2706.5	2746.2	2693.9	2551.1
37.5°	1692.8	1776.9	1878.4	1911.7	1981.5	2140.2	2341.7	2489.2	2586.0	2590.7	2479.7
40°	1465.9	1508.7	1589.7	1640.4	1708.6	1841.9	2038.6	2233.8	2379.7	2428.9	2370.2
42.5°	1273.9	1307.3	1367.6	1429.4	1491.3	1592.8	1773.7	1956.1	2152.9	2251.2	2249.6
45°	1121.6	1156.5	1197.8	1248.6	1291.4	1400.9	1543.7	1730.9	1900.6	2052.9	2091.0
47.5°	988.4	1018.5	1069.3	1091.5	1120.1	1223.2	1346.9	1521.4	1697.5	1872.1	1916.5
50°	890.0	915.4	950.3	964.6	996.3	1072.5	1174.0	1315.2	1510.3	1670.6	1753.1
52.5°	801.2	820.2	847.2	858.3	880.5	937.6	1029.6	1140.7	1302.5	1467.5	1583.3
55°	725.0	737.7	756.8	769.4	785.3	836.1	904.3	1004.2	1143.9	1286.6	1399.3
57.5°	653.6	663.2	682.2	688.5	701.2	740.9	788.5	872.6	1001.1	1128.0	1237.5
60°	587.0	593.3	604.5	618.7	628.2	655.2	699.6	769.4	872.6	988.4	1077.2
62.5°	523.5	533.1	536.2	542.6	550.5	575.9	610.8	661.6	752.0	847.2	940.8
65°	458.5	466.4	472.8	474.4	482.3	501.3	533.1	577.5	636.2	718.7	805.9
67.5°	398.2	403.0	406.1	412.5	420.4	429.9	455.3	488.6	542.6	609.2	679.0
70°	342.7	342.7	347.4	349.0	358.5	369.7	380.8	412.5	460.1	514.0	561.6
72.5°	282.4	290.3	288.7	296.7	295.1	303.0	317.3	337.9	372.8	415.7	461.7
75°	230.0	234.8	234.8	234.8	238.0	244.3	252.3	271.3	298.3	333.2	360.1
77.5°	179.3	182.4	182.4	182.4	184.0	190.4	198.3	211.0	230.0	250.7	266.5
80°	128.5	131.7	131.7	134.9	134.9	136.4	144.4	150.7	160.2	176.1	192.0
82.5°	87.3	88.8	92.0	92.0	90.4	93.6	95.2	101.5	111.1	114.2	125.3
85°	47.6	49.2	50.8	50.8	52.4	55.5	53.9	60.3	60.3	66.6	69.8
87.5°	19.0	22.2	22.2	20.6	22.2	22.2	22.2	25.4	27.0	28.6	27.0
90°	21.6	20.6	19.6	19.6	19.6	18.6	17.6	16.7	17.6	15.7	13.7
92.5°	93.1	99.9	114.6	126.8	139.1	176.4	236.1	319.4	384.1	336.0	244.0
95°	269.4	299.8	347.8	395.3	442.8	574.1	726.0	821.0	798.5	602.5	368.4
97.5°	627.0	685.8	752.4	807.3	862.2	969.9	1045.4	1029.7	854.3	577.1	336.0
100°	935.6	995.4	1080.6	1116.8	1153.1	1201.2	1181.6	1038.5	787.7	511.4	311.6
102.5°	1217.8	1257.0	1301.1	1310.9	1320.7	1291.3	1174.7	965.0	704.4	467.3	304.7
105°	1398.1	1405.9	1404.0	1383.9	1363.8	1266.8	1097.3	872.9	642.7	445.8	308.6
107.5°	1463.7	1446.1	1403.0	1361.8	1320.7	1185.5	1002.3	797.5	602.5	439.9	320.4
110°	1448.0	1406.9	1337.3	1283.4	1229.6	1087.5	918.0	743.6	583.9	441.9	334.1

TEST NUMBER: P1025031

CATALOG NUMBER: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1374.6	1322.6	1241.3	1187.4	1133.5	1001.3	856.3	713.2	575.1	447.7	348.8
115°	1284.4	1225.6	1148.2	1101.2	1054.2	939.6	819.1	696.6	573.1	455.6	364.5
117.5°	1194.3	1143.3	1074.8	1033.6	992.5	899.4	797.5	687.8	572.2	463.4	380.1
120°	1121.8	1078.7	1022.8	988.0	953.3	874.9	783.8	680.9	572.2	472.2	396.8
122.5°	1067.9	1032.6	987.6	958.2	928.8	859.2	772.0	673.1	571.2	481.0	412.5
125°	1031.7	1003.2	964.1	937.2	910.2	842.6	758.3	664.3	570.2	489.9	428.1
127.5°	1007.2	981.7	942.5	917.0	891.6	824.0	742.6	652.5	568.2	496.7	441.9
130°	983.7	959.2	919.0	893.0	867.1	800.4	723.0	641.7	567.3	504.6	454.6
132.5°	958.2	929.8	890.6	864.6	838.7	774.0	702.5	631.9	566.3	511.4	467.3
135°	922.9	895.5	856.3	831.8	807.3	747.5	683.9	622.1	565.3	518.3	478.1
137.5°	884.7	856.3	819.1	796.6	774.0	722.1	666.2	613.3	565.3	522.2	485.9
140°	838.7	817.1	782.8	762.2	741.7	697.6	651.5	606.5	564.3	527.1	493.8
142.5°	796.5	776.9	747.5	730.4	713.2	677.0	637.8	600.6	564.3	531.0	499.7
145°	756.4	739.7	715.2	701.5	687.8	658.4	625.1	593.7	562.4	532.0	503.6
147.5°	722.1	707.4	688.8	677.5	666.2	641.7	614.3	587.8	559.4	533.0	507.5
150°	692.7	679.9	664.3	655.4	646.6	627.0	604.5	581.0	556.5	533.0	510.4
152.5°	666.2	656.4	643.7	636.8	630.0	612.3	593.7	573.1	551.6	531.0	512.4
155°	642.7	634.9	625.1	619.2	613.3	598.6	582.9	565.3	546.7	529.1	513.4
157.5°	621.1	615.3	607.4	602.5	597.6	584.9	571.2	557.5	541.8	527.1	513.4
160°	601.6	595.7	589.8	585.9	582.0	571.2	560.4	548.6	535.9	524.2	513.4
162.5°	582.9	577.1	573.1	569.7	566.3	558.4	549.6	540.8	530.0	521.2	513.4
165°	565.3	561.4	557.5	555.0	552.6	545.7	539.8	532.0	524.2	517.3	511.4
167.5°	548.6	545.7	543.8	542.3	540.8	534.9	530.0	524.2	518.3	513.4	509.5
170°	534.0	533.0	531.0	529.6	528.1	524.2	521.2	516.3	512.4	509.5	507.5
172.5°	521.2	520.2	519.3	518.3	517.3	515.3	513.4	509.5	506.5	505.5	505.5
175°	511.4	509.5	509.5	509.5	509.5	507.5	506.5	504.6	502.6	502.6	503.6
177.5°	503.6	502.6	503.6	503.1	502.6	502.6	501.6	500.6	499.7	499.7	501.6
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1025031

CATALOG NUMBER: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	1975.2	1968.8	1964.1	1964.1	1949.8	1935.5	1927.6	1924.4	1921.2	1908.5	1891.1
5°	2056.1	2035.5	2021.2	2006.9	1983.1	1957.7	1932.3	1918.1	1897.4	1868.9	1848.3
7.5°	2146.5	2097.3	2081.5	2064.0	2016.4	1973.6	1938.7	1908.5	1875.2	1838.7	1802.2
10°	2222.7	2170.3	2135.4	2105.3	2043.4	1986.3	1933.9	1889.5	1846.7	1799.1	1754.7
12.5°	2295.6	2221.1	2184.6	2140.2	2075.1	1992.6	1924.4	1868.9	1805.4	1756.2	1702.3
15°	2397.2	2271.8	2211.6	2183.0	2095.7	1999.0	1916.5	1834.0	1781.6	1707.1	1659.5
17.5°	2413.0	2311.5	2271.8	2198.9	2094.2	1984.7	1889.5	1807.0	1727.7	1661.1	1599.2
20°	2468.6	2335.3	2271.8	2225.8	2087.8	1976.8	1872.1	1765.8	1689.6	1618.2	1548.4
22.5°	2503.5	2352.8	2286.1	2213.1	2081.5	1948.2	1824.5	1732.4	1638.8	1565.9	1510.3
25°	2494.0	2343.2	2268.7	2200.5	2040.2	1907.0	1795.9	1678.5	1591.2	1511.9	1438.9
27.5°	2489.2	2319.4	2240.1	2164.0	2013.3	1873.6	1734.0	1638.8	1542.1	1450.0	1396.1
30°	2476.5	2289.3	2197.3	2114.8	1957.7	1811.8	1692.8	1581.7	1485.0	1400.9	1329.5
32.5°	2433.7	2238.5	2149.7	2060.8	1897.4	1751.5	1630.9	1527.8	1431.0	1343.8	1275.5
35°	2376.6	2178.2	2081.5	1987.9	1824.5	1676.9	1565.9	1458.0	1367.6	1283.5	1218.4
37.5°	2319.4	2108.4	2018.0	1910.1	1759.4	1605.5	1491.3	1394.5	1310.4	1223.2	1151.8
40°	2236.9	2025.9	1926.0	1834.0	1657.9	1513.5	1408.8	1321.5	1239.0	1156.5	1096.3
42.5°	2124.3	1935.5	1832.4	1730.9	1565.9	1423.1	1321.5	1243.8	1166.1	1097.8	1031.2
45°	2010.1	1826.0	1734.0	1643.6	1464.3	1329.5	1235.9	1164.5	1099.4	1024.9	970.9
47.5°	1872.1	1716.6	1624.6	1535.7	1366.0	1231.1	1145.4	1078.8	1018.5	956.7	905.9
50°	1730.9	1596.0	1511.9	1419.9	1258.1	1135.9	1051.8	996.3	947.1	888.4	847.2
52.5°	1578.6	1461.2	1389.8	1300.9	1158.1	1045.5	959.8	904.3	863.0	820.2	783.7
55°	1416.7	1331.1	1254.9	1183.5	1048.7	947.1	871.0	821.8	793.2	753.6	721.9
57.5°	1270.8	1188.3	1142.3	1061.4	944.0	844.0	783.7	742.5	709.2	685.4	660.0
60°	1118.5	1051.8	1001.1	942.4	839.3	755.2	691.7	667.9	633.0	615.6	604.5
62.5°	972.5	924.9	877.3	832.9	740.9	661.6	614.0	583.8	563.2	545.8	536.2
65°	834.5	790.1	756.8	717.1	640.9	577.5	533.1	509.3	488.6	483.9	472.8
67.5°	699.6	680.6	644.1	612.4	547.3	498.2	464.8	434.7	423.6	418.8	409.3
70°	585.4	563.2	534.6	507.7	458.5	415.7	385.5	374.4	358.5	357.0	345.9
72.5°	482.3	455.3	434.7	414.1	377.6	339.5	323.6	307.8	299.8	293.5	288.7
75°	382.3	363.3	349.0	331.6	299.8	274.5	252.3	245.9	241.1	239.6	236.4
77.5°	285.6	272.9	266.5	249.1	226.9	204.7	195.1	185.6	185.6	182.4	184.0
80°	203.1	195.1	187.2	177.7	158.6	149.1	141.2	134.9	131.7	130.1	131.7
82.5°	128.5	123.7	122.2	115.8	103.1	98.4	92.0	87.3	87.3	87.3	87.3
85°	71.4	71.4	71.4	61.9	57.1	52.4	49.2	47.6	47.6	47.6	49.2
87.5°	30.1	30.1	25.4	25.4	23.8	20.6	19.0	19.0	20.6	20.6	22.2
90°	13.7	7.8	7.8	7.8	6.9	5.9	2.9	1.0	2.9	5.9	6.9
92.5°	148.9	88.2	75.4	62.7	45.1	30.4	19.6	13.7	19.6	30.4	45.1
95°	207.7	122.5	101.9	81.3	57.8	45.1	35.3	32.3	35.3	45.1	57.8
97.5°	197.9	130.3	112.6	95.0	74.5	62.7	53.9	53.9	53.9	62.7	74.5
100°	200.8	143.0	127.4	111.7	93.1	81.3	74.5	74.5	74.5	81.3	93.1
102.5°	210.6	159.7	145.0	130.3	112.7	101.9	96.0	94.1	96.0	101.9	112.7
105°	227.3	180.3	166.1	151.9	134.2	122.5	117.6	114.6	117.6	122.5	134.2
107.5°	244.9	201.8	187.6	173.4	156.8	144.0	139.1	137.2	139.1	144.0	156.8
110°	265.5	222.4	209.2	195.9	178.3	166.6	161.7	159.7	161.7	166.6	178.3

TEST NUMBER: P1025031

CATALOG NUMBER: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	285.1	244.0	230.8	217.5	199.9	189.1	183.2	181.3	183.2	189.1	199.9
115°	305.7	266.5	253.2	240.0	221.4	211.6	204.8	201.8	204.8	211.6	221.4
117.5°	325.3	288.0	274.3	260.6	243.0	232.2	226.3	223.4	226.3	232.2	243.0
120°	345.8	308.6	294.9	281.2	264.5	253.8	246.9	244.9	246.9	253.8	264.5
122.5°	365.4	328.2	315.0	301.8	283.1	273.3	266.5	264.5	266.5	273.3	283.1
125°	383.1	347.8	334.1	320.4	301.8	291.0	285.1	281.2	285.1	291.0	301.8
127.5°	399.7	365.4	351.7	338.0	318.4	306.7	299.8	296.9	299.8	306.7	318.4
130°	416.4	383.1	368.9	354.7	336.0	321.4	313.5	309.6	313.5	321.4	336.0
132.5°	430.1	396.8	383.6	370.3	349.8	336.0	325.3	322.3	325.3	336.0	349.8
135°	442.8	410.5	397.8	385.0	364.5	347.8	338.0	334.1	338.0	347.8	364.5
137.5°	452.6	422.3	410.0	397.8	376.2	360.5	349.8	345.8	349.8	360.5	376.2
140°	462.4	433.0	421.2	409.5	389.0	372.3	361.5	358.6	361.5	372.3	389.0
142.5°	471.3	442.8	431.6	420.3	400.7	385.0	375.2	372.3	375.2	385.0	400.7
145°	477.1	451.7	440.9	430.1	411.5	397.8	388.0	385.0	388.0	397.8	411.5
147.5°	484.0	459.5	449.7	439.9	424.2	409.5	400.7	399.7	400.7	409.5	424.2
150°	488.9	467.3	458.0	448.7	434.0	422.3	414.4	413.4	414.4	422.3	434.0
152.5°	492.8	474.2	465.8	457.5	444.8	434.0	426.2	426.2	426.2	434.0	444.8
155°	496.7	480.1	472.8	465.4	454.6	444.8	438.9	437.9	438.9	444.8	454.6
157.5°	499.7	485.0	479.1	473.2	463.4	455.6	449.7	449.7	449.7	455.6	463.4
160°	501.6	489.9	484.5	479.1	471.3	464.4	460.5	460.5	460.5	464.4	471.3
162.5°	503.6	492.8	488.9	485.0	478.1	472.2	469.3	470.3	469.3	472.2	478.1
165°	503.6	494.8	491.8	488.9	484.0	479.1	477.1	477.1	477.1	479.1	484.0
167.5°	503.6	496.7	494.2	491.8	488.9	485.0	484.0	485.0	484.0	485.0	488.9
170°	502.6	497.7	496.2	494.8	492.8	489.9	488.9	489.9	488.9	489.9	492.8
172.5°	501.6	498.7	497.7	496.7	495.7	493.8	493.8	494.8	493.8	493.8	495.7
175°	500.6	498.7	498.7	498.7	497.7	496.7	496.7	497.7	496.7	496.7	497.7
177.5°	499.7	498.7	498.7	498.7	498.7	497.7	498.7	499.7	498.7	497.7	498.7
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1025031

CATALOG NUMBER: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	1886.3	1880.0	1883.2	1867.3	1853.0	1832.4	1814.9	1811.8	1808.6	1818.1	1811.8
5°	1832.4	1824.5	1816.5	1797.5	1768.9	1751.5	1726.1	1724.5	1715.0	1700.7	1703.9
7.5°	1773.7	1768.9	1757.8	1727.7	1702.3	1672.2	1651.5	1634.1	1626.1	1613.5	1608.7
10°	1726.1	1708.6	1699.1	1665.8	1635.7	1603.9	1577.0	1564.3	1550.0	1538.9	1531.0
12.5°	1661.1	1656.3	1629.3	1602.4	1577.0	1540.5	1519.9	1483.4	1464.3	1473.8	1470.7
15°	1618.2	1596.0	1589.7	1551.6	1508.7	1485.0	1446.9	1423.1	1415.1	1400.9	1383.4
17.5°	1561.1	1546.8	1524.6	1489.7	1440.5	1407.2	1380.2	1358.0	1348.5	1329.5	1315.2
20°	1507.2	1483.4	1465.9	1434.2	1386.6	1343.8	1310.4	1296.2	1272.4	1256.5	1248.6
22.5°	1458.0	1440.5	1415.1	1367.6	1326.3	1285.1	1245.4	1224.8	1202.6	1193.0	1180.3
25°	1397.7	1369.1	1351.7	1299.3	1254.9	1221.6	1185.1	1158.1	1145.4	1129.6	1126.4
27.5°	1339.0	1312.0	1291.4	1245.4	1191.5	1148.6	1126.4	1107.4	1085.2	1085.2	1077.2
30°	1280.3	1261.3	1229.5	1185.1	1134.3	1093.1	1067.7	1050.3	1042.3	1036.0	1034.4
32.5°	1221.6	1196.2	1177.2	1116.9	1078.8	1040.7	1021.7	1007.4	997.9	996.3	997.9
35°	1161.3	1132.8	1113.7	1059.8	1021.7	986.8	978.9	966.2	961.4	959.8	967.8
37.5°	1097.8	1075.6	1051.8	1007.4	964.6	944.0	928.1	923.3	921.7	931.3	934.4
40°	1039.1	1020.1	997.9	950.3	918.6	896.4	888.4	883.7	890.0	899.5	904.3
42.5°	983.6	956.7	939.2	896.4	867.8	855.1	845.6	845.6	851.9	863.0	871.0
45°	924.9	904.3	886.8	848.8	823.4	809.1	807.5	809.1	817.0	825.0	834.5
47.5°	867.8	847.2	828.1	796.4	774.2	766.3	764.7	766.3	779.0	790.1	801.2
50°	815.5	793.2	775.8	745.6	728.2	718.7	720.3	728.2	737.7	753.6	767.9
52.5°	753.6	737.7	721.9	694.9	679.0	672.7	677.4	683.8	701.2	712.3	729.8
55°	693.3	679.0	666.3	645.7	633.0	628.2	631.4	640.9	655.2	674.3	694.9
57.5°	637.8	621.9	609.2	594.9	580.7	582.2	583.8	596.5	614.0	631.4	655.2
60°	575.9	566.4	555.3	537.8	531.5	531.5	536.2	550.5	566.4	594.9	615.6
62.5°	520.4	507.7	499.7	488.6	479.1	480.7	491.8	504.5	523.5	547.3	574.3
65°	463.3	449.0	442.6	433.1	429.9	431.5	439.5	458.5	479.1	499.7	525.1
67.5°	399.8	395.0	388.7	379.2	382.3	383.9	391.9	407.7	429.9	450.6	479.1
70°	345.9	336.3	334.7	326.8	326.8	331.6	347.4	358.5	379.2	401.4	431.5
72.5°	288.7	280.8	280.8	274.5	279.2	284.0	291.9	307.8	326.8	349.0	374.4
75°	230.0	226.9	230.0	226.9	226.9	234.8	244.3	257.0	277.6	301.4	322.1
77.5°	177.7	177.7	176.1	180.9	180.9	185.6	198.3	211.0	226.9	245.9	268.1
80°	130.1	130.1	130.1	134.9	139.6	139.6	147.5	163.4	177.7	190.4	211.0
82.5°	88.8	88.8	88.8	92.0	98.4	98.4	107.9	117.4	133.3	144.4	153.9
85°	53.9	53.9	52.4	55.5	57.1	61.9	69.8	76.2	84.1	93.6	103.1
87.5°	23.8	23.8	25.4	27.0	28.6	31.7	34.9	38.1	46.0	49.2	53.9
90°	7.8	7.8	7.8	13.7	13.7	15.7	17.6	16.7	17.6	18.6	19.6
92.5°	62.7	75.4	88.2	148.9	244.0	336.0	384.1	319.4	236.1	176.4	139.1
95°	81.3	101.9	122.5	207.7	368.4	602.5	798.5	821.0	726.0	574.1	442.8
97.5°	95.0	112.6	130.3	197.9	336.0	577.1	854.3	1029.7	1045.4	969.9	862.2
100°	111.7	127.4	143.0	200.8	311.6	511.4	787.7	1038.5	1181.6	1201.2	1153.1
102.5°	130.3	145.0	159.7	210.6	304.7	467.3	704.4	965.0	1174.7	1291.3	1320.7
105°	151.9	166.1	180.3	227.3	308.6	445.8	642.7	872.9	1097.3	1266.8	1363.8
107.5°	173.4	187.6	201.8	244.9	320.4	439.9	602.5	797.5	1002.3	1185.5	1320.7
110°	195.9	209.2	222.4	265.5	334.1	441.9	583.9	743.6	918.0	1087.5	1229.6

TEST NUMBER: P1025031

CATALOG NUMBER: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	217.5	230.8	244.0	285.1	348.8	447.7	575.1	713.2	856.3	1001.3	1133.5
115°	240.0	253.2	266.5	305.7	364.5	455.6	573.1	696.6	819.1	939.6	1054.2
117.5°	260.6	274.3	288.0	325.3	380.1	463.4	572.2	687.8	797.5	899.4	992.5
120°	281.2	294.9	308.6	345.8	396.8	472.2	572.2	680.9	783.8	874.9	953.3
122.5°	301.8	315.0	328.2	365.4	412.5	481.0	571.2	673.1	772.0	859.2	928.8
125°	320.4	334.1	347.8	383.1	428.1	489.9	570.2	664.3	758.3	842.6	910.2
127.5°	338.0	351.7	365.4	399.7	441.9	496.7	568.2	652.5	742.6	824.0	891.6
130°	354.7	368.9	383.1	416.4	454.6	504.6	567.3	641.7	723.0	800.4	867.1
132.5°	370.3	383.6	396.8	430.1	467.3	511.4	566.3	631.9	702.5	774.0	838.7
135°	385.0	397.8	410.5	442.8	478.1	518.3	565.3	622.1	683.9	747.5	807.3
137.5°	397.8	410.0	422.3	452.6	485.9	522.2	565.3	613.3	666.2	722.1	774.0
140°	409.5	421.2	433.0	462.4	493.8	527.1	564.3	606.5	651.5	697.6	741.7
142.5°	420.3	431.6	442.8	471.3	499.7	531.0	564.3	600.6	637.8	677.0	713.2
145°	430.1	440.9	451.7	477.1	503.6	532.0	562.4	593.7	625.1	658.4	687.8
147.5°	439.9	449.7	459.5	484.0	507.5	533.0	559.4	587.8	614.3	641.7	666.2
150°	448.7	458.0	467.3	488.9	510.4	533.0	556.5	581.0	604.5	627.0	646.6
152.5°	457.5	465.8	474.2	492.8	512.4	531.0	551.6	573.1	593.7	612.3	630.0
155°	465.4	472.8	480.1	496.7	513.4	529.1	546.7	565.3	582.9	598.6	613.3
157.5°	473.2	479.1	485.0	499.7	513.4	527.1	541.8	557.5	571.2	584.9	597.6
160°	479.1	484.5	489.9	501.6	513.4	524.2	535.9	548.6	560.4	571.2	582.0
162.5°	485.0	488.9	492.8	503.6	513.4	521.2	530.0	540.8	549.6	558.4	566.3
165°	488.9	491.8	494.8	503.6	511.4	517.3	524.2	532.0	539.8	545.7	552.6
167.5°	491.8	494.2	496.7	503.6	509.5	513.4	518.3	524.2	530.0	534.9	540.8
170°	494.8	496.2	497.7	502.6	507.5	509.5	512.4	516.3	521.2	524.2	528.1
172.5°	496.7	497.7	498.7	501.6	505.5	505.5	506.5	509.5	513.4	515.3	517.3
175°	498.7	498.7	498.7	500.6	503.6	502.6	502.6	504.6	506.5	507.5	509.5
177.5°	498.7	498.7	498.7	499.7	501.6	499.7	499.7	500.6	501.6	502.6	502.6
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1025031

CATALOG NUMBER: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	1807.0	1805.4	1797.5	1800.7	1791.1	1794.3	1799.1	1800.7	1807.0	1802.2	1800.7
5°	1696.0	1692.8	1688.0	1683.3	1681.7	1688.0	1676.9	1680.1	1683.3	1688.0	1694.4
7.5°	1605.5	1603.9	1599.2	1591.2	1588.1	1584.9	1586.5	1597.6	1596.0	1594.4	1605.5
10°	1523.0	1524.6	1515.1	1513.5	1504.0	1502.4	1504.0	1507.2	1511.9	1518.3	1519.9
12.5°	1437.4	1458.0	1440.5	1434.2	1419.9	1427.8	1431.0	1416.7	1424.7	1429.4	1453.2
15°	1383.4	1373.9	1362.8	1362.8	1356.4	1353.3	1345.3	1356.4	1362.8	1372.3	1369.1
17.5°	1308.9	1293.0	1286.6	1280.3	1281.9	1288.2	1270.8	1296.2	1296.2	1300.9	1293.0
20°	1243.8	1231.1	1223.2	1220.0	1215.2	1212.1	1210.5	1216.8	1226.4	1229.5	1237.5
22.5°	1175.6	1175.6	1162.9	1158.1	1155.0	1150.2	1158.1	1153.4	1159.7	1166.1	1178.8
25°	1118.5	1118.5	1113.7	1107.4	1102.6	1099.4	1104.2	1102.6	1107.4	1115.3	1118.5
27.5°	1072.5	1067.7	1066.1	1064.5	1062.9	1064.5	1062.9	1067.7	1072.5	1074.1	1070.9
30°	1032.8	1028.0	1029.6	1029.6	1031.2	1029.6	1028.0	1032.8	1034.4	1031.2	1032.8
32.5°	996.3	996.3	999.5	1001.1	1001.1	1002.7	1004.2	1001.1	1002.7	997.9	999.5
35°	966.2	969.3	972.5	974.1	975.7	974.1	977.3	975.7	972.5	969.3	967.8
37.5°	936.0	939.2	945.5	947.1	951.9	953.5	950.3	950.3	948.7	942.4	939.2
40°	904.3	907.5	915.4	920.2	923.3	928.1	924.9	924.9	918.6	912.2	907.5
42.5°	874.2	880.5	888.4	893.2	899.5	899.5	899.5	896.4	888.4	882.1	877.3
45°	844.0	845.6	856.7	864.6	871.0	871.0	871.0	866.2	861.5	848.8	842.4
47.5°	810.7	815.5	828.1	836.1	842.4	844.0	844.0	839.3	829.7	818.6	810.7
50°	774.2	782.1	796.4	807.5	815.5	818.6	813.9	810.7	799.6	786.9	777.4
52.5°	739.3	748.8	766.3	775.8	786.9	788.5	786.9	782.1	769.4	752.0	744.1
55°	704.4	712.3	731.4	747.2	756.8	759.9	756.8	748.8	733.0	715.5	707.6
57.5°	666.3	677.4	698.1	713.9	725.0	726.6	723.4	715.5	702.8	680.6	669.5
60°	626.7	640.9	661.6	677.4	691.7	693.3	690.1	679.0	663.2	640.9	631.4
62.5°	587.0	598.1	621.9	639.4	650.5	658.4	652.0	640.9	625.1	602.9	588.6
65°	541.0	556.9	577.5	593.3	606.0	607.6	604.5	594.9	577.5	553.7	542.6
67.5°	496.6	507.7	528.3	548.9	553.7	558.4	553.7	544.2	529.9	509.3	493.4
70°	442.6	452.1	477.5	491.8	498.2	502.9	499.7	490.2	477.5	458.5	445.8
72.5°	388.7	396.6	420.4	431.5	444.2	442.6	441.0	434.7	417.2	404.6	396.6
75°	331.6	341.1	357.0	371.2	376.0	376.0	376.0	371.2	360.1	339.5	331.6
77.5°	279.2	284.0	296.7	304.6	309.4	311.0	309.4	301.4	295.1	280.8	276.0
80°	214.2	226.9	236.4	238.0	244.3	244.3	244.3	241.1	234.8	220.5	218.9
82.5°	161.8	165.0	174.5	179.3	182.4	180.9	180.9	174.5	172.9	165.0	161.8
85°	109.5	114.2	112.6	119.0	120.6	117.4	117.4	120.6	112.6	114.2	109.5
87.5°	60.3	60.3	63.5	61.9	68.2	68.2	65.0	66.6	63.5	61.9	60.3
90°	19.6	19.6	20.6	21.6	20.6	20.6	20.6	21.6	20.6	19.6	19.6
92.5°	126.8	114.6	99.9	93.1	89.2	89.2	89.2	93.1	99.9	114.6	126.8
95°	395.3	347.8	299.8	269.4	251.8	239.1	251.8	269.4	299.8	347.8	395.3
97.5°	807.3	752.4	685.8	627.0	597.6	574.1	597.6	627.0	685.8	752.4	807.3
100°	1116.8	1080.6	995.4	935.6	906.3	898.4	906.3	935.6	995.4	1080.6	1116.8
102.5°	1310.9	1301.1	1257.0	1217.8	1186.5	1180.6	1186.5	1217.8	1257.0	1301.1	1310.9
105°	1383.9	1404.0	1405.9	1398.1	1384.4	1378.5	1384.4	1398.1	1405.9	1404.0	1383.9
107.5°	1361.8	1403.0	1446.1	1463.7	1471.6	1472.5	1471.6	1463.7	1446.1	1403.0	1361.8
110°	1283.4	1337.3	1406.9	1448.0	1465.7	1474.5	1465.7	1448.0	1406.9	1337.3	1283.4

TEST NUMBER: P1025031

CATALOG NUMBER: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1187.4	1241.3	1322.6	1374.6	1401.0	1416.7	1401.0	1374.6	1322.6	1241.3	1187.4
115°	1101.2	1148.2	1225.6	1284.4	1315.8	1323.6	1315.8	1284.4	1225.6	1148.2	1101.2
117.5°	1033.6	1074.8	1143.3	1194.3	1227.6	1232.5	1227.6	1194.3	1143.3	1074.8	1033.6
120°	988.0	1022.8	1078.7	1121.8	1147.3	1158.0	1147.3	1121.8	1078.7	1022.8	988.0
122.5°	958.2	987.6	1032.6	1067.9	1088.5	1099.3	1088.5	1067.9	1032.6	987.6	958.2
125°	937.2	964.1	1003.2	1031.7	1050.3	1056.2	1050.3	1031.7	1003.2	964.1	937.2
127.5°	917.0	942.5	981.7	1007.2	1022.8	1028.7	1022.8	1007.2	981.7	942.5	917.0
130°	893.0	919.0	959.2	983.7	999.3	1005.2	999.3	983.7	959.2	919.0	893.0
132.5°	864.6	890.6	929.8	958.2	972.9	978.8	972.9	958.2	929.8	890.6	864.6
135°	831.8	856.3	895.5	922.9	938.6	944.5	938.6	922.9	895.5	856.3	831.8
137.5°	796.6	819.1	856.3	884.7	897.4	904.3	897.4	884.7	856.3	819.1	796.6
140°	762.2	782.8	817.1	838.7	852.4	860.2	852.4	838.7	817.1	782.8	762.2
142.5°	730.4	747.5	776.9	796.5	808.3	813.2	808.3	796.5	776.9	747.5	730.4
145°	701.5	715.2	739.7	756.4	766.2	771.0	766.2	756.4	739.7	715.2	701.5
147.5°	677.5	688.8	707.4	722.1	729.9	731.9	729.9	722.1	707.4	688.8	677.5
150°	655.4	664.3	679.9	692.7	698.5	699.5	698.5	692.7	679.9	664.3	655.4
152.5°	636.8	643.7	656.4	666.2	669.2	670.1	669.2	666.2	656.4	643.7	636.8
155°	619.2	625.1	634.9	642.7	645.6	645.6	645.6	642.7	634.9	625.1	619.2
157.5°	602.5	607.4	615.3	621.1	623.1	623.1	623.1	621.1	615.3	607.4	602.5
160°	585.9	589.8	595.7	601.6	602.5	602.5	602.5	601.6	595.7	589.8	585.9
162.5°	569.7	573.1	577.1	582.9	583.9	582.9	583.9	582.9	577.1	573.1	569.7
165°	555.0	557.5	561.4	565.3	564.3	563.3	564.3	565.3	561.4	557.5	555.0
167.5°	542.3	543.8	545.7	548.6	548.6	547.7	548.6	548.6	545.7	543.8	542.3
170°	529.6	531.0	533.0	534.0	533.0	533.0	533.0	534.0	533.0	531.0	529.6
172.5°	518.3	519.3	520.2	521.2	520.2	518.3	520.2	521.2	520.2	519.3	518.3
175°	509.5	509.5	509.5	511.4	509.5	507.5	509.5	511.4	509.5	509.5	509.5
177.5°	503.1	503.6	502.6	503.6	501.6	499.7	501.6	503.6	502.6	503.6	503.1
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1025031

CATALOG NUMBER: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	1800.7	1810.2	1800.7	1807.0	1810.2	1818.1	1821.3	1835.6	1840.3	1851.4	1851.4
5°	1692.8	1697.5	1699.1	1705.5	1711.8	1727.7	1738.8	1759.4	1783.2	1786.4	1800.7
7.5°	1605.5	1613.5	1626.1	1621.4	1632.5	1656.3	1670.6	1696.0	1719.8	1732.4	1749.9
10°	1527.8	1537.3	1542.1	1546.8	1567.4	1588.1	1610.3	1627.7	1659.5	1678.5	1692.8
12.5°	1464.3	1456.4	1465.9	1483.4	1507.2	1519.9	1550.0	1577.0	1600.8	1621.4	1634.1
15°	1381.8	1388.2	1397.7	1427.8	1434.2	1465.9	1477.0	1507.2	1551.6	1570.6	1586.5
17.5°	1302.5	1323.1	1342.2	1353.3	1372.3	1397.7	1429.4	1462.7	1491.3	1513.5	1532.5
20°	1239.0	1259.7	1270.8	1278.7	1297.7	1332.6	1362.8	1404.0	1440.5	1458.0	1483.4
22.5°	1188.3	1188.3	1204.1	1227.9	1239.0	1272.4	1297.7	1342.2	1381.8	1404.0	1427.8
25°	1124.8	1134.3	1147.0	1167.7	1183.5	1210.5	1247.0	1285.1	1327.9	1346.9	1377.1
27.5°	1072.5	1083.6	1101.0	1105.8	1121.6	1145.4	1183.5	1224.8	1269.2	1289.8	1315.2
30°	1032.8	1039.1	1045.5	1055.0	1069.3	1089.9	1121.6	1158.1	1212.1	1227.9	1259.7
32.5°	997.9	1001.1	1004.2	1012.2	1020.1	1040.7	1066.1	1105.8	1150.2	1174.0	1202.6
35°	966.2	963.0	964.6	969.3	977.3	985.2	1012.2	1045.5	1086.7	1115.3	1137.5
37.5°	936.0	929.7	928.1	928.1	931.3	940.8	961.4	990.0	1034.4	1058.2	1080.4
40°	902.7	896.4	893.2	891.6	890.0	896.4	912.2	940.8	975.7	997.9	1023.3
42.5°	871.0	864.6	856.7	855.1	851.9	855.1	866.2	893.2	923.3	945.5	966.2
45°	839.3	828.1	818.6	812.3	813.9	809.1	817.0	837.7	872.6	886.8	907.5
47.5°	804.3	791.7	779.0	772.6	766.3	769.4	772.6	790.1	820.2	834.5	855.1
50°	771.0	753.6	739.3	731.4	726.6	723.4	726.6	744.1	766.3	779.0	796.4
52.5°	733.0	715.5	701.2	688.5	682.2	677.4	679.0	694.9	715.5	728.2	745.6
55°	698.1	675.8	656.8	640.9	636.2	634.6	633.0	644.1	661.6	674.3	688.5
57.5°	658.4	636.2	615.6	596.5	587.0	585.4	585.4	588.6	610.8	620.3	628.2
60°	618.7	594.9	572.7	555.3	541.0	536.2	534.6	541.0	552.1	561.6	572.7
62.5°	574.3	550.5	523.5	507.7	493.4	480.7	485.5	487.1	502.9	507.7	517.2
65°	531.5	504.5	482.3	456.9	441.0	433.1	429.9	433.1	445.8	447.4	453.7
67.5°	482.3	456.9	429.9	412.5	398.2	383.9	380.8	380.8	387.1	391.9	399.8
70°	434.7	409.3	379.2	360.1	345.9	333.2	328.4	326.8	331.6	334.7	342.7
72.5°	379.2	353.8	331.6	311.0	293.5	284.0	279.2	276.0	280.8	284.0	285.6
75°	320.5	299.8	277.6	257.0	245.9	236.4	230.0	225.3	228.5	228.5	228.5
77.5°	264.9	244.3	226.9	212.6	198.3	187.2	182.4	177.7	179.3	179.3	182.4
80°	206.2	192.0	177.7	165.0	152.3	142.8	139.6	134.9	131.7	130.1	130.1
82.5°	152.3	141.2	128.5	117.4	111.1	101.5	98.4	92.0	92.0	90.4	90.4
85°	101.5	95.2	82.5	74.6	69.8	65.0	61.9	58.7	53.9	53.9	52.4
87.5°	53.9	50.8	47.6	38.1	38.1	33.3	31.7	30.1	25.4	27.0	27.0
90°	19.6	18.6	17.6	16.7	17.6	15.7	13.7	13.7	7.8	7.8	7.8
92.5°	139.1	176.4	236.1	319.4	384.1	336.0	244.0	148.9	88.2	75.4	62.7
95°	442.8	574.1	726.0	821.0	798.5	602.5	368.4	207.7	122.5	101.9	81.3
97.5°	862.2	969.9	1045.4	1029.7	854.3	577.1	336.0	197.9	130.3	112.6	95.0
100°	1153.1	1201.2	1181.6	1038.5	787.7	511.4	311.6	200.8	143.0	127.4	111.7
102.5°	1320.7	1291.3	1174.7	965.0	704.4	467.3	304.7	210.6	159.7	145.0	130.3
105°	1363.8	1266.8	1097.3	872.9	642.7	445.8	308.6	227.3	180.3	166.1	151.9
107.5°	1320.7	1185.5	1002.3	797.5	602.5	439.9	320.4	244.9	201.8	187.6	173.4
110°	1229.6	1087.5	918.0	743.6	583.9	441.9	334.1	265.5	222.4	209.2	195.9

TEST NUMBER: P1025031

CATALOG NUMBER: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1133.5	1001.3	856.3	713.2	575.1	447.7	348.8	285.1	244.0	230.8	217.5
115°	1054.2	939.6	819.1	696.6	573.1	455.6	364.5	305.7	266.5	253.2	240.0
117.5°	992.5	899.4	797.5	687.8	572.2	463.4	380.1	325.3	288.0	274.3	260.6
120°	953.3	874.9	783.8	680.9	572.2	472.2	396.8	345.8	308.6	294.9	281.2
122.5°	928.8	859.2	772.0	673.1	571.2	481.0	412.5	365.4	328.2	315.0	301.8
125°	910.2	842.6	758.3	664.3	570.2	489.9	428.1	383.1	347.8	334.1	320.4
127.5°	891.6	824.0	742.6	652.5	568.2	496.7	441.9	399.7	365.4	351.7	338.0
130°	867.1	800.4	723.0	641.7	567.3	504.6	454.6	416.4	383.1	368.9	354.7
132.5°	838.7	774.0	702.5	631.9	566.3	511.4	467.3	430.1	396.8	383.6	370.3
135°	807.3	747.5	683.9	622.1	565.3	518.3	478.1	442.8	410.5	397.8	385.0
137.5°	774.0	722.1	666.2	613.3	565.3	522.2	485.9	452.6	422.3	410.0	397.8
140°	741.7	697.6	651.5	606.5	564.3	527.1	493.8	462.4	433.0	421.2	409.5
142.5°	713.2	677.0	637.8	600.6	564.3	531.0	499.7	471.3	442.8	431.6	420.3
145°	687.8	658.4	625.1	593.7	562.4	532.0	503.6	477.1	451.7	440.9	430.1
147.5°	666.2	641.7	614.3	587.8	559.4	533.0	507.5	484.0	459.5	449.7	439.9
150°	646.6	627.0	604.5	581.0	556.5	533.0	510.4	488.9	467.3	458.0	448.7
152.5°	630.0	612.3	593.7	573.1	551.6	531.0	512.4	492.8	474.2	465.8	457.5
155°	613.3	598.6	582.9	565.3	546.7	529.1	513.4	496.7	480.1	472.8	465.4
157.5°	597.6	584.9	571.2	557.5	541.8	527.1	513.4	499.7	485.0	479.1	473.2
160°	582.0	571.2	560.4	548.6	535.9	524.2	513.4	501.6	489.9	484.5	479.1
162.5°	566.3	558.4	549.6	540.8	530.0	521.2	513.4	503.6	492.8	488.9	485.0
165°	552.6	545.7	539.8	532.0	524.2	517.3	511.4	503.6	494.8	491.8	488.9
167.5°	540.8	534.9	530.0	524.2	518.3	513.4	509.5	503.6	496.7	494.2	491.8
170°	528.1	524.2	521.2	516.3	512.4	509.5	507.5	502.6	497.7	496.2	494.8
172.5°	517.3	515.3	513.4	509.5	506.5	505.5	505.5	501.6	498.7	497.7	496.7
175°	509.5	507.5	506.5	504.6	502.6	502.6	503.6	500.6	498.7	498.7	498.7
177.5°	502.6	502.6	501.6	500.6	499.7	499.7	501.6	499.7	498.7	498.7	498.7
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1025031

CATALOG NUMBER: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1914.9	1914.9	1914.9	1914.9
2.5°	1862.5	1878.4	1892.7	1914.9
5°	1821.3	1843.5	1873.6	1907.0
7.5°	1773.7	1808.6	1848.3	1894.3
10°	1729.3	1768.9	1819.7	1875.2
12.5°	1683.3	1730.9	1786.4	1846.7
15°	1630.9	1678.5	1740.4	1821.3
17.5°	1583.3	1640.4	1707.1	1792.7
20°	1527.8	1581.7	1654.7	1753.1
22.5°	1478.6	1540.5	1621.4	1707.1
25°	1424.7	1478.6	1559.5	1662.6
27.5°	1370.7	1437.4	1515.1	1615.0
30°	1318.4	1373.9	1458.0	1562.7
32.5°	1261.3	1327.9	1405.6	1504.0
35°	1199.4	1262.8	1335.8	1442.1
37.5°	1143.9	1205.7	1280.3	1373.9
40°	1082.0	1147.0	1215.2	1308.9
42.5°	1021.7	1080.4	1148.6	1234.3
45°	963.0	1013.8	1075.6	1150.2
47.5°	902.7	945.5	1002.7	1069.3
50°	837.7	883.7	926.5	982.0
52.5°	777.4	817.0	851.9	898.0
55°	718.7	745.6	774.2	809.1
57.5°	656.8	677.4	698.1	734.5
60°	594.9	614.0	625.1	648.9
62.5°	534.6	542.6	556.9	571.1
65°	468.0	479.1	487.1	504.5
67.5°	407.7	412.5	420.4	431.5
70°	344.3	355.4	358.5	366.5
72.5°	290.3	295.1	298.3	299.8
75°	230.0	234.8	238.0	247.5
77.5°	180.9	179.3	185.6	187.2
80°	133.3	128.5	130.1	136.4
82.5°	87.3	88.8	87.3	87.3
85°	53.9	52.4	49.2	50.8
87.5°	23.8	23.8	22.2	22.2
90°	6.9	5.9	2.9	1.0
92.5°	45.1	30.4	19.6	13.7
95°	57.8	45.1	35.3	32.3
97.5°	74.5	62.7	53.9	53.9
100°	93.1	81.3	74.5	74.5
102.5°	112.7	101.9	96.0	94.1
105°	134.2	122.5	117.6	114.6
107.5°	156.8	144.0	139.1	137.2
110°	178.3	166.6	161.7	159.7



TEST NUMBER: P1025031

CATALOG NUMBER: S124DIP-B1195D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	199.9	189.1	183.2	181.3
115°	221.4	211.6	204.8	201.8
117.5°	243.0	232.2	226.3	223.4
120°	264.5	253.8	246.9	244.9
122.5°	283.1	273.3	266.5	264.5
125°	301.8	291.0	285.1	281.2
127.5°	318.4	306.7	299.8	296.9
130°	336.0	321.4	313.5	309.6
132.5°	349.8	336.0	325.3	322.3
135°	364.5	347.8	338.0	334.1
137.5°	376.2	360.5	349.8	345.8
140°	389.0	372.3	361.5	358.6
142.5°	400.7	385.0	375.2	372.3
145°	411.5	397.8	388.0	385.0
147.5°	424.2	409.5	400.7	399.7
150°	434.0	422.3	414.4	413.4
152.5°	444.8	434.0	426.2	426.2
155°	454.6	444.8	438.9	437.9
157.5°	463.4	455.6	449.7	449.7
160°	471.3	464.4	460.5	460.5
162.5°	478.1	472.2	469.3	470.3
165°	484.0	479.1	477.1	477.1
167.5°	488.9	485.0	484.0	485.0
170°	492.8	489.9	488.9	489.9
172.5°	495.7	493.8	493.8	494.8
175°	497.7	496.7	496.7	497.7
177.5°	498.7	497.7	498.7	499.7
180°	498.7	498.7	498.7	498.7

(END OF REPORT)