

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026179

Luminaire Tested: S124RDIP-B1195D590UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026179
REPORT IS A COMBINATION OF REPORTS P999159 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D590UB30-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6881.0 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026179

CATALOG NUMBER: S124RDIP-B1195D590UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026179

CATALOG NUMBER: S124RDIP-B1195D590UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75
1	103	98	95	91	97	93	90	87	84	81	79	75	73	71	67	65	64
2	94	86	80	75	89	82	77	72	74	69	66	66	63	60	59	57	54
3	86	76	69	63	81	73	66	61	65	60	56	59	55	51	53	49	47
4	79	68	60	54	74	65	57	52	58	53	48	53	48	44	47	44	41
5	73	61	52	46	68	58	50	45	53	46	42	47	42	39	43	39	36
6	67	55	46	41	63	52	45	39	48	41	37	43	38	34	39	35	31
7	62	50	42	36	59	47	40	35	43	37	32	39	34	30	36	31	28
8	58	45	37	32	55	43	36	31	40	33	29	36	31	27	33	29	25
9	54	42	34	29	51	40	33	28	36	30	26	33	28	25	30	26	23
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17042	17042	17042
5°	17044	16536	16538
10°	16899	16014	15824
15°	16667	15365	14981
20°	16362	14624	14021
25°	15983	13825	13083
30°	15611	13009	12029
35°	15202	12183	11000
40°	14716	11293	9942
45°	14259	10411	8895
50°	13741	9447	7830
55°	13180	8459	6733
60°	12557	7410	5648
65°	11957	6207	4604
70°	11104	4941	3518
75°	10008	3594	2460
80°	8357	2207	1769
85°	6287	1271	973

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14259 cd/sqm

TEST NUMBER: P1026179

CATALOG NUMBER: S124RDIP-B1195D590UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.5	2.9
10°-20°	547.9	8.0
20°-30°	791.1	11.5
30°-40°	896.6	13.0
40°-50°	865.7	12.6
50°-60°	719.7	10.5
60°-70°	496.8	7.2
70°-80°	251.0	3.6
80°-90°	65.3	0.9
90°-100°	48.2	0.7
100°-110°	144.3	2.1
110°-120°	245.1	3.6
120°-130°	323.2	4.7
130°-140°	363.1	5.3
140°-150°	356.8	5.2
150°-160°	300.1	4.4
160°-170°	199.7	2.9
170°-180°	69.9	1.0
0°-30°	1535.6	22.3
0°-40°	2432.1	35.3
0°-60°	4017.5	58.4
0°-90°	4830.6	70.2
90°-120°	437.5	6.4
90°-150°	1480.7	21.5
90°-180°	2050.0	29.8
0°-180°	6881.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2090	2090	2090	2090	2090	
5°	2087	2080	2061	2077	2074	198
15°	1988	1973	1933	1930	1919	560
25°	1797	1768	1703	1676	1660	828
35°	1554	1503	1423	1368	1339	971
45°	1267	1208	1112	1034	1005	977
55°	960	896	792	709	678	859
65°	653	584	482	413	394	645
75°	347	288	213	176	166	366
85°	86	54	50	46	46	95
90°	2	8	13	16	17	8
95°	34	39	43	45	45	37
105°	133	134	136	138	140	141
115°	249	249	248	248	247	246
125°	363	363	362	361	360	323
135°	468	472	472	470	469	362
145°	569	571	572	571	569	356
155°	652	652	651	653	651	300
165°	709	708	706	710	708	200
175°	738	735	734	738	734	70
180°	739	739	739	739	739	

TEST NUMBER: P1026179

CATALOG NUMBER: S124RDIP-B1195D590UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2089.9	2089.9	2089.9	2089.9	2089.9
2.5°	2096.3	2089.9	2072.3	2089.9	2088.3
5°	2086.7	2080.3	2061.1	2077.1	2073.9
7.5°	2072.3	2065.9	2041.9	2053.1	2048.3
10°	2049.9	2041.9	2013.1	2019.5	2013.1
12.5°	2021.1	2011.5	1976.3	1979.5	1969.9
15°	1987.5	1973.1	1933.1	1929.9	1918.7
17.5°	1949.1	1928.3	1881.9	1873.9	1857.9
20°	1902.7	1881.9	1827.5	1814.7	1793.9
22.5°	1851.5	1827.5	1768.3	1747.5	1731.5
25°	1797.1	1768.3	1702.7	1675.5	1659.5
27.5°	1741.1	1705.9	1637.1	1605.1	1582.6
30°	1681.9	1641.9	1566.6	1526.6	1501.0
32.5°	1619.5	1573.0	1494.6	1446.6	1422.6
35°	1553.8	1502.6	1422.6	1368.2	1339.4
37.5°	1485.0	1432.2	1344.2	1285.0	1256.2
40°	1411.4	1358.6	1267.4	1200.2	1171.4
42.5°	1341.0	1285.0	1189.0	1120.2	1089.8
45°	1267.4	1208.2	1112.2	1033.8	1005.0
47.5°	1192.2	1131.4	1032.2	950.5	918.5
50°	1115.4	1053.0	950.5	870.5	840.1
52.5°	1037.0	976.2	870.5	788.9	756.9
55°	960.2	896.1	792.1	708.9	678.5
57.5°	884.9	817.7	715.3	630.5	608.1
60°	803.3	739.3	636.9	553.7	528.1
62.5°	729.7	662.5	556.9	481.7	462.5
65°	652.9	584.1	481.7	412.9	393.7
67.5°	572.9	507.3	411.3	350.5	328.1
70°	497.7	430.5	339.3	286.4	270.4
72.5°	417.7	358.5	273.6	230.4	216.0
75°	347.3	288.0	212.8	176.0	166.4
77.5°	273.6	222.4	158.4	132.8	129.6
80°	203.2	156.8	108.8	104.0	102.4
82.5°	142.4	100.8	78.4	75.2	73.6
85°	86.4	54.4	49.6	46.4	46.4
87.5°	36.8	24.0	22.4	20.8	22.4
90°	1.7	8.0	12.6	16.0	17.1
92.5°	14.9	22.3	25.1	26.9	27.4
95°	34.3	39.4	43.4	45.2	45.2
97.5°	54.9	59.4	64.0	66.3	66.3
100°	80.0	82.3	87.4	88.6	88.6
102.5°	106.3	106.9	111.4	113.2	113.7
105°	133.2	133.7	136.0	137.7	139.5
107.5°	161.2	161.7	162.3	164.6	164.0
110°	189.7	190.9	190.3	189.2	190.9



TEST NUMBER: P1026179

CATALOG NUMBER: S124RDIP-B1195D590UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	219.5	219.5	218.3	218.3	218.3
115°	249.2	249.2	248.0	247.5	246.9
117.5°	277.2	277.2	276.6	274.9	273.2
120°	305.2	307.5	305.8	302.9	304.1
122.5°	334.3	334.9	334.3	332.6	329.8
125°	362.9	362.9	362.3	361.2	360.1
127.5°	388.6	390.4	389.2	388.1	387.5
130°	416.1	417.8	417.8	416.6	414.4
132.5°	444.1	445.2	444.7	443.5	442.9
135°	468.1	471.5	471.5	470.4	468.7
137.5°	494.9	496.7	497.8	496.1	496.7
140°	521.8	522.9	522.9	522.4	521.8
142.5°	546.4	547.5	547.0	547.0	547.0
145°	568.7	571.0	571.5	571.0	569.2
147.5°	591.5	594.4	593.8	593.2	592.7
150°	612.1	614.4	614.4	614.4	613.8
152.5°	631.5	632.7	633.3	635.0	633.3
155°	651.5	651.5	651.0	653.3	651.0
157.5°	668.7	667.5	667.5	669.3	667.5
160°	683.5	683.0	682.4	684.1	681.3
162.5°	697.3	695.6	695.0	698.4	695.6
165°	709.3	707.6	706.4	709.8	707.6
167.5°	719.0	716.7	716.7	720.1	716.7
170°	727.0	724.1	724.7	728.1	724.1
172.5°	732.7	730.4	730.4	734.4	730.4
175°	737.8	735.0	734.4	738.4	734.4
177.5°	740.1	737.3	737.3	741.3	736.7
180°	739.0	739.0	739.0	739.0	739.0

(END OF REPORT)