

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025136

Luminaire Tested: S124DIP-B1195D365UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025136
REPORT IS A COMBINATION OF REPORTS P995571 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B1195D365UB30-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6447.6 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025136

CATALOG NUMBER: S124DIP-B1195D365UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1025136

CATALOG NUMBER: S124DIP-B1195D365UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	80		
1	104	100	96	92	100	96	92	89	88	85	82	80	78	76	74	72	70	67		
2	95	87	81	75	91	84	78	73	77	72	68	71	67	64	65	62	59	56		
3	87	77	69	63	83	74	67	61	68	62	57	62	58	54	57	54	50	47		
4	79	68	60	53	76	65	58	52	60	54	49	56	50	46	51	47	43	41		
5	73	61	52	46	70	59	51	45	54	48	42	50	45	40	46	42	38	35		
6	68	55	46	40	64	53	45	39	49	42	37	45	40	35	42	37	33	31		
7	63	50	41	35	60	48	40	35	45	38	33	41	36	31	38	34	30	28		
8	58	45	37	32	56	44	36	31	41	34	29	38	32	28	35	30	27	25		
9	54	41	34	28	52	40	33	28	37	31	27	35	29	25	33	28	24	22		
10	51	38	31	26	49	37	30	25	35	28	24	32	27	23	30	26	22	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16285	16285	16285
5°	16299	15817	15836
10°	16161	15378	15270
15°	15929	14856	14632
20°	15633	14291	13971
25°	15300	13695	13259
30°	14899	13050	12478
35°	14482	12389	11722
40°	14048	11678	10919
45°	13593	10965	10169
50°	13090	10275	9337
55°	12542	9467	8511
60°	11982	8583	7650
65°	11341	7671	6681
70°	10604	6572	5643
75°	9501	5298	4518
80°	8094	3829	3178
85°	6287	2132	1710

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13593 cd/sqm

TEST NUMBER: P1025136

CATALOG NUMBER: S124DIP-B1195D365UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.2	2.9
10°-20°	530.3	8.2
20°-30°	780.5	12.1
30°-40°	907.3	14.1
40°-50°	907.2	14.1
50°-60°	793.4	12.3
60°-70°	589.1	9.1
70°-80°	334.2	5.2
80°-90°	96.4	1.5
90°-100°	134.4	2.1
100°-110°	273.5	4.2
110°-120°	243.7	3.8
120°-130°	204.7	3.2
130°-140°	170.9	2.6
140°-150°	130.5	2.0
150°-160°	91.7	1.4
160°-170°	53.9	0.8
170°-180°	17.5	0.3
0°-30°	1499.1	23.2
0°-40°	2406.3	37.3
0°-60°	4107.0	63.7
0°-90°	5126.7	79.5
90°-120°	651.6	10.1
90°-150°	1157.7	18.0
90°-180°	1321.0	20.5
0°-180°	6447.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1997	1997	1997	1997	1997	
5°	1996	1989	1972	1989	1986	189
15°	1900	1893	1869	1879	1874	535
25°	1720	1709	1687	1688	1682	792
35°	1480	1469	1447	1435	1427	926
45°	1208	1197	1171	1154	1149	931
55°	914	909	886	867	858	818
65°	619	611	595	579	571	613
75°	330	322	314	307	306	350
85°	86	86	83	83	82	93
90°	0	3	6	7	8	6
95°	12	37	290	143	87	13
105°	42	60	233	502	500	44
115°	73	92	208	400	480	73
125°	102	121	207	340	383	91
135°	121	144	205	302	343	94
145°	140	160	204	255	280	88
155°	159	172	198	225	234	73
165°	173	178	190	201	204	49
175°	181	181	182	185	184	17
180°	181	181	181	181	181	

TEST NUMBER: P1025136

CATALOG NUMBER: S124DIP-B1195D365UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1997.1	1997.1	1997.1	1997.1	1997.1
2.5°	2003.5	1998.7	1981.1	1997.1	1995.5
5°	1995.5	1989.1	1971.5	1989.1	1985.9
7.5°	1981.1	1974.7	1955.5	1969.9	1968.3
10°	1960.3	1953.9	1933.1	1945.9	1942.7
12.5°	1933.1	1926.7	1904.3	1918.7	1913.9
15°	1899.5	1893.1	1869.1	1878.7	1873.9
17.5°	1861.1	1853.1	1830.7	1837.1	1833.9
20°	1817.9	1809.9	1785.9	1790.7	1787.5
22.5°	1771.5	1760.3	1736.3	1745.9	1739.5
25°	1720.3	1709.1	1686.7	1688.3	1681.9
27.5°	1662.7	1651.5	1630.7	1627.5	1619.5
30°	1605.1	1592.3	1571.5	1565.1	1557.1
32.5°	1544.2	1533.0	1510.6	1502.6	1494.6
35°	1480.2	1469.0	1446.6	1435.4	1427.4
37.5°	1413.0	1403.4	1379.4	1368.2	1357.0
40°	1347.4	1334.6	1310.6	1294.6	1286.6
42.5°	1277.0	1270.6	1243.4	1224.2	1219.4
45°	1208.2	1197.0	1171.4	1153.8	1149.0
47.5°	1136.2	1128.2	1104.2	1085.0	1072.2
50°	1062.6	1056.2	1033.8	1011.4	1001.8
52.5°	990.6	982.6	958.6	939.4	926.5
55°	913.7	908.9	886.5	867.3	857.7
57.5°	841.7	836.9	814.5	795.3	785.7
60°	766.5	758.5	737.7	723.3	715.3
62.5°	692.9	686.5	664.1	651.3	643.3
65°	619.3	611.3	595.3	579.3	571.3
67.5°	544.1	537.7	521.7	505.7	504.1
70°	475.3	464.1	451.3	438.5	433.7
72.5°	401.7	390.5	380.9	371.3	366.5
75°	329.7	321.7	313.7	307.2	305.6
77.5°	259.2	256.0	248.0	246.4	241.6
80°	196.8	192.0	188.8	185.6	184.0
82.5°	136.0	134.4	134.4	132.8	131.2
85°	86.4	86.4	83.2	83.2	81.6
87.5°	41.6	40.0	38.4	38.4	38.4
90°	0.4	2.8	6.4	7.1	7.5
92.5°	5.0	27.4	139.4	46.0	32.4
95°	11.7	37.0	289.8	143.4	86.8
97.5°	19.6	40.9	310.1	293.0	208.4
100°	27.0	46.2	285.9	405.4	326.1
102.5°	34.1	52.6	255.7	475.8	428.5
105°	41.6	60.2	233.3	502.3	500.3
107.5°	49.8	68.1	218.7	494.3	534.5
110°	58.0	75.9	211.9	465.8	535.2

TEST NUMBER: P1025136

CATALOG NUMBER: S124DIP-B1195D365UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.8	83.7	208.7	431.0	514.2
115°	73.3	91.9	208.0	399.7	480.4
117.5°	81.1	99.6	207.7	375.2	447.4
120°	88.9	107.0	207.7	358.6	420.3
122.5°	96.0	114.3	207.3	347.8	399.0
125°	102.1	121.2	207.0	340.2	383.3
127.5°	107.7	127.6	206.3	332.8	373.4
130°	112.4	133.8	205.9	324.2	364.9
132.5°	117.0	139.2	205.5	313.8	355.2
135°	121.3	144.4	205.2	301.9	342.8
137.5°	125.5	148.9	205.2	289.1	328.2
140°	130.2	152.9	204.8	276.6	312.2
142.5°	135.1	156.6	204.8	265.1	295.2
145°	139.8	160.0	204.1	254.6	279.9
147.5°	145.1	163.2	203.1	245.9	265.6
150°	150.1	166.2	202.0	237.9	253.9
152.5°	154.7	169.1	200.2	231.2	243.2
155°	159.0	171.6	198.4	224.8	234.3
157.5°	163.2	173.9	196.6	218.7	226.2
160°	167.1	175.9	194.5	212.6	218.7
162.5°	170.7	177.4	192.4	206.8	211.6
165°	173.2	178.5	190.2	201.4	204.5
167.5°	176.0	179.4	188.1	196.9	198.8
170°	177.8	180.1	186.0	192.2	193.4
172.5°	179.6	180.6	183.8	188.2	188.1
175°	180.6	181.0	182.4	184.9	184.2
177.5°	181.4	181.0	181.4	182.6	181.4
180°	181.0	181.0	181.0	181.0	181.0

(END OF REPORT)