

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026216

Luminaire Tested: S124RDIP-B1195D810UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026216
REPORT IS A COMBINATION OF REPORTS P999206 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D810UB35-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7700.7 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026216

CATALOG NUMBER: S124RDIP-B1195D810UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026216

CATALOG NUMBER: S124RDIP-B1195D810UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68
1	101	97	93	89	95	91	88	85	80	78	75	70	68	66	61	59	58
2	92	85	79	74	86	80	75	70	71	66	63	62	59	56	54	52	50
3	84	75	68	62	79	71	64	59	63	57	53	55	51	48	48	45	43
4	77	67	59	53	72	63	56	50	56	50	46	49	45	41	43	40	37
5	71	60	51	45	67	56	49	43	50	44	40	44	40	36	39	35	32
6	66	54	45	40	62	51	43	38	45	39	35	40	35	32	35	32	29
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	32	29	26
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	30	26	23
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21
10	49	37	30	25	46	35	29	24	32	26	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17116	17116	17116
5°	17118	16608	16610
10°	16973	16084	15893
15°	16740	15431	15046
20°	16434	14687	14082
25°	16052	13885	13139
30°	15679	13066	12082
35°	15268	12236	11047
40°	14780	11342	9985
45°	14321	10456	8933
50°	13800	9489	7864
55°	13237	8496	6762
60°	12612	7443	5673
65°	12008	6234	4624
70°	11150	4961	3534
75°	10052	3611	2471
80°	8394	2217	1777
85°	6316	1276	977

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14321 cd/sqm

TEST NUMBER: P1026216

CATALOG NUMBER: S124RDIP-B1195D810UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.4	2.6
10°-20°	550.3	7.1
20°-30°	794.5	10.3
30°-40°	900.5	11.7
40°-50°	869.4	11.3
50°-60°	722.8	9.4
60°-70°	498.9	6.5
70°-80°	252.1	3.3
80°-90°	65.5	0.9
90°-100°	290.0	3.8
100°-110°	589.8	7.7
110°-120°	525.7	6.8
120°-130°	441.6	5.7
130°-140°	368.5	4.8
140°-150°	281.4	3.7
150°-160°	197.8	2.6
160°-170°	116.4	1.5
170°-180°	37.8	0.5
0°-30°	1542.2	20.0
0°-40°	2442.7	31.7
0°-60°	4035.0	52.4
0°-90°	4851.5	63.0
90°-120°	1405.6	18.3
90°-150°	2497.2	32.4
90°-180°	2849.0	37.0
0°-180°	7700.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2099	2099	2099	2099	2099	
5°	2096	2089	2070	2086	2083	199
15°	1996	1982	1942	1938	1927	563
25°	1805	1776	1710	1683	1667	832
35°	1561	1509	1429	1374	1345	975
45°	1273	1213	1117	1038	1009	982
55°	964	900	796	712	682	863
65°	656	587	484	415	395	648
75°	349	289	214	177	167	368
85°	87	55	50	47	47	95
90°	1	6	14	15	16	7
95°	25	80	625	310	187	28
105°	90	130	503	1083	1079	96
115°	158	198	449	862	1036	157
125°	220	262	446	734	827	196
135°	262	311	443	651	739	202
145°	301	345	440	549	604	189
155°	343	370	428	485	506	158
165°	374	385	410	434	441	106
175°	390	390	394	399	397	37
180°	390	390	390	390	390	

TEST NUMBER: P1026216

CATALOG NUMBER: S124RDIP-B1195D810UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2099.0	2099.0	2099.0	2099.0	2099.0
2.5°	2105.4	2099.0	2081.3	2099.0	2097.4
5°	2095.8	2089.4	2070.1	2086.2	2082.9
7.5°	2081.3	2074.9	2050.8	2062.1	2057.2
10°	2058.8	2050.8	2021.9	2028.3	2021.9
12.5°	2029.9	2020.3	1984.9	1988.1	1978.5
15°	1996.2	1981.7	1941.5	1938.3	1927.0
17.5°	1957.6	1936.7	1890.1	1882.0	1866.0
20°	1911.0	1890.1	1835.4	1822.6	1801.7
22.5°	1859.5	1835.4	1776.0	1755.1	1739.0
25°	1804.9	1776.0	1710.1	1682.7	1666.7
27.5°	1748.6	1713.3	1644.2	1612.0	1589.5
30°	1689.2	1649.0	1573.5	1533.3	1507.6
32.5°	1626.5	1579.9	1501.1	1452.9	1428.8
35°	1560.6	1509.2	1428.8	1374.2	1345.2
37.5°	1491.5	1438.5	1350.1	1290.6	1261.7
40°	1417.6	1364.5	1272.9	1205.4	1176.5
42.5°	1346.8	1290.6	1194.2	1125.0	1094.5
45°	1272.9	1213.4	1117.0	1038.3	1009.3
47.5°	1197.4	1136.3	1036.7	954.7	922.5
50°	1120.2	1057.5	954.7	874.3	843.8
52.5°	1041.5	980.4	874.3	792.4	760.2
55°	964.3	900.0	795.6	712.0	681.5
57.5°	888.8	821.3	718.4	633.2	610.7
60°	806.8	742.5	639.7	556.1	530.4
62.5°	732.9	665.4	559.3	483.8	464.5
65°	655.7	586.6	483.8	414.7	395.4
67.5°	575.4	509.5	413.1	352.0	329.5
70°	499.8	432.3	340.7	287.7	271.6
72.5°	419.5	360.0	274.8	231.4	217.0
75°	348.8	289.3	213.8	176.8	167.1
77.5°	274.8	223.4	159.1	133.4	130.2
80°	204.1	157.5	109.3	104.5	102.9
82.5°	143.0	101.3	78.8	75.5	73.9
85°	86.8	54.6	49.8	46.6	46.6
87.5°	37.0	24.1	22.5	20.9	22.5
90°	0.8	6.1	13.8	15.3	16.1
92.5°	10.7	59.0	300.7	99.3	69.8
95°	25.3	79.8	625.1	309.5	187.2
97.5°	42.2	88.2	668.8	632.0	449.5
100°	58.3	99.7	616.7	874.4	703.4
102.5°	73.6	113.5	551.5	1026.2	924.3
105°	89.7	130.0	503.2	1083.4	1079.2
107.5°	107.4	146.9	471.7	1066.2	1152.8
110°	125.0	163.8	457.1	1004.8	1154.4

TEST NUMBER: P1026216

CATALOG NUMBER: S124RDIP-B1195D810UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.9	180.6	450.2	929.6	1109.1
115°	158.0	198.2	448.7	862.1	1036.2
117.5°	174.9	214.8	447.9	809.2	964.9
120°	191.8	230.8	447.9	773.6	906.6
122.5°	207.1	246.6	447.2	750.2	860.6
125°	220.1	261.6	446.4	733.7	826.8
127.5°	232.4	275.4	444.9	718.0	805.4
130°	242.4	288.8	444.1	699.2	787.0
132.5°	252.3	300.2	443.3	676.9	766.2
135°	261.6	311.4	442.6	651.2	739.4
137.5°	270.8	321.0	442.6	623.6	708.0
140°	280.7	329.8	441.8	596.7	673.4
142.5°	291.5	337.8	441.8	571.8	636.6
145°	301.4	345.2	440.3	549.2	603.6
147.5°	312.9	352.0	438.0	530.4	573.0
150°	323.7	358.6	435.7	513.1	547.6
152.5°	333.7	364.7	431.8	498.6	524.6
155°	342.9	370.0	428.0	484.8	505.5
157.5°	352.1	375.1	424.2	471.8	487.8
160°	360.5	379.3	419.6	458.6	471.7
162.5°	368.2	382.8	415.0	446.0	456.4
165°	373.5	385.0	410.4	434.5	441.0
167.5°	379.7	387.0	405.8	424.6	428.8
170°	383.5	388.5	401.1	414.6	417.3
172.5°	387.3	389.6	396.5	405.8	405.8
175°	389.6	390.4	393.5	398.8	397.3
177.5°	391.2	390.4	391.2	393.8	391.2
180°	390.4	390.4	390.4	390.4	390.4

(END OF REPORT)