

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025154

Luminaire Tested: S124DIP-B1195D365UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025154
REPORT IS A COMBINATION OF REPORTS P995589 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B1195D365UB40-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6410.6 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025154

CATALOG NUMBER: S124DIP-B1195D365UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1025154

CATALOG NUMBER: S124DIP-B1195D365UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	80		
1	104	100	96	92	100	96	92	89	88	85	82	80	78	76	74	72	70	67		
2	95	87	81	75	91	84	78	73	77	72	68	71	67	64	65	62	59	56		
3	87	77	69	63	83	74	67	61	68	62	57	62	58	54	57	54	50	47		
4	79	68	60	53	76	65	58	52	60	54	49	56	50	46	51	47	43	41		
5	73	61	52	46	70	59	51	45	54	48	42	50	45	40	46	42	38	35		
6	68	55	46	40	64	53	45	39	49	42	37	45	40	35	42	37	33	31		
7	63	50	41	35	60	48	40	35	45	38	33	41	36	31	38	34	30	28		
8	58	45	37	32	56	44	36	31	41	34	29	38	32	28	35	30	27	25		
9	54	41	34	28	52	40	33	28	37	31	27	35	29	25	33	28	24	22		
10	51	38	31	26	49	37	30	25	35	28	24	32	27	23	30	26	22	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16193	16193	16193
5°	16206	15728	15747
10°	16069	15291	15184
15°	15839	14772	14549
20°	15545	14210	13892
25°	15213	13617	13184
30°	14814	12976	12407
35°	14400	12318	11656
40°	13969	11612	10857
45°	13517	10904	10111
50°	13016	10216	9284
55°	12472	9414	8463
60°	11915	8534	7608
65°	11277	7627	6644
70°	10544	6534	5610
75°	9446	5267	4493
80°	8049	3809	3161
85°	6251	2119	1702

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13517 cd/sqm

TEST NUMBER: P1025154

CATALOG NUMBER: S124DIP-B1195D365UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.2	2.9
10°-20°	527.3	8.2
20°-30°	776.1	12.1
30°-40°	902.1	14.1
40°-50°	902.1	14.1
50°-60°	789.0	12.3
60°-70°	585.7	9.1
70°-80°	332.3	5.2
80°-90°	95.9	1.5
90°-100°	133.6	2.1
100°-110°	271.8	4.2
110°-120°	242.3	3.8
120°-130°	203.5	3.2
130°-140°	169.8	2.6
140°-150°	129.7	2.0
150°-160°	91.2	1.4
160°-170°	53.6	0.8
170°-180°	17.4	0.3
0°-30°	1490.6	23.3
0°-40°	2392.7	37.3
0°-60°	4083.7	63.7
0°-90°	5097.7	79.5
90°-120°	647.7	10.1
90°-150°	1150.7	17.9
90°-180°	1313.0	20.5
0°-180°	6410.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1986	1986	1986	1986	1986	
5°	1984	1978	1960	1978	1975	188
15°	1889	1882	1858	1868	1863	532
25°	1710	1699	1677	1679	1672	787
35°	1472	1461	1438	1427	1419	920
45°	1201	1190	1165	1147	1142	926
55°	909	904	882	862	853	814
65°	616	608	592	576	568	609
75°	328	320	312	306	304	348
85°	86	86	83	83	81	92
90°	0	3	6	7	7	6
95°	12	37	288	143	86	13
105°	41	60	232	499	497	44
115°	73	91	207	397	478	72
125°	101	121	206	338	381	90
135°	120	144	204	300	341	93
145°	139	159	203	253	278	87
155°	158	171	197	223	233	73
165°	172	177	189	200	203	49
175°	180	180	181	184	183	17
180°	180	180	180	180	180	

TEST NUMBER: P1025154

CATALOG NUMBER: S124DIP-B1195D365UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1985.8	1985.8	1985.8	1985.8	1985.8
2.5°	1992.2	1987.4	1969.9	1985.8	1984.2
5°	1984.2	1977.9	1960.4	1977.9	1974.7
7.5°	1969.9	1963.5	1944.5	1958.8	1957.2
10°	1949.2	1942.9	1922.2	1934.9	1931.7
12.5°	1922.2	1915.8	1893.5	1907.9	1903.1
15°	1888.8	1882.4	1858.5	1868.1	1863.3
17.5°	1850.6	1842.6	1820.3	1826.7	1823.5
20°	1807.6	1799.7	1775.8	1780.6	1777.4
22.5°	1761.5	1750.3	1726.5	1736.0	1729.6
25°	1710.5	1699.4	1677.1	1678.7	1672.4
27.5°	1653.3	1642.1	1621.4	1618.3	1610.3
30°	1596.0	1583.2	1562.6	1556.2	1548.2
32.5°	1535.5	1524.4	1502.1	1494.1	1486.2
35°	1471.9	1460.7	1438.4	1427.3	1419.4
37.5°	1405.0	1395.5	1371.6	1360.5	1349.3
40°	1339.8	1327.1	1303.2	1287.3	1279.3
42.5°	1269.8	1263.4	1236.4	1217.3	1212.5
45°	1201.4	1190.2	1164.8	1147.3	1142.5
47.5°	1129.8	1121.8	1097.9	1078.8	1066.1
50°	1056.6	1050.2	1027.9	1005.6	996.1
52.5°	985.0	977.0	953.1	934.0	921.3
55°	908.6	903.8	881.5	862.4	852.9
57.5°	837.0	832.2	809.9	790.8	781.3
60°	762.2	754.2	733.5	719.2	711.3
62.5°	689.0	682.6	660.3	647.6	639.7
65°	615.8	607.8	591.9	576.0	568.1
67.5°	541.0	534.6	518.7	502.8	501.2
70°	472.6	461.4	448.7	436.0	431.2
72.5°	399.4	388.3	378.7	369.2	364.4
75°	327.8	319.8	311.9	305.5	303.9
77.5°	257.8	254.6	246.6	245.0	240.3
80°	195.7	190.9	187.8	184.6	183.0
82.5°	135.3	133.7	133.7	132.1	130.5
85°	85.9	85.9	82.7	82.7	81.2
87.5°	41.4	39.8	38.2	38.2	38.2
90°	0.4	2.8	6.4	7.1	7.4
92.5°	4.9	27.2	138.6	45.8	32.2
95°	11.7	36.8	288.1	142.6	86.2
97.5°	19.4	40.6	308.2	291.2	207.1
100°	26.9	46.0	284.2	403.0	324.1
102.5°	33.9	52.3	254.1	472.9	425.9
105°	41.4	59.9	231.9	499.2	497.3
107.5°	49.5	67.7	217.4	491.2	531.2
110°	57.6	75.4	210.7	463.0	531.9

TEST NUMBER: P1025154

CATALOG NUMBER: S124DIP-B1195D365UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.4	83.2	207.5	428.4	511.1
115°	72.8	91.4	206.8	397.2	477.5
117.5°	80.6	99.0	206.4	372.8	444.6
120°	88.4	106.4	206.4	356.4	417.8
122.5°	95.4	113.6	206.1	345.7	396.6
125°	101.4	120.6	205.7	338.1	381.0
127.5°	107.1	126.8	205.0	330.8	371.1
130°	111.7	133.0	204.6	322.2	362.6
132.5°	116.3	138.4	204.3	312.0	353.1
135°	120.5	143.5	203.9	300.0	340.7
137.5°	124.8	147.9	203.9	287.4	326.2
140°	129.4	152.0	203.6	275.0	310.3
142.5°	134.3	155.7	203.6	263.5	293.4
145°	138.9	159.0	202.9	253.0	278.2
147.5°	144.2	162.2	201.8	244.4	264.0
150°	149.2	165.2	200.8	236.4	252.4
152.5°	153.7	168.1	199.0	229.8	241.8
155°	158.0	170.6	197.2	223.4	232.9
157.5°	162.2	172.8	195.5	217.4	224.8
160°	166.1	174.8	193.3	211.4	217.4
162.5°	169.7	176.4	191.2	205.6	210.3
165°	172.1	177.4	189.1	200.2	203.2
167.5°	175.0	178.3	187.0	195.6	197.6
170°	176.7	179.0	184.9	191.0	192.3
172.5°	178.5	179.6	182.7	187.0	187.0
175°	179.6	179.9	181.3	183.8	183.1
177.5°	180.3	179.9	180.3	181.5	180.3
180°	179.9	179.9	179.9	179.9	179.9

(END OF REPORT)