

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026258

Luminaire Tested: S124RDIP-B350D1035UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026258
REPORT IS A COMBINATION OF REPORTS P999258 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D1035UB50-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4869.0 lumens
Efficiency: N/A
Efficacy: 117.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026258

CATALOG NUMBER: S124RDIP-B350D1035UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026258

CATALOG NUMBER: S124RDIP-B350D1035UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35
1	93	89	85	82	83	80	76	74	62	60	58	46	45	44	32	31	30
2	85	78	72	67	75	70	65	61	55	51	48	41	39	37	28	27	26
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	25	23	22
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19
5	65	54	46	40	58	48	42	37	38	34	30	29	26	23	20	18	17
6	60	48	40	35	53	43	37	32	34	30	26	26	23	20	18	16	15
7	55	43	36	30	49	39	33	28	31	26	23	24	20	18	17	15	13
8	51	39	32	27	45	35	29	25	28	24	20	22	18	16	15	13	12
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	11
10	44	33	26	21	39	30	23	19	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4718	4718	4718
5°	4719	4579	4579
10°	4679	4434	4381
15°	4615	4254	4148
20°	4530	4049	3882
25°	4426	3827	3622
30°	4323	3602	3331
35°	4209	3373	3045
40°	4075	3127	2752
45°	3948	2882	2462
50°	3804	2616	2168
55°	3649	2342	1864
60°	3477	2051	1564
65°	3311	1719	1275
70°	3074	1367	974
75°	2769	995	682
80°	2316	610	491
85°	1739	351	268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3948 cd/sqm

TEST NUMBER: P1026258

CATALOG NUMBER: S124RDIP-B350D1035UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.4	1.1
10°-20°	151.7	3.1
20°-30°	219.0	4.5
30°-40°	248.2	5.1
40°-50°	239.7	4.9
50°-60°	199.3	4.1
60°-70°	137.5	2.8
70°-80°	69.5	1.4
80°-90°	19.5	0.4
90°-100°	359.3	7.4
100°-110°	730.8	15.0
110°-120°	651.4	13.4
120°-130°	547.2	11.2
130°-140°	456.6	9.4
140°-150°	348.7	7.2
150°-160°	245.1	5.0
160°-170°	144.2	3.0
170°-180°	46.9	1.0
0°-30°	425.2	8.7
0°-40°	673.4	13.8
0°-60°	1112.3	22.8
0°-90°	1338.8	27.5
90°-120°	1741.5	35.8
90°-150°	3094.0	63.5
90°-180°	3530.0	72.5
0°-180°	4869.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	579	579	579	579	579	
5°	578	576	571	575	574	55
15°	550	546	535	534	531	155
25°	498	490	471	464	460	229
35°	430	416	394	379	371	269
45°	351	334	308	286	278	271
55°	266	248	219	196	188	238
65°	181	162	133	114	109	179
75°	96	80	59	49	46	101
85°	24	15	14	13	13	26
90°	1	8	17	19	20	3
95°	31	99	774	384	232	34
105°	111	161	623	1342	1337	118
115°	196	246	556	1068	1284	194
125°	273	324	553	909	1024	243
135°	324	386	548	807	916	250
145°	374	428	546	680	748	234
155°	425	459	530	601	626	196
165°	463	477	508	538	546	131
175°	483	484	488	494	492	46
180°	484	484	484	484	484	

TEST NUMBER: P1026258

CATALOG NUMBER: S124RDIP-B350D1035UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	578.6	578.6	578.6	578.6	578.6
2.5°	580.4	578.6	573.8	578.6	578.2
5°	577.7	576.0	570.7	575.1	574.2
7.5°	573.8	572.0	565.3	568.4	567.1
10°	567.6	565.3	557.4	559.1	557.4
12.5°	559.6	556.9	547.2	548.1	545.4
15°	550.3	546.3	535.2	534.3	531.2
17.5°	539.6	533.9	521.0	518.8	514.4
20°	526.8	521.0	506.0	502.4	496.7
22.5°	512.6	506.0	489.6	483.8	479.4
25°	497.6	489.6	471.4	463.9	459.5
27.5°	482.0	472.3	453.3	444.4	438.2
30°	465.7	454.6	433.8	422.7	415.6
32.5°	448.4	435.5	413.8	400.5	393.9
35°	430.2	416.0	393.9	378.8	370.8
37.5°	411.2	396.5	372.2	355.8	347.8
40°	390.8	376.2	350.9	332.3	324.3
42.5°	371.3	355.8	329.2	310.1	301.7
45°	350.9	334.5	307.9	286.2	278.2
47.5°	330.1	313.2	285.8	263.2	254.3
50°	308.8	291.5	263.2	241.0	232.6
52.5°	287.1	270.3	241.0	218.4	209.6
55°	265.8	248.1	219.3	196.3	187.9
57.5°	245.0	226.4	198.0	174.6	168.4
60°	222.4	204.7	176.3	153.3	146.2
62.5°	202.0	183.4	154.2	133.4	128.0
65°	180.8	161.7	133.4	114.3	109.0
67.5°	158.6	140.4	113.9	97.0	90.8
70°	137.8	119.2	93.9	79.3	74.9
72.5°	115.6	99.2	75.8	63.8	59.8
75°	96.1	79.8	58.9	48.7	46.1
77.5°	75.8	61.6	43.9	36.8	35.9
80°	56.3	43.4	30.1	28.8	28.4
82.5°	39.4	27.9	21.7	20.8	20.4
85°	23.9	15.1	13.7	12.8	12.8
87.5°	10.2	6.6	6.2	5.8	6.2
90°	1.0	7.6	17.1	19.0	20.0
92.5°	13.3	73.2	372.5	123.0	86.5
95°	31.4	98.8	774.5	383.5	231.9
97.5°	52.3	109.3	828.7	783.1	556.9
100°	72.2	123.6	764.1	1083.4	871.5
102.5°	91.2	140.6	683.3	1271.6	1145.2
105°	111.2	161.1	623.4	1342.4	1337.1
107.5°	133.0	182.0	584.5	1321.0	1428.4
110°	154.9	202.9	566.4	1245.0	1430.3

TEST NUMBER: P1026258

CATALOG NUMBER: S124RDIP-B350D1035UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	175.8	223.8	557.9	1151.8	1374.2
115°	195.8	245.6	556.0	1068.2	1283.9
117.5°	216.7	266.1	555.0	1002.6	1195.5
120°	237.6	286.0	555.0	958.4	1123.3
122.5°	256.6	305.5	554.1	929.4	1066.3
125°	272.7	324.1	553.1	909.0	1024.5
127.5°	288.0	341.2	551.2	889.5	997.9
130°	300.3	357.8	550.2	866.2	975.1
132.5°	312.7	372.0	549.3	838.7	949.4
135°	324.1	385.8	548.3	806.8	916.1
137.5°	335.5	397.7	548.3	772.6	877.2
140°	347.8	408.6	547.4	739.3	834.4
142.5°	361.1	418.6	547.4	708.5	788.8
145°	373.5	427.6	545.5	680.4	747.9
147.5°	387.7	436.2	542.6	657.2	709.9
150°	401.0	444.3	539.8	635.8	678.5
152.5°	413.4	451.9	535.0	617.8	650.0
155°	424.8	458.6	530.3	600.6	626.3
157.5°	436.2	464.7	525.5	584.4	604.4
160°	446.7	470.0	519.8	568.3	584.5
162.5°	456.2	474.2	514.1	552.6	565.5
165°	462.8	477.0	508.4	538.4	546.4
167.5°	470.4	479.4	502.7	526.0	531.2
170°	475.2	481.4	497.0	513.7	517.0
172.5°	479.9	482.8	491.3	502.8	502.7
175°	482.8	483.7	487.5	494.2	492.3
177.5°	484.7	483.7	484.7	488.0	484.7
180°	483.7	483.7	483.7	483.7	483.7

(END OF REPORT)