

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025267

Luminaire Tested: S124DIP-B350D1035UB30-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025267
REPORT IS A COMBINATION OF REPORTS P995747 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B350D1035UB30-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4951.0 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025267

CATALOG NUMBER: S124DIP-B350D1035UB30-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1025267

CATALOG NUMBER: S124DIP-B350D1035UB30-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34			26
1	92	88	84	80	82	78	75	72	61	58	56	44	43	42	29	29	28			21
2	83	76	70	65	74	68	63	58	53	49	46	39	36	34	26	24	23			17
3	76	67	59	54	67	60	53	48	46	42	38	34	31	29	22	21	19			14
4	69	59	51	45	61	52	46	41	41	36	32	30	27	24	20	18	16			12
5	63	52	44	38	56	47	40	35	36	31	28	27	23	21	18	16	14			10
6	58	46	39	33	52	42	35	30	33	28	24	24	21	18	16	14	12			9
7	54	42	34	29	48	37	31	26	29	24	21	22	18	16	15	13	11			8
8	50	38	30	25	44	34	27	23	27	22	18	20	16	14	13	11	10			7
9	46	34	27	22	41	31	24	20	24	20	16	18	15	12	12	10	9			6
10	43	31	24	20	38	28	22	18	22	18	14	17	13	11	11	9	8			6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3356	3356	3356
5°	3365	3268	3274
10°	3343	3204	3194
15°	3312	3132	3105
20°	3265	3054	3018
25°	3213	2967	2925
30°	3157	2881	2829
35°	3093	2794	2744
40°	3041	2710	2656
45°	2966	2631	2577
50°	2901	2542	2495
55°	2833	2455	2400
60°	2729	2348	2311
65°	2617	2233	2205
70°	2479	2100	2080
75°	2285	1954	1962
80°	2065	1803	1838
85°	1776	1653	1738

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 3392 cd/sqm

TEST NUMBER: P1025267

CATALOG NUMBER: S124DIP-B350D1035UB30-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.0	0.8
10°-20°	111.7	2.3
20°-30°	168.9	3.4
30°-40°	204.4	4.1
40°-50°	216.0	4.4
50°-60°	203.3	4.1
60°-70°	168.7	3.4
70°-80°	118.4	2.4
80°-90°	69.5	1.4
90°-100°	123.0	2.5
100°-110°	278.9	5.6
110°-120°	443.6	9.0
120°-130°	570.0	11.5
130°-140°	632.6	12.8
140°-150°	617.9	12.5
150°-160°	518.9	10.5
160°-170°	345.3	7.0
170°-180°	120.9	2.4
0°-30°	319.6	6.5
0°-40°	524.0	10.6
0°-60°	943.3	19.1
0°-90°	1299.9	26.3
90°-120°	845.5	17.1
90°-150°	2666.0	53.8
90°-180°	3651.0	73.7
0°-180°	4951.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	412	412	412	412	412	
5°	412	411	407	411	411	39
15°	395	395	394	398	398	111
25°	361	364	365	370	371	166
35°	316	322	326	333	334	198
45°	264	272	281	289	291	204
55°	206	216	230	239	242	184
65°	143	158	173	185	188	142
75°	79	96	116	129	133	84
85°	24	44	64	78	83	25
90°	10	40	67	87	92	9
95°	65	89	115	131	135	69
105°	234	245	266	280	287	249
115°	434	438	451	460	462	428
125°	629	629	639	646	647	561
135°	810	816	819	825	825	627
145°	984	987	988	990	989	616
155°	1126	1126	1126	1130	1126	518
165°	1226	1223	1221	1227	1223	346
175°	1276	1271	1270	1277	1270	121
180°	1278	1278	1278	1278	1278	

TEST NUMBER: P1025267

CATALOG NUMBER: S124DIP-B350D1035UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	411.5	411.5	411.5	411.5	411.5
2.5°	413.4	412.0	408.3	411.5	411.0
5°	412.0	410.6	407.4	411.0	410.6
7.5°	409.2	408.3	405.5	409.7	409.2
10°	405.5	405.1	402.8	406.9	406.4
12.5°	400.4	400.4	399.1	402.8	402.8
15°	394.9	395.4	394.0	398.1	397.7
17.5°	387.5	388.9	388.5	392.6	392.2
20°	379.7	381.1	381.6	386.2	386.2
22.5°	371.0	372.8	373.7	378.3	379.3
25°	361.3	364.0	365.4	370.5	371.0
27.5°	350.7	354.8	356.7	361.3	361.7
30°	340.1	343.8	347.0	352.1	353.0
32.5°	328.6	333.2	336.9	342.8	343.8
35°	316.1	321.6	326.3	332.7	334.1
37.5°	303.7	310.1	315.7	322.1	323.5
40°	291.7	297.7	304.1	311.1	312.9
42.5°	277.9	284.8	292.6	300.5	301.8
45°	263.6	272.3	281.1	288.9	291.2
47.5°	250.2	259.0	269.1	277.0	279.7
50°	235.5	245.6	255.8	265.0	267.7
52.5°	220.7	230.9	242.8	252.1	254.8
55°	206.4	216.1	229.9	239.2	241.9
57.5°	190.3	202.3	215.7	226.7	229.0
60°	174.6	186.6	201.8	212.4	216.1
62.5°	159.4	172.8	188.0	198.6	202.3
65°	142.9	157.6	173.3	184.8	188.5
67.5°	127.2	142.9	159.4	171.0	174.6
70°	111.1	126.7	144.2	156.7	159.9
72.5°	95.4	111.5	130.4	142.4	146.1
75°	79.3	96.3	115.7	128.6	132.7
77.5°	64.1	82.0	102.3	115.2	119.8
80°	50.2	68.7	88.9	102.8	106.4
82.5°	36.4	55.8	76.0	90.3	94.5
85°	24.4	43.8	64.5	78.3	82.9
87.5°	15.2	34.1	54.4	67.7	71.9
90°	10.4	39.6	67.3	86.7	92.3
92.5°	32.6	61.5	86.4	102.2	106.8
95°	65.3	89.4	115.2	130.6	134.8
97.5°	100.4	121.7	148.5	164.4	168.5
100°	143.4	159.4	186.2	200.7	203.9
102.5°	188.9	200.0	225.4	240.4	245.1
105°	234.4	244.6	265.6	280.1	286.7
107.5°	282.8	291.7	308.7	324.2	326.5
110°	331.8	340.2	355.4	364.0	370.7

TEST NUMBER: P1025267

CATALOG NUMBER: S124DIP-B350D1035UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	382.7	388.3	401.5	411.6	415.3
115°	433.7	437.8	450.6	459.7	461.9
117.5°	482.1	484.8	497.7	504.3	505.1
120°	530.0	535.4	545.8	550.0	555.7
122.5°	580.4	581.4	592.8	599.1	597.4
125°	629.3	628.9	639.4	646.2	647.0
127.5°	673.8	676.3	683.6	689.9	692.1
130°	720.8	723.3	730.7	737.0	735.8
132.5°	769.2	770.7	775.3	781.1	783.0
135°	810.2	816.2	819.4	824.8	824.6
137.5°	856.7	859.2	863.0	867.0	870.2
140°	903.1	904.7	905.1	910.1	911.4
142.5°	945.2	947.2	945.7	950.8	952.6
145°	983.8	987.2	988.2	990.0	988.8
147.5°	1023.3	1027.7	1026.7	1026.3	1027.1
150°	1058.9	1062.3	1062.3	1062.3	1061.3
152.5°	1092.0	1093.9	1094.9	1097.9	1094.9
155°	1126.5	1126.5	1125.6	1129.5	1125.6
157.5°	1156.2	1154.2	1154.2	1157.2	1154.2
160°	1181.9	1180.9	1179.9	1182.9	1177.9
162.5°	1205.6	1202.6	1201.7	1207.6	1202.6
165°	1226.4	1223.4	1221.4	1227.3	1223.4
167.5°	1243.2	1239.2	1239.2	1245.1	1239.2
170°	1257.0	1252.1	1253.0	1259.0	1252.1
172.5°	1266.9	1262.9	1262.9	1269.8	1262.9
175°	1275.8	1270.8	1269.8	1276.8	1269.8
177.5°	1279.7	1274.8	1274.8	1281.7	1273.8
180°	1277.7	1277.7	1277.7	1277.7	1277.7

(END OF REPORT)