

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026272

Luminaire Tested: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026272
REPORT IS A COMBINATION OF REPORTS P999282 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5639.0 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026272

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1026272

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	93	89	85	82	82	79	76	73	61	59	58	45	44	43	30	30	29
2	84	78	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25
3	77	68	61	56	69	61	55	51	48	44	41	35	33	31	24	23	21
4	71	60	53	47	63	54	48	43	43	38	35	32	29	26	22	20	19
5	65	54	46	40	58	48	42	37	38	33	30	28	25	23	19	18	16
6	60	48	40	35	53	43	37	32	34	29	26	26	23	20	18	16	14
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13
8	51	39	32	27	45	35	29	25	28	23	20	21	18	16	15	13	11
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10
10	44	33	26	21	39	30	23	19	24	19	16	18	15	13	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4684	4684	4684	4684
5°	4684	5292	4692	4045
10°	4659	6101	4655	3518
15°	4603	6866	4603	2945
20°	4546	7445	4522	2594
25°	4474	7477	4454	2342
30°	4400	6357	4365	2170
35°	4293	4797	4238	2041
40°	4175	3476	4092	1940
45°	3978	2642	3879	1851
50°	3746	2135	3644	1721
55°	3495	1768	3380	1548
60°	3242	1495	3097	1287
65°	2925	1217	2831	1023
70°	2633	987	2510	831
75°	2308	711	2147	609
80°	1904	472	1732	447
85°	1383	243	1142	243

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 5864 cd/sqm

TEST NUMBER: P1026272

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.6	1.0
10°-20°	168.0	3.0
20°-30°	263.1	4.7
30°-40°	292.2	5.2
40°-50°	258.9	4.6
50°-60°	201.8	3.6
60°-70°	132.0	2.3
70°-80°	64.8	1.1
80°-90°	19.0	0.3
90°-100°	98.3	1.7
100°-110°	294.4	5.2
110°-120°	500.1	8.9
120°-130°	659.6	11.7
130°-140°	740.8	13.1
140°-150°	728.1	12.9
150°-160°	612.4	10.9
160°-170°	407.5	7.2
170°-180°	142.7	2.5
0°-30°	486.7	8.6
0°-40°	778.8	13.8
0°-60°	1239.5	22.0
0°-90°	1455.2	25.8
90°-120°	892.8	15.8
90°-150°	3021.3	53.6
90°-180°	4184.0	74.2
0°-180°	5639.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	574	574	574	574	574	
5°	574	664	574	507	574	54
15°	549	879	549	377	549	155
25°	503	948	501	297	503	232
35°	439	584	433	248	439	274
45°	354	298	345	209	354	273
55°	255	178	246	156	255	228
65°	160	104	155	88	160	159
75°	80	48	74	41	80	85
85°	19	12	16	12	19	21
90°	4	35	4	35	4	6
95°	70	92	70	92	70	76
105°	272	284	272	284	272	288
115°	508	504	508	504	508	501
125°	740	735	740	735	740	660
135°	955	956	955	956	955	739
145°	1160	1162	1160	1162	1160	726
155°	1329	1328	1329	1328	1329	612
165°	1447	1444	1447	1444	1447	408
175°	1506	1498	1506	1498	1506	143
180°	1508	1508	1508	1508	1508	

TEST NUMBER: P1026272

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4
2.5°	575.3	580.4	583.2	585.5	590.1	592.0	595.7	596.6	600.3	599.9	598.5
5°	573.5	582.3	588.7	595.7	604.0	608.6	613.7	621.1	624.8	629.9	633.2
7.5°	570.2	582.3	592.9	603.6	617.0	624.4	630.9	642.4	652.2	660.5	669.7
10°	565.1	580.4	596.1	610.5	629.0	637.8	647.5	664.6	678.1	689.6	704.5
12.5°	557.3	578.6	596.1	615.6	639.2	651.2	664.2	684.6	700.3	719.3	737.8
15°	548.9	572.5	595.7	621.1	648.0	661.9	674.8	702.1	726.2	748.0	768.3
17.5°	539.7	565.6	591.1	619.3	651.7	668.8	684.1	717.0	743.3	771.6	791.9
20°	528.6	556.8	586.0	617.4	654.0	673.0	690.1	727.6	756.8	787.3	812.8
22.5°	516.5	547.1	579.0	613.3	651.2	672.1	692.0	732.2	766.0	794.2	828.5
25°	503.1	535.5	568.4	604.5	647.1	669.7	690.1	729.9	766.0	803.0	836.4
27.5°	489.2	522.6	556.8	594.8	638.3	660.5	683.6	722.0	764.2	804.4	838.2
30°	474.0	506.4	542.5	578.6	624.8	647.1	670.7	712.3	758.1	798.4	835.0
32.5°	457.3	490.6	524.9	562.4	607.7	631.8	653.5	700.8	747.5	787.3	821.6
35°	438.8	470.3	502.7	541.1	586.0	607.7	633.6	682.7	729.9	772.0	794.2
37.5°	418.9	449.0	479.0	517.0	560.0	586.4	611.9	661.4	711.4	739.6	751.2
40°	400.4	426.7	453.1	489.7	533.2	560.5	586.4	637.8	681.8	703.5	694.7
42.5°	376.8	404.1	427.7	461.5	505.4	530.9	557.3	610.5	646.1	654.9	633.2
45°	353.6	376.3	399.0	431.8	478.1	499.9	528.1	577.6	607.3	599.4	567.5
47.5°	330.9	349.4	370.7	402.7	444.3	470.3	496.6	539.7	560.5	549.4	505.0
50°	304.1	322.6	344.8	372.6	412.9	437.9	458.7	498.5	514.2	486.9	433.2
52.5°	278.6	294.8	313.8	339.7	378.1	400.8	423.5	457.8	462.8	431.4	374.9
55°	254.6	267.5	287.4	308.3	343.4	367.5	383.2	412.4	411.0	371.7	323.1
57.5°	229.6	241.6	255.0	276.8	310.1	328.2	345.3	370.7	357.3	324.0	275.9
60°	207.4	214.3	227.7	248.5	276.8	292.5	305.9	319.8	308.3	272.2	235.1
62.5°	182.8	190.7	200.4	217.1	242.1	256.9	266.6	272.6	260.6	232.8	199.0
65°	159.7	166.6	176.8	191.6	210.6	221.7	226.8	231.0	224.5	193.0	166.2
67.5°	138.9	143.5	152.7	162.5	182.8	185.6	192.5	194.4	181.4	157.4	136.1
70°	118.0	122.7	126.8	138.4	147.6	152.7	154.1	154.1	141.2	125.4	107.8
72.5°	98.6	101.4	105.5	113.4	118.5	122.2	124.0	121.7	109.7	96.7	83.8
75°	80.1	81.5	85.2	90.3	94.4	93.0	92.6	89.8	81.0	71.7	64.3
77.5°	61.6	62.5	66.7	68.0	68.0	69.4	67.6	64.8	57.4	50.5	47.2
80°	46.3	47.7	48.1	49.1	48.1	48.1	46.7	42.1	38.4	35.2	32.9
82.5°	31.9	32.9	33.3	31.9	32.9	31.5	29.2	25.9	23.6	23.1	22.2
85°	19.0	19.4	19.0	19.0	17.6	17.1	15.3	14.8	13.9	13.9	13.4
87.5°	9.3	8.8	7.9	6.9	6.9	6.5	6.9	6.0	6.9	6.5	6.0
90°	3.5	6.3	9.2	12.0	14.9	16.3	17.3	19.4	21.5	23.6	25.7
92.5°	30.3	33.7	37.1	40.4	43.8	45.5	46.1	47.4	48.7	50.0	51.3
95°	70.0	72.3	74.7	77.0	79.3	80.5	81.4	83.2	85.0	86.8	88.6
97.5°	112.0	114.1	116.1	118.2	120.3	121.3	122.3	124.4	126.5	128.5	130.6
100°	163.3	164.3	165.3	166.4	167.4	167.9	169.1	171.4	173.7	176.1	178.4
102.5°	216.9	217.2	217.4	217.7	218.0	218.1	219.1	221.2	223.3	225.3	227.4
105°	271.7	272.0	272.2	272.5	272.8	272.9	273.4	274.5	275.5	276.6	277.6
107.5°	328.9	329.1	329.4	329.6	329.9	330.0	330.1	330.4	330.7	330.9	331.2
110°	387.2	387.7	388.2	388.7	389.2	389.5	389.4	389.1	388.8	388.6	388.3

TEST NUMBER: P1026272

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	447.8	447.8	447.8	447.8	447.8	447.8	447.5	447.0	446.5	446.0	445.5
115°	508.5	508.5	508.5	508.5	508.5	508.5	508.2	507.7	507.2	506.6	506.1
117.5°	565.6	565.6	565.6	565.6	565.6	565.6	565.5	565.2	564.9	564.7	564.4
120°	622.7	623.7	624.8	625.8	626.9	627.4	627.0	626.2	625.5	624.7	623.9
122.5°	682.2	682.5	682.7	683.0	683.3	683.4	683.3	683.0	682.7	682.5	682.2
125°	740.5	740.5	740.5	740.5	740.5	740.5	740.4	740.1	739.9	739.6	739.4
127.5°	793.0	793.8	794.6	795.3	796.1	796.5	796.2	795.7	795.2	794.7	794.2
130°	849.0	849.8	850.6	851.3	852.1	852.5	852.5	852.5	852.5	852.5	852.5
132.5°	906.1	906.6	907.2	907.7	908.2	908.5	908.4	908.1	907.8	907.6	907.3
135°	955.1	956.7	958.2	959.8	961.3	962.1	962.1	962.1	962.1	962.1	962.1
137.5°	1009.9	1010.7	1011.5	1012.2	1013.0	1013.4	1013.7	1014.2	1014.7	1015.2	1015.7
140°	1064.7	1065.2	1065.8	1066.3	1066.8	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1
142.5°	1114.9	1115.4	1115.9	1116.4	1116.9	1117.2	1117.1	1116.8	1116.5	1116.3	1116.0
145°	1160.3	1161.3	1162.4	1163.4	1164.5	1165.0	1165.1	1165.4	1165.7	1165.9	1166.2
147.5°	1207.0	1208.3	1209.6	1210.9	1212.2	1212.8	1212.7	1212.4	1212.2	1211.9	1211.7
150°	1249.0	1250.0	1251.0	1252.1	1253.1	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6
152.5°	1288.6	1289.1	1289.7	1290.2	1290.7	1291.0	1291.1	1291.4	1291.6	1291.9	1292.1
155°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.3	1329.0	1328.8	1328.5	1328.3
157.5°	1364.4	1363.9	1363.4	1362.9	1362.4	1362.1	1362.1	1362.1	1362.1	1362.1	1362.1
160°	1394.7	1394.5	1394.2	1394.0	1393.7	1393.6	1393.5	1393.2	1392.9	1392.7	1392.4
162.5°	1422.7	1421.9	1421.1	1420.4	1419.6	1419.2	1419.1	1418.8	1418.6	1418.3	1418.1
165°	1447.2	1446.4	1445.6	1444.9	1444.1	1443.7	1443.4	1442.9	1442.4	1441.9	1441.4
167.5°	1467.1	1466.1	1465.0	1464.0	1462.9	1462.4	1462.4	1462.4	1462.4	1462.4	1462.4
170°	1483.4	1482.1	1480.8	1479.5	1478.2	1477.5	1477.6	1477.9	1478.2	1478.4	1478.7
172.5°	1495.0	1494.0	1493.0	1491.9	1490.9	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
175°	1505.5	1504.2	1502.9	1501.6	1500.3	1499.7	1499.6	1499.3	1499.0	1498.8	1498.5
177.5°	1510.2	1508.9	1507.6	1506.3	1505.0	1504.4	1504.4	1504.4	1504.4	1504.4	1504.4
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9

TEST NUMBER: P1026272

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4
2.5°	602.2	607.3	607.7	612.3	611.0	608.6	612.8	610.0	615.6	613.7	616.1
5°	637.3	644.3	650.3	654.0	660.5	659.1	666.0	663.7	668.8	663.7	670.2
7.5°	678.5	690.1	696.1	705.8	708.6	709.1	717.4	719.3	722.5	719.3	723.0
10°	718.8	732.7	746.6	754.4	759.5	766.5	773.9	777.1	779.4	776.2	778.5
12.5°	755.4	777.1	792.4	808.1	811.8	817.9	825.7	824.8	834.1	832.2	836.4
15°	789.2	813.2	831.7	844.2	854.4	859.5	874.3	875.2	874.8	879.4	876.6
17.5°	819.2	839.6	866.0	882.2	894.7	894.7	903.0	920.1	918.8	918.3	921.1
20°	843.8	866.9	891.4	918.8	928.9	930.8	942.4	951.2	952.5	952.5	952.5
22.5°	862.3	889.6	916.0	935.4	943.3	949.8	959.9	965.5	967.4	966.4	967.4
25°	871.5	897.5	924.3	941.9	946.5	950.2	951.2	954.4	953.9	948.4	951.6
27.5°	873.4	898.4	916.0	920.6	918.3	916.0	901.2	902.6	898.4	890.1	893.3
30°	865.1	878.5	878.0	863.7	859.5	849.8	836.4	816.5	800.3	793.3	795.6
32.5°	835.0	835.0	818.3	785.9	771.6	754.0	729.9	711.9	690.6	685.9	694.7
35°	793.3	769.7	739.2	696.6	674.8	661.9	620.2	607.3	589.2	584.1	588.3
37.5°	728.5	689.2	644.7	604.9	586.4	563.3	526.7	508.2	495.2	486.5	490.6
40°	655.9	608.2	561.9	512.8	492.5	473.5	446.2	429.5	408.7	409.6	411.0
42.5°	586.4	530.4	478.6	433.2	413.8	398.0	379.1	358.7	351.3	349.0	346.7
45°	512.8	453.1	404.5	370.7	353.2	338.3	320.8	309.2	300.4	298.5	300.9
47.5°	443.4	393.0	346.7	315.2	300.9	293.4	279.6	268.9	263.4	258.7	261.5
50°	380.5	333.3	296.2	269.8	259.7	254.6	241.6	236.1	230.5	229.1	228.6
52.5°	328.6	288.4	256.4	235.1	227.3	224.5	214.8	206.9	202.3	203.7	204.6
55°	281.4	247.2	222.2	205.0	198.6	195.3	188.4	182.8	179.6	178.2	179.1
57.5°	239.8	210.1	192.1	178.2	173.1	171.7	164.3	162.5	160.1	158.8	158.8
60°	201.8	181.0	164.3	156.4	150.9	149.5	143.9	141.6	141.2	139.8	138.9
62.5°	169.9	152.7	141.2	132.8	130.5	130.1	126.4	123.6	122.2	121.3	121.3
65°	142.1	129.6	119.9	113.9	112.0	111.1	106.9	106.0	105.1	104.1	103.7
67.5°	118.5	107.4	100.4	96.3	94.0	94.4	92.1	90.3	90.3	89.8	89.3
70°	95.8	88.9	82.8	80.5	79.6	78.7	77.8	76.4	75.9	75.9	75.9
72.5°	75.4	70.8	67.6	66.2	65.3	64.3	63.4	63.4	63.4	62.9	62.9
75°	57.9	56.0	53.7	52.3	52.3	53.2	51.8	50.5	49.1	48.1	48.6
77.5°	43.5	42.6	41.2	38.9	39.3	38.4	38.4	37.5	38.0	38.0	37.0
80°	31.9	30.5	30.1	28.7	29.2	28.7	28.2	28.2	27.3	27.3	27.3
82.5°	22.2	20.8	20.8	20.4	19.9	19.9	19.4	19.4	19.9	19.0	19.0
85°	13.4	13.0	13.0	12.0	12.0	12.0	12.0	12.5	12.0	11.6	11.6
87.5°	6.0	6.5	6.0	5.6	5.6	5.6	5.1	5.1	4.6	5.1	5.1
90°	27.3	28.8	30.4	31.9	32.7	33.0	33.5	34.0	34.5	35.0	34.5
92.5°	52.1	52.9	53.6	54.4	54.8	54.9	55.2	55.5	55.7	56.0	55.7
95°	89.4	90.2	90.9	91.7	92.1	92.1	92.1	92.1	92.1	92.1	92.1
97.5°	131.6	132.7	133.7	134.8	135.3	135.3	135.3	135.3	135.3	135.3	135.3
100°	178.9	179.5	180.0	180.5	180.8	180.8	180.8	180.8	180.8	180.8	180.8
102.5°	228.2	229.0	229.7	230.5	230.9	231.0	231.3	231.6	231.8	232.1	231.8
105°	278.4	279.1	279.9	280.6	281.0	281.4	282.2	282.9	283.7	284.5	283.7
107.5°	332.2	333.3	334.3	335.4	335.9	335.8	335.5	335.2	335.0	334.7	335.0
110°	387.8	387.3	386.8	386.3	386.0	386.4	387.2	387.9	388.7	389.5	388.7

TEST NUMBER: P1026272

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5
115°	505.9	505.6	505.4	505.1	505.0	504.9	504.6	504.3	504.1	503.8	504.1
117.5°	563.6	562.8	562.1	561.3	560.9	560.5	559.7	559.0	558.2	557.4	558.2
120°	622.6	621.3	620.0	618.7	618.1	618.4	618.9	619.4	619.9	620.4	619.9
122.5°	681.4	680.6	679.9	679.1	678.7	678.1	676.8	675.5	674.2	672.9	674.2
125°	738.9	738.3	737.8	737.3	737.0	736.7	736.2	735.7	735.2	734.7	735.2
127.5°	793.7	793.1	792.6	792.1	791.8	791.7	791.4	791.2	790.9	790.7	790.9
130°	852.0	851.4	850.9	850.4	850.1	849.6	848.6	847.5	846.5	845.5	846.5
132.5°	906.8	906.3	905.8	905.3	905.0	904.9	904.6	904.3	904.1	903.8	904.1
135°	961.6	961.1	960.6	960.1	959.8	959.4	958.6	957.9	957.1	956.3	957.1
137.5°	1014.9	1014.1	1013.4	1012.6	1012.2	1012.3	1012.6	1012.9	1013.1	1013.4	1013.1
140°	1066.8	1066.6	1066.3	1066.0	1065.9	1065.8	1065.5	1065.2	1065.0	1064.7	1065.0
142.5°	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0
145°	1165.9	1165.7	1165.4	1165.1	1165.0	1164.6	1163.8	1163.1	1162.3	1161.5	1162.3
147.5°	1211.4	1211.2	1210.9	1210.6	1210.5	1210.4	1210.1	1209.8	1209.6	1209.3	1209.6
150°	1253.6	1253.6	1253.6	1253.6	1253.6	1253.5	1253.2	1253.0	1252.7	1252.5	1252.7
152.5°	1292.9	1293.7	1294.4	1295.2	1295.6	1295.2	1294.4	1293.7	1292.9	1292.1	1292.9
155°	1329.3	1330.3	1331.4	1332.4	1332.9	1332.4	1331.4	1330.3	1329.3	1328.3	1329.3
157.5°	1362.9	1363.7	1364.4	1365.2	1365.6	1365.2	1364.4	1363.7	1362.9	1362.1	1362.9
160°	1393.2	1394.0	1394.7	1395.5	1395.9	1395.3	1394.0	1392.7	1391.4	1390.1	1391.4
162.5°	1419.7	1421.2	1422.8	1424.3	1425.1	1424.4	1423.1	1421.8	1420.5	1419.2	1420.5
165°	1443.0	1444.5	1446.1	1447.6	1448.4	1447.9	1446.8	1445.8	1444.7	1443.7	1444.7
167.5°	1464.0	1465.5	1467.1	1468.6	1469.4	1468.6	1467.1	1465.5	1464.0	1462.4	1464.0
170°	1480.3	1481.8	1483.4	1484.9	1485.7	1484.8	1483.0	1481.1	1479.3	1477.5	1479.3
172.5°	1492.2	1494.0	1495.8	1497.6	1498.5	1497.6	1495.8	1494.0	1492.2	1490.4	1492.2
175°	1500.3	1502.1	1504.0	1505.8	1506.7	1505.8	1504.0	1502.1	1500.3	1498.5	1500.3
177.5°	1506.2	1508.0	1509.8	1511.6	1512.5	1511.5	1509.4	1507.3	1505.3	1503.2	1505.3
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9

TEST NUMBER: P1026272

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4
2.5°	617.4	614.2	613.7	613.7	608.6	611.4	605.9	599.9	597.1	597.1	592.0
5°	668.8	665.6	662.3	657.2	657.2	654.5	645.7	636.9	630.4	624.8	618.8
7.5°	721.6	718.3	709.1	704.0	706.8	701.2	689.6	674.8	663.7	654.9	642.4
10°	779.0	770.2	765.5	762.8	753.1	747.0	733.6	711.9	698.0	686.4	670.2
12.5°	825.7	828.5	810.9	812.3	802.6	794.2	773.4	752.6	731.8	715.6	691.5
15°	876.2	867.8	857.2	848.9	845.6	835.4	817.9	790.1	767.4	741.9	714.6
17.5°	916.0	909.5	899.3	891.4	884.5	860.0	845.2	820.6	789.6	764.6	731.3
20°	949.8	943.7	929.4	924.3	911.8	894.2	872.9	835.0	807.2	779.9	747.5
22.5°	964.1	958.1	945.6	939.1	931.2	914.1	893.8	857.7	823.4	789.2	754.9
25°	952.1	952.1	946.1	943.7	936.8	921.5	900.7	870.2	833.6	796.6	755.8
27.5°	893.8	905.3	909.5	911.8	911.8	912.3	897.9	868.3	832.7	796.6	754.0
30°	809.5	829.0	846.1	851.2	860.0	869.7	875.7	861.4	829.4	791.5	748.9
32.5°	703.5	728.5	760.5	768.3	780.4	809.5	825.7	831.7	814.1	780.8	735.5
35°	598.0	629.5	648.9	673.0	684.1	727.1	763.2	785.0	780.8	760.9	719.7
37.5°	505.9	523.9	547.5	573.0	595.2	636.4	681.3	723.4	740.6	730.8	699.8
40°	417.5	438.8	467.0	487.8	503.1	544.3	599.9	645.7	683.2	689.2	670.2
42.5°	355.0	376.3	393.4	416.1	428.1	467.9	517.0	574.4	618.8	642.4	634.1
45°	306.9	319.8	333.7	346.7	361.5	396.7	442.0	505.0	555.0	588.3	591.5
47.5°	264.7	276.3	288.4	300.4	308.7	336.0	377.7	429.1	483.7	529.5	547.5
50°	235.1	240.7	249.5	256.4	266.1	289.7	323.1	367.5	425.4	474.9	498.5
52.5°	206.0	212.9	219.9	225.9	232.3	249.0	279.6	318.0	368.0	418.9	448.0
55°	181.4	187.0	193.5	197.6	201.3	216.1	239.3	268.9	312.0	360.1	396.2
57.5°	161.5	163.8	169.4	171.7	175.9	187.9	204.6	231.0	265.7	312.4	342.0
60°	139.8	144.4	148.6	150.4	153.7	162.0	173.6	198.1	228.2	262.4	296.2
62.5°	122.2	124.0	127.3	129.6	131.9	140.7	150.4	168.9	191.6	220.3	251.3
65°	106.0	106.9	108.8	112.0	113.4	119.9	125.4	138.9	160.1	181.9	212.9
67.5°	89.3	90.3	92.6	94.4	95.8	100.0	106.0	115.7	127.3	151.4	168.5
70°	76.4	76.4	77.8	78.7	80.1	81.9	85.2	92.6	103.2	118.5	134.2
72.5°	63.9	63.9	63.9	65.3	65.3	66.7	68.5	73.6	81.0	93.0	103.2
75°	49.5	50.0	50.9	50.9	51.4	53.2	54.6	56.0	59.7	67.6	76.8
77.5°	37.5	38.4	38.9	38.0	38.9	38.9	40.7	42.6	44.4	46.7	53.7
80°	27.8	28.2	27.3	27.8	27.8	28.7	29.6	29.2	30.1	32.9	34.7
82.5°	18.5	19.0	19.0	19.0	19.0	20.4	20.4	19.9	20.4	20.8	21.3
85°	11.6	11.1	11.1	11.6	11.1	11.1	11.6	12.0	11.6	12.0	12.5
87.5°	5.1	5.1	5.1	5.1	4.6	4.6	5.1	4.6	5.1	4.6	4.2
90°	34.0	33.5	33.0	32.7	31.9	30.4	28.8	27.3	25.7	23.6	21.5
92.5°	55.5	55.2	54.9	54.8	54.4	53.6	52.9	52.1	51.3	50.0	48.7
95°	92.1	92.1	92.1	92.1	91.7	90.9	90.2	89.4	88.6	86.8	85.0
97.5°	135.3	135.3	135.3	135.3	134.8	133.7	132.7	131.6	130.6	128.5	126.5
100°	180.8	180.8	180.8	180.8	180.5	180.0	179.5	178.9	178.4	176.1	173.7
102.5°	231.6	231.3	231.0	230.9	230.5	229.7	229.0	228.2	227.4	225.3	223.3
105°	282.9	282.2	281.4	281.0	280.6	279.9	279.1	278.4	277.6	276.6	275.5
107.5°	335.2	335.5	335.8	335.9	335.4	334.3	333.3	332.2	331.2	330.9	330.7
110°	387.9	387.2	386.4	386.0	386.3	386.8	387.3	387.8	388.3	388.6	388.8

TEST NUMBER: P1026272

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	446.0	446.5
115°	504.3	504.6	504.9	505.0	505.1	505.4	505.6	505.9	506.1	506.6	507.2
117.5°	559.0	559.7	560.5	560.9	561.3	562.1	562.8	563.6	564.4	564.7	564.9
120°	619.4	618.9	618.4	618.1	618.7	620.0	621.3	622.6	623.9	624.7	625.5
122.5°	675.5	676.8	678.1	678.7	679.1	679.9	680.6	681.4	682.2	682.5	682.7
125°	735.7	736.2	736.7	737.0	737.3	737.8	738.3	738.9	739.4	739.6	739.9
127.5°	791.2	791.4	791.7	791.8	792.1	792.6	793.1	793.7	794.2	794.7	795.2
130°	847.5	848.6	849.6	850.1	850.4	850.9	851.4	852.0	852.5	852.5	852.5
132.5°	904.3	904.6	904.9	905.0	905.3	905.8	906.3	906.8	907.3	907.6	907.8
135°	957.9	958.6	959.4	959.8	960.1	960.6	961.1	961.6	962.1	962.1	962.1
137.5°	1012.9	1012.6	1012.3	1012.2	1012.6	1013.4	1014.1	1014.9	1015.7	1015.2	1014.7
140°	1065.2	1065.5	1065.8	1065.9	1066.0	1066.3	1066.6	1066.8	1067.1	1067.1	1067.1
142.5°	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.3	1116.5
145°	1163.1	1163.8	1164.6	1165.0	1165.1	1165.4	1165.7	1165.9	1166.2	1165.9	1165.7
147.5°	1209.8	1210.1	1210.4	1210.5	1210.6	1210.9	1211.2	1211.4	1211.7	1211.9	1212.2
150°	1253.0	1253.2	1253.5	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6
152.5°	1293.7	1294.4	1295.2	1295.6	1295.2	1294.4	1293.7	1292.9	1292.1	1291.9	1291.6
155°	1330.3	1331.4	1332.4	1332.9	1332.4	1331.4	1330.3	1329.3	1328.3	1328.5	1328.8
157.5°	1363.7	1364.4	1365.2	1365.6	1365.2	1364.4	1363.7	1362.9	1362.1	1362.1	1362.1
160°	1392.7	1394.0	1395.3	1395.9	1395.5	1394.7	1394.0	1393.2	1392.4	1392.7	1392.9
162.5°	1421.8	1423.1	1424.4	1425.1	1424.3	1422.8	1421.2	1419.7	1418.1	1418.3	1418.6
165°	1445.8	1446.8	1447.9	1448.4	1447.6	1446.1	1444.5	1443.0	1441.4	1441.9	1442.4
167.5°	1465.5	1467.1	1468.6	1469.4	1468.6	1467.1	1465.5	1464.0	1462.4	1462.4	1462.4
170°	1481.1	1483.0	1484.8	1485.7	1484.9	1483.4	1481.8	1480.3	1478.7	1478.4	1478.2
172.5°	1494.0	1495.8	1497.6	1498.5	1497.6	1495.8	1494.0	1492.2	1490.4	1490.4	1490.4
175°	1502.1	1504.0	1505.8	1506.7	1505.8	1504.0	1502.1	1500.3	1498.5	1498.8	1499.0
177.5°	1507.3	1509.4	1511.5	1512.5	1511.6	1509.8	1508.0	1506.2	1504.4	1504.4	1504.4
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9

TEST NUMBER: P1026272

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4
2.5°	589.2	586.9	585.5	585.0	580.9	578.6	577.2	576.2	574.9	571.2	567.9
5°	611.4	604.9	601.7	598.0	591.5	584.1	578.1	574.4	569.8	562.4	555.4
7.5°	632.2	622.5	616.1	611.0	599.9	587.8	578.1	570.2	561.4	551.3	541.5
10°	654.0	638.3	629.9	622.1	605.9	590.1	576.2	564.7	552.2	538.8	528.1
12.5°	671.1	650.3	641.0	629.9	610.0	591.5	573.9	558.2	542.0	527.6	512.4
15°	691.0	665.1	654.5	640.1	612.8	588.7	566.1	548.9	532.3	511.0	494.8
17.5°	702.6	672.5	657.2	644.7	615.1	586.0	559.6	538.3	518.9	497.6	480.4
20°	714.2	679.9	662.8	645.2	610.0	579.0	551.3	525.8	505.4	482.3	464.7
22.5°	717.9	678.1	660.0	643.8	606.8	572.1	540.1	514.2	490.6	467.5	447.6
25°	717.9	677.6	656.3	635.5	596.6	561.0	529.0	500.8	474.4	451.3	431.4
27.5°	710.5	668.4	646.1	627.2	586.9	548.5	515.6	484.6	459.1	436.0	413.3
30°	701.2	654.9	632.7	610.0	571.2	534.6	498.9	470.3	443.4	417.0	396.7
32.5°	689.6	640.6	616.1	592.9	551.7	513.8	480.9	452.7	427.2	399.9	377.2
35°	673.0	619.3	592.0	571.6	531.8	492.5	461.0	433.2	408.7	380.5	355.9
37.5°	651.7	599.9	572.1	547.1	505.9	469.8	440.2	413.3	389.3	363.3	336.0
40°	626.7	572.5	548.5	522.1	478.6	444.3	416.6	392.5	368.4	343.9	317.5
42.5°	598.5	544.8	517.9	492.5	450.8	417.0	391.1	369.4	347.1	324.5	296.2
45°	564.7	514.2	488.3	464.2	424.0	389.3	365.6	344.8	325.8	302.7	277.7
47.5°	526.7	482.7	456.4	430.4	391.1	361.0	337.9	320.3	304.1	280.9	258.3
50°	489.7	446.2	424.9	398.5	362.4	334.2	310.6	295.8	283.3	260.6	240.2
52.5°	442.9	410.1	389.7	367.0	332.3	303.6	285.1	272.2	257.3	239.8	221.7
55°	401.8	371.2	355.0	333.7	299.5	274.0	258.3	246.2	234.7	218.9	204.6
57.5°	355.0	336.0	319.8	301.3	267.5	245.8	231.9	221.7	211.1	198.1	186.5
60°	305.9	297.1	281.4	266.6	237.9	218.9	207.4	198.1	187.9	177.3	167.6
62.5°	262.4	257.3	248.1	236.5	209.7	193.5	181.9	175.0	167.6	157.8	148.6
65°	221.2	218.9	210.1	201.8	183.3	168.9	158.8	154.6	146.3	138.9	130.5
67.5°	184.7	181.9	176.8	173.1	157.4	143.9	138.9	133.3	126.4	120.8	113.9
70°	147.6	147.2	143.9	139.3	131.0	121.3	116.2	112.5	105.5	101.4	96.3
72.5°	114.8	117.1	114.3	112.5	106.9	100.0	95.3	93.0	87.5	84.2	80.5
75°	85.6	87.5	88.9	85.6	84.2	81.0	76.8	74.5	71.7	67.1	65.7
77.5°	58.3	62.5	62.5	63.4	63.9	62.0	58.8	56.9	53.7	52.8	50.9
80°	38.4	42.1	42.6	43.5	44.9	44.9	42.6	42.1	38.9	38.4	37.0
82.5°	22.2	25.5	27.3	28.7	28.2	30.1	28.2	27.8	25.9	25.9	25.0
85°	12.0	12.5	13.4	14.3	15.3	16.2	16.2	15.7	15.3	14.8	13.9
87.5°	4.6	4.6	5.1	4.6	5.1	6.0	6.5	6.5	6.0	5.6	4.6
90°	19.4	17.3	16.3	14.9	12.0	9.2	6.3	3.5	6.3	9.2	12.0
92.5°	47.4	46.1	45.5	43.8	40.4	37.1	33.7	30.3	33.7	37.1	40.4
95°	83.2	81.4	80.5	79.3	77.0	74.7	72.3	70.0	72.3	74.7	77.0
97.5°	124.4	122.3	121.3	120.3	118.2	116.1	114.1	112.0	114.1	116.1	118.2
100°	171.4	169.1	167.9	167.4	166.4	165.3	164.3	163.3	164.3	165.3	166.4
102.5°	221.2	219.1	218.1	218.0	217.7	217.4	217.2	216.9	217.2	217.4	217.7
105°	274.5	273.4	272.9	272.8	272.5	272.2	272.0	271.7	272.0	272.2	272.5
107.5°	330.4	330.1	330.0	329.9	329.6	329.4	329.1	328.9	329.1	329.4	329.6
110°	389.1	389.4	389.5	389.2	388.7	388.2	387.7	387.2	387.7	388.2	388.7

TEST NUMBER: P1026272

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	447.0	447.5	447.8	447.8	447.8	447.8	447.8	447.8	447.8	447.8	447.8
115°	507.7	508.2	508.5	508.5	508.5	508.5	508.5	508.5	508.5	508.5	508.5
117.5°	565.2	565.5	565.6	565.6	565.6	565.6	565.6	565.6	565.6	565.6	565.6
120°	626.2	627.0	627.4	626.9	625.8	624.8	623.7	622.7	623.7	624.8	625.8
122.5°	683.0	683.3	683.4	683.3	683.0	682.7	682.5	682.2	682.5	682.7	683.0
125°	740.1	740.4	740.5	740.5	740.5	740.5	740.5	740.5	740.5	740.5	740.5
127.5°	795.7	796.2	796.5	796.1	795.3	794.6	793.8	793.0	793.8	794.6	795.3
130°	852.5	852.5	852.5	852.1	851.3	850.6	849.8	849.0	849.8	850.6	851.3
132.5°	908.1	908.4	908.5	908.2	907.7	907.2	906.6	906.1	906.6	907.2	907.7
135°	962.1	962.1	962.1	961.3	959.8	958.2	956.7	955.1	956.7	958.2	959.8
137.5°	1014.2	1013.7	1013.4	1013.0	1012.2	1011.5	1010.7	1009.9	1010.7	1011.5	1012.2
140°	1067.1	1067.1	1067.1	1066.8	1066.3	1065.8	1065.2	1064.7	1065.2	1065.8	1066.3
142.5°	1116.8	1117.1	1117.2	1116.9	1116.4	1115.9	1115.4	1114.9	1115.4	1115.9	1116.4
145°	1165.4	1165.1	1165.0	1164.5	1163.4	1162.4	1161.3	1160.3	1161.3	1162.4	1163.4
147.5°	1212.4	1212.7	1212.8	1212.2	1210.9	1209.6	1208.3	1207.0	1208.3	1209.6	1210.9
150°	1253.6	1253.6	1253.6	1253.1	1252.1	1251.0	1250.0	1249.0	1250.0	1251.0	1252.1
152.5°	1291.4	1291.1	1291.0	1290.7	1290.2	1289.7	1289.1	1288.6	1289.1	1289.7	1290.2
155°	1329.0	1329.3	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
157.5°	1362.1	1362.1	1362.1	1362.4	1362.9	1363.4	1363.9	1364.4	1363.9	1363.4	1362.9
160°	1393.2	1393.5	1393.6	1393.7	1394.0	1394.2	1394.5	1394.7	1394.5	1394.2	1394.0
162.5°	1418.8	1419.1	1419.2	1419.6	1420.4	1421.1	1421.9	1422.7	1421.9	1421.1	1420.4
165°	1442.9	1443.4	1443.7	1444.1	1444.9	1445.6	1446.4	1447.2	1446.4	1445.6	1444.9
167.5°	1462.4	1462.4	1462.4	1462.9	1464.0	1465.0	1466.1	1467.1	1466.1	1465.0	1464.0
170°	1477.9	1477.6	1477.5	1478.2	1479.5	1480.8	1482.1	1483.4	1482.1	1480.8	1479.5
172.5°	1490.4	1490.4	1490.4	1490.9	1491.9	1493.0	1494.0	1495.0	1494.0	1493.0	1491.9
175°	1499.3	1499.6	1499.7	1500.3	1501.6	1502.9	1504.2	1505.5	1504.2	1502.9	1501.6
177.5°	1504.4	1504.4	1504.4	1505.0	1506.3	1507.6	1508.9	1510.2	1508.9	1507.6	1506.3
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9

TEST NUMBER: P1026272

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4
2.5°	565.1	564.2	563.3	559.6	556.3	550.8	546.2	544.3	543.8	544.3	542.9
5°	548.9	548.5	545.2	538.8	532.7	526.3	521.6	517.0	514.2	514.2	511.0
7.5°	533.7	530.4	527.6	519.3	512.4	503.6	496.6	492.5	490.2	485.1	485.1
10°	517.5	512.8	509.1	501.3	491.1	482.3	473.5	468.4	464.2	460.5	459.1
12.5°	501.3	497.6	490.6	482.3	472.1	461.0	451.7	448.0	438.3	430.4	430.9
15°	486.0	477.7	474.4	462.4	450.4	439.7	426.3	415.6	407.8	402.7	396.2
17.5°	468.9	460.5	454.5	444.3	428.6	411.9	399.0	384.6	376.8	368.0	363.8
20°	449.9	442.9	438.3	422.1	403.1	383.2	368.9	360.1	351.3	344.8	341.1
22.5°	433.7	424.9	419.3	397.6	376.8	356.9	345.7	338.3	330.9	325.4	323.5
25°	412.9	407.8	394.3	375.4	349.9	336.5	326.8	317.1	312.9	309.2	305.0
27.5°	395.7	383.2	374.0	349.0	333.3	318.0	308.3	300.9	295.8	292.1	288.8
30°	374.4	362.9	349.9	329.1	314.7	300.4	291.6	285.6	280.0	277.7	274.9
32.5°	352.2	341.6	329.1	312.4	294.8	283.7	276.8	270.3	266.6	264.3	261.0
35°	332.3	318.9	310.6	294.8	280.5	268.0	261.5	256.0	251.8	250.9	250.4
37.5°	311.0	300.9	293.0	276.8	264.7	254.1	248.1	242.1	239.8	239.3	237.4
40°	292.5	283.7	276.3	261.0	248.1	238.4	233.7	230.0	227.7	227.7	227.3
42.5°	276.3	267.1	259.7	245.8	234.2	225.4	220.3	216.6	215.7	216.1	215.7
45°	258.3	250.4	243.0	228.6	218.9	212.4	206.9	205.0	203.7	204.1	204.6
47.5°	241.1	234.7	227.3	215.7	204.6	197.6	194.4	192.5	192.5	192.5	193.5
50°	225.9	218.5	212.0	200.0	189.8	184.2	181.4	179.1	179.6	180.0	180.5
52.5°	207.8	201.3	196.7	184.7	177.3	170.3	167.1	167.6	167.1	167.1	168.0
55°	192.1	185.6	181.0	169.9	162.5	157.8	155.1	153.7	154.1	153.2	155.1
57.5°	174.5	168.9	165.7	155.1	148.6	144.4	142.1	139.8	140.7	140.2	139.8
60°	159.2	152.7	147.6	140.2	134.7	129.6	128.2	125.9	126.8	125.9	125.4
62.5°	141.6	136.5	132.8	125.4	120.8	116.6	113.4	112.0	111.5	110.2	108.8
65°	124.0	121.3	117.6	110.2	105.5	102.3	100.4	99.0	98.6	94.9	90.7
67.5°	107.8	106.0	102.3	96.7	92.6	89.3	86.6	84.2	81.5	78.7	76.4
70°	92.6	89.8	87.5	82.4	78.7	75.4	72.7	69.9	68.5	65.7	64.8
72.5°	77.8	75.0	72.7	68.0	64.8	61.6	60.6	57.4	56.0	55.5	55.5
75°	62.5	60.2	58.8	54.6	51.8	49.5	48.1	47.2	46.3	45.4	44.0
77.5°	47.7	46.3	45.4	42.6	40.3	38.9	38.4	35.2	34.3	33.3	32.4
80°	34.7	34.3	33.3	31.0	30.1	26.8	26.8	25.9	25.5	25.5	25.5
82.5°	23.6	22.7	22.2	19.9	19.4	19.0	18.5	18.1	18.5	18.1	18.5
85°	12.5	12.0	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.1	11.6
87.5°	4.6	4.6	4.6	4.6	4.2	4.6	4.6	4.2	4.6	4.6	4.6
90°	14.9	16.3	17.3	19.4	21.5	23.6	25.7	27.3	28.8	30.4	31.9
92.5°	43.8	45.5	46.1	47.4	48.7	50.0	51.3	52.1	52.9	53.6	54.4
95°	79.3	80.5	81.4	83.2	85.0	86.8	88.6	89.4	90.2	90.9	91.7
97.5°	120.3	121.3	122.3	124.4	126.5	128.5	130.6	131.6	132.7	133.7	134.8
100°	167.4	167.9	169.1	171.4	173.7	176.1	178.4	178.9	179.5	180.0	180.5
102.5°	218.0	218.1	219.1	221.2	223.3	225.3	227.4	228.2	229.0	229.7	230.5
105°	272.8	272.9	273.4	274.5	275.5	276.6	277.6	278.4	279.1	279.9	280.6
107.5°	329.9	330.0	330.1	330.4	330.7	330.9	331.2	332.2	333.3	334.3	335.4
110°	389.2	389.5	389.4	389.1	388.8	388.6	388.3	387.8	387.3	386.8	386.3

TEST NUMBER: P1026272

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	447.8	447.8	447.5	447.0	446.5	446.0	445.5	445.5	445.5	445.5	445.5
115°	508.5	508.5	508.2	507.7	507.2	506.6	506.1	505.9	505.6	505.4	505.1
117.5°	565.6	565.6	565.5	565.2	564.9	564.7	564.4	563.6	562.8	562.1	561.3
120°	626.9	627.4	627.0	626.2	625.5	624.7	623.9	622.6	621.3	620.0	618.7
122.5°	683.3	683.4	683.3	683.0	682.7	682.5	682.2	681.4	680.6	679.9	679.1
125°	740.5	740.5	740.4	740.1	739.9	739.6	739.4	738.9	738.3	737.8	737.3
127.5°	796.1	796.5	796.2	795.7	795.2	794.7	794.2	793.7	793.1	792.6	792.1
130°	852.1	852.5	852.5	852.5	852.5	852.5	852.5	852.0	851.4	850.9	850.4
132.5°	908.2	908.5	908.4	908.1	907.8	907.6	907.3	906.8	906.3	905.8	905.3
135°	961.3	962.1	962.1	962.1	962.1	962.1	962.1	961.6	961.1	960.6	960.1
137.5°	1013.0	1013.4	1013.7	1014.2	1014.7	1015.2	1015.7	1014.9	1014.1	1013.4	1012.6
140°	1066.8	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1	1066.8	1066.6	1066.3	1066.0
142.5°	1116.9	1117.2	1117.1	1116.8	1116.5	1116.3	1116.0	1116.0	1116.0	1116.0	1116.0
145°	1164.5	1165.0	1165.1	1165.4	1165.7	1165.9	1166.2	1165.9	1165.7	1165.4	1165.1
147.5°	1212.2	1212.8	1212.7	1212.4	1212.2	1211.9	1211.7	1211.4	1211.2	1210.9	1210.6
150°	1253.1	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6
152.5°	1290.7	1291.0	1291.1	1291.4	1291.6	1291.9	1292.1	1292.9	1293.7	1294.4	1295.2
155°	1329.4	1329.4	1329.3	1329.0	1328.8	1328.5	1328.3	1329.3	1330.3	1331.4	1332.4
157.5°	1362.4	1362.1	1362.1	1362.1	1362.1	1362.1	1362.1	1362.9	1363.7	1364.4	1365.2
160°	1393.7	1393.6	1393.5	1393.2	1392.9	1392.7	1392.4	1393.2	1394.0	1394.7	1395.5
162.5°	1419.6	1419.2	1419.1	1418.8	1418.6	1418.3	1418.1	1419.7	1421.2	1422.8	1424.3
165°	1444.1	1443.7	1443.4	1442.9	1442.4	1441.9	1441.4	1443.0	1444.5	1446.1	1447.6
167.5°	1462.9	1462.4	1462.4	1462.4	1462.4	1462.4	1462.4	1464.0	1465.5	1467.1	1468.6
170°	1478.2	1477.5	1477.6	1477.9	1478.2	1478.4	1478.7	1480.3	1481.8	1483.4	1484.9
172.5°	1490.9	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1492.2	1494.0	1495.8	1497.6
175°	1500.3	1499.7	1499.6	1499.3	1499.0	1498.8	1498.5	1500.3	1502.1	1504.0	1505.8
177.5°	1505.0	1504.4	1504.4	1504.4	1504.4	1504.4	1504.4	1506.2	1508.0	1509.8	1511.6
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9

TEST NUMBER: P1026272

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4
2.5°	542.9	544.8	542.5	543.8	540.6	540.1	540.6	540.6	541.1	541.5	542.0
5°	512.4	511.9	509.1	507.3	505.9	507.3	508.2	509.1	508.2	509.1	509.6
7.5°	483.7	482.3	480.9	477.7	478.6	477.7	480.4	479.0	479.0	481.4	483.2
10°	458.2	455.4	454.5	450.8	448.0	447.6	450.8	452.2	453.6	454.5	458.2
12.5°	425.4	421.2	418.0	419.3	411.5	414.7	415.6	413.8	419.3	425.8	422.1
15°	390.2	390.6	384.2	381.8	375.4	377.2	377.7	382.3	386.9	386.5	392.0
17.5°	364.3	361.5	355.9	355.5	352.7	354.1	353.6	357.3	355.9	358.2	362.9
20°	340.2	338.3	333.7	331.9	332.8	331.9	332.3	332.8	334.2	339.3	338.3
22.5°	321.2	318.9	318.9	316.6	313.8	312.9	315.2	316.6	318.4	319.4	321.7
25°	304.6	302.7	300.4	299.0	296.7	297.1	298.5	300.4	301.8	303.6	305.5
27.5°	287.4	287.4	285.1	284.7	283.7	283.3	285.1	286.0	286.0	287.4	289.3
30°	274.0	274.0	271.7	271.2	270.8	270.8	272.2	272.6	273.1	274.5	275.4
32.5°	261.0	260.6	259.7	260.1	259.7	260.1	260.1	260.6	261.5	262.0	263.8
35°	249.0	249.5	248.5	248.5	248.1	248.5	249.5	249.9	250.4	251.3	251.3
37.5°	237.4	238.4	237.9	239.3	239.3	239.3	239.3	240.2	240.2	240.2	239.8
40°	227.3	227.3	226.8	227.7	228.6	228.6	229.1	229.1	229.6	229.6	229.1
42.5°	215.7	216.6	218.0	218.5	219.4	218.9	220.3	219.9	220.3	219.4	218.5
45°	205.0	205.0	206.9	208.7	209.2	209.2	209.2	210.1	209.2	207.8	207.4
47.5°	193.5	194.4	195.3	197.6	198.1	198.1	198.1	198.1	197.2	197.2	197.2
50°	181.9	182.4	182.8	183.8	185.1	184.7	184.7	184.7	186.5	184.7	185.1
52.5°	168.0	168.5	168.9	170.8	170.3	170.3	170.8	170.8	172.2	171.7	170.8
55°	154.1	154.1	155.1	155.1	155.1	156.0	156.4	157.4	156.9	157.4	157.8
57.5°	140.2	139.3	138.9	138.9	140.2	139.8	140.2	140.2	142.1	143.0	143.5
60°	124.0	124.0	123.6	120.8	120.8	120.3	121.7	122.7	123.6	127.7	127.3
62.5°	107.4	105.5	103.7	104.1	101.4	102.8	101.8	102.8	105.5	108.8	109.2
65°	90.7	89.3	87.5	87.0	86.1	87.5	87.0	87.5	88.9	90.7	93.0
67.5°	75.9	75.4	74.5	74.1	74.1	74.1	75.0	75.0	75.4	76.8	78.2
70°	64.8	64.3	64.8	63.9	64.3	63.9	64.3	64.8	65.3	65.7	67.1
72.5°	54.6	54.6	54.6	53.7	54.6	54.2	54.2	54.6	55.1	55.5	56.5
75°	43.5	42.6	41.7	40.7	40.3	41.2	41.7	41.2	42.6	44.4	44.4
77.5°	32.9	32.4	32.4	32.4	32.9	32.4	33.3	32.9	33.3	33.3	34.3
80°	25.5	25.0	25.5	25.5	25.0	25.9	25.5	25.5	25.9	26.4	25.9
82.5°	18.5	19.0	18.5	18.5	18.5	19.4	18.5	18.5	18.5	19.0	19.0
85°	11.6	11.6	11.6	11.6	12.0	11.6	12.0	11.6	12.5	12.0	12.0
87.5°	4.2	4.6	5.1	5.1	5.1	5.1	4.6	5.1	5.6	5.1	5.6
90°	32.7	33.0	33.5	34.0	34.5	35.0	34.5	34.0	33.5	33.0	32.7
92.5°	54.8	54.9	55.2	55.5	55.7	56.0	55.7	55.5	55.2	54.9	54.8
95°	92.1	92.1	92.1	92.1	92.1	92.1	92.1	92.1	92.1	92.1	92.1
97.5°	135.3	135.3	135.3	135.3	135.3	135.3	135.3	135.3	135.3	135.3	135.3
100°	180.8	180.8	180.8	180.8	180.8	180.8	180.8	180.8	180.8	180.8	180.8
102.5°	230.9	231.0	231.3	231.6	231.8	232.1	231.8	231.6	231.3	231.0	230.9
105°	281.0	281.4	282.2	282.9	283.7	284.5	283.7	282.9	282.2	281.4	281.0
107.5°	335.9	335.8	335.5	335.2	335.0	334.7	335.0	335.2	335.5	335.8	335.9
110°	386.0	386.4	387.2	387.9	388.7	389.5	388.7	387.9	387.2	386.4	386.0

TEST NUMBER: P1026272

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5
115°	505.0	504.9	504.6	504.3	504.1	503.8	504.1	504.3	504.6	504.9	505.0
117.5°	560.9	560.5	559.7	559.0	558.2	557.4	558.2	559.0	559.7	560.5	560.9
120°	618.1	618.4	618.9	619.4	619.9	620.4	619.9	619.4	618.9	618.4	618.1
122.5°	678.7	678.1	676.8	675.5	674.2	672.9	674.2	675.5	676.8	678.1	678.7
125°	737.0	736.7	736.2	735.7	735.2	734.7	735.2	735.7	736.2	736.7	737.0
127.5°	791.8	791.7	791.4	791.2	790.9	790.7	790.9	791.2	791.4	791.7	791.8
130°	850.1	849.6	848.6	847.5	846.5	845.5	846.5	847.5	848.6	849.6	850.1
132.5°	905.0	904.9	904.6	904.3	904.1	903.8	904.1	904.3	904.6	904.9	905.0
135°	959.8	959.4	958.6	957.9	957.1	956.3	957.1	957.9	958.6	959.4	959.8
137.5°	1012.2	1012.3	1012.6	1012.9	1013.1	1013.4	1013.1	1012.9	1012.6	1012.3	1012.2
140°	1065.9	1065.8	1065.5	1065.2	1065.0	1064.7	1065.0	1065.2	1065.5	1065.8	1065.9
142.5°	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0
145°	1165.0	1164.6	1163.8	1163.1	1162.3	1161.5	1162.3	1163.1	1163.8	1164.6	1165.0
147.5°	1210.5	1210.4	1210.1	1209.8	1209.6	1209.3	1209.6	1209.8	1210.1	1210.4	1210.5
150°	1253.6	1253.5	1253.2	1253.0	1252.7	1252.5	1252.7	1253.0	1253.2	1253.5	1253.6
152.5°	1295.6	1295.2	1294.4	1293.7	1292.9	1292.1	1292.9	1293.7	1294.4	1295.2	1295.6
155°	1332.9	1332.4	1331.4	1330.3	1329.3	1328.3	1329.3	1330.3	1331.4	1332.4	1332.9
157.5°	1365.6	1365.2	1364.4	1363.7	1362.9	1362.1	1362.9	1363.7	1364.4	1365.2	1365.6
160°	1395.9	1395.3	1394.0	1392.7	1391.4	1390.1	1391.4	1392.7	1394.0	1395.3	1395.9
162.5°	1425.1	1424.4	1423.1	1421.8	1420.5	1419.2	1420.5	1421.8	1423.1	1424.4	1425.1
165°	1448.4	1447.9	1446.8	1445.8	1444.7	1443.7	1444.7	1445.8	1446.8	1447.9	1448.4
167.5°	1469.4	1468.6	1467.1	1465.5	1464.0	1462.4	1464.0	1465.5	1467.1	1468.6	1469.4
170°	1485.7	1484.8	1483.0	1481.1	1479.3	1477.5	1479.3	1481.1	1483.0	1484.8	1485.7
172.5°	1498.5	1497.6	1495.8	1494.0	1492.2	1490.4	1492.2	1494.0	1495.8	1497.6	1498.5
175°	1506.7	1505.8	1504.0	1502.1	1500.3	1498.5	1500.3	1502.1	1504.0	1505.8	1506.7
177.5°	1512.5	1511.5	1509.4	1507.3	1505.3	1503.2	1505.3	1507.3	1509.4	1511.5	1512.5
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9

TEST NUMBER: P1026272

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4
2.5°	543.8	546.2	545.2	542.0	543.4	546.2	548.9	552.6	555.0	556.8	557.7
5°	511.9	516.1	515.1	515.1	517.0	521.6	526.3	534.1	536.9	540.1	544.8
7.5°	483.7	486.9	489.7	490.6	493.4	499.4	505.4	514.2	521.2	524.9	527.6
10°	458.7	461.0	465.2	467.5	470.3	477.7	486.5	495.7	502.7	509.1	512.8
12.5°	426.7	436.0	441.6	445.3	449.0	460.1	467.0	477.2	485.5	491.5	497.1
15°	391.1	402.2	405.5	419.8	429.1	437.9	448.5	460.5	468.4	475.3	482.7
17.5°	361.0	368.9	372.6	387.9	395.7	409.6	424.9	440.2	452.2	457.3	464.7
20°	342.0	346.2	353.6	358.7	367.0	383.2	399.9	418.4	436.5	441.6	449.0
22.5°	322.6	328.2	333.3	340.2	346.7	357.8	374.4	394.8	414.2	423.5	432.3
25°	305.0	310.6	313.8	321.2	327.2	338.3	349.9	370.7	393.9	401.8	415.6
27.5°	291.1	294.4	299.9	303.2	310.1	320.3	330.9	346.7	369.4	382.8	396.2
30°	277.2	279.6	284.2	288.8	293.9	300.9	312.9	328.2	349.0	360.6	374.0
32.5°	263.4	267.1	269.8	273.1	278.6	287.0	295.3	310.1	326.8	339.7	353.2
35°	251.8	253.2	256.9	260.6	264.3	271.7	280.5	294.8	309.6	319.8	331.9
37.5°	239.3	241.6	244.4	245.8	251.8	256.4	265.7	276.8	294.4	300.9	312.9
40°	229.6	229.1	231.9	234.2	237.0	244.4	249.9	262.0	275.9	286.0	293.4
42.5°	217.5	217.5	218.5	221.2	224.9	229.6	236.1	246.2	260.6	268.0	276.8
45°	207.8	206.4	206.9	208.7	211.1	215.7	222.2	231.0	245.3	251.3	260.6
47.5°	196.2	194.9	194.9	196.7	198.6	201.8	206.9	217.1	228.6	236.5	243.5
50°	183.3	183.8	183.3	184.7	185.6	188.8	194.4	202.7	213.4	219.9	227.7
52.5°	171.3	170.3	169.9	170.8	172.6	175.0	181.0	188.4	198.6	205.0	212.0
55°	156.4	157.4	157.4	157.4	160.1	161.1	165.7	173.1	183.3	188.4	194.9
57.5°	143.0	142.6	143.5	143.0	145.3	148.6	152.3	157.8	168.0	173.1	179.1
60°	128.2	128.7	129.1	129.1	131.0	134.2	138.4	143.5	151.8	156.9	162.5
62.5°	110.2	112.5	114.8	115.7	118.5	120.8	123.6	129.1	136.5	140.2	145.3
65°	93.0	96.3	99.5	101.8	103.7	106.0	109.7	114.8	120.8	124.5	129.6
67.5°	78.2	80.5	84.7	87.0	90.7	93.5	95.8	100.0	107.4	108.8	112.9
70°	67.6	68.5	70.4	72.2	76.4	78.7	81.5	85.6	91.2	94.4	96.7
72.5°	56.9	57.4	58.3	60.2	62.0	64.8	68.0	71.7	76.8	78.2	81.5
75°	45.4	48.1	48.1	49.5	50.9	52.3	55.1	58.8	62.0	64.3	66.2
77.5°	33.8	35.2	36.1	38.4	40.3	41.7	43.5	46.3	48.1	50.0	51.4
80°	26.4	26.8	27.3	27.3	28.2	30.1	31.9	33.8	36.1	37.0	38.4
82.5°	19.4	19.4	19.4	20.4	20.8	21.3	21.3	22.2	24.5	25.5	26.8
85°	12.5	12.5	12.5	12.5	13.0	13.4	13.9	14.3	14.3	14.3	15.3
87.5°	5.1	6.0	5.6	6.0	6.0	6.0	6.0	6.5	6.5	6.9	6.9
90°	31.9	30.4	28.8	27.3	25.7	23.6	21.5	19.4	17.3	16.3	14.9
92.5°	54.4	53.6	52.9	52.1	51.3	50.0	48.7	47.4	46.1	45.5	43.8
95°	91.7	90.9	90.2	89.4	88.6	86.8	85.0	83.2	81.4	80.5	79.3
97.5°	134.8	133.7	132.7	131.6	130.6	128.5	126.5	124.4	122.3	121.3	120.3
100°	180.5	180.0	179.5	178.9	178.4	176.1	173.7	171.4	169.1	167.9	167.4
102.5°	230.5	229.7	229.0	228.2	227.4	225.3	223.3	221.2	219.1	218.1	218.0
105°	280.6	279.9	279.1	278.4	277.6	276.6	275.5	274.5	273.4	272.9	272.8
107.5°	335.4	334.3	333.3	332.2	331.2	330.9	330.7	330.4	330.1	330.0	329.9
110°	386.3	386.8	387.3	387.8	388.3	388.6	388.8	389.1	389.4	389.5	389.2

TEST NUMBER: P1026272

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	445.5	445.5	445.5	445.5	445.5	446.0	446.5	447.0	447.5	447.8	447.8
115°	505.1	505.4	505.6	505.9	506.1	506.6	507.2	507.7	508.2	508.5	508.5
117.5°	561.3	562.1	562.8	563.6	564.4	564.7	564.9	565.2	565.5	565.6	565.6
120°	618.7	620.0	621.3	622.6	623.9	624.7	625.5	626.2	627.0	627.4	626.9
122.5°	679.1	679.9	680.6	681.4	682.2	682.5	682.7	683.0	683.3	683.4	683.3
125°	737.3	737.8	738.3	738.9	739.4	739.6	739.9	740.1	740.4	740.5	740.5
127.5°	792.1	792.6	793.1	793.7	794.2	794.7	795.2	795.7	796.2	796.5	796.1
130°	850.4	850.9	851.4	852.0	852.5	852.5	852.5	852.5	852.5	852.5	852.1
132.5°	905.3	905.8	906.3	906.8	907.3	907.6	907.8	908.1	908.4	908.5	908.2
135°	960.1	960.6	961.1	961.6	962.1	962.1	962.1	962.1	962.1	962.1	961.3
137.5°	1012.6	1013.4	1014.1	1014.9	1015.7	1015.2	1014.7	1014.2	1013.7	1013.4	1013.0
140°	1066.0	1066.3	1066.6	1066.8	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1	1066.8
142.5°	1116.0	1116.0	1116.0	1116.0	1116.0	1116.3	1116.5	1116.8	1117.1	1117.2	1116.9
145°	1165.1	1165.4	1165.7	1165.9	1166.2	1165.9	1165.7	1165.4	1165.1	1165.0	1164.5
147.5°	1210.6	1210.9	1211.2	1211.4	1211.7	1211.9	1212.2	1212.4	1212.7	1212.8	1212.2
150°	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.6	1253.1
152.5°	1295.2	1294.4	1293.7	1292.9	1292.1	1291.9	1291.6	1291.4	1291.1	1291.0	1290.7
155°	1332.4	1331.4	1330.3	1329.3	1328.3	1328.5	1328.8	1329.0	1329.3	1329.4	1329.4
157.5°	1365.2	1364.4	1363.7	1362.9	1362.1	1362.1	1362.1	1362.1	1362.1	1362.1	1362.4
160°	1395.5	1394.7	1394.0	1393.2	1392.4	1392.7	1392.9	1393.2	1393.5	1393.6	1393.7
162.5°	1424.3	1422.8	1421.2	1419.7	1418.1	1418.3	1418.6	1418.8	1419.1	1419.2	1419.6
165°	1447.6	1446.1	1444.5	1443.0	1441.4	1441.9	1442.4	1442.9	1443.4	1443.7	1444.1
167.5°	1468.6	1467.1	1465.5	1464.0	1462.4	1462.4	1462.4	1462.4	1462.4	1462.4	1462.9
170°	1484.9	1483.4	1481.8	1480.3	1478.7	1478.4	1478.2	1477.9	1477.6	1477.5	1478.2
172.5°	1497.6	1495.8	1494.0	1492.2	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.9
175°	1505.8	1504.0	1502.1	1500.3	1498.5	1498.8	1499.0	1499.3	1499.6	1499.7	1500.3
177.5°	1511.6	1509.8	1508.0	1506.2	1504.4	1504.4	1504.4	1504.4	1504.4	1504.4	1505.0
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9

TEST NUMBER: P1026272

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	574.4	574.4	574.4	574.4
2.5°	561.4	564.2	568.8	575.3
5°	548.5	556.3	563.7	573.5
7.5°	536.9	546.2	556.3	570.2
10°	523.5	535.1	548.0	565.1
12.5°	507.7	523.9	538.8	557.3
15°	496.2	508.2	527.2	548.9
17.5°	480.0	496.2	515.1	539.7
20°	464.7	481.8	503.1	528.6
22.5°	448.5	467.9	489.2	516.5
25°	431.8	452.7	474.0	503.1
27.5°	416.6	435.5	459.6	489.2
30°	398.0	419.8	442.9	474.0
32.5°	380.0	402.7	426.3	457.3
35°	360.6	383.2	409.2	438.8
37.5°	341.6	366.6	390.2	418.9
40°	320.8	346.7	371.2	400.4
42.5°	300.4	327.2	351.8	376.8
45°	281.4	307.8	330.0	353.6
47.5°	263.4	287.0	309.6	330.9
50°	245.8	265.7	286.5	304.1
52.5°	227.3	246.2	262.9	278.6
55°	210.6	225.4	240.2	254.6
57.5°	190.7	205.5	218.5	229.6
60°	174.0	183.3	195.8	207.4
62.5°	155.1	165.7	175.4	182.8
65°	136.5	145.8	153.2	159.7
67.5°	120.8	126.4	131.9	138.9
70°	101.8	106.5	112.9	118.0
72.5°	85.6	89.3	92.6	98.6
75°	69.4	72.7	74.5	80.1
77.5°	53.7	56.9	58.3	61.6
80°	41.2	41.7	43.5	46.3
82.5°	28.2	29.2	29.6	31.9
85°	16.2	18.5	18.1	19.0
87.5°	6.9	7.4	8.3	9.3
90°	12.0	9.2	6.3	3.5
92.5°	40.4	37.1	33.7	30.3
95°	77.0	74.7	72.3	70.0
97.5°	118.2	116.1	114.1	112.0
100°	166.4	165.3	164.3	163.3
102.5°	217.7	217.4	217.2	216.9
105°	272.5	272.2	272.0	271.7
107.5°	329.6	329.4	329.1	328.9
110°	388.7	388.2	387.7	387.2



TEST NUMBER: P1026272

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	447.8	447.8	447.8	447.8
115°	508.5	508.5	508.5	508.5
117.5°	565.6	565.6	565.6	565.6
120°	625.8	624.8	623.7	622.7
122.5°	683.0	682.7	682.5	682.2
125°	740.5	740.5	740.5	740.5
127.5°	795.3	794.6	793.8	793.0
130°	851.3	850.6	849.8	849.0
132.5°	907.7	907.2	906.6	906.1
135°	959.8	958.2	956.7	955.1
137.5°	1012.2	1011.5	1010.7	1009.9
140°	1066.3	1065.8	1065.2	1064.7
142.5°	1116.4	1115.9	1115.4	1114.9
145°	1163.4	1162.4	1161.3	1160.3
147.5°	1210.9	1209.6	1208.3	1207.0
150°	1252.1	1251.0	1250.0	1249.0
152.5°	1290.2	1289.7	1289.1	1288.6
155°	1329.4	1329.4	1329.4	1329.4
157.5°	1362.9	1363.4	1363.9	1364.4
160°	1394.0	1394.2	1394.5	1394.7
162.5°	1420.4	1421.1	1421.9	1422.7
165°	1444.9	1445.6	1446.4	1447.2
167.5°	1464.0	1465.0	1466.1	1467.1
170°	1479.5	1480.8	1482.1	1483.4
172.5°	1491.9	1493.0	1494.0	1495.0
175°	1501.6	1502.9	1504.2	1505.5
177.5°	1506.3	1507.6	1508.9	1510.2
180°	1507.9	1507.9	1507.9	1507.9

(END OF REPORT)