

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026288

Luminaire Tested: S124RDIP-B350D1205UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026288
REPORT IS A COMBINATION OF REPORTS P999298 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D1205UB50-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5487.2 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026288

CATALOG NUMBER: S124RDIP-B350D1205UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026288

CATALOG NUMBER: S124RDIP-B350D1205UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33
1	92	88	84	81	82	79	75	73	61	59	57	44	43	42	29	28	28
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24
3	77	68	61	55	68	61	55	50	47	43	40	34	32	30	23	21	20
4	70	60	52	47	62	54	47	42	42	37	34	31	28	25	20	19	17
5	64	53	46	40	57	48	41	36	37	33	29	28	24	22	18	17	15
6	59	48	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13
7	54	43	35	30	48	38	32	27	30	26	22	23	19	17	15	13	12
8	50	39	31	26	45	35	28	24	27	23	20	21	17	15	14	12	11
9	47	35	28	23	42	32	26	21	25	21	17	19	16	13	13	11	10
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4718	4718	4718
5°	4719	4579	4579
10°	4679	4434	4381
15°	4615	4254	4148
20°	4530	4049	3882
25°	4426	3827	3622
30°	4323	3602	3331
35°	4209	3373	3045
40°	4075	3127	2752
45°	3948	2882	2462
50°	3804	2616	2168
55°	3649	2342	1864
60°	3477	2051	1564
65°	3311	1719	1275
70°	3074	1367	974
75°	2769	995	682
80°	2316	610	491
85°	1739	351	268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3948 cd/sqm

TEST NUMBER: P1026288

CATALOG NUMBER: S124RDIP-B350D1205UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.4	1.0
10°-20°	151.7	2.8
20°-30°	219.0	4.0
30°-40°	248.2	4.5
40°-50°	239.7	4.4
50°-60°	199.3	3.6
60°-70°	137.5	2.5
70°-80°	69.5	1.3
80°-90°	19.8	0.4
90°-100°	422.2	7.7
100°-110°	858.7	15.6
110°-120°	765.4	13.9
120°-130°	642.9	11.7
130°-140°	536.5	9.8
140°-150°	409.8	7.5
150°-160°	288.0	5.2
160°-170°	169.4	3.1
170°-180°	55.1	1.0
0°-30°	425.2	7.7
0°-40°	673.4	12.3
0°-60°	1112.3	20.3
0°-90°	1339.2	24.4
90°-120°	2046.3	37.3
90°-150°	3635.6	66.3
90°-180°	4148.0	75.6
0°-180°	5487.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	579	579	579	579	579	
5°	578	576	571	575	574	55
15°	550	546	535	534	531	155
25°	498	490	471	464	460	229
35°	430	416	394	379	371	269
45°	351	334	308	286	278	271
55°	266	248	219	196	188	238
65°	181	162	133	114	109	179
75°	96	80	59	49	46	101
85°	24	15	14	13	13	26
90°	1	9	20	22	24	4
95°	37	116	910	451	272	40
105°	131	189	732	1577	1571	139
115°	230	289	653	1255	1509	228
125°	320	381	650	1068	1204	286
135°	381	453	644	948	1076	294
145°	439	502	641	800	879	275
155°	499	539	623	706	736	230
165°	544	561	597	633	642	154
175°	567	568	573	581	578	54
180°	568	568	568	568	568	

TEST NUMBER: P1026288

CATALOG NUMBER: S124RDIP-B350D1205UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	578.6	578.6	578.6	578.6	578.6
2.5°	580.4	578.6	573.8	578.6	578.2
5°	577.7	576.0	570.7	575.1	574.2
7.5°	573.8	572.0	565.3	568.4	567.1
10°	567.6	565.3	557.4	559.1	557.4
12.5°	559.6	556.9	547.2	548.1	545.4
15°	550.3	546.3	535.2	534.3	531.2
17.5°	539.6	533.9	521.0	518.8	514.4
20°	526.8	521.0	506.0	502.4	496.7
22.5°	512.6	506.0	489.6	483.8	479.4
25°	497.6	489.6	471.4	463.9	459.5
27.5°	482.0	472.3	453.3	444.4	438.2
30°	465.7	454.6	433.8	422.7	415.6
32.5°	448.4	435.5	413.8	400.5	393.9
35°	430.2	416.0	393.9	378.8	370.8
37.5°	411.2	396.5	372.2	355.8	347.8
40°	390.8	376.2	350.9	332.3	324.3
42.5°	371.3	355.8	329.2	310.1	301.7
45°	350.9	334.5	307.9	286.2	278.2
47.5°	330.1	313.2	285.8	263.2	254.3
50°	308.8	291.5	263.2	241.0	232.6
52.5°	287.1	270.3	241.0	218.4	209.6
55°	265.8	248.1	219.3	196.3	187.9
57.5°	245.0	226.4	198.0	174.6	168.4
60°	222.4	204.7	176.3	153.3	146.2
62.5°	202.0	183.4	154.2	133.4	128.0
65°	180.8	161.7	133.4	114.3	109.0
67.5°	158.6	140.4	113.9	97.0	90.8
70°	137.8	119.2	93.9	79.3	74.9
72.5°	115.6	99.2	75.8	63.8	59.8
75°	96.1	79.8	58.9	48.7	46.1
77.5°	75.8	61.6	43.9	36.8	35.9
80°	56.3	43.4	30.1	28.8	28.4
82.5°	39.4	27.9	21.7	20.8	20.4
85°	23.9	15.1	13.7	12.8	12.8
87.5°	10.2	6.6	6.2	5.8	6.2
90°	1.1	8.9	20.1	22.3	23.5
92.5°	15.6	86.0	437.7	144.6	101.6
95°	36.9	116.2	910.1	450.6	272.5
97.5°	61.4	128.4	973.8	920.2	654.4
100°	84.9	145.2	897.8	1273.0	1024.0
102.5°	107.2	165.2	802.9	1494.2	1345.6
105°	130.7	189.3	732.5	1577.3	1571.2
107.5°	156.3	213.8	686.8	1552.2	1678.4
110°	182.0	238.4	665.5	1462.8	1680.6

TEST NUMBER: P1026288

CATALOG NUMBER: S124RDIP-B350D1205UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	206.6	263.0	655.5	1353.4	1614.7
115°	230.0	288.6	653.3	1255.2	1508.6
117.5°	254.6	312.6	652.1	1178.1	1404.8
120°	279.2	336.2	652.1	1126.2	1319.9
122.5°	301.5	359.0	651.0	1092.1	1252.9
125°	320.5	380.8	649.9	1068.1	1203.8
127.5°	338.4	400.9	647.7	1045.2	1172.5
130°	352.9	420.4	646.6	1017.9	1145.7
132.5°	367.4	437.2	645.4	985.5	1115.6
135°	380.8	453.4	644.3	948.1	1076.5
137.5°	394.2	467.4	644.3	907.9	1030.7
140°	408.7	480.2	643.2	868.8	980.5
142.5°	424.3	491.9	643.2	832.4	926.9
145°	438.9	502.5	641.0	799.6	878.8
147.5°	455.6	512.6	637.6	772.2	834.2
150°	471.2	522.0	634.3	747.0	797.3
152.5°	485.8	531.0	628.7	725.8	763.8
155°	499.2	538.8	623.1	705.7	735.9
157.5°	512.6	546.1	617.5	686.8	710.2
160°	524.8	552.2	610.8	667.8	686.8
162.5°	536.0	557.2	604.1	649.3	664.4
165°	543.8	560.6	597.4	632.6	642.1
167.5°	552.8	563.4	590.7	618.1	624.2
170°	558.3	565.6	584.0	603.6	607.5
172.5°	563.9	567.3	577.3	590.7	590.7
175°	567.3	568.4	572.9	580.7	578.4
177.5°	569.5	568.4	569.5	573.4	569.5
180°	568.4	568.4	568.4	568.4	568.4

(END OF REPORT)