

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026294

Luminaire Tested: S124RDIP-B350D365UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026294
REPORT IS A COMBINATION OF REPORTS P999304 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D365UB27-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2688.6 lumens
Efficiency: N/A
Efficacy: 120.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026294

CATALOG NUMBER: S124RDIP-B350D365UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026294

CATALOG NUMBER: S124RDIP-B350D365UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	57
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	51	50	49	49	49	44
2	90	83	77	71	83	77	71	67	65	61	58	55	52	50	45	43	42	42	42	37
3	82	73	66	60	76	68	61	56	58	53	49	49	45	42	40	38	36	36	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	36	36	33	31	31	31	27
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	33	30	27	27	27	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	24	24	21
7	59	47	39	33	54	44	37	32	38	32	28	32	28	25	27	24	21	21	21	19
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	19	19	17
9	51	39	31	26	47	36	30	25	32	26	23	27	23	20	23	20	17	17	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	22	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4863	4863	4863
5°	4864	4719	4719
10°	4823	4570	4516
15°	4757	4384	4275
20°	4670	4173	4001
25°	4561	3945	3733
30°	4454	3713	3432
35°	4338	3477	3139
40°	4200	3223	2837
45°	4069	2971	2538
50°	3921	2695	2234
55°	3761	2414	1921
60°	3583	2114	1612
65°	3412	1772	1313
70°	3168	1410	1004
75°	2856	1025	702
80°	2385	631	504
85°	1797	364	277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4069 cd/sqm

TEST NUMBER: P1026294

CATALOG NUMBER: S124RDIP-B350D365UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.1	2.1
10°-20°	156.4	5.8
20°-30°	225.7	8.4
30°-40°	255.9	9.5
40°-50°	247.0	9.2
50°-60°	205.4	7.6
60°-70°	141.8	5.3
70°-80°	71.6	2.7
80°-90°	18.9	0.7
90°-100°	133.3	5.0
100°-110°	271.2	10.1
110°-120°	241.7	9.0
120°-130°	203.0	7.6
130°-140°	169.4	6.3
140°-150°	129.4	4.8
150°-160°	91.0	3.4
160°-170°	53.5	2.0
170°-180°	17.4	0.6
0°-30°	438.2	16.3
0°-40°	694.0	25.8
0°-60°	1146.4	42.6
0°-90°	1378.7	51.3
90°-120°	646.2	24.0
90°-150°	1148.1	42.7
90°-180°	1310.0	48.7
0°-180°	2688.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	596	596	596	596	596	
5°	596	594	588	593	592	57
15°	567	563	552	551	548	160
25°	513	505	486	478	474	236
35°	443	429	406	390	382	277
45°	362	345	317	295	287	279
55°	274	256	226	202	194	245
65°	186	167	138	118	112	184
75°	99	82	61	50	48	105
85°	25	16	14	13	13	27
90°	0	3	6	7	7	2
95°	12	37	287	142	86	13
105°	41	60	231	498	496	44
115°	73	91	206	396	476	72
125°	101	120	205	337	380	90
135°	120	143	204	299	340	93
145°	139	159	202	252	278	87
155°	158	170	197	223	232	73
165°	172	177	189	200	203	49
175°	179	180	181	183	183	17
180°	180	180	180	180	180	

TEST NUMBER: P1026294

CATALOG NUMBER: S124RDIP-B350D365UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	596.4	596.4	596.4	596.4	596.4
2.5°	598.2	596.4	591.4	596.4	595.9
5°	595.5	593.6	588.2	592.7	591.8
7.5°	591.4	589.5	582.7	585.9	584.5
10°	585.0	582.7	574.5	576.3	574.5
12.5°	576.7	574.0	564.0	564.9	562.1
15°	567.2	563.0	551.6	550.7	547.5
17.5°	556.2	550.3	537.0	534.7	530.2
20°	543.0	537.0	521.5	517.8	511.9
22.5°	528.3	521.5	504.6	498.7	494.1
25°	512.8	504.6	485.9	478.1	473.5
27.5°	496.8	486.8	467.1	458.0	451.6
30°	479.9	468.5	447.1	435.6	428.3
32.5°	462.1	448.9	426.5	412.8	406.0
35°	443.4	428.8	406.0	390.4	382.2
37.5°	423.8	408.7	383.6	366.7	358.5
40°	402.8	387.7	361.7	342.5	334.3
42.5°	382.7	366.7	339.3	319.7	311.0
45°	361.7	344.8	317.4	295.0	286.8
47.5°	340.2	322.8	294.5	271.2	262.1
50°	318.3	300.5	271.2	248.4	239.7
52.5°	295.9	278.6	248.4	225.1	216.0
55°	274.0	255.7	226.0	202.3	193.6
57.5°	252.5	233.3	204.1	179.9	173.5
60°	229.2	211.0	181.7	158.0	150.7
62.5°	208.2	189.1	158.9	137.5	132.0
65°	186.3	166.7	137.5	117.8	112.3
67.5°	163.5	144.8	117.4	100.0	93.6
70°	142.0	122.8	96.8	81.7	77.2
72.5°	119.2	102.3	78.1	65.8	61.6
75°	99.1	82.2	60.7	50.2	47.5
77.5°	78.1	63.5	45.2	37.9	37.0
80°	58.0	44.8	31.1	29.7	29.2
82.5°	40.6	28.8	22.4	21.5	21.0
85°	24.7	15.5	14.2	13.2	13.2
87.5°	10.5	6.8	6.4	5.9	6.4
90°	0.4	2.8	6.3	7.1	7.4
92.5°	4.9	27.2	138.2	45.7	32.1
95°	11.6	36.7	287.4	142.3	86.0
97.5°	19.4	40.6	307.5	290.6	206.6
100°	26.8	45.8	283.5	402.0	323.4
102.5°	33.9	52.2	253.5	471.8	424.9
105°	41.3	59.8	231.3	498.1	496.2
107.5°	49.4	67.5	216.9	490.2	530.0
110°	57.5	75.2	210.2	462.0	530.7



TEST NUMBER: P1026294

CATALOG NUMBER: S124RDIP-B350D365UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.2	83.0	207.0	427.4	509.9
115°	72.6	91.2	206.3	396.4	476.4
117.5°	80.4	98.8	205.9	372.0	443.6
120°	88.2	106.2	205.9	355.6	416.8
122.5°	95.2	113.4	205.6	344.9	395.7
125°	101.2	120.2	205.2	337.3	380.1
127.5°	106.8	126.6	204.5	330.0	370.3
130°	111.4	132.8	204.2	321.5	361.8
132.5°	116.0	138.0	203.8	311.2	352.3
135°	120.2	143.2	203.5	299.4	339.9
137.5°	124.5	147.6	203.5	286.7	325.5
140°	129.1	151.6	203.1	274.4	309.6
142.5°	134.0	155.4	203.1	262.9	292.7
145°	138.6	158.7	202.4	252.5	277.5
147.5°	143.9	161.9	201.4	243.8	263.4
150°	148.8	164.8	200.3	235.9	251.8
152.5°	153.4	167.7	198.5	229.2	241.2
155°	157.6	170.2	196.8	222.9	232.4
157.5°	161.9	172.4	195.0	216.8	224.3
160°	165.7	174.4	192.9	210.9	216.9
162.5°	169.3	176.0	190.8	205.0	209.8
165°	171.7	177.0	188.7	199.8	202.8
167.5°	174.6	177.9	186.5	195.2	197.1
170°	176.3	178.6	184.4	190.6	191.8
172.5°	178.1	179.2	182.3	186.6	186.5
175°	179.1	179.5	180.9	183.4	182.7
177.5°	179.8	179.5	179.8	181.1	179.8
180°	179.5	179.5	179.5	179.5	179.5

(END OF REPORT)