

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026305

Luminaire Tested: S124RDIP-B350D365UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026305
REPORT IS A COMBINATION OF REPORTS P999325 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D365UB35-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2678.0 lumens
Efficiency: N/A
Efficacy: 120.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026305

CATALOG NUMBER: S124RDIP-B350D365UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026305

CATALOG NUMBER: S124RDIP-B350D365UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	99	94	91	87	91	87	84	81	75	72	70	63	61	60	52	51	50
2	90	83	77	72	83	77	72	67	66	62	58	55	53	50	46	44	42
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	38	36
4	75	65	57	51	69	60	53	48	52	47	42	44	40	37	37	34	31
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	28
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	28	24	22
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	24	20	18
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4927	4927	4927
5°	4927	4780	4781
10°	4885	4630	4575
15°	4819	4441	4331
20°	4730	4228	4053
25°	4620	3996	3782
30°	4513	3761	3477
35°	4395	3522	3180
40°	4254	3265	2874
45°	4122	3010	2571
50°	3972	2731	2264
55°	3811	2446	1946
60°	3630	2142	1633
65°	3456	1794	1331
70°	3210	1429	1017
75°	2893	1039	711
80°	2418	639	511
85°	1819	366	281

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4122 cd/sqm

TEST NUMBER: P1026305

CATALOG NUMBER: S124RDIP-B350D365UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.8	2.1
10°-20°	158.4	5.9
20°-30°	228.7	8.5
30°-40°	259.2	9.7
40°-50°	250.3	9.3
50°-60°	208.1	7.8
60°-70°	143.6	5.4
70°-80°	72.6	2.7
80°-90°	19.4	0.7
90°-100°	30.1	1.1
100°-110°	90.1	3.4
110°-120°	153.1	5.7
120°-130°	201.9	7.5
130°-140°	226.8	8.5
140°-150°	222.9	8.3
150°-160°	187.5	7.0
160°-170°	124.8	4.7
170°-180°	43.7	1.6
0°-30°	443.9	16.6
0°-40°	703.1	26.3
0°-60°	1161.4	43.4
0°-90°	1397.0	52.2
90°-120°	273.3	10.2
90°-150°	925.1	34.5
90°-180°	1281.0	47.8
0°-180°	2678.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	604	604	604	604	604	
5°	603	601	596	600	600	57
15°	575	570	559	558	555	162
25°	520	511	492	484	480	239
35°	449	434	411	396	387	281
45°	366	349	322	299	290	283
55°	278	259	229	205	196	248
65°	189	169	139	119	114	186
75°	100	83	62	51	48	106
85°	25	16	14	13	13	27
90°	1	5	8	10	11	3
95°	21	25	27	28	28	23
105°	83	84	85	86	87	88
115°	156	156	155	155	154	154
125°	227	227	226	226	225	202
135°	292	295	295	294	293	226
145°	355	357	357	357	356	222
155°	407	407	407	408	407	187
165°	443	442	441	444	442	125
175°	461	459	459	461	459	44
180°	462	462	462	462	462	

TEST NUMBER: P1026305

CATALOG NUMBER: S124RDIP-B350D365UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	604.2	604.2	604.2	604.2	604.2
2.5°	606.0	604.2	599.1	604.2	603.7
5°	603.2	601.4	595.8	600.5	599.5
7.5°	599.1	597.2	590.3	593.5	592.1
10°	592.6	590.3	582.0	583.8	582.0
12.5°	584.3	581.5	571.3	572.3	569.5
15°	574.6	570.4	558.8	557.9	554.7
17.5°	563.5	557.4	544.0	541.7	537.1
20°	550.0	544.0	528.3	524.6	518.6
22.5°	535.2	528.3	511.2	505.2	500.5
25°	519.5	511.2	492.2	484.4	479.7
27.5°	503.3	493.1	473.3	464.0	457.5
30°	486.2	474.6	452.9	441.3	433.9
32.5°	468.2	454.7	432.1	418.2	411.3
35°	449.2	434.4	411.3	395.5	387.2
37.5°	429.3	414.0	388.6	371.5	363.1
40°	408.0	392.8	366.4	347.0	338.6
42.5°	387.7	371.5	343.7	323.8	315.0
45°	366.4	349.3	321.5	298.8	290.5
47.5°	344.6	327.1	298.4	274.8	265.5
50°	322.4	304.4	274.8	251.7	242.9
52.5°	299.8	282.2	251.7	228.1	218.8
55°	277.6	259.1	229.0	204.9	196.1
57.5°	255.8	236.4	206.8	182.3	175.8
60°	232.2	213.7	184.1	160.1	152.7
62.5°	211.0	191.5	161.0	139.2	133.7
65°	188.7	168.9	139.2	119.4	113.8
67.5°	165.6	146.6	118.9	101.3	94.8
70°	143.9	124.4	98.1	82.8	78.2
72.5°	120.7	103.6	79.1	66.6	62.5
75°	100.4	83.3	61.5	50.9	48.1
77.5°	79.1	64.3	45.8	38.4	37.5
80°	58.8	45.3	31.5	30.1	29.6
82.5°	41.2	29.1	22.7	21.7	21.3
85°	25.0	15.7	14.3	13.4	13.4
87.5°	10.6	6.9	6.5	6.0	6.5
90°	1.1	5.0	7.9	10.0	10.7
92.5°	9.3	13.9	15.7	16.8	17.1
95°	21.4	24.6	27.1	28.2	28.2
97.5°	34.3	37.1	40.0	41.4	41.4
100°	50.0	51.4	54.6	55.3	55.3
102.5°	66.4	66.8	69.6	70.7	71.1
105°	83.2	83.6	85.0	86.1	87.1
107.5°	100.7	101.0	101.4	102.8	102.5
110°	118.5	119.3	118.9	118.2	119.3



TEST NUMBER: P1026305

CATALOG NUMBER: S124RDIP-B350D365UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	137.1	137.1	136.4	136.4	136.4
115°	155.7	155.7	155.0	154.6	154.3
117.5°	173.2	173.2	172.8	171.7	170.7
120°	190.7	192.1	191.0	189.2	190.0
122.5°	208.9	209.2	208.9	207.8	206.0
125°	226.7	226.7	226.4	225.7	225.0
127.5°	242.8	243.9	243.2	242.4	242.1
130°	259.9	261.0	261.0	260.3	258.9
132.5°	277.4	278.2	277.8	277.1	276.7
135°	292.4	294.6	294.6	293.9	292.8
137.5°	309.2	310.3	311.0	309.9	310.3
140°	326.0	326.7	326.7	326.4	326.0
142.5°	341.4	342.1	341.7	341.7	341.7
145°	355.3	356.7	357.1	356.7	355.6
147.5°	369.6	371.3	371.0	370.6	370.3
150°	382.4	383.8	383.8	383.8	383.5
152.5°	394.6	395.3	395.6	396.7	395.6
155°	407.1	407.1	406.7	408.1	406.7
157.5°	417.8	417.1	417.1	418.1	417.1
160°	427.1	426.7	426.3	427.4	425.6
162.5°	435.6	434.6	434.2	436.3	434.6
165°	443.1	442.0	441.3	443.5	442.0
167.5°	449.2	447.8	447.8	449.9	447.8
170°	454.2	452.4	452.8	454.9	452.4
172.5°	457.8	456.3	456.3	458.8	456.3
175°	461.0	459.2	458.8	461.3	458.8
177.5°	462.4	460.6	460.6	463.1	460.3
180°	461.7	461.7	461.7	461.7	461.7

(END OF REPORT)