

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026311

Luminaire Tested: S124RDIP-B350D365UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026311
REPORT IS A COMBINATION OF REPORTS P999331 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D365UB40-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2652.0 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026311

CATALOG NUMBER: S124RDIP-B350D365UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026311

CATALOG NUMBER: S124RDIP-B350D365UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	99	94	91	87	91	87	84	81	75	72	70	63	61	60	52	51	50
2	90	83	77	72	83	77	72	67	66	62	58	55	53	50	46	44	42
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	38	36
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	31
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	28
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	28	24	22
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	24	20	18
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4880	4880	4880
5°	4881	4736	4737
10°	4840	4586	4531
15°	4773	4400	4291
20°	4686	4188	4016
25°	4578	3959	3747
30°	4471	3726	3445
35°	4354	3489	3150
40°	4214	3235	2847
45°	4084	2981	2547
50°	3935	2705	2242
55°	3775	2423	1928
60°	3597	2122	1617
65°	3425	1777	1318
70°	3179	1415	1008
75°	2867	1030	705
80°	2394	633	506
85°	1797	364	279

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4084 cd/sqm

TEST NUMBER: P1026311

CATALOG NUMBER: S124RDIP-B350D365UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.3	2.1
10°-20°	156.9	5.9
20°-30°	226.6	8.5
30°-40°	256.8	9.7
40°-50°	247.9	9.3
50°-60°	206.1	7.8
60°-70°	142.3	5.4
70°-80°	71.9	2.7
80°-90°	19.2	0.7
90°-100°	29.8	1.1
100°-110°	89.2	3.4
110°-120°	151.6	5.7
120°-130°	199.9	7.5
130°-140°	224.5	8.5
140°-150°	220.7	8.3
150°-160°	185.6	7.0
160°-170°	123.5	4.7
170°-180°	43.2	1.6
0°-30°	439.8	16.6
0°-40°	696.6	26.3
0°-60°	1150.6	43.4
0°-90°	1384.0	52.2
90°-120°	270.6	10.2
90°-150°	915.7	34.5
90°-180°	1268.0	47.8
0°-180°	2652.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	598	598	598	598	598	
5°	598	596	590	595	594	57
15°	569	565	554	553	550	160
25°	515	506	488	480	475	237
35°	445	430	407	392	384	278
45°	363	346	318	296	288	280
55°	275	257	227	203	194	246
65°	187	167	138	118	113	185
75°	100	82	61	50	48	105
85°	25	16	14	13	13	27
90°	1	5	8	10	11	3
95°	21	24	27	28	28	23
105°	82	83	84	85	86	87
115°	154	154	153	153	153	152
125°	224	224	224	223	223	200
135°	290	292	292	291	290	224
145°	352	353	353	353	352	220
155°	403	403	403	404	403	185
165°	439	438	437	439	438	124
175°	456	454	454	457	454	43
180°	457	457	457	457	457	

TEST NUMBER: P1026311

CATALOG NUMBER: S124RDIP-B350D365UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	598.5	598.5	598.5	598.5	598.5
2.5°	600.4	598.5	593.5	598.5	598.1
5°	597.6	595.8	590.3	594.9	594.0
7.5°	593.5	591.7	584.8	588.0	586.6
10°	587.1	584.8	576.5	578.4	576.5
12.5°	578.8	576.1	566.0	566.9	564.2
15°	569.2	565.1	553.6	552.7	549.5
17.5°	558.2	552.3	539.0	536.7	532.1
20°	544.9	539.0	523.4	519.7	513.8
22.5°	530.3	523.4	506.4	500.5	495.9
25°	514.7	506.4	487.6	479.8	475.3
27.5°	498.6	488.6	468.8	459.7	453.3
30°	481.7	470.2	448.7	437.2	429.9
32.5°	463.8	450.5	428.1	414.3	407.4
35°	445.0	430.3	407.4	391.8	383.6
37.5°	425.3	410.2	385.0	368.0	359.8
40°	404.2	389.1	363.0	343.7	335.5
42.5°	384.1	368.0	340.5	320.8	312.1
45°	363.0	346.0	318.5	296.1	287.8
47.5°	341.4	324.0	295.6	272.2	263.1
50°	319.4	301.6	272.2	249.3	240.6
52.5°	297.0	279.6	249.3	225.9	216.8
55°	275.0	256.6	226.9	203.0	194.3
57.5°	253.4	234.2	204.9	180.6	174.2
60°	230.1	211.7	182.4	158.6	151.2
62.5°	209.0	189.7	159.5	137.9	132.4
65°	187.0	167.3	137.9	118.2	112.7
67.5°	164.1	145.3	117.8	100.4	94.0
70°	142.5	123.3	97.2	82.0	77.5
72.5°	119.6	102.7	78.4	66.0	61.9
75°	99.5	82.5	61.0	50.4	47.7
77.5°	78.4	63.7	45.4	38.0	37.1
80°	58.2	44.9	31.2	29.8	29.3
82.5°	40.8	28.9	22.5	21.5	21.1
85°	24.7	15.6	14.2	13.3	13.3
87.5°	10.5	6.9	6.4	6.0	6.4
90°	1.1	4.9	7.8	9.9	10.6
92.5°	9.2	13.8	15.6	16.6	17.0
95°	21.2	24.4	26.9	27.9	27.9
97.5°	33.9	36.8	39.6	41.0	41.0
100°	49.5	50.9	54.1	54.8	54.8
102.5°	65.7	66.1	68.9	70.0	70.3
105°	82.4	82.7	84.1	85.2	86.2
107.5°	99.7	100.0	100.4	101.8	101.4
110°	117.3	118.1	117.7	117.0	118.1

TEST NUMBER: P1026311

CATALOG NUMBER: S124RDIP-B350D365UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	135.7	135.7	135.0	135.0	135.0
115°	154.1	154.1	153.4	153.0	152.7
117.5°	171.4	171.4	171.1	170.0	168.9
120°	188.7	190.2	189.1	187.3	188.0
122.5°	206.8	207.1	206.8	205.7	203.9
125°	224.4	224.4	224.1	223.4	222.7
127.5°	240.3	241.4	240.7	240.0	239.6
130°	257.3	258.4	258.4	257.7	256.2
132.5°	274.6	275.3	275.0	274.3	273.9
135°	289.5	291.6	291.6	290.9	289.8
137.5°	306.1	307.1	307.9	306.8	307.1
140°	322.7	323.4	323.4	323.0	322.7
142.5°	337.9	338.6	338.2	338.2	338.2
145°	351.7	353.1	353.4	353.1	352.0
147.5°	365.8	367.6	367.2	366.9	366.5
150°	378.5	380.0	380.0	380.0	379.6
152.5°	390.6	391.3	391.6	392.7	391.6
155°	402.9	402.9	402.6	404.0	402.6
157.5°	413.5	412.8	412.8	413.9	412.8
160°	422.7	422.4	422.0	423.1	421.3
162.5°	431.2	430.1	429.8	431.9	430.1
165°	438.6	437.6	436.9	439.0	437.6
167.5°	444.6	443.2	443.2	445.3	443.2
170°	449.6	447.8	448.2	450.3	447.8
172.5°	453.1	451.7	451.7	454.2	451.7
175°	456.3	454.5	454.2	456.7	454.2
177.5°	457.7	455.9	455.9	458.4	455.6
180°	457.0	457.0	457.0	457.0	457.0

(END OF REPORT)