

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026317

Luminaire Tested: S124RDIP-B350D365UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026317
REPORT IS A COMBINATION OF REPORTS P999337 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D365UB50-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2564.0 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026317

CATALOG NUMBER: S124RDIP-B350D365UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026317

CATALOG NUMBER: S124RDIP-B350D365UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	99	94	91	87	91	87	84	81	75	72	70	63	61	60	52	51	50
2	90	83	77	72	83	77	72	67	66	62	58	55	53	50	46	44	42
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	38	36
4	75	65	57	51	69	60	53	48	52	47	42	44	40	37	37	34	31
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	28
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	28	24	22
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	24	20	18
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4718	4718	4718
5°	4719	4579	4579
10°	4679	4434	4381
15°	4615	4254	4148
20°	4530	4049	3882
25°	4426	3827	3622
30°	4323	3602	3331
35°	4209	3373	3045
40°	4075	3127	2752
45°	3948	2882	2462
50°	3804	2616	2168
55°	3649	2342	1864
60°	3477	2051	1564
65°	3311	1719	1275
70°	3074	1367	974
75°	2769	995	682
80°	2316	610	491
85°	1739	351	268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3948 cd/sqm

TEST NUMBER: P1026317

CATALOG NUMBER: S124RDIP-B350D365UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.4	2.1
10°-20°	151.7	5.9
20°-30°	219.0	8.5
30°-40°	248.2	9.7
40°-50°	239.7	9.3
50°-60°	199.3	7.8
60°-70°	137.5	5.4
70°-80°	69.5	2.7
80°-90°	18.6	0.7
90°-100°	28.8	1.1
100°-110°	86.3	3.4
110°-120°	146.5	5.7
120°-130°	193.3	7.5
130°-140°	217.1	8.5
140°-150°	213.4	8.3
150°-160°	179.5	7.0
160°-170°	119.4	4.7
170°-180°	41.8	1.6
0°-30°	425.2	16.6
0°-40°	673.4	26.3
0°-60°	1112.3	43.4
0°-90°	1337.9	52.2
90°-120°	261.6	10.2
90°-150°	885.4	34.5
90°-180°	1226.0	47.8
0°-180°	2564.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	579	579	579	579	579	
5°	578	576	571	575	574	55
15°	550	546	535	534	531	155
25°	498	490	471	464	460	229
35°	430	416	394	379	371	269
45°	351	334	308	286	278	271
55°	266	248	219	196	188	238
65°	181	162	133	114	109	179
75°	96	80	59	49	46	101
85°	24	15	14	13	13	26
90°	1	5	8	10	10	3
95°	20	24	26	27	27	22
105°	80	80	81	82	83	84
115°	149	149	148	148	148	147
125°	217	217	217	216	215	193
135°	280	282	282	281	280	217
145°	340	341	342	341	340	213
155°	390	390	389	391	389	179
165°	424	423	422	424	423	120
175°	441	440	439	442	439	42
180°	442	442	442	442	442	

TEST NUMBER: P1026317

CATALOG NUMBER: S124RDIP-B350D365UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	578.6	578.6	578.6	578.6	578.6
2.5°	580.4	578.6	573.8	578.6	578.2
5°	577.7	576.0	570.7	575.1	574.2
7.5°	573.8	572.0	565.3	568.4	567.1
10°	567.6	565.3	557.4	559.1	557.4
12.5°	559.6	556.9	547.2	548.1	545.4
15°	550.3	546.3	535.2	534.3	531.2
17.5°	539.6	533.9	521.0	518.8	514.4
20°	526.8	521.0	506.0	502.4	496.7
22.5°	512.6	506.0	489.6	483.8	479.4
25°	497.6	489.6	471.4	463.9	459.5
27.5°	482.0	472.3	453.3	444.4	438.2
30°	465.7	454.6	433.8	422.7	415.6
32.5°	448.4	435.5	413.8	400.5	393.9
35°	430.2	416.0	393.9	378.8	370.8
37.5°	411.2	396.5	372.2	355.8	347.8
40°	390.8	376.2	350.9	332.3	324.3
42.5°	371.3	355.8	329.2	310.1	301.7
45°	350.9	334.5	307.9	286.2	278.2
47.5°	330.1	313.2	285.8	263.2	254.3
50°	308.8	291.5	263.2	241.0	232.6
52.5°	287.1	270.3	241.0	218.4	209.6
55°	265.8	248.1	219.3	196.3	187.9
57.5°	245.0	226.4	198.0	174.6	168.4
60°	222.4	204.7	176.3	153.3	146.2
62.5°	202.0	183.4	154.2	133.4	128.0
65°	180.8	161.7	133.4	114.3	109.0
67.5°	158.6	140.4	113.9	97.0	90.8
70°	137.8	119.2	93.9	79.3	74.9
72.5°	115.6	99.2	75.8	63.8	59.8
75°	96.1	79.8	58.9	48.7	46.1
77.5°	75.8	61.6	43.9	36.8	35.9
80°	56.3	43.4	30.1	28.8	28.4
82.5°	39.4	27.9	21.7	20.8	20.4
85°	23.9	15.1	13.7	12.8	12.8
87.5°	10.2	6.6	6.2	5.8	6.2
90°	1.0	4.8	7.5	9.6	10.3
92.5°	8.9	13.3	15.0	16.1	16.4
95°	20.5	23.6	26.0	27.0	27.0
97.5°	32.8	35.5	38.3	39.6	39.6
100°	47.8	49.2	52.3	53.0	53.0
102.5°	63.6	63.9	66.6	67.7	68.0
105°	79.6	80.0	81.3	82.4	83.4
107.5°	96.4	96.7	97.1	98.4	98.1
110°	113.5	114.1	113.8	113.1	114.1



TEST NUMBER: P1026317

CATALOG NUMBER: S124RDIP-B350D365UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	131.2	131.2	130.5	130.5	130.5
115°	149.0	149.0	148.3	148.0	147.6
117.5°	165.7	165.7	165.4	164.4	163.4
120°	182.5	183.9	182.8	181.1	181.8
122.5°	199.9	200.3	199.9	198.9	197.2
125°	217.0	217.0	216.7	216.0	215.3
127.5°	232.4	233.4	232.7	232.0	231.7
130°	248.8	249.8	249.8	249.1	247.8
132.5°	265.5	266.2	265.9	265.2	264.9
135°	279.9	281.9	281.9	281.3	280.2
137.5°	296.0	297.0	297.7	296.6	297.0
140°	312.0	312.7	312.7	312.4	312.0
142.5°	326.7	327.4	327.1	327.1	327.1
145°	340.0	341.4	341.7	341.4	340.4
147.5°	353.7	355.4	355.1	354.7	354.4
150°	366.0	367.4	367.4	367.4	367.0
152.5°	377.6	378.3	378.7	379.7	378.7
155°	389.6	389.6	389.3	390.6	389.3
157.5°	399.8	399.2	399.2	400.2	399.2
160°	408.7	408.4	408.0	409.1	407.4
162.5°	416.9	415.9	415.6	417.6	415.9
165°	424.1	423.1	422.4	424.5	423.1
167.5°	429.9	428.6	428.6	430.6	428.6
170°	434.7	433.0	433.3	435.4	433.0
172.5°	438.1	436.8	436.8	439.1	436.8
175°	441.2	439.5	439.1	441.5	439.1
177.5°	442.6	440.9	440.9	443.2	440.5
180°	441.9	441.9	441.9	441.9	441.9

(END OF REPORT)