

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026335

Luminaire Tested: S124RDIP-B350D590UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026335
REPORT IS A COMBINATION OF REPORTS P999365 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D590UB35-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3457.0 lumens
Efficiency: N/A
Efficacy: 121.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026335

CATALOG NUMBER: S124RDIP-B350D590UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026335

CATALOG NUMBER: S124RDIP-B350D590UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	96	92	88	85	87	84	81	78	69	66	64	55	53	52	42	41	40
2	87	80	74	69	79	73	68	64	60	57	54	48	46	44	37	36	34
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29
4	73	63	55	49	66	57	51	46	48	43	39	38	35	32	30	27	25
5	67	56	48	42	61	51	44	39	43	37	33	34	31	28	27	24	22
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	25	22	20
7	57	45	37	32	52	42	35	30	35	30	26	28	25	22	22	20	18
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	19	16	14
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4927	4927	4927
5°	4927	4780	4781
10°	4885	4630	4575
15°	4819	4441	4331
20°	4730	4228	4053
25°	4620	3996	3782
30°	4513	3761	3477
35°	4395	3522	3180
40°	4254	3265	2874
45°	4122	3010	2571
50°	3972	2731	2264
55°	3811	2446	1946
60°	3630	2142	1633
65°	3456	1794	1331
70°	3210	1429	1017
75°	2893	1039	711
80°	2418	639	511
85°	1819	366	281

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4122 cd/sqm

TEST NUMBER: P1026335

CATALOG NUMBER: S124RDIP-B350D590UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.8	1.6
10°-20°	158.4	4.6
20°-30°	228.7	6.6
30°-40°	259.2	7.5
40°-50°	250.3	7.2
50°-60°	208.1	6.0
60°-70°	143.6	4.2
70°-80°	72.6	2.1
80°-90°	20.0	0.6
90°-100°	48.4	1.4
100°-110°	144.9	4.2
110°-120°	246.2	7.1
120°-130°	324.7	9.4
130°-140°	364.7	10.5
140°-150°	358.4	10.4
150°-160°	301.4	8.7
160°-170°	200.6	5.8
170°-180°	70.2	2.0
0°-30°	443.9	12.8
0°-40°	703.1	20.3
0°-60°	1161.4	33.6
0°-90°	1397.6	40.4
90°-120°	439.5	12.7
90°-150°	1487.2	43.0
90°-180°	2059.0	59.6
0°-180°	3457.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	604	604	604	604	604	
5°	603	601	596	600	600	57
15°	575	570	559	558	555	162
25°	520	511	492	484	480	239
35°	449	434	411	396	387	281
45°	366	349	322	299	290	283
55°	278	259	229	205	196	248
65°	189	169	139	119	114	186
75°	100	83	62	51	48	106
85°	25	16	14	13	13	27
90°	2	8	13	16	17	4
95°	34	40	44	45	45	37
105°	134	134	137	138	140	142
115°	250	250	249	249	248	247
125°	364	364	364	363	362	325
135°	470	474	474	472	471	364
145°	571	574	574	574	572	358
155°	654	654	654	656	654	301
165°	712	711	710	713	711	201
175°	741	738	738	742	738	70
180°	742	742	742	742	742	

TEST NUMBER: P1026335

CATALOG NUMBER: S124RDIP-B350D590UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	604.2	604.2	604.2	604.2	604.2
2.5°	606.0	604.2	599.1	604.2	603.7
5°	603.2	601.4	595.8	600.5	599.5
7.5°	599.1	597.2	590.3	593.5	592.1
10°	592.6	590.3	582.0	583.8	582.0
12.5°	584.3	581.5	571.3	572.3	569.5
15°	574.6	570.4	558.8	557.9	554.7
17.5°	563.5	557.4	544.0	541.7	537.1
20°	550.0	544.0	528.3	524.6	518.6
22.5°	535.2	528.3	511.2	505.2	500.5
25°	519.5	511.2	492.2	484.4	479.7
27.5°	503.3	493.1	473.3	464.0	457.5
30°	486.2	474.6	452.9	441.3	433.9
32.5°	468.2	454.7	432.1	418.2	411.3
35°	449.2	434.4	411.3	395.5	387.2
37.5°	429.3	414.0	388.6	371.5	363.1
40°	408.0	392.8	366.4	347.0	338.6
42.5°	387.7	371.5	343.7	323.8	315.0
45°	366.4	349.3	321.5	298.8	290.5
47.5°	344.6	327.1	298.4	274.8	265.5
50°	322.4	304.4	274.8	251.7	242.9
52.5°	299.8	282.2	251.7	228.1	218.8
55°	277.6	259.1	229.0	204.9	196.1
57.5°	255.8	236.4	206.8	182.3	175.8
60°	232.2	213.7	184.1	160.1	152.7
62.5°	211.0	191.5	161.0	139.2	133.7
65°	188.7	168.9	139.2	119.4	113.8
67.5°	165.6	146.6	118.9	101.3	94.8
70°	143.9	124.4	98.1	82.8	78.2
72.5°	120.7	103.6	79.1	66.6	62.5
75°	100.4	83.3	61.5	50.9	48.1
77.5°	79.1	64.3	45.8	38.4	37.5
80°	58.8	45.3	31.5	30.1	29.6
82.5°	41.2	29.1	22.7	21.7	21.3
85°	25.0	15.7	14.3	13.4	13.4
87.5°	10.6	6.9	6.5	6.0	6.5
90°	1.7	8.0	12.6	16.1	17.2
92.5°	14.9	22.4	25.3	27.0	27.6
95°	34.4	39.6	43.6	45.3	45.3
97.5°	55.1	59.7	64.3	66.6	66.6
100°	80.4	82.7	87.8	89.0	89.0
102.5°	106.8	107.3	111.9	113.7	114.2
105°	133.8	134.3	136.6	138.3	140.1
107.5°	161.9	162.5	163.0	165.3	164.7
110°	190.6	191.7	191.2	190.0	191.7

TEST NUMBER: P1026335

CATALOG NUMBER: S124RDIP-B350D590UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	220.4	220.4	219.3	219.3	219.3
115°	250.3	250.3	249.1	248.6	248.0
117.5°	278.4	278.4	277.8	276.1	274.4
120°	306.5	308.8	307.1	304.2	305.4
122.5°	335.8	336.4	335.8	334.1	331.2
125°	364.5	364.5	363.9	362.8	361.6
127.5°	390.3	392.1	390.9	389.8	389.2
130°	417.9	419.6	419.6	418.5	416.2
132.5°	446.0	447.2	446.6	445.5	444.9
135°	470.1	473.6	473.6	472.4	470.7
137.5°	497.1	498.8	500.0	498.3	498.8
140°	524.1	525.2	525.2	524.7	524.1
142.5°	548.8	549.9	549.4	549.4	549.4
145°	571.2	573.5	574.0	573.5	571.7
147.5°	594.1	597.0	596.4	595.8	595.3
150°	614.8	617.1	617.1	617.1	616.5
152.5°	634.3	635.5	636.0	637.8	636.0
155°	654.4	654.4	653.8	656.1	653.8
157.5°	671.6	670.5	670.5	672.2	670.5
160°	686.5	686.0	685.4	687.1	684.3
162.5°	700.3	698.6	698.0	701.5	698.6
165°	712.4	710.7	709.5	713.0	710.7
167.5°	722.1	719.8	719.8	723.3	719.8
170°	730.2	727.3	727.9	731.3	727.3
172.5°	735.9	733.6	733.6	737.6	733.6
175°	741.1	738.2	737.6	741.7	737.6
177.5°	743.4	740.5	740.5	744.5	739.9
180°	742.2	742.2	742.2	742.2	742.2

(END OF REPORT)