

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025505

Luminaire Tested: S124DIP-B575D1035UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025505
REPORT IS A COMBINATION OF REPORTS P996060 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B575D1035UB35-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6182.4 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025505

CATALOG NUMBER: S124DIP-B575D1035UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1025505

CATALOG NUMBER: S124DIP-B575D1035UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	47	47	47
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	42	41	40	40	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	34	34	34	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	33	30	29	29	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	25	25	21
5	67	55	47	41	60	51	44	38	42	37	33	34	30	27	26	24	21	21	21	18
6	61	49	41	36	56	45	38	33	38	32	28	30	27	24	24	21	19	19	19	16
7	57	44	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	17	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	15	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	16	13	13	13	11
10	46	34	27	22	41	31	25	20	26	21	18	21	18	15	17	14	12	12	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7920	7920	7920
5°	7927	7692	7702
10°	7860	7479	7426
15°	7747	7225	7116
20°	7603	6951	6794
25°	7441	6660	6449
30°	7246	6347	6069
35°	7043	6026	5701
40°	6832	5680	5310
45°	6611	5333	4946
50°	6367	4997	4541
55°	6100	4605	4140
60°	5828	4175	3721
65°	5516	3730	3249
70°	5156	3196	2744
75°	4619	2575	2199
80°	3936	1862	1546
85°	3056	1038	832

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6611 cd/sqm

TEST NUMBER: P1025505

CATALOG NUMBER: S124DIP-B575D1035UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	1.5
10°-20°	257.9	4.2
20°-30°	379.6	6.1
30°-40°	441.2	7.1
40°-50°	441.2	7.1
50°-60°	385.9	6.2
60°-70°	286.5	4.6
70°-80°	162.5	2.6
80°-90°	48.5	0.8
90°-100°	375.3	6.1
100°-110°	763.4	12.3
110°-120°	680.4	11.0
120°-130°	571.5	9.2
130°-140°	476.9	7.7
140°-150°	364.2	5.9
150°-160°	256.0	4.1
160°-170°	150.6	2.4
170°-180°	49.0	0.8
0°-30°	729.1	11.8
0°-40°	1170.3	18.9
0°-60°	1997.4	32.3
0°-90°	2495.0	40.4
90°-120°	1819.1	29.4
90°-150°	3231.8	52.3
90°-180°	3687.0	59.6
0°-180°	6182.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	970	967	959	967	966	92
15°	924	921	909	914	911	260
25°	837	831	820	821	818	385
35°	720	714	704	698	694	450
45°	588	582	570	561	559	453
55°	444	442	431	422	417	398
65°	301	297	290	282	278	298
75°	160	156	152	149	149	170
85°	42	42	40	40	40	45
90°	1	8	18	20	21	5
95°	33	103	809	400	242	36
105°	116	168	651	1402	1397	124
115°	204	257	581	1116	1341	203
125°	285	338	578	950	1070	254
135°	338	403	573	843	957	262
145°	390	447	570	711	781	245
155°	444	479	554	627	654	205
165°	483	498	531	562	571	137
175°	504	505	509	516	514	48
180°	505	505	505	505	505	

TEST NUMBER: P1025505

CATALOG NUMBER: S124DIP-B575D1035UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	971.3	971.3	971.3	971.3	971.3
2.5°	974.4	972.1	963.5	971.3	970.5
5°	970.5	967.4	958.8	967.4	965.8
7.5°	963.5	960.4	951.1	958.1	957.3
10°	953.4	950.3	940.2	946.4	944.8
12.5°	940.2	937.0	926.1	933.2	930.8
15°	923.8	920.7	909.0	913.7	911.4
17.5°	905.1	901.2	890.3	893.5	891.9
20°	884.1	880.2	868.6	870.9	869.3
22.5°	861.6	856.1	844.4	849.1	846.0
25°	836.6	831.2	820.3	821.1	818.0
27.5°	808.6	803.2	793.1	791.5	787.6
30°	780.6	774.4	764.3	761.2	757.3
32.5°	751.0	745.6	734.7	730.8	726.9
35°	719.9	714.5	703.6	698.1	694.2
37.5°	687.2	682.5	670.9	665.4	660.0
40°	655.3	649.1	637.4	629.6	625.7
42.5°	621.1	618.0	604.7	595.4	593.0
45°	587.6	582.2	569.7	561.1	558.8
47.5°	552.6	548.7	537.0	527.7	521.4
50°	516.8	513.7	502.8	491.9	487.2
52.5°	481.8	477.9	466.2	456.8	450.6
55°	444.4	442.1	431.2	421.8	417.2
57.5°	409.4	407.0	396.1	386.8	382.1
60°	372.8	368.9	358.8	351.8	347.9
62.5°	337.0	333.9	323.0	316.8	312.9
65°	301.2	297.3	289.5	281.7	277.8
67.5°	264.6	261.5	253.7	245.9	245.2
70°	231.1	225.7	219.5	213.2	210.9
72.5°	195.3	189.9	185.2	180.6	178.2
75°	160.3	156.4	152.5	149.4	148.7
77.5°	126.1	124.5	120.6	119.9	117.5
80°	95.7	93.4	91.8	90.3	89.5
82.5°	66.2	65.4	65.4	64.6	63.8
85°	42.0	42.0	40.5	40.5	39.7
87.5°	20.2	19.5	18.7	18.7	18.7
90°	1.0	7.9	17.9	19.9	20.8
92.5°	13.9	76.4	389.1	128.6	90.3
95°	32.8	103.2	809.0	400.5	242.2
97.5°	54.6	114.2	865.6	818.0	581.7
100°	75.4	129.0	798.1	1131.6	910.3
102.5°	95.3	146.9	713.7	1328.2	1196.2
105°	116.1	168.3	651.2	1402.2	1396.7
107.5°	139.0	190.1	610.5	1379.8	1492.0
110°	161.8	211.9	591.6	1300.4	1494.0

TEST NUMBER: P1025505

CATALOG NUMBER: S124DIP-B575D1035UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	183.6	233.8	582.7	1203.1	1435.4
115°	204.5	256.6	580.7	1115.8	1341.1
117.5°	226.3	278.0	579.7	1047.3	1248.8
120°	248.2	298.8	579.7	1001.2	1173.3
122.5°	268.0	319.1	578.7	970.8	1113.8
125°	284.9	338.5	577.7	949.5	1070.1
127.5°	300.8	356.4	575.8	929.2	1042.3
130°	313.7	373.7	574.8	904.8	1018.5
132.5°	326.6	388.6	573.8	876.0	991.7
135°	338.5	403.0	572.8	842.8	956.9
137.5°	350.4	415.4	572.8	807.0	916.2
140°	363.3	426.8	571.8	772.3	871.6
142.5°	377.2	437.3	571.8	740.0	823.9
145°	390.1	446.7	569.8	710.8	781.2
147.5°	405.0	455.6	566.8	686.4	741.5
150°	418.9	464.0	563.8	664.1	708.8
152.5°	431.8	472.0	558.9	645.2	679.0
155°	443.7	479.0	553.9	627.3	654.2
157.5°	455.6	485.4	548.9	610.5	631.3
160°	466.6	490.8	543.0	593.6	610.5
162.5°	476.5	495.4	537.0	577.2	590.6
165°	483.4	498.3	531.1	562.3	570.8
167.5°	491.4	500.8	525.1	549.4	554.9
170°	496.3	502.8	519.2	536.6	540.0
172.5°	501.3	504.3	513.2	525.1	525.1
175°	504.3	505.3	509.2	516.2	514.2
177.5°	506.3	505.3	506.3	509.7	506.3
180°	505.3	505.3	505.3	505.3	505.3

(END OF REPORT)