

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026348

Luminaire Tested: S124RDIP-B350D590UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026348
REPORT IS A COMBINATION OF REPORTS P999378 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D590UB50-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3380.1 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026348

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026348

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47
1	96	92	88	84	87	83	80	77	68	66	64	54	53	52	41	41	40
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	37	35	34
3	80	71	63	58	72	64	58	53	53	49	45	43	39	37	33	31	29
4	73	63	55	49	66	57	51	45	47	42	38	38	34	32	29	27	25
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	27	24	22
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19
7	57	45	37	32	52	41	35	30	35	29	26	28	24	21	22	19	17
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4718	4718	4718
5°	4719	4579	4579
10°	4679	4434	4381
15°	4615	4254	4148
20°	4530	4049	3882
25°	4426	3827	3622
30°	4323	3602	3331
35°	4209	3373	3045
40°	4075	3127	2752
45°	3948	2882	2462
50°	3804	2616	2168
55°	3649	2342	1864
60°	3477	2051	1564
65°	3311	1719	1275
70°	3074	1367	974
75°	2769	995	682
80°	2316	610	491
85°	1739	351	268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3948 cd/sqm

TEST NUMBER: P1026348

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.4	1.6
10°-20°	151.7	4.5
20°-30°	219.0	6.5
30°-40°	248.2	7.3
40°-50°	239.7	7.1
50°-60°	199.3	5.9
60°-70°	137.5	4.1
70°-80°	69.5	2.1
80°-90°	18.7	0.6
90°-100°	207.8	6.1
100°-110°	422.7	12.5
110°-120°	376.8	11.1
120°-130°	316.5	9.4
130°-140°	264.1	7.8
140°-150°	201.7	6.0
150°-160°	141.8	4.2
160°-170°	83.4	2.5
170°-180°	27.1	0.8
0°-30°	425.2	12.6
0°-40°	673.4	19.9
0°-60°	1112.3	32.9
0°-90°	1338.1	39.6
90°-120°	1007.4	29.8
90°-150°	1789.7	52.9
90°-180°	2042.0	60.4
0°-180°	3380.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	579	579	579	579	579	
5°	578	576	571	575	574	55
15°	550	546	535	534	531	155
25°	498	490	471	464	460	229
35°	430	416	394	379	371	269
45°	351	334	308	286	278	271
55°	266	248	219	196	188	238
65°	181	162	133	114	109	179
75°	96	80	59	49	46	101
85°	24	15	14	13	13	26
90°	0	4	10	11	12	3
95°	18	57	448	222	134	20
105°	64	93	361	776	774	69
115°	113	142	322	618	743	112
125°	158	187	320	526	593	141
135°	188	223	317	467	530	145
145°	216	247	316	394	433	136
155°	246	265	307	347	362	113
165°	268	276	294	311	316	76
175°	279	280	282	286	285	27
180°	280	280	280	280	280	

TEST NUMBER: P1026348

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	578.6	578.6	578.6	578.6	578.6
2.5°	580.4	578.6	573.8	578.6	578.2
5°	577.7	576.0	570.7	575.1	574.2
7.5°	573.8	572.0	565.3	568.4	567.1
10°	567.6	565.3	557.4	559.1	557.4
12.5°	559.6	556.9	547.2	548.1	545.4
15°	550.3	546.3	535.2	534.3	531.2
17.5°	539.6	533.9	521.0	518.8	514.4
20°	526.8	521.0	506.0	502.4	496.7
22.5°	512.6	506.0	489.6	483.8	479.4
25°	497.6	489.6	471.4	463.9	459.5
27.5°	482.0	472.3	453.3	444.4	438.2
30°	465.7	454.6	433.8	422.7	415.6
32.5°	448.4	435.5	413.8	400.5	393.9
35°	430.2	416.0	393.9	378.8	370.8
37.5°	411.2	396.5	372.2	355.8	347.8
40°	390.8	376.2	350.9	332.3	324.3
42.5°	371.3	355.8	329.2	310.1	301.7
45°	350.9	334.5	307.9	286.2	278.2
47.5°	330.1	313.2	285.8	263.2	254.3
50°	308.8	291.5	263.2	241.0	232.6
52.5°	287.1	270.3	241.0	218.4	209.6
55°	265.8	248.1	219.3	196.3	187.9
57.5°	245.0	226.4	198.0	174.6	168.4
60°	222.4	204.7	176.3	153.3	146.2
62.5°	202.0	183.4	154.2	133.4	128.0
65°	180.8	161.7	133.4	114.3	109.0
67.5°	158.6	140.4	113.9	97.0	90.8
70°	137.8	119.2	93.9	79.3	74.9
72.5°	115.6	99.2	75.8	63.8	59.8
75°	96.1	79.8	58.9	48.7	46.1
77.5°	75.8	61.6	43.9	36.8	35.9
80°	56.3	43.4	30.1	28.8	28.4
82.5°	39.4	27.9	21.7	20.8	20.4
85°	23.9	15.1	13.7	12.8	12.8
87.5°	10.2	6.6	6.2	5.8	6.2
90°	0.5	4.4	9.9	11.0	11.5
92.5°	7.7	42.4	215.5	71.2	50.0
95°	18.1	57.2	448.0	221.8	134.1
97.5°	30.2	63.2	479.4	453.0	322.1
100°	41.8	71.5	442.0	626.6	504.1
102.5°	52.8	81.4	395.2	735.5	662.4
105°	64.3	93.2	360.6	776.4	773.5
107.5°	77.0	105.2	338.1	764.1	826.2
110°	89.6	117.4	327.6	720.2	827.3

TEST NUMBER: P1026348

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	101.7	129.4	322.7	666.2	794.9
115°	113.2	142.1	321.6	617.9	742.7
117.5°	125.3	153.9	321.0	580.0	691.5
120°	137.4	165.5	321.0	554.4	649.8
122.5°	148.4	176.8	320.5	537.6	616.8
125°	157.8	187.4	319.9	525.8	592.6
127.5°	166.6	197.4	318.8	514.5	577.2
130°	173.7	207.0	318.3	501.0	564.0
132.5°	180.9	215.2	317.7	485.2	549.2
135°	187.5	223.2	317.2	466.8	529.9
137.5°	194.1	230.0	317.2	447.0	507.4
140°	201.2	236.4	316.6	427.6	482.7
142.5°	208.9	242.2	316.6	409.8	456.3
145°	216.0	247.4	315.5	393.6	432.6
147.5°	224.3	252.3	313.9	380.2	410.6
150°	232.0	257.0	312.2	367.8	392.5
152.5°	239.1	261.4	309.5	357.4	376.0
155°	245.7	265.2	306.7	347.4	362.3
157.5°	252.3	268.8	304.0	338.0	349.6
160°	258.4	271.8	300.7	328.7	338.1
162.5°	263.9	274.3	297.4	319.6	327.1
165°	267.7	276.0	294.1	311.4	316.1
167.5°	272.1	277.4	290.8	304.2	307.3
170°	274.9	278.5	287.5	297.1	299.0
172.5°	277.6	279.2	284.2	290.8	290.8
175°	279.3	279.8	282.0	285.9	284.8
177.5°	280.4	279.8	280.4	282.3	280.4
180°	279.8	279.8	279.8	279.8	279.8

(END OF REPORT)