

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025603

Luminaire Tested: S124DIP-B575D365UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025603
REPORT IS A COMBINATION OF REPORTS P996188 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B575D365UB40-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3737.0 lumens
Efficiency: N/A
Efficacy: 112.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025603

CATALOG NUMBER: S124DIP-B575D365UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1025603

CATALOG NUMBER: S124DIP-B575D365UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66		
1	101	97	93	89	95	91	88	85	81	78	76	71	69	68	63	61	60	56		
2	92	85	78	73	87	80	74	69	71	67	63	63	59	56	55	53	50	47		
3	84	74	67	61	79	70	64	58	63	57	53	55	51	48	49	46	43	39		
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	44	40	37	34		
5	71	59	50	44	66	56	48	43	50	44	39	44	39	36	39	35	32	29		
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	28	26		
7	61	48	40	34	57	45	38	33	41	35	30	37	32	28	33	28	25	23		
8	56	44	36	30	53	41	34	29	37	31	27	34	28	25	30	26	23	20		
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21	18		
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7841	7841	7841
5°	7848	7615	7625
10°	7781	7404	7353
15°	7669	7153	7045
20°	7527	6880	6726
25°	7367	6594	6384
30°	7173	6283	6008
35°	6973	5965	5644
40°	6763	5623	5258
45°	6545	5280	4896
50°	6302	4947	4495
55°	6038	4558	4098
60°	5770	4133	3683
65°	5461	3693	3217
70°	5104	3164	2717
75°	4573	2550	2176
80°	3899	1844	1530
85°	3027	1028	824

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6545 cd/sqm

TEST NUMBER: P1025603

CATALOG NUMBER: S124DIP-B575D365UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.6	2.4
10°-20°	255.3	6.8
20°-30°	375.8	10.1
30°-40°	436.8	11.7
40°-50°	436.8	11.7
50°-60°	382.0	10.2
60°-70°	283.6	7.6
70°-80°	160.9	4.3
80°-90°	47.1	1.3
90°-100°	29.8	0.8
100°-110°	89.2	2.4
110°-120°	151.6	4.1
120°-130°	199.9	5.3
130°-140°	224.5	6.0
140°-150°	220.7	5.9
150°-160°	185.6	5.0
160°-170°	123.5	3.3
170°-180°	43.2	1.2
0°-30°	721.7	19.3
0°-40°	1158.6	31.0
0°-60°	1977.4	52.9
0°-90°	2469.0	66.1
90°-120°	270.6	7.2
90°-150°	915.7	24.5
90°-180°	1268.0	33.9
0°-180°	3737.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	962	962	962	962	962	
5°	961	958	949	958	956	91
15°	914	912	900	904	902	258
25°	828	823	812	813	810	381
35°	713	707	696	691	687	446
45°	582	576	564	556	553	448
55°	440	438	427	418	413	394
65°	298	294	287	279	275	295
75°	159	155	151	148	147	168
85°	42	42	40	40	39	45
90°	1	5	8	10	11	4
95°	21	24	27	28	28	23
105°	82	83	84	85	86	87
115°	154	154	153	153	153	152
125°	224	224	224	223	223	200
135°	290	292	292	291	290	224
145°	352	353	353	353	352	220
155°	403	403	403	404	403	185
165°	439	438	437	439	438	124
175°	456	454	454	457	454	43
180°	457	457	457	457	457	

TEST NUMBER: P1025603

CATALOG NUMBER: S124DIP-B575D365UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	961.5	961.5	961.5	961.5	961.5
2.5°	964.6	962.3	953.8	961.5	960.8
5°	960.8	957.7	949.2	957.7	956.2
7.5°	953.8	950.8	941.5	948.4	947.7
10°	943.8	940.7	930.7	936.9	935.4
12.5°	930.7	927.6	916.9	923.8	921.5
15°	914.5	911.5	899.9	904.5	902.2
17.5°	896.1	892.2	881.4	884.5	883.0
20°	875.3	871.4	859.8	862.2	860.6
22.5°	852.9	847.5	836.0	840.6	837.5
25°	828.3	822.9	812.1	812.8	809.8
27.5°	800.5	795.1	785.1	783.6	779.7
30°	772.8	766.6	756.6	753.5	749.7
32.5°	743.5	738.1	727.3	723.5	719.6
35°	712.7	707.3	696.5	691.1	687.3
37.5°	680.3	675.7	664.1	658.8	653.4
40°	648.7	642.6	631.0	623.3	619.5
42.5°	614.8	611.8	598.7	589.4	587.1
45°	581.7	576.3	564.0	555.5	553.2
47.5°	547.0	543.2	531.6	522.4	516.2
50°	511.6	508.5	497.7	486.9	482.3
52.5°	476.9	473.1	461.5	452.3	446.1
55°	439.9	437.6	426.8	417.6	413.0
57.5°	405.3	403.0	392.2	382.9	378.3
60°	369.1	365.2	355.2	348.3	344.4
62.5°	333.6	330.5	319.7	313.6	309.7
65°	298.2	294.3	286.6	278.9	275.1
67.5°	262.0	258.9	251.2	243.5	242.7
70°	228.8	223.4	217.3	211.1	208.8
72.5°	193.4	188.0	183.4	178.7	176.4
75°	158.7	154.9	151.0	147.9	147.2
77.5°	124.8	123.3	119.4	118.7	116.3
80°	94.8	92.5	90.9	89.4	88.6
82.5°	65.5	64.7	64.7	63.9	63.2
85°	41.6	41.6	40.1	40.1	39.3
87.5°	20.0	19.3	18.5	18.5	18.5
90°	1.1	4.9	7.8	9.9	10.6
92.5°	9.2	13.8	15.6	16.6	17.0
95°	21.2	24.4	26.9	27.9	27.9
97.5°	33.9	36.8	39.6	41.0	41.0
100°	49.5	50.9	54.1	54.8	54.8
102.5°	65.7	66.1	68.9	70.0	70.3
105°	82.4	82.7	84.1	85.2	86.2
107.5°	99.7	100.0	100.4	101.8	101.4
110°	117.3	118.1	117.7	117.0	118.1



TEST NUMBER: P1025603

CATALOG NUMBER: S124DIP-B575D365UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	135.7	135.7	135.0	135.0	135.0
115°	154.1	154.1	153.4	153.0	152.7
117.5°	171.4	171.4	171.1	170.0	168.9
120°	188.7	190.2	189.1	187.3	188.0
122.5°	206.8	207.1	206.8	205.7	203.9
125°	224.4	224.4	224.1	223.4	222.7
127.5°	240.3	241.4	240.7	240.0	239.6
130°	257.3	258.4	258.4	257.7	256.2
132.5°	274.6	275.3	275.0	274.3	273.9
135°	289.5	291.6	291.6	290.9	289.8
137.5°	306.1	307.1	307.9	306.8	307.1
140°	322.7	323.4	323.4	323.0	322.7
142.5°	337.9	338.6	338.2	338.2	338.2
145°	351.7	353.1	353.4	353.1	352.0
147.5°	365.8	367.6	367.2	366.9	366.5
150°	378.5	380.0	380.0	380.0	379.6
152.5°	390.6	391.3	391.6	392.7	391.6
155°	402.9	402.9	402.6	404.0	402.6
157.5°	413.5	412.8	412.8	413.9	412.8
160°	422.7	422.4	422.0	423.1	421.3
162.5°	431.2	430.1	429.8	431.9	430.1
165°	438.6	437.6	436.9	439.0	437.6
167.5°	444.6	443.2	443.2	445.3	443.2
170°	449.6	447.8	448.2	450.3	447.8
172.5°	453.1	451.7	451.7	454.2	451.7
175°	456.3	454.5	454.2	456.7	454.2
177.5°	457.7	455.9	455.9	458.4	455.6
180°	457.0	457.0	457.0	457.0	457.0

(END OF REPORT)