

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026381

Luminaire Tested: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026381
REPORT IS A COMBINATION OF REPORTS P999421 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6044.0 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026381

CATALOG NUMBER: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1026381

CATALOG NUMBER: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	96	92	88	85	87	84	81	78	69	66	65	55	53	52	42	41	40
2	88	81	75	70	80	74	69	64	61	57	54	49	46	44	37	36	34
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	33	31	30
4	73	63	55	50	67	58	51	46	48	43	39	39	35	32	30	28	26
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	25	23
6	62	50	43	37	56	46	40	35	39	34	30	32	28	25	25	22	20
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	17	15
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7774	7774	7774	7774
5°	7774	8784	7787	6714
10°	7733	10126	7726	5839
15°	7640	11397	7640	4889
20°	7544	12357	7505	4305
25°	7427	12409	7393	3888
30°	7302	10552	7245	3601
35°	7125	7962	7035	3388
40°	6928	5770	6793	3221
45°	6603	4385	6439	3073
50°	6217	3544	6047	2857
55°	5800	2935	5610	2569
60°	5381	2481	5140	2136
65°	4853	2022	4699	1698
70°	4370	1639	4165	1379
75°	3830	1181	3565	1011
80°	3159	782	2875	743
85°	2292	402	1899	402

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 9732 cd/sqm

TEST NUMBER: P1026381

CATALOG NUMBER: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.3	1.5
10°-20°	278.8	4.6
20°-30°	436.7	7.2
30°-40°	484.9	8.0
40°-50°	429.7	7.1
50°-60°	334.9	5.5
60°-70°	219.1	3.6
70°-80°	107.5	1.8
80°-90°	28.1	0.5
90°-100°	361.4	6.0
100°-110°	754.6	12.5
110°-120°	670.7	11.1
120°-130°	564.6	9.3
130°-140°	471.1	7.8
140°-150°	359.7	6.0
150°-160°	252.9	4.2
160°-170°	148.7	2.5
170°-180°	48.4	0.8
0°-30°	807.8	13.4
0°-40°	1292.7	21.4
0°-60°	2057.3	34.0
0°-90°	2412.0	39.9
90°-120°	1786.7	29.6
90°-150°	3182.1	52.6
90°-180°	3632.0	60.1
0°-180°	6044.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	953	953	953	953	953	
5°	952	1102	953	842	952	90
15°	911	1460	911	626	911	257
25°	835	1574	831	493	835	385
35°	728	970	719	412	728	455
45°	587	496	572	347	587	453
55°	422	296	409	259	422	378
65°	265	173	257	145	265	264
75°	133	80	124	68	133	141
85°	32	19	26	19	32	36
90°	1	21	1	21	1	4
95°	32	239	32	239	32	35
105°	115	1378	115	1378	115	122
115°	202	1324	202	1324	202	200
125°	281	1056	281	1056	281	251
135°	334	944	334	944	334	258
145°	385	771	385	771	385	242
155°	438	646	438	646	438	202
165°	477	563	477	563	477	135
175°	498	508	498	508	498	47
180°	499	499	499	499	499	

TEST NUMBER: P1026381

CATALOG NUMBER: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4
2.5°	954.9	963.4	968.0	971.8	979.5	982.6	988.7	990.2	996.4	995.6	993.3
5°	951.8	966.4	977.2	988.7	1002.5	1010.2	1018.7	1031.0	1037.1	1045.6	1050.9
7.5°	946.5	966.4	984.1	1001.8	1024.0	1036.3	1047.1	1066.3	1082.4	1096.3	1111.6
10°	938.0	963.4	989.5	1013.3	1044.0	1058.6	1074.7	1103.2	1125.4	1144.7	1169.2
12.5°	924.9	960.3	989.5	1021.7	1060.9	1080.9	1102.4	1136.2	1162.3	1193.8	1224.6
15°	911.1	950.3	988.7	1031.0	1075.5	1098.6	1120.1	1165.4	1205.3	1241.5	1275.3
17.5°	895.8	938.8	981.0	1027.9	1081.7	1110.1	1135.4	1190.0	1233.8	1280.6	1314.4
20°	877.3	924.2	972.6	1024.8	1085.5	1117.0	1145.4	1207.6	1256.0	1306.8	1349.0
22.5°	857.3	908.0	961.0	1017.9	1080.9	1115.5	1148.5	1215.3	1271.4	1318.3	1375.1
25°	835.1	888.8	943.4	1003.3	1074.0	1111.6	1145.4	1211.5	1271.4	1332.9	1388.2
27.5°	812.0	867.3	924.2	987.2	1059.4	1096.3	1134.7	1198.4	1268.3	1335.2	1391.3
30°	786.7	840.4	900.4	960.3	1037.1	1074.0	1113.2	1182.3	1258.4	1325.2	1385.9
32.5°	759.0	814.3	871.2	933.4	1008.7	1048.6	1084.7	1163.1	1240.7	1306.8	1363.6
35°	728.3	780.5	834.3	898.1	972.6	1008.7	1051.7	1133.1	1211.5	1281.4	1318.3
37.5°	695.2	745.2	795.1	858.1	929.6	973.3	1015.6	1097.8	1180.8	1227.6	1246.8
40°	664.5	708.3	752.1	812.8	885.0	930.3	973.3	1058.6	1131.6	1167.7	1153.1
42.5°	625.3	670.7	709.8	765.9	838.9	881.2	924.9	1013.3	1072.4	1087.0	1050.9
45°	586.9	624.6	662.2	716.8	793.6	829.7	876.5	958.7	1007.9	994.9	941.8
47.5°	549.3	580.0	615.3	668.4	737.5	780.5	824.3	895.8	930.3	911.9	838.1
50°	504.7	535.5	572.3	618.4	685.3	726.7	761.3	827.4	853.5	808.2	719.1
52.5°	462.5	489.4	520.9	563.9	627.6	665.3	702.9	759.8	768.2	716.0	622.3
55°	422.5	444.0	477.1	511.6	570.0	610.0	636.1	684.5	682.2	616.9	536.2
57.5°	381.0	401.0	423.3	459.4	514.7	544.7	573.1	615.3	593.1	537.8	457.9
60°	344.2	355.7	378.0	412.5	459.4	485.5	507.8	530.8	511.6	451.7	390.3
62.5°	303.4	316.5	332.6	360.3	401.8	426.4	442.5	452.5	432.5	386.4	330.3
65°	265.0	276.6	293.5	318.0	349.5	368.0	376.4	383.3	372.6	320.3	275.8
67.5°	230.5	238.1	253.5	269.6	303.4	308.1	319.6	322.7	301.1	261.2	225.9
70°	195.9	203.6	210.5	229.7	245.1	253.5	255.8	255.8	234.3	208.2	179.0
72.5°	163.6	168.2	175.2	188.2	196.7	202.8	205.9	202.0	182.1	160.6	139.0
75°	132.9	135.2	141.4	149.8	156.7	154.4	153.6	149.0	134.4	119.1	106.8
77.5°	102.2	103.7	110.6	112.9	112.9	115.2	112.2	107.6	95.3	83.7	78.4
80°	76.8	79.1	79.9	81.4	79.9	79.9	77.6	69.9	63.8	58.4	54.5
82.5°	53.0	54.5	55.3	53.0	54.5	52.2	48.4	43.0	39.2	38.4	36.9
85°	31.5	32.3	31.5	31.5	29.2	28.4	25.4	24.6	23.0	23.0	22.3
87.5°	15.4	14.6	13.1	11.5	11.5	10.8	11.5	10.0	11.5	10.8	10.0
90°	1.0	2.9	5.9	6.9	7.8	7.8	7.8	13.7	13.7	15.7	17.6
92.5°	13.7	19.6	30.4	45.1	62.7	75.4	88.2	148.9	244.0	336.0	384.1
95°	32.3	35.3	45.1	57.8	81.3	101.9	122.5	207.7	368.4	602.5	798.5
97.5°	53.9	53.9	62.7	74.5	95.0	112.6	130.3	197.9	336.0	577.1	854.3
100°	74.5	74.5	81.3	93.1	111.7	127.4	143.0	200.8	311.6	511.4	787.7
102.5°	94.1	96.0	101.9	112.7	130.3	145.0	159.7	210.6	304.7	467.3	704.4
105°	114.6	117.6	122.5	134.2	151.9	166.1	180.3	227.3	308.6	445.8	642.7
107.5°	137.2	139.1	144.0	156.8	173.4	187.6	201.8	244.9	320.4	439.9	602.5
110°	159.7	161.7	166.6	178.3	195.9	209.2	222.4	265.5	334.1	441.9	583.9

TEST NUMBER: P1026381

CATALOG NUMBER: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	181.3	183.2	189.1	199.9	217.5	230.8	244.0	285.1	348.8	447.7	575.1
115°	201.8	204.8	211.6	221.4	240.0	253.2	266.5	305.7	364.5	455.6	573.1
117.5°	223.4	226.3	232.2	243.0	260.6	274.3	288.0	325.3	380.1	463.4	572.2
120°	244.9	246.9	253.8	264.5	281.2	294.9	308.6	345.8	396.8	472.2	572.2
122.5°	264.5	266.5	273.3	283.1	301.8	315.0	328.2	365.4	412.5	481.0	571.2
125°	281.2	285.1	291.0	301.8	320.4	334.1	347.8	383.1	428.1	489.9	570.2
127.5°	296.9	299.8	306.7	318.4	338.0	351.7	365.4	399.7	441.9	496.7	568.2
130°	309.6	313.5	321.4	336.0	354.7	368.9	383.1	416.4	454.6	504.6	567.3
132.5°	322.3	325.3	336.0	349.8	370.3	383.6	396.8	430.1	467.3	511.4	566.3
135°	334.1	338.0	347.8	364.5	385.0	397.8	410.5	442.8	478.1	518.3	565.3
137.5°	345.8	349.8	360.5	376.2	397.8	410.0	422.3	452.6	485.9	522.2	565.3
140°	358.6	361.5	372.3	389.0	409.5	421.2	433.0	462.4	493.8	527.1	564.3
142.5°	372.3	375.2	385.0	400.7	420.3	431.6	442.8	471.3	499.7	531.0	564.3
145°	385.0	388.0	397.8	411.5	430.1	440.9	451.7	477.1	503.6	532.0	562.4
147.5°	399.7	400.7	409.5	424.2	439.9	449.7	459.5	484.0	507.5	533.0	559.4
150°	413.4	414.4	422.3	434.0	448.7	458.0	467.3	488.9	510.4	533.0	556.5
152.5°	426.2	426.2	434.0	444.8	457.5	465.8	474.2	492.8	512.4	531.0	551.6
155°	437.9	438.9	444.8	454.6	465.4	472.8	480.1	496.7	513.4	529.1	546.7
157.5°	449.7	449.7	455.6	463.4	473.2	479.1	485.0	499.7	513.4	527.1	541.8
160°	460.5	460.5	464.4	471.3	479.1	484.5	489.9	501.6	513.4	524.2	535.9
162.5°	470.3	469.3	472.2	478.1	485.0	488.9	492.8	503.6	513.4	521.2	530.0
165°	477.1	477.1	479.1	484.0	488.9	491.8	494.8	503.6	511.4	517.3	524.2
167.5°	485.0	484.0	485.0	488.9	491.8	494.2	496.7	503.6	509.5	513.4	518.3
170°	489.9	488.9	489.9	492.8	494.8	496.2	497.7	502.6	507.5	509.5	512.4
172.5°	494.8	493.8	493.8	495.7	496.7	497.7	498.7	501.6	505.5	505.5	506.5
175°	497.7	496.7	496.7	497.7	498.7	498.7	498.7	500.6	503.6	502.6	502.6
177.5°	499.7	498.7	497.7	498.7	498.7	498.7	498.7	499.7	501.6	499.7	499.7
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1026381

CATALOG NUMBER: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4
2.5°	999.5	1007.9	1008.7	1016.4	1014.1	1010.2	1017.1	1012.5	1021.7	1018.7	1022.5
5°	1057.8	1069.4	1079.4	1085.5	1096.3	1094.0	1105.5	1101.6	1110.1	1101.6	1112.4
7.5°	1126.2	1145.4	1155.4	1171.5	1176.2	1176.9	1190.7	1193.8	1199.2	1193.8	1200.0
10°	1193.1	1216.1	1239.1	1252.2	1260.7	1272.2	1284.5	1289.8	1293.7	1288.3	1292.2
12.5°	1253.7	1289.8	1315.2	1341.3	1347.5	1357.5	1370.5	1369.0	1384.3	1381.3	1388.2
15°	1309.8	1349.8	1380.5	1401.2	1418.1	1426.6	1451.2	1452.7	1451.9	1459.6	1455.0
17.5°	1359.8	1393.6	1437.3	1464.2	1485.0	1485.0	1498.8	1527.2	1524.9	1524.2	1528.8
20°	1400.5	1438.9	1479.6	1524.9	1541.8	1544.9	1564.1	1578.7	1581.0	1581.0	1581.0
22.5°	1431.2	1476.5	1520.3	1552.6	1565.6	1576.4	1593.3	1602.5	1605.6	1604.1	1605.6
25°	1446.6	1489.6	1534.1	1563.3	1571.0	1577.2	1578.7	1584.1	1583.3	1574.1	1579.5
27.5°	1449.6	1491.1	1520.3	1528.0	1524.2	1520.3	1495.7	1498.0	1491.1	1477.3	1482.7
30°	1435.8	1458.1	1457.3	1433.5	1426.6	1410.5	1388.2	1355.1	1328.3	1316.7	1320.6
32.5°	1385.9	1385.9	1358.2	1304.4	1280.6	1251.4	1211.5	1181.5	1146.2	1138.5	1153.1
35°	1316.7	1277.6	1226.9	1156.2	1120.1	1098.6	1029.4	1007.9	978.0	969.5	976.4
37.5°	1209.2	1143.9	1070.1	1004.1	973.3	934.9	874.2	843.5	822.0	807.4	814.3
40°	1088.6	1009.4	932.6	851.2	817.4	785.9	740.6	712.9	678.3	679.9	682.2
42.5°	973.3	880.4	794.3	719.1	686.8	660.7	629.2	595.4	583.1	579.2	575.4
45°	851.2	752.1	671.4	615.3	586.2	561.6	532.4	513.2	498.6	495.5	499.3
47.5°	736.0	652.2	575.4	523.2	499.3	487.1	464.0	446.3	437.1	429.4	434.0
50°	631.5	553.1	491.7	447.9	431.0	422.5	401.0	391.8	382.6	380.3	379.5
52.5°	545.4	478.6	425.6	390.3	377.2	372.6	356.5	343.4	335.7	338.0	339.6
55°	467.1	410.2	368.7	340.3	329.6	324.2	312.7	303.4	298.1	295.8	297.3
57.5°	397.9	348.8	318.8	295.8	287.3	285.0	272.7	269.6	265.8	263.5	263.5
60°	334.9	300.4	272.7	259.7	250.4	248.1	238.9	235.1	234.3	232.0	230.5
62.5°	281.9	253.5	234.3	220.5	216.6	215.9	209.7	205.1	202.8	201.3	201.3
65°	235.8	215.1	199.0	189.0	185.9	184.4	177.5	175.9	174.4	172.9	172.1
67.5°	196.7	178.2	166.7	159.8	155.9	156.7	152.9	149.8	149.8	149.0	148.3
70°	159.0	147.5	137.5	133.7	132.1	130.6	129.1	126.8	126.0	126.0	126.0
72.5°	125.2	117.5	112.2	109.9	108.3	106.8	105.2	105.2	105.2	104.5	104.5
75°	96.0	93.0	89.1	86.8	86.8	88.3	86.0	83.7	81.4	79.9	80.7
77.5°	72.2	70.7	68.4	64.5	65.3	63.8	63.8	62.2	63.0	63.0	61.5
80°	53.0	50.7	49.9	47.6	48.4	47.6	46.9	46.9	45.3	45.3	45.3
82.5°	36.9	34.6	34.6	33.8	33.0	33.0	32.3	32.3	33.0	31.5	31.5
85°	22.3	21.5	21.5	20.0	20.0	20.0	20.0	20.7	20.0	19.2	19.2
87.5°	10.0	10.8	10.0	9.2	9.2	9.2	8.5	8.5	7.7	8.5	8.5
90°	16.7	17.6	18.6	19.6	19.6	19.6	20.6	21.6	20.6	20.6	20.6
92.5°	319.4	236.1	176.4	139.1	126.8	114.6	99.9	93.1	89.2	89.2	89.2
95°	821.0	726.0	574.1	442.8	395.3	347.8	299.8	269.4	251.8	239.1	251.8
97.5°	1029.7	1045.4	969.9	862.2	807.3	752.4	685.8	627.0	597.6	574.1	597.6
100°	1038.5	1181.6	1201.2	1153.1	1116.8	1080.6	995.4	935.6	906.3	898.4	906.3
102.5°	965.0	1174.7	1291.3	1320.7	1310.9	1301.1	1257.0	1217.8	1186.5	1180.6	1186.5
105°	872.9	1097.3	1266.8	1363.8	1383.9	1404.0	1405.9	1398.1	1384.4	1378.5	1384.4
107.5°	797.5	1002.3	1185.5	1320.7	1361.8	1403.0	1446.1	1463.7	1471.6	1472.5	1471.6
110°	743.6	918.0	1087.5	1229.6	1283.4	1337.3	1406.9	1448.0	1465.7	1474.5	1465.7

TEST NUMBER: P1026381

CATALOG NUMBER: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	713.2	856.3	1001.3	1133.5	1187.4	1241.3	1322.6	1374.6	1401.0	1416.7	1401.0
115°	696.6	819.1	939.6	1054.2	1101.2	1148.2	1225.6	1284.4	1315.8	1323.6	1315.8
117.5°	687.8	797.5	899.4	992.5	1033.6	1074.8	1143.3	1194.3	1227.6	1232.5	1227.6
120°	680.9	783.8	874.9	953.3	988.0	1022.8	1078.7	1121.8	1147.3	1158.0	1147.3
122.5°	673.1	772.0	859.2	928.8	958.2	987.6	1032.6	1067.9	1088.5	1099.3	1088.5
125°	664.3	758.3	842.6	910.2	937.2	964.1	1003.2	1031.7	1050.3	1056.2	1050.3
127.5°	652.5	742.6	824.0	891.6	917.0	942.5	981.7	1007.2	1022.8	1028.7	1022.8
130°	641.7	723.0	800.4	867.1	893.0	919.0	959.2	983.7	999.3	1005.2	999.3
132.5°	631.9	702.5	774.0	838.7	864.6	890.6	929.8	958.2	972.9	978.8	972.9
135°	622.1	683.9	747.5	807.3	831.8	856.3	895.5	922.9	938.6	944.5	938.6
137.5°	613.3	666.2	722.1	774.0	796.6	819.1	856.3	884.7	897.4	904.3	897.4
140°	606.5	651.5	697.6	741.7	762.2	782.8	817.1	838.7	852.4	860.2	852.4
142.5°	600.6	637.8	677.0	713.2	730.4	747.5	776.9	796.5	808.3	813.2	808.3
145°	593.7	625.1	658.4	687.8	701.5	715.2	739.7	756.4	766.2	771.0	766.2
147.5°	587.8	614.3	641.7	666.2	677.5	688.8	707.4	722.1	729.9	731.9	729.9
150°	581.0	604.5	627.0	646.6	655.4	664.3	679.9	692.7	698.5	699.5	698.5
152.5°	573.1	593.7	612.3	630.0	636.8	643.7	656.4	666.2	669.2	670.1	669.2
155°	565.3	582.9	598.6	613.3	619.2	625.1	634.9	642.7	645.6	645.6	645.6
157.5°	557.5	571.2	584.9	597.6	602.5	607.4	615.3	621.1	623.1	623.1	623.1
160°	548.6	560.4	571.2	582.0	585.9	589.8	595.7	601.6	602.5	602.5	602.5
162.5°	540.8	549.6	558.4	566.3	569.7	573.1	577.1	582.9	583.9	582.9	583.9
165°	532.0	539.8	545.7	552.6	555.0	557.5	561.4	565.3	564.3	563.3	564.3
167.5°	524.2	530.0	534.9	540.8	542.3	543.8	545.7	548.6	548.6	547.7	548.6
170°	516.3	521.2	524.2	528.1	529.6	531.0	533.0	534.0	533.0	533.0	533.0
172.5°	509.5	513.4	515.3	517.3	518.3	519.3	520.2	521.2	520.2	518.3	520.2
175°	504.6	506.5	507.5	509.5	509.5	509.5	509.5	511.4	509.5	507.5	509.5
177.5°	500.6	501.6	502.6	502.6	503.1	503.6	502.6	503.6	501.6	499.7	501.6
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1026381

CATALOG NUMBER: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4
2.5°	1024.8	1019.4	1018.7	1018.7	1010.2	1014.8	1005.6	995.6	991.0	991.0	982.6
5°	1110.1	1104.7	1099.3	1090.9	1090.9	1086.3	1071.7	1057.1	1046.3	1037.1	1027.1
7.5°	1197.7	1192.3	1176.9	1168.5	1173.1	1163.9	1144.7	1120.1	1101.6	1087.0	1066.3
10°	1292.9	1278.3	1270.6	1266.0	1249.9	1239.9	1217.6	1181.5	1158.5	1139.3	1112.4
12.5°	1370.5	1375.1	1345.9	1348.2	1332.1	1318.3	1283.7	1249.1	1214.6	1187.7	1147.7
15°	1454.2	1440.4	1422.8	1408.9	1403.5	1386.6	1357.5	1311.4	1273.7	1231.5	1186.1
17.5°	1520.3	1509.6	1492.7	1479.6	1468.1	1427.4	1402.8	1362.1	1310.6	1269.1	1213.8
20°	1576.4	1566.4	1542.6	1534.1	1513.4	1484.2	1448.9	1385.9	1339.8	1294.5	1240.7
22.5°	1600.2	1590.2	1569.5	1558.7	1545.7	1517.2	1483.4	1423.5	1366.7	1309.8	1253.0
25°	1580.2	1580.2	1570.3	1566.4	1554.9	1529.5	1495.0	1444.3	1383.6	1322.1	1254.5
27.5°	1483.4	1502.6	1509.6	1513.4	1513.4	1514.2	1490.4	1441.2	1382.0	1322.1	1251.4
30°	1343.6	1375.9	1404.3	1412.8	1427.4	1443.5	1453.5	1429.7	1376.7	1313.7	1243.0
32.5°	1167.7	1209.2	1262.2	1275.3	1295.2	1343.6	1370.5	1380.5	1351.3	1296.0	1220.7
35°	992.5	1044.8	1077.1	1117.0	1135.4	1206.9	1266.8	1302.9	1296.0	1263.0	1194.6
37.5°	839.7	869.6	908.8	951.1	987.9	1056.3	1130.8	1200.7	1229.2	1213.0	1161.6
40°	692.9	728.3	775.1	809.7	835.1	903.4	995.6	1071.7	1133.9	1143.9	1112.4
42.5°	589.2	624.6	653.0	690.6	710.6	776.7	858.1	953.4	1027.1	1066.3	1052.5
45°	509.3	530.8	553.9	575.4	600.0	658.4	733.7	838.1	921.1	976.4	981.8
47.5°	439.4	458.6	478.6	498.6	512.4	557.7	626.9	712.1	802.8	878.8	908.8
50°	390.3	399.5	414.1	425.6	441.7	480.9	536.2	610.0	706.0	788.2	827.4
52.5°	341.9	353.4	364.9	374.9	385.6	413.3	464.0	527.8	610.7	695.2	743.6
55°	301.1	310.4	321.1	328.0	334.2	358.8	397.2	446.3	517.8	597.7	657.6
57.5°	268.1	272.0	281.2	285.0	291.9	311.9	339.6	383.3	441.0	518.6	567.7
60°	232.0	239.7	246.6	249.7	255.1	268.9	288.1	328.8	378.7	435.6	491.7
62.5°	202.8	205.9	211.3	215.1	218.9	233.5	249.7	280.4	318.0	365.7	417.1
65°	175.9	177.5	180.5	185.9	188.2	199.0	208.2	230.5	265.8	301.9	353.4
67.5°	148.3	149.8	153.6	156.7	159.0	165.9	175.9	192.1	211.3	251.2	279.6
70°	126.8	126.8	129.1	130.6	132.9	136.0	141.4	153.6	171.3	196.7	222.8
72.5°	106.0	106.0	106.0	108.3	108.3	110.6	113.7	122.1	134.4	154.4	171.3
75°	82.2	83.0	84.5	84.5	85.3	88.3	90.7	93.0	99.1	112.2	127.5
77.5°	62.2	63.8	64.5	63.0	64.5	64.5	67.6	70.7	73.7	77.6	89.1
80°	46.1	46.9	45.3	46.1	46.1	47.6	49.2	48.4	49.9	54.5	57.6
82.5°	30.7	31.5	31.5	31.5	31.5	33.8	33.8	33.0	33.8	34.6	35.3
85°	19.2	18.4	18.4	19.2	18.4	18.4	19.2	20.0	19.2	20.0	20.7
87.5°	8.5	8.5	8.5	8.5	7.7	7.7	8.5	7.7	8.5	7.7	6.9
90°	21.6	20.6	19.6	19.6	19.6	18.6	17.6	16.7	17.6	15.7	13.7
92.5°	93.1	99.9	114.6	126.8	139.1	176.4	236.1	319.4	384.1	336.0	244.0
95°	269.4	299.8	347.8	395.3	442.8	574.1	726.0	821.0	798.5	602.5	368.4
97.5°	627.0	685.8	752.4	807.3	862.2	969.9	1045.4	1029.7	854.3	577.1	336.0
100°	935.6	995.4	1080.6	1116.8	1153.1	1201.2	1181.6	1038.5	787.7	511.4	311.6
102.5°	1217.8	1257.0	1301.1	1310.9	1320.7	1291.3	1174.7	965.0	704.4	467.3	304.7
105°	1398.1	1405.9	1404.0	1383.9	1363.8	1266.8	1097.3	872.9	642.7	445.8	308.6
107.5°	1463.7	1446.1	1403.0	1361.8	1320.7	1185.5	1002.3	797.5	602.5	439.9	320.4
110°	1448.0	1406.9	1337.3	1283.4	1229.6	1087.5	918.0	743.6	583.9	441.9	334.1

TEST NUMBER: P1026381

CATALOG NUMBER: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1374.6	1322.6	1241.3	1187.4	1133.5	1001.3	856.3	713.2	575.1	447.7	348.8
115°	1284.4	1225.6	1148.2	1101.2	1054.2	939.6	819.1	696.6	573.1	455.6	364.5
117.5°	1194.3	1143.3	1074.8	1033.6	992.5	899.4	797.5	687.8	572.2	463.4	380.1
120°	1121.8	1078.7	1022.8	988.0	953.3	874.9	783.8	680.9	572.2	472.2	396.8
122.5°	1067.9	1032.6	987.6	958.2	928.8	859.2	772.0	673.1	571.2	481.0	412.5
125°	1031.7	1003.2	964.1	937.2	910.2	842.6	758.3	664.3	570.2	489.9	428.1
127.5°	1007.2	981.7	942.5	917.0	891.6	824.0	742.6	652.5	568.2	496.7	441.9
130°	983.7	959.2	919.0	893.0	867.1	800.4	723.0	641.7	567.3	504.6	454.6
132.5°	958.2	929.8	890.6	864.6	838.7	774.0	702.5	631.9	566.3	511.4	467.3
135°	922.9	895.5	856.3	831.8	807.3	747.5	683.9	622.1	565.3	518.3	478.1
137.5°	884.7	856.3	819.1	796.6	774.0	722.1	666.2	613.3	565.3	522.2	485.9
140°	838.7	817.1	782.8	762.2	741.7	697.6	651.5	606.5	564.3	527.1	493.8
142.5°	796.5	776.9	747.5	730.4	713.2	677.0	637.8	600.6	564.3	531.0	499.7
145°	756.4	739.7	715.2	701.5	687.8	658.4	625.1	593.7	562.4	532.0	503.6
147.5°	722.1	707.4	688.8	677.5	666.2	641.7	614.3	587.8	559.4	533.0	507.5
150°	692.7	679.9	664.3	655.4	646.6	627.0	604.5	581.0	556.5	533.0	510.4
152.5°	666.2	656.4	643.7	636.8	630.0	612.3	593.7	573.1	551.6	531.0	512.4
155°	642.7	634.9	625.1	619.2	613.3	598.6	582.9	565.3	546.7	529.1	513.4
157.5°	621.1	615.3	607.4	602.5	597.6	584.9	571.2	557.5	541.8	527.1	513.4
160°	601.6	595.7	589.8	585.9	582.0	571.2	560.4	548.6	535.9	524.2	513.4
162.5°	582.9	577.1	573.1	569.7	566.3	558.4	549.6	540.8	530.0	521.2	513.4
165°	565.3	561.4	557.5	555.0	552.6	545.7	539.8	532.0	524.2	517.3	511.4
167.5°	548.6	545.7	543.8	542.3	540.8	534.9	530.0	524.2	518.3	513.4	509.5
170°	534.0	533.0	531.0	529.6	528.1	524.2	521.2	516.3	512.4	509.5	507.5
172.5°	521.2	520.2	519.3	518.3	517.3	515.3	513.4	509.5	506.5	505.5	505.5
175°	511.4	509.5	509.5	509.5	509.5	507.5	506.5	504.6	502.6	502.6	503.6
177.5°	503.6	502.6	503.6	503.1	502.6	502.6	501.6	500.6	499.7	499.7	501.6
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1026381

CATALOG NUMBER: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4
2.5°	978.0	974.1	971.8	971.0	964.1	960.3	958.0	956.4	954.1	948.0	942.6
5°	1014.8	1004.1	998.7	992.5	981.8	969.5	959.5	953.4	945.7	933.4	921.9
7.5°	1049.4	1033.3	1022.5	1014.1	995.6	975.6	959.5	946.5	931.9	915.0	898.8
10°	1085.5	1059.4	1045.6	1032.5	1005.6	979.5	956.4	937.2	916.5	894.2	876.5
12.5°	1113.9	1079.4	1064.0	1045.6	1012.5	981.8	952.6	926.5	899.6	875.8	850.4
15°	1147.0	1103.9	1086.3	1062.5	1017.1	977.2	939.5	911.1	883.5	848.1	821.2
17.5°	1166.2	1116.2	1090.9	1070.1	1021.0	972.6	928.8	893.4	861.2	825.8	797.4
20°	1185.4	1128.5	1100.1	1070.9	1012.5	961.0	915.0	872.7	838.9	800.5	771.3
22.5°	1191.5	1125.4	1095.5	1068.6	1007.1	949.5	896.5	853.5	814.3	775.9	742.9
25°	1191.5	1124.7	1089.3	1054.8	990.2	931.1	878.1	831.2	787.4	749.0	716.0
27.5°	1179.2	1109.3	1072.4	1040.9	974.1	910.3	855.8	804.3	762.1	723.7	686.0
30°	1163.9	1087.0	1050.2	1012.5	948.0	887.3	828.1	780.5	736.0	692.2	658.4
32.5°	1144.7	1063.2	1022.5	984.1	915.7	852.7	798.2	751.3	709.1	663.7	626.1
35°	1117.0	1027.9	982.6	948.8	882.7	817.4	765.2	719.1	678.3	631.5	590.8
37.5°	1081.7	995.6	949.5	908.0	839.7	779.7	730.6	686.0	646.1	603.1	557.7
40°	1040.2	950.3	910.3	866.6	794.3	737.5	691.4	651.5	611.5	570.8	527.0
42.5°	993.3	904.2	859.6	817.4	748.3	692.2	649.1	613.0	576.2	538.5	491.7
45°	937.2	853.5	810.5	770.5	703.7	646.1	606.9	572.3	540.8	502.4	460.9
47.5°	874.2	801.3	757.5	714.4	649.1	599.2	560.8	531.6	504.7	466.3	428.7
50°	812.8	740.6	705.2	661.4	601.5	554.7	515.5	490.9	470.2	432.5	398.7
52.5°	735.2	680.6	646.8	609.2	551.6	504.0	473.2	451.7	427.1	397.9	368.0
55°	666.8	616.1	589.2	553.9	497.0	454.8	428.7	408.7	389.5	363.4	339.6
57.5°	589.2	557.7	530.8	500.1	444.0	407.9	384.9	368.0	350.3	328.8	309.6
60°	507.8	493.2	467.1	442.5	394.9	363.4	344.2	328.8	311.9	294.2	278.1
62.5°	435.6	427.1	411.8	392.6	348.0	321.1	301.9	290.4	278.1	262.0	246.6
65°	367.2	363.4	348.8	334.9	304.2	280.4	263.5	256.6	242.8	230.5	216.6
67.5°	306.5	301.9	293.5	287.3	261.2	238.9	230.5	221.2	209.7	200.5	189.0
70°	245.1	244.3	238.9	231.2	217.4	201.3	192.8	186.7	175.2	168.2	159.8
72.5°	190.5	194.4	189.8	186.7	177.5	165.9	158.3	154.4	145.2	139.8	133.7
75°	142.1	145.2	147.5	142.1	139.8	134.4	127.5	123.7	119.1	111.4	109.1
77.5°	96.8	103.7	103.7	105.2	106.0	102.9	97.6	94.5	89.1	87.6	84.5
80°	63.8	69.9	70.7	72.2	74.5	74.5	70.7	69.9	64.5	63.8	61.5
82.5°	36.9	42.3	45.3	47.6	46.9	49.9	46.9	46.1	43.0	43.0	41.5
85°	20.0	20.7	22.3	23.8	25.4	26.9	26.9	26.1	25.4	24.6	23.0
87.5°	7.7	7.7	8.5	7.7	8.5	10.0	10.8	10.8	10.0	9.2	7.7
90°	13.7	7.8	7.8	7.8	6.9	5.9	2.9	1.0	2.9	5.9	6.9
92.5°	148.9	88.2	75.4	62.7	45.1	30.4	19.6	13.7	19.6	30.4	45.1
95°	207.7	122.5	101.9	81.3	57.8	45.1	35.3	32.3	35.3	45.1	57.8
97.5°	197.9	130.3	112.6	95.0	74.5	62.7	53.9	53.9	53.9	62.7	74.5
100°	200.8	143.0	127.4	111.7	93.1	81.3	74.5	74.5	74.5	81.3	93.1
102.5°	210.6	159.7	145.0	130.3	112.7	101.9	96.0	94.1	96.0	101.9	112.7
105°	227.3	180.3	166.1	151.9	134.2	122.5	117.6	114.6	117.6	122.5	134.2
107.5°	244.9	201.8	187.6	173.4	156.8	144.0	139.1	137.2	139.1	144.0	156.8
110°	265.5	222.4	209.2	195.9	178.3	166.6	161.7	159.7	161.7	166.6	178.3

TEST NUMBER: P1026381

CATALOG NUMBER: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	285.1	244.0	230.8	217.5	199.9	189.1	183.2	181.3	183.2	189.1	199.9
115°	305.7	266.5	253.2	240.0	221.4	211.6	204.8	201.8	204.8	211.6	221.4
117.5°	325.3	288.0	274.3	260.6	243.0	232.2	226.3	223.4	226.3	232.2	243.0
120°	345.8	308.6	294.9	281.2	264.5	253.8	246.9	244.9	246.9	253.8	264.5
122.5°	365.4	328.2	315.0	301.8	283.1	273.3	266.5	264.5	266.5	273.3	283.1
125°	383.1	347.8	334.1	320.4	301.8	291.0	285.1	281.2	285.1	291.0	301.8
127.5°	399.7	365.4	351.7	338.0	318.4	306.7	299.8	296.9	299.8	306.7	318.4
130°	416.4	383.1	368.9	354.7	336.0	321.4	313.5	309.6	313.5	321.4	336.0
132.5°	430.1	396.8	383.6	370.3	349.8	336.0	325.3	322.3	325.3	336.0	349.8
135°	442.8	410.5	397.8	385.0	364.5	347.8	338.0	334.1	338.0	347.8	364.5
137.5°	452.6	422.3	410.0	397.8	376.2	360.5	349.8	345.8	349.8	360.5	376.2
140°	462.4	433.0	421.2	409.5	389.0	372.3	361.5	358.6	361.5	372.3	389.0
142.5°	471.3	442.8	431.6	420.3	400.7	385.0	375.2	372.3	375.2	385.0	400.7
145°	477.1	451.7	440.9	430.1	411.5	397.8	388.0	385.0	388.0	397.8	411.5
147.5°	484.0	459.5	449.7	439.9	424.2	409.5	400.7	399.7	400.7	409.5	424.2
150°	488.9	467.3	458.0	448.7	434.0	422.3	414.4	413.4	414.4	422.3	434.0
152.5°	492.8	474.2	465.8	457.5	444.8	434.0	426.2	426.2	426.2	434.0	444.8
155°	496.7	480.1	472.8	465.4	454.6	444.8	438.9	437.9	438.9	444.8	454.6
157.5°	499.7	485.0	479.1	473.2	463.4	455.6	449.7	449.7	449.7	455.6	463.4
160°	501.6	489.9	484.5	479.1	471.3	464.4	460.5	460.5	460.5	464.4	471.3
162.5°	503.6	492.8	488.9	485.0	478.1	472.2	469.3	470.3	469.3	472.2	478.1
165°	503.6	494.8	491.8	488.9	484.0	479.1	477.1	477.1	477.1	479.1	484.0
167.5°	503.6	496.7	494.2	491.8	488.9	485.0	484.0	485.0	484.0	485.0	488.9
170°	502.6	497.7	496.2	494.8	492.8	489.9	488.9	489.9	488.9	489.9	492.8
172.5°	501.6	498.7	497.7	496.7	495.7	493.8	493.8	494.8	493.8	493.8	495.7
175°	500.6	498.7	498.7	498.7	497.7	496.7	496.7	497.7	496.7	496.7	497.7
177.5°	499.7	498.7	498.7	498.7	498.7	497.7	498.7	499.7	498.7	497.7	498.7
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1026381

CATALOG NUMBER: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4
2.5°	938.0	936.5	934.9	928.8	923.4	914.2	906.5	903.4	902.7	903.4	901.1
5°	911.1	910.3	905.0	894.2	884.2	873.5	865.8	858.1	853.5	853.5	848.1
7.5°	885.8	880.4	875.8	861.9	850.4	835.8	824.3	817.4	813.6	805.1	805.1
10°	858.9	851.2	845.0	832.0	815.1	800.5	785.9	777.4	770.5	764.4	762.1
12.5°	832.0	825.8	814.3	800.5	783.6	765.2	749.8	743.6	727.5	714.4	715.2
15°	806.6	792.8	787.4	767.5	747.5	729.8	707.5	689.9	676.8	668.4	657.6
17.5°	778.2	764.4	754.4	737.5	711.4	683.7	662.2	638.4	625.3	610.7	603.8
20°	746.7	735.2	727.5	700.6	669.1	636.1	612.3	597.7	583.1	572.3	566.2
22.5°	719.8	705.2	696.0	659.9	625.3	592.3	573.9	561.6	549.3	540.1	537.0
25°	685.3	676.8	654.5	623.0	580.8	558.5	542.4	526.2	519.3	513.2	506.3
27.5°	656.8	636.1	620.7	579.2	553.1	527.8	511.6	499.3	490.9	484.7	479.4
30°	621.5	602.3	580.8	546.2	522.4	498.6	484.0	474.0	464.8	460.9	456.3
32.5°	584.6	566.9	546.2	518.6	489.4	470.9	459.4	448.6	442.5	438.7	433.3
35°	551.6	529.3	515.5	489.4	465.5	444.8	434.0	424.8	417.9	416.4	415.6
37.5°	516.2	499.3	486.3	459.4	439.4	421.8	411.8	401.8	397.9	397.2	394.1
40°	485.5	470.9	458.6	433.3	411.8	395.6	388.0	381.8	378.0	378.0	377.2
42.5°	458.6	443.3	431.0	407.9	388.7	374.1	365.7	359.5	358.0	358.8	358.0
45°	428.7	415.6	403.3	379.5	363.4	352.6	343.4	340.3	338.0	338.8	339.6
47.5°	400.2	389.5	377.2	358.0	339.6	328.0	322.7	319.6	319.6	319.6	321.1
50°	374.9	362.6	351.8	331.9	315.0	305.8	301.1	297.3	298.1	298.8	299.6
52.5°	344.9	334.2	326.5	306.5	294.2	282.7	277.3	278.1	277.3	277.3	278.9
55°	318.8	308.1	300.4	281.9	269.6	262.0	257.4	255.1	255.8	254.3	257.4
57.5°	289.6	280.4	275.0	257.4	246.6	239.7	235.8	232.0	233.5	232.8	232.0
60°	264.3	253.5	245.1	232.8	223.6	215.1	212.8	209.0	210.5	209.0	208.2
62.5°	235.1	226.6	220.5	208.2	200.5	193.6	188.2	185.9	185.1	182.8	180.5
65°	205.9	201.3	195.1	182.8	175.2	169.8	166.7	164.4	163.6	157.5	150.6
67.5°	179.0	175.9	169.8	160.6	153.6	148.3	143.7	139.8	135.2	130.6	126.8
70°	153.6	149.0	145.2	136.7	130.6	125.2	120.6	116.0	113.7	109.1	107.6
72.5°	129.1	124.5	120.6	112.9	107.6	102.2	100.6	95.3	93.0	92.2	92.2
75°	103.7	99.9	97.6	90.7	86.0	82.2	79.9	78.4	76.8	75.3	73.0
77.5°	79.1	76.8	75.3	70.7	66.8	64.5	63.8	58.4	56.8	55.3	53.8
80°	57.6	56.8	55.3	51.5	49.9	44.6	44.6	43.0	42.3	42.3	42.3
82.5°	39.2	37.6	36.9	33.0	32.3	31.5	30.7	30.0	30.7	30.0	30.7
85°	20.7	20.0	19.2	19.2	19.2	19.2	19.2	19.2	19.2	18.4	19.2
87.5°	7.7	7.7	7.7	7.7	6.9	7.7	7.7	6.9	7.7	7.7	7.7
90°	7.8	7.8	7.8	13.7	13.7	15.7	17.6	16.7	17.6	18.6	19.6
92.5°	62.7	75.4	88.2	148.9	244.0	336.0	384.1	319.4	236.1	176.4	139.1
95°	81.3	101.9	122.5	207.7	368.4	602.5	798.5	821.0	726.0	574.1	442.8
97.5°	95.0	112.6	130.3	197.9	336.0	577.1	854.3	1029.7	1045.4	969.9	862.2
100°	111.7	127.4	143.0	200.8	311.6	511.4	787.7	1038.5	1181.6	1201.2	1153.1
102.5°	130.3	145.0	159.7	210.6	304.7	467.3	704.4	965.0	1174.7	1291.3	1320.7
105°	151.9	166.1	180.3	227.3	308.6	445.8	642.7	872.9	1097.3	1266.8	1363.8
107.5°	173.4	187.6	201.8	244.9	320.4	439.9	602.5	797.5	1002.3	1185.5	1320.7
110°	195.9	209.2	222.4	265.5	334.1	441.9	583.9	743.6	918.0	1087.5	1229.6

TEST NUMBER: P1026381

CATALOG NUMBER: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	217.5	230.8	244.0	285.1	348.8	447.7	575.1	713.2	856.3	1001.3	1133.5
115°	240.0	253.2	266.5	305.7	364.5	455.6	573.1	696.6	819.1	939.6	1054.2
117.5°	260.6	274.3	288.0	325.3	380.1	463.4	572.2	687.8	797.5	899.4	992.5
120°	281.2	294.9	308.6	345.8	396.8	472.2	572.2	680.9	783.8	874.9	953.3
122.5°	301.8	315.0	328.2	365.4	412.5	481.0	571.2	673.1	772.0	859.2	928.8
125°	320.4	334.1	347.8	383.1	428.1	489.9	570.2	664.3	758.3	842.6	910.2
127.5°	338.0	351.7	365.4	399.7	441.9	496.7	568.2	652.5	742.6	824.0	891.6
130°	354.7	368.9	383.1	416.4	454.6	504.6	567.3	641.7	723.0	800.4	867.1
132.5°	370.3	383.6	396.8	430.1	467.3	511.4	566.3	631.9	702.5	774.0	838.7
135°	385.0	397.8	410.5	442.8	478.1	518.3	565.3	622.1	683.9	747.5	807.3
137.5°	397.8	410.0	422.3	452.6	485.9	522.2	565.3	613.3	666.2	722.1	774.0
140°	409.5	421.2	433.0	462.4	493.8	527.1	564.3	606.5	651.5	697.6	741.7
142.5°	420.3	431.6	442.8	471.3	499.7	531.0	564.3	600.6	637.8	677.0	713.2
145°	430.1	440.9	451.7	477.1	503.6	532.0	562.4	593.7	625.1	658.4	687.8
147.5°	439.9	449.7	459.5	484.0	507.5	533.0	559.4	587.8	614.3	641.7	666.2
150°	448.7	458.0	467.3	488.9	510.4	533.0	556.5	581.0	604.5	627.0	646.6
152.5°	457.5	465.8	474.2	492.8	512.4	531.0	551.6	573.1	593.7	612.3	630.0
155°	465.4	472.8	480.1	496.7	513.4	529.1	546.7	565.3	582.9	598.6	613.3
157.5°	473.2	479.1	485.0	499.7	513.4	527.1	541.8	557.5	571.2	584.9	597.6
160°	479.1	484.5	489.9	501.6	513.4	524.2	535.9	548.6	560.4	571.2	582.0
162.5°	485.0	488.9	492.8	503.6	513.4	521.2	530.0	540.8	549.6	558.4	566.3
165°	488.9	491.8	494.8	503.6	511.4	517.3	524.2	532.0	539.8	545.7	552.6
167.5°	491.8	494.2	496.7	503.6	509.5	513.4	518.3	524.2	530.0	534.9	540.8
170°	494.8	496.2	497.7	502.6	507.5	509.5	512.4	516.3	521.2	524.2	528.1
172.5°	496.7	497.7	498.7	501.6	505.5	505.5	506.5	509.5	513.4	515.3	517.3
175°	498.7	498.7	498.7	500.6	503.6	502.6	502.6	504.6	506.5	507.5	509.5
177.5°	498.7	498.7	498.7	499.7	501.6	499.7	499.7	500.6	501.6	502.6	502.6
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1026381

CATALOG NUMBER: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4
2.5°	901.1	904.2	900.4	902.7	897.3	896.5	897.3	897.3	898.1	898.8	899.6
5°	850.4	849.7	845.0	842.0	839.7	842.0	843.5	845.0	843.5	845.0	845.8
7.5°	802.8	800.5	798.2	792.8	794.3	792.8	797.4	795.1	795.1	799.0	802.0
10°	760.5	755.9	754.4	748.3	743.6	742.9	748.3	750.6	752.9	754.4	760.5
12.5°	706.0	699.1	693.7	696.0	683.0	688.3	689.9	686.8	696.0	706.8	700.6
15°	647.6	648.4	637.6	633.8	623.0	626.1	626.9	634.6	642.2	641.5	650.7
17.5°	604.6	600.0	590.8	590.0	585.4	587.7	586.9	593.1	590.8	594.6	602.3
20°	564.6	561.6	553.9	550.8	552.4	550.8	551.6	552.4	554.7	563.1	561.6
22.5°	533.1	529.3	529.3	525.5	520.9	519.3	523.2	525.5	528.5	530.1	533.9
25°	505.5	502.4	498.6	496.3	492.4	493.2	495.5	498.6	500.9	504.0	507.0
27.5°	477.1	477.1	473.2	472.5	470.9	470.2	473.2	474.8	474.8	477.1	480.1
30°	454.8	454.8	450.9	450.2	449.4	449.4	451.7	452.5	453.3	455.6	457.1
32.5°	433.3	432.5	431.0	431.7	431.0	431.7	431.7	432.5	434.0	434.8	437.9
35°	413.3	414.1	412.5	412.5	411.8	412.5	414.1	414.8	415.6	417.1	417.1
37.5°	394.1	395.6	394.9	397.2	397.2	397.2	397.2	398.7	398.7	398.7	397.9
40°	377.2	377.2	376.4	378.0	379.5	379.5	380.3	380.3	381.0	381.0	380.3
42.5°	358.0	359.5	361.8	362.6	364.1	363.4	365.7	364.9	365.7	364.1	362.6
45°	340.3	340.3	343.4	346.5	347.2	347.2	347.2	348.8	347.2	344.9	344.2
47.5°	321.1	322.7	324.2	328.0	328.8	328.8	328.8	328.8	327.3	327.3	327.3
50°	301.9	302.7	303.4	305.0	307.3	306.5	306.5	306.5	309.6	306.5	307.3
52.5°	278.9	279.6	280.4	283.5	282.7	282.7	283.5	283.5	285.8	285.0	283.5
55°	255.8	255.8	257.4	257.4	257.4	258.9	259.7	261.2	260.4	261.2	262.0
57.5°	232.8	231.2	230.5	230.5	232.8	232.0	232.8	232.8	235.8	237.4	238.1
60°	205.9	205.9	205.1	200.5	200.5	199.7	202.0	203.6	205.1	212.0	211.3
62.5°	178.2	175.2	172.1	172.9	168.2	170.5	169.0	170.5	175.2	180.5	181.3
65°	150.6	148.3	145.2	144.4	142.9	145.2	144.4	145.2	147.5	150.6	154.4
67.5°	126.0	125.2	123.7	122.9	122.9	122.9	124.5	124.5	125.2	127.5	129.8
70°	107.6	106.8	107.6	106.0	106.8	106.0	106.8	107.6	108.3	109.1	111.4
72.5°	90.7	90.7	90.7	89.1	90.7	89.9	89.9	90.7	91.4	92.2	93.7
75°	72.2	70.7	69.1	67.6	66.8	68.4	69.1	68.4	70.7	73.7	73.7
77.5°	54.5	53.8	53.8	53.8	54.5	53.8	55.3	54.5	55.3	55.3	56.8
80°	42.3	41.5	42.3	42.3	41.5	43.0	42.3	42.3	43.0	43.8	43.0
82.5°	30.7	31.5	30.7	30.7	30.7	32.3	30.7	30.7	30.7	31.5	31.5
85°	19.2	19.2	19.2	19.2	20.0	19.2	20.0	19.2	20.7	20.0	20.0
87.5°	6.9	7.7	8.5	8.5	8.5	8.5	7.7	8.5	9.2	8.5	9.2
90°	19.6	19.6	20.6	21.6	20.6	20.6	20.6	21.6	20.6	19.6	19.6
92.5°	126.8	114.6	99.9	93.1	89.2	89.2	89.2	93.1	99.9	114.6	126.8
95°	395.3	347.8	299.8	269.4	251.8	239.1	251.8	269.4	299.8	347.8	395.3
97.5°	807.3	752.4	685.8	627.0	597.6	574.1	597.6	627.0	685.8	752.4	807.3
100°	1116.8	1080.6	995.4	935.6	906.3	898.4	906.3	935.6	995.4	1080.6	1116.8
102.5°	1310.9	1301.1	1257.0	1217.8	1186.5	1180.6	1186.5	1217.8	1257.0	1301.1	1310.9
105°	1383.9	1404.0	1405.9	1398.1	1384.4	1378.5	1384.4	1398.1	1405.9	1404.0	1383.9
107.5°	1361.8	1403.0	1446.1	1463.7	1471.6	1472.5	1471.6	1463.7	1446.1	1403.0	1361.8
110°	1283.4	1337.3	1406.9	1448.0	1465.7	1474.5	1465.7	1448.0	1406.9	1337.3	1283.4

TEST NUMBER: P1026381

CATALOG NUMBER: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1187.4	1241.3	1322.6	1374.6	1401.0	1416.7	1401.0	1374.6	1322.6	1241.3	1187.4
115°	1101.2	1148.2	1225.6	1284.4	1315.8	1323.6	1315.8	1284.4	1225.6	1148.2	1101.2
117.5°	1033.6	1074.8	1143.3	1194.3	1227.6	1232.5	1227.6	1194.3	1143.3	1074.8	1033.6
120°	988.0	1022.8	1078.7	1121.8	1147.3	1158.0	1147.3	1121.8	1078.7	1022.8	988.0
122.5°	958.2	987.6	1032.6	1067.9	1088.5	1099.3	1088.5	1067.9	1032.6	987.6	958.2
125°	937.2	964.1	1003.2	1031.7	1050.3	1056.2	1050.3	1031.7	1003.2	964.1	937.2
127.5°	917.0	942.5	981.7	1007.2	1022.8	1028.7	1022.8	1007.2	981.7	942.5	917.0
130°	893.0	919.0	959.2	983.7	999.3	1005.2	999.3	983.7	959.2	919.0	893.0
132.5°	864.6	890.6	929.8	958.2	972.9	978.8	972.9	958.2	929.8	890.6	864.6
135°	831.8	856.3	895.5	922.9	938.6	944.5	938.6	922.9	895.5	856.3	831.8
137.5°	796.6	819.1	856.3	884.7	897.4	904.3	897.4	884.7	856.3	819.1	796.6
140°	762.2	782.8	817.1	838.7	852.4	860.2	852.4	838.7	817.1	782.8	762.2
142.5°	730.4	747.5	776.9	796.5	808.3	813.2	808.3	796.5	776.9	747.5	730.4
145°	701.5	715.2	739.7	756.4	766.2	771.0	766.2	756.4	739.7	715.2	701.5
147.5°	677.5	688.8	707.4	722.1	729.9	731.9	729.9	722.1	707.4	688.8	677.5
150°	655.4	664.3	679.9	692.7	698.5	699.5	698.5	692.7	679.9	664.3	655.4
152.5°	636.8	643.7	656.4	666.2	669.2	670.1	669.2	666.2	656.4	643.7	636.8
155°	619.2	625.1	634.9	642.7	645.6	645.6	645.6	642.7	634.9	625.1	619.2
157.5°	602.5	607.4	615.3	621.1	623.1	623.1	623.1	621.1	615.3	607.4	602.5
160°	585.9	589.8	595.7	601.6	602.5	602.5	602.5	601.6	595.7	589.8	585.9
162.5°	569.7	573.1	577.1	582.9	583.9	582.9	583.9	582.9	577.1	573.1	569.7
165°	555.0	557.5	561.4	565.3	564.3	563.3	564.3	565.3	561.4	557.5	555.0
167.5°	542.3	543.8	545.7	548.6	548.6	547.7	548.6	548.6	545.7	543.8	542.3
170°	529.6	531.0	533.0	534.0	533.0	533.0	533.0	534.0	533.0	531.0	529.6
172.5°	518.3	519.3	520.2	521.2	520.2	518.3	520.2	521.2	520.2	519.3	518.3
175°	509.5	509.5	509.5	511.4	509.5	507.5	509.5	511.4	509.5	509.5	509.5
177.5°	503.1	503.6	502.6	503.6	501.6	499.7	501.6	503.6	502.6	503.6	503.1
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1026381

CATALOG NUMBER: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4	953.4
2.5°	902.7	906.5	905.0	899.6	901.9	906.5	911.1	917.3	921.1	924.2	925.7
5°	849.7	856.6	855.0	855.0	858.1	865.8	873.5	886.5	891.1	896.5	904.2
7.5°	802.8	808.2	812.8	814.3	818.9	828.9	838.9	853.5	865.0	871.2	875.8
10°	761.3	765.2	772.1	775.9	780.5	792.8	807.4	822.8	834.3	845.0	851.2
12.5°	708.3	723.7	732.9	739.0	745.2	763.6	775.1	792.0	805.9	815.9	825.1
15°	649.1	667.6	673.0	696.8	712.1	726.7	744.4	764.4	777.4	789.0	801.3
17.5°	599.2	612.3	618.4	643.8	656.8	679.9	705.2	730.6	750.6	759.0	771.3
20°	567.7	574.6	586.9	595.4	609.2	636.1	663.7	694.5	724.4	732.9	745.2
22.5°	535.5	544.7	553.1	564.6	575.4	593.8	621.5	655.3	687.6	702.9	717.5
25°	506.3	515.5	520.9	533.1	543.1	561.6	580.8	615.3	653.8	666.8	689.9
27.5°	483.2	488.6	497.8	503.2	514.7	531.6	549.3	575.4	613.0	635.3	657.6
30°	460.2	464.0	471.7	479.4	487.8	499.3	519.3	544.7	579.2	598.4	620.7
32.5°	437.1	443.3	447.9	453.3	462.5	476.3	490.1	514.7	542.4	563.9	586.2
35°	417.9	420.2	426.4	432.5	438.7	450.9	465.5	489.4	513.9	530.8	550.8
37.5°	397.2	401.0	405.6	407.9	417.9	425.6	441.0	459.4	488.6	499.3	519.3
40°	381.0	380.3	384.9	388.7	393.3	405.6	414.8	434.8	457.9	474.8	487.1
42.5°	361.1	361.1	362.6	367.2	373.4	381.0	391.8	408.7	432.5	444.8	459.4
45°	344.9	342.6	343.4	346.5	350.3	358.0	368.7	383.3	407.2	417.1	432.5
47.5°	325.7	323.4	323.4	326.5	329.6	334.9	343.4	360.3	379.5	392.6	404.1
50°	304.2	305.0	304.2	306.5	308.1	313.4	322.7	336.5	354.2	364.9	378.0
52.5°	284.2	282.7	281.9	283.5	286.5	290.4	300.4	312.7	329.6	340.3	351.8
55°	259.7	261.2	261.2	261.2	265.8	267.3	275.0	287.3	304.2	312.7	323.4
57.5°	237.4	236.6	238.1	237.4	241.2	246.6	252.7	262.0	278.9	287.3	297.3
60°	212.8	213.6	214.3	214.3	217.4	222.8	229.7	238.1	252.0	260.4	269.6
62.5°	182.8	186.7	190.5	192.1	196.7	200.5	205.1	214.3	226.6	232.8	241.2
65°	154.4	159.8	165.2	169.0	172.1	175.9	182.1	190.5	200.5	206.7	215.1
67.5°	129.8	133.7	140.6	144.4	150.6	155.2	159.0	165.9	178.2	180.5	187.4
70°	112.2	113.7	116.8	119.8	126.8	130.6	135.2	142.1	151.3	156.7	160.6
72.5°	94.5	95.3	96.8	99.9	102.9	107.6	112.9	119.1	127.5	129.8	135.2
75°	75.3	79.9	79.9	82.2	84.5	86.8	91.4	97.6	102.9	106.8	109.9
77.5°	56.1	58.4	59.9	63.8	66.8	69.1	72.2	76.8	79.9	83.0	85.3
80°	43.8	44.6	45.3	45.3	46.9	49.9	53.0	56.1	59.9	61.5	63.8
82.5°	32.3	32.3	32.3	33.8	34.6	35.3	35.3	36.9	40.7	42.3	44.6
85°	20.7	20.7	20.7	20.7	21.5	22.3	23.0	23.8	23.8	23.8	25.4
87.5°	8.5	10.0	9.2	10.0	10.0	10.0	10.0	10.8	10.8	11.5	11.5
90°	19.6	18.6	17.6	16.7	17.6	15.7	13.7	13.7	7.8	7.8	7.8
92.5°	139.1	176.4	236.1	319.4	384.1	336.0	244.0	148.9	88.2	75.4	62.7
95°	442.8	574.1	726.0	821.0	798.5	602.5	368.4	207.7	122.5	101.9	81.3
97.5°	862.2	969.9	1045.4	1029.7	854.3	577.1	336.0	197.9	130.3	112.6	95.0
100°	1153.1	1201.2	1181.6	1038.5	787.7	511.4	311.6	200.8	143.0	127.4	111.7
102.5°	1320.7	1291.3	1174.7	965.0	704.4	467.3	304.7	210.6	159.7	145.0	130.3
105°	1363.8	1266.8	1097.3	872.9	642.7	445.8	308.6	227.3	180.3	166.1	151.9
107.5°	1320.7	1185.5	1002.3	797.5	602.5	439.9	320.4	244.9	201.8	187.6	173.4
110°	1229.6	1087.5	918.0	743.6	583.9	441.9	334.1	265.5	222.4	209.2	195.9

TEST NUMBER: P1026381

CATALOG NUMBER: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1133.5	1001.3	856.3	713.2	575.1	447.7	348.8	285.1	244.0	230.8	217.5
115°	1054.2	939.6	819.1	696.6	573.1	455.6	364.5	305.7	266.5	253.2	240.0
117.5°	992.5	899.4	797.5	687.8	572.2	463.4	380.1	325.3	288.0	274.3	260.6
120°	953.3	874.9	783.8	680.9	572.2	472.2	396.8	345.8	308.6	294.9	281.2
122.5°	928.8	859.2	772.0	673.1	571.2	481.0	412.5	365.4	328.2	315.0	301.8
125°	910.2	842.6	758.3	664.3	570.2	489.9	428.1	383.1	347.8	334.1	320.4
127.5°	891.6	824.0	742.6	652.5	568.2	496.7	441.9	399.7	365.4	351.7	338.0
130°	867.1	800.4	723.0	641.7	567.3	504.6	454.6	416.4	383.1	368.9	354.7
132.5°	838.7	774.0	702.5	631.9	566.3	511.4	467.3	430.1	396.8	383.6	370.3
135°	807.3	747.5	683.9	622.1	565.3	518.3	478.1	442.8	410.5	397.8	385.0
137.5°	774.0	722.1	666.2	613.3	565.3	522.2	485.9	452.6	422.3	410.0	397.8
140°	741.7	697.6	651.5	606.5	564.3	527.1	493.8	462.4	433.0	421.2	409.5
142.5°	713.2	677.0	637.8	600.6	564.3	531.0	499.7	471.3	442.8	431.6	420.3
145°	687.8	658.4	625.1	593.7	562.4	532.0	503.6	477.1	451.7	440.9	430.1
147.5°	666.2	641.7	614.3	587.8	559.4	533.0	507.5	484.0	459.5	449.7	439.9
150°	646.6	627.0	604.5	581.0	556.5	533.0	510.4	488.9	467.3	458.0	448.7
152.5°	630.0	612.3	593.7	573.1	551.6	531.0	512.4	492.8	474.2	465.8	457.5
155°	613.3	598.6	582.9	565.3	546.7	529.1	513.4	496.7	480.1	472.8	465.4
157.5°	597.6	584.9	571.2	557.5	541.8	527.1	513.4	499.7	485.0	479.1	473.2
160°	582.0	571.2	560.4	548.6	535.9	524.2	513.4	501.6	489.9	484.5	479.1
162.5°	566.3	558.4	549.6	540.8	530.0	521.2	513.4	503.6	492.8	488.9	485.0
165°	552.6	545.7	539.8	532.0	524.2	517.3	511.4	503.6	494.8	491.8	488.9
167.5°	540.8	534.9	530.0	524.2	518.3	513.4	509.5	503.6	496.7	494.2	491.8
170°	528.1	524.2	521.2	516.3	512.4	509.5	507.5	502.6	497.7	496.2	494.8
172.5°	517.3	515.3	513.4	509.5	506.5	505.5	505.5	501.6	498.7	497.7	496.7
175°	509.5	507.5	506.5	504.6	502.6	502.6	503.6	500.6	498.7	498.7	498.7
177.5°	502.6	502.6	501.6	500.6	499.7	499.7	501.6	499.7	498.7	498.7	498.7
180°	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7	498.7

TEST NUMBER: P1026381

CATALOG NUMBER: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	953.4	953.4	953.4	953.4
2.5°	931.9	936.5	944.1	954.9
5°	910.3	923.4	935.7	951.8
7.5°	891.1	906.5	923.4	946.5
10°	868.9	888.1	909.6	938.0
12.5°	842.7	869.6	894.2	924.9
15°	823.5	843.5	875.0	911.1
17.5°	796.6	823.5	855.0	895.8
20°	771.3	799.7	835.1	877.3
22.5°	744.4	776.7	812.0	857.3
25°	716.8	751.3	786.7	835.1
27.5°	691.4	722.9	762.8	812.0
30°	660.7	696.8	735.2	786.7
32.5°	630.7	668.4	707.5	759.0
35°	598.4	636.1	679.1	728.3
37.5°	566.9	608.4	647.6	695.2
40°	532.4	575.4	616.1	664.5
42.5°	498.6	543.1	583.9	625.3
45°	467.1	510.9	547.7	586.9
47.5°	437.1	476.3	513.9	549.3
50°	407.9	441.0	475.5	504.7
52.5°	377.2	408.7	436.4	462.5
55°	349.5	374.1	398.7	422.5
57.5°	316.5	341.1	362.6	381.0
60°	288.9	304.2	325.0	344.2
62.5°	257.4	275.0	291.2	303.4
65°	226.6	242.0	254.3	265.0
67.5°	200.5	209.7	218.9	230.5
70°	169.0	176.7	187.4	195.9
72.5°	142.1	148.3	153.6	163.6
75°	115.2	120.6	123.7	132.9
77.5°	89.1	94.5	96.8	102.2
80°	68.4	69.1	72.2	76.8
82.5°	46.9	48.4	49.2	53.0
85°	26.9	30.7	30.0	31.5
87.5°	11.5	12.3	13.8	15.4
90°	6.9	5.9	2.9	1.0
92.5°	45.1	30.4	19.6	13.7
95°	57.8	45.1	35.3	32.3
97.5°	74.5	62.7	53.9	53.9
100°	93.1	81.3	74.5	74.5
102.5°	112.7	101.9	96.0	94.1
105°	134.2	122.5	117.6	114.6
107.5°	156.8	144.0	139.1	137.2
110°	178.3	166.6	161.7	159.7



TEST NUMBER: P1026381

CATALOG NUMBER: S124RDIP-B575D1035UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	199.9	189.1	183.2	181.3
115°	221.4	211.6	204.8	201.8
117.5°	243.0	232.2	226.3	223.4
120°	264.5	253.8	246.9	244.9
122.5°	283.1	273.3	266.5	264.5
125°	301.8	291.0	285.1	281.2
127.5°	318.4	306.7	299.8	296.9
130°	336.0	321.4	313.5	309.6
132.5°	349.8	336.0	325.3	322.3
135°	364.5	347.8	338.0	334.1
137.5°	376.2	360.5	349.8	345.8
140°	389.0	372.3	361.5	358.6
142.5°	400.7	385.0	375.2	372.3
145°	411.5	397.8	388.0	385.0
147.5°	424.2	409.5	400.7	399.7
150°	434.0	422.3	414.4	413.4
152.5°	444.8	434.0	426.2	426.2
155°	454.6	444.8	438.9	437.9
157.5°	463.4	455.6	449.7	449.7
160°	471.3	464.4	460.5	460.5
162.5°	478.1	472.2	469.3	470.3
165°	484.0	479.1	477.1	477.1
167.5°	488.9	485.0	484.0	485.0
170°	492.8	489.9	488.9	489.9
172.5°	495.7	493.8	493.8	494.8
175°	497.7	496.7	496.7	497.7
177.5°	498.7	497.7	498.7	499.7
180°	498.7	498.7	498.7	498.7

(END OF REPORT)