

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026389

Luminaire Tested: S124RDIP-B575D1035UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026389
REPORT IS A COMBINATION OF REPORTS P999439 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D1035UB30-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5887.0 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026389

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026389

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	96	92	88	84	87	83	80	77	68	66	64	54	53	52	42	41	40
2	87	80	74	69	79	73	68	64	60	56	53	48	46	43	37	35	34
3	80	71	64	58	72	65	58	54	53	49	45	43	40	37	33	31	29
4	73	63	55	49	66	57	51	45	47	42	39	38	35	32	29	27	25
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	27	24	22
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	19
7	57	45	37	32	52	41	35	30	35	29	26	28	24	21	22	19	17
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16
9	49	37	30	25	45	34	28	24	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8255	8255	8255
5°	8255	8009	8010
10°	8185	7757	7665
15°	8073	7442	7257
20°	7925	7084	6791
25°	7741	6696	6337
30°	7561	6301	5826
35°	7363	5901	5328
40°	7127	5470	4815
45°	6907	5043	4308
50°	6655	4576	3792
55°	6384	4098	3261
60°	6082	3589	2736
65°	5791	3006	2230
70°	5379	2393	1704
75°	4847	1741	1192
80°	4047	1069	857
85°	3049	615	472

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6907 cd/sqm

TEST NUMBER: P1026389

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.2	1.6
10°-20°	265.4	4.5
20°-30°	383.2	6.5
30°-40°	434.3	7.4
40°-50°	419.3	7.1
50°-60°	348.6	5.9
60°-70°	240.6	4.1
70°-80°	121.6	2.1
80°-90°	33.6	0.6
90°-100°	83.3	1.4
100°-110°	249.5	4.2
110°-120°	423.8	7.2
120°-130°	558.9	9.5
130°-140°	627.7	10.7
140°-150°	617.0	10.5
150°-160°	518.9	8.8
160°-170°	345.3	5.9
170°-180°	120.9	2.1
0°-30°	743.8	12.6
0°-40°	1178.0	20.0
0°-60°	1945.9	33.1
0°-90°	2341.7	39.8
90°-120°	756.6	12.9
90°-150°	2560.2	43.5
90°-180°	3545.0	60.2
0°-180°	5887.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1012	1012	1012	1012	1012	
5°	1011	1008	998	1006	1004	96
15°	963	956	936	935	929	271
25°	870	856	825	812	804	401
35°	753	728	689	663	649	470
45°	614	585	539	501	487	473
55°	465	434	384	343	329	416
65°	316	283	233	200	191	312
75°	168	140	103	85	81	177
85°	42	26	24	22	22	46
90°	3	14	22	28	30	7
95°	59	68	75	78	78	64
105°	230	231	235	238	241	244
115°	431	431	429	428	427	425
125°	628	628	626	624	623	559
135°	809	815	815	813	810	626
145°	983	987	988	987	984	615
155°	1126	1126	1126	1130	1126	518
165°	1226	1223	1221	1227	1223	346
175°	1276	1271	1270	1277	1270	121
180°	1278	1278	1278	1278	1278	

TEST NUMBER: P1026389

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1012.3	1012.3	1012.3	1012.3	1012.3
2.5°	1015.4	1012.3	1003.8	1012.3	1011.5
5°	1010.7	1007.6	998.3	1006.1	1004.5
7.5°	1003.8	1000.7	989.0	994.5	992.1
10°	992.9	989.0	975.1	978.2	975.1
12.5°	979.0	974.3	957.3	958.8	954.2
15°	962.7	955.7	936.3	934.8	929.4
17.5°	944.1	934.0	911.5	907.6	899.9
20°	921.6	911.5	885.2	879.0	868.9
22.5°	896.8	885.2	856.5	846.4	838.7
25°	870.4	856.5	824.7	811.5	803.8
27.5°	843.3	826.3	792.9	777.4	766.6
30°	814.6	795.3	758.8	739.5	727.0
32.5°	784.4	761.9	723.9	700.7	689.1
35°	752.6	727.8	689.1	662.7	648.8
37.5°	719.3	693.7	651.1	622.4	608.5
40°	683.6	658.1	613.9	581.3	567.4
42.5°	649.5	622.4	575.9	542.6	527.8
45°	613.9	585.2	538.7	500.7	486.8
47.5°	577.5	548.0	499.9	460.4	444.9
50°	540.2	510.0	460.4	421.7	406.9
52.5°	502.3	472.8	421.7	382.1	366.6
55°	465.1	434.1	383.7	343.4	328.6
57.5°	428.6	396.1	346.5	305.4	294.5
60°	389.1	358.1	308.5	268.2	255.8
62.5°	353.4	320.9	269.7	233.3	224.0
65°	316.2	282.9	233.3	200.0	190.7
67.5°	277.5	245.7	199.2	169.7	158.9
70°	241.1	208.5	164.3	138.7	131.0
72.5°	202.3	173.6	132.5	111.6	104.6
75°	168.2	139.5	103.1	85.3	80.6
77.5°	132.5	107.7	76.7	64.3	62.8
80°	98.4	76.0	52.7	50.4	49.6
82.5°	69.0	48.8	38.0	36.4	35.7
85°	41.9	26.4	24.0	22.5	22.5
87.5°	17.8	11.6	10.9	10.1	10.9
90°	3.0	13.8	21.7	27.7	29.6
92.5°	25.7	38.5	43.5	46.4	47.4
95°	59.3	68.2	75.1	78.1	78.1
97.5°	94.9	102.8	110.7	114.6	114.6
100°	138.3	142.3	151.2	153.2	153.2
102.5°	183.8	184.8	192.7	195.7	196.7
105°	230.3	231.2	235.2	238.2	241.1
107.5°	278.7	279.7	280.6	284.6	283.6
110°	328.1	330.1	329.1	327.1	330.1

TEST NUMBER: P1026389

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	379.5	379.5	377.5	377.5	377.5
115°	430.9	430.9	428.9	427.9	426.9
117.5°	479.3	479.3	478.3	475.3	472.4
120°	527.7	531.7	528.7	523.7	525.7
122.5°	578.1	579.1	578.1	575.1	570.2
125°	627.5	627.5	626.5	624.5	622.6
127.5°	672.0	674.9	673.0	671.0	670.0
130°	719.4	722.4	722.4	720.4	716.4
132.5°	767.8	769.8	768.8	766.8	765.9
135°	809.3	815.3	815.3	813.3	810.3
137.5°	855.8	858.7	860.7	857.8	858.7
140°	902.2	904.2	904.2	903.2	902.2
142.5°	944.7	946.7	945.7	945.7	945.7
145°	983.3	987.2	988.2	987.2	984.2
147.5°	1022.8	1027.7	1026.7	1025.8	1024.8
150°	1058.4	1062.3	1062.3	1062.3	1061.3
152.5°	1092.0	1093.9	1094.9	1097.9	1094.9
155°	1126.5	1126.5	1125.6	1129.5	1125.6
157.5°	1156.2	1154.2	1154.2	1157.2	1154.2
160°	1181.9	1180.9	1179.9	1182.9	1177.9
162.5°	1205.6	1202.6	1201.7	1207.6	1202.6
165°	1226.4	1223.4	1221.4	1227.3	1223.4
167.5°	1243.2	1239.2	1239.2	1245.1	1239.2
170°	1257.0	1252.1	1253.0	1259.0	1252.1
172.5°	1266.9	1262.9	1262.9	1269.8	1262.9
175°	1275.8	1270.8	1269.8	1276.8	1269.8
177.5°	1279.7	1274.8	1274.8	1281.7	1273.8
180°	1277.7	1277.7	1277.7	1277.7	1277.7

(END OF REPORT)