

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026395

Luminaire Tested: S124RDIP-B575D1035UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026395
REPORT IS A COMBINATION OF REPORTS P999445 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D1035UB35-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5912.0 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026395

CATALOG NUMBER: S124RDIP-B575D1035UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026395

CATALOG NUMBER: S124RDIP-B575D1035UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	96	92	88	84	87	83	80	77	68	66	64	54	53	52	42	41	40
2	87	80	74	69	79	73	68	64	60	56	53	48	46	43	37	35	34
3	80	71	64	58	72	65	58	54	53	49	45	43	40	37	33	31	29
4	73	63	55	49	66	57	51	45	47	42	39	38	35	32	29	27	25
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	27	24	22
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	19
7	57	45	37	32	52	41	35	30	35	29	26	28	24	21	22	19	17
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16
9	49	37	30	25	45	34	28	24	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8290	8290	8290
5°	8291	8044	8044
10°	8221	7790	7698
15°	8108	7474	7287
20°	7959	7114	6820
25°	7775	6724	6364
30°	7594	6328	5852
35°	7394	5926	5350
40°	7159	5493	4836
45°	6936	5064	4326
50°	6684	4596	3809
55°	6412	4115	3275
60°	6109	3604	2748
65°	5816	3019	2240
70°	5401	2403	1712
75°	4867	1748	1198
80°	4068	1073	860
85°	3056	618	474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6936 cd/sqm

TEST NUMBER: P1026395

CATALOG NUMBER: S124RDIP-B575D1035UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.6	1.6
10°-20°	266.5	4.5
20°-30°	384.8	6.5
30°-40°	436.1	7.4
40°-50°	421.1	7.1
50°-60°	350.1	5.9
60°-70°	241.6	4.1
70°-80°	122.1	2.1
80°-90°	33.7	0.6
90°-100°	83.6	1.4
100°-110°	250.5	4.2
110°-120°	425.6	7.2
120°-130°	561.3	9.5
130°-140°	630.4	10.7
140°-150°	619.6	10.5
150°-160°	521.1	8.8
160°-170°	346.7	5.9
170°-180°	121.4	2.1
0°-30°	747.0	12.6
0°-40°	1183.1	20.0
0°-60°	1954.3	33.1
0°-90°	2351.8	39.8
90°-120°	759.7	12.9
90°-150°	2571.0	43.5
90°-180°	3560.0	60.2
0°-180°	5912.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1017	1017	1017	1017	1017	
5°	1015	1012	1003	1010	1009	96
15°	967	960	940	939	933	272
25°	874	860	828	815	807	403
35°	756	731	692	666	652	472
45°	616	588	541	503	489	475
55°	467	436	385	345	330	418
65°	318	284	234	201	192	314
75°	169	140	104	86	81	178
85°	42	26	24	23	23	46
90°	3	14	22	28	30	7
95°	60	68	75	78	78	64
105°	231	232	236	239	242	245
115°	433	433	431	430	429	427
125°	630	630	629	627	625	562
135°	813	819	819	817	814	629
145°	987	991	992	991	988	618
155°	1131	1131	1130	1134	1130	521
165°	1232	1229	1227	1232	1229	347
175°	1281	1276	1275	1282	1275	122
180°	1283	1283	1283	1283	1283	

TEST NUMBER: P1026395

CATALOG NUMBER: S124RDIP-B575D1035UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1016.6	1016.6	1016.6	1016.6	1016.6
2.5°	1019.7	1016.6	1008.1	1016.6	1015.8
5°	1015.1	1011.9	1002.6	1010.4	1008.8
7.5°	1008.1	1004.9	993.3	998.7	996.4
10°	997.2	993.3	979.3	982.4	979.3
12.5°	983.1	978.5	961.3	962.9	958.2
15°	966.8	959.8	940.3	938.8	933.3
17.5°	948.1	938.0	915.4	911.5	903.7
20°	925.5	915.4	889.0	882.7	872.6
22.5°	900.6	889.0	860.2	850.0	842.3
25°	874.2	860.2	828.2	815.0	807.2
27.5°	846.9	829.8	796.3	780.8	769.9
30°	818.1	798.7	762.1	742.6	730.2
32.5°	787.8	765.2	727.0	703.7	692.0
35°	755.8	730.9	692.0	665.5	651.5
37.5°	722.4	696.7	653.9	625.1	611.1
40°	686.6	660.9	616.5	583.8	569.8
42.5°	652.3	625.1	578.4	544.9	530.1
45°	616.5	587.7	541.0	502.9	488.8
47.5°	579.9	550.3	502.1	462.4	446.8
50°	542.6	512.2	462.4	423.5	408.7
52.5°	504.4	474.8	423.5	383.8	368.2
55°	467.1	435.9	385.3	344.8	330.1
57.5°	430.5	397.8	348.0	306.7	295.8
60°	390.8	359.6	309.8	269.3	256.9
62.5°	355.0	322.3	270.9	234.3	225.0
65°	317.6	284.1	234.3	200.8	191.5
67.5°	278.7	246.8	200.1	170.5	159.6
70°	242.1	209.4	165.0	139.3	131.6
72.5°	203.2	174.4	133.1	112.1	105.1
75°	168.9	140.1	103.5	85.6	81.0
77.5°	133.1	108.2	77.1	64.6	63.1
80°	98.9	76.3	52.9	50.6	49.8
82.5°	69.3	49.0	38.1	36.6	35.8
85°	42.0	26.5	24.1	22.6	22.6
87.5°	17.9	11.7	10.9	10.1	10.9
90°	3.0	13.9	21.8	27.8	29.8
92.5°	25.8	38.7	43.7	46.6	47.6
95°	59.5	68.5	75.4	78.4	78.4
97.5°	95.3	103.2	111.1	115.1	115.1
100°	138.9	142.9	151.8	153.8	153.8
102.5°	184.6	185.6	193.5	196.5	197.5
105°	231.2	232.2	236.2	239.2	242.1
107.5°	279.9	280.8	281.8	285.8	284.8
110°	329.5	331.5	330.5	328.5	331.5

TEST NUMBER: P1026395

CATALOG NUMBER: S124RDIP-B575D1035UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	381.1	381.1	379.1	379.1	379.1
115°	432.7	432.7	430.7	429.7	428.7
117.5°	481.3	481.3	480.3	477.3	474.4
120°	529.9	533.9	530.9	526.0	527.9
122.5°	580.5	581.5	580.5	577.6	572.6
125°	630.2	630.2	629.2	627.2	625.2
127.5°	674.8	677.8	675.8	673.8	672.8
130°	722.5	725.4	725.4	723.4	719.5
132.5°	771.1	773.1	772.1	770.1	769.1
135°	812.8	818.7	818.7	816.7	813.8
137.5°	859.4	862.4	864.4	861.4	862.4
140°	906.0	908.0	908.0	907.0	906.0
142.5°	948.7	950.7	949.7	949.7	949.7
145°	987.4	991.4	992.4	991.4	988.4
147.5°	1027.1	1032.1	1031.1	1030.1	1029.1
150°	1062.8	1066.8	1066.8	1066.8	1065.8
152.5°	1096.6	1098.6	1099.6	1102.5	1099.6
155°	1131.3	1131.3	1130.3	1134.3	1130.3
157.5°	1161.1	1159.1	1159.1	1162.1	1159.1
160°	1186.9	1185.9	1184.9	1187.9	1182.9
162.5°	1210.7	1207.7	1206.7	1212.7	1207.7
165°	1231.5	1228.6	1226.6	1232.5	1228.6
167.5°	1248.4	1244.4	1244.4	1250.4	1244.4
170°	1262.3	1257.3	1258.3	1264.3	1257.3
172.5°	1272.2	1268.3	1268.3	1275.2	1268.3
175°	1281.2	1276.2	1275.2	1282.2	1275.2
177.5°	1285.1	1280.2	1280.2	1287.1	1279.2
180°	1283.1	1283.1	1283.1	1283.1	1283.1

(END OF REPORT)