

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026396

Luminaire Tested: S124RDIP-B575D1035UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026396
REPORT IS A COMBINATION OF REPORTS P999446 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D1035UB35-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6038.4 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026396

CATALOG NUMBER: S124RDIP-B575D1035UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026396

CATALOG NUMBER: S124RDIP-B575D1035UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39		
1	96	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33		
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	36	35	33	28		
3	80	70	63	58	72	64	58	53	53	48	45	42	39	37	32	30	29	24		
4	73	62	55	49	66	57	50	45	47	42	38	38	34	31	29	27	25	21		
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18		
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16		
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	22	19	17	14		
8	53	41	33	28	48	38	31	26	31	26	23	25	22	19	20	17	15	13		
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	12		
10	46	34	27	22	42	31	25	21	26	22	18	22	18	15	17	15	13	11		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8290	8290	8290
5°	8291	8044	8044
10°	8221	7790	7698
15°	8108	7474	7287
20°	7959	7114	6820
25°	7775	6724	6364
30°	7594	6328	5852
35°	7394	5926	5350
40°	7159	5493	4836
45°	6936	5064	4326
50°	6684	4596	3809
55°	6412	4115	3275
60°	6109	3604	2748
65°	5816	3019	2240
70°	5401	2403	1712
75°	4867	1748	1198
80°	4068	1073	860
85°	3056	618	474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6936 cd/sqm

TEST NUMBER: P1026396

CATALOG NUMBER: S124RDIP-B575D1035UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.6	1.6
10°-20°	266.5	4.4
20°-30°	384.8	6.4
30°-40°	436.1	7.2
40°-50°	421.1	7.0
50°-60°	350.1	5.8
60°-70°	241.6	4.0
70°-80°	122.1	2.0
80°-90°	32.9	0.5
90°-100°	375.3	6.2
100°-110°	763.4	12.6
110°-120°	680.4	11.3
120°-130°	571.5	9.5
130°-140°	476.9	7.9
140°-150°	364.2	6.0
150°-160°	256.0	4.2
160°-170°	150.6	2.5
170°-180°	49.0	0.8
0°-30°	747.0	12.4
0°-40°	1183.1	19.6
0°-60°	1954.3	32.4
0°-90°	2351.0	38.9
90°-120°	1819.1	30.1
90°-150°	3231.8	53.5
90°-180°	3687.0	61.1
0°-180°	6038.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1017	1017	1017	1017	1017	
5°	1015	1012	1003	1010	1009	96
15°	967	960	940	939	933	272
25°	874	860	828	815	807	403
35°	756	731	692	666	652	472
45°	616	588	541	503	489	475
55°	467	436	385	345	330	418
65°	318	284	234	201	192	314
75°	169	140	104	86	81	178
85°	42	26	24	23	23	46
90°	1	8	18	20	21	5
95°	33	103	809	400	242	36
105°	116	168	651	1402	1397	124
115°	204	257	581	1116	1341	203
125°	285	338	578	950	1070	254
135°	338	403	573	843	957	262
145°	390	447	570	711	781	245
155°	444	479	554	627	654	205
165°	483	498	531	562	571	137
175°	504	505	509	516	514	48
180°	505	505	505	505	505	

TEST NUMBER: P1026396

CATALOG NUMBER: S124RDIP-B575D1035UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1016.6	1016.6	1016.6	1016.6	1016.6
2.5°	1019.7	1016.6	1008.1	1016.6	1015.8
5°	1015.1	1011.9	1002.6	1010.4	1008.8
7.5°	1008.1	1004.9	993.3	998.7	996.4
10°	997.2	993.3	979.3	982.4	979.3
12.5°	983.1	978.5	961.3	962.9	958.2
15°	966.8	959.8	940.3	938.8	933.3
17.5°	948.1	938.0	915.4	911.5	903.7
20°	925.5	915.4	889.0	882.7	872.6
22.5°	900.6	889.0	860.2	850.0	842.3
25°	874.2	860.2	828.2	815.0	807.2
27.5°	846.9	829.8	796.3	780.8	769.9
30°	818.1	798.7	762.1	742.6	730.2
32.5°	787.8	765.2	727.0	703.7	692.0
35°	755.8	730.9	692.0	665.5	651.5
37.5°	722.4	696.7	653.9	625.1	611.1
40°	686.6	660.9	616.5	583.8	569.8
42.5°	652.3	625.1	578.4	544.9	530.1
45°	616.5	587.7	541.0	502.9	488.8
47.5°	579.9	550.3	502.1	462.4	446.8
50°	542.6	512.2	462.4	423.5	408.7
52.5°	504.4	474.8	423.5	383.8	368.2
55°	467.1	435.9	385.3	344.8	330.1
57.5°	430.5	397.8	348.0	306.7	295.8
60°	390.8	359.6	309.8	269.3	256.9
62.5°	355.0	322.3	270.9	234.3	225.0
65°	317.6	284.1	234.3	200.8	191.5
67.5°	278.7	246.8	200.1	170.5	159.6
70°	242.1	209.4	165.0	139.3	131.6
72.5°	203.2	174.4	133.1	112.1	105.1
75°	168.9	140.1	103.5	85.6	81.0
77.5°	133.1	108.2	77.1	64.6	63.1
80°	98.9	76.3	52.9	50.6	49.8
82.5°	69.3	49.0	38.1	36.6	35.8
85°	42.0	26.5	24.1	22.6	22.6
87.5°	17.9	11.7	10.9	10.1	10.9
90°	1.0	7.9	17.9	19.9	20.8
92.5°	13.9	76.4	389.1	128.6	90.3
95°	32.8	103.2	809.0	400.5	242.2
97.5°	54.6	114.2	865.6	818.0	581.7
100°	75.4	129.0	798.1	1131.6	910.3
102.5°	95.3	146.9	713.7	1328.2	1196.2
105°	116.1	168.3	651.2	1402.2	1396.7
107.5°	139.0	190.1	610.5	1379.8	1492.0
110°	161.8	211.9	591.6	1300.4	1494.0

TEST NUMBER: P1026396

CATALOG NUMBER: S124RDIP-B575D1035UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	183.6	233.8	582.7	1203.1	1435.4
115°	204.5	256.6	580.7	1115.8	1341.1
117.5°	226.3	278.0	579.7	1047.3	1248.8
120°	248.2	298.8	579.7	1001.2	1173.3
122.5°	268.0	319.1	578.7	970.8	1113.8
125°	284.9	338.5	577.7	949.5	1070.1
127.5°	300.8	356.4	575.8	929.2	1042.3
130°	313.7	373.7	574.8	904.8	1018.5
132.5°	326.6	388.6	573.8	876.0	991.7
135°	338.5	403.0	572.8	842.8	956.9
137.5°	350.4	415.4	572.8	807.0	916.2
140°	363.3	426.8	571.8	772.3	871.6
142.5°	377.2	437.3	571.8	740.0	823.9
145°	390.1	446.7	569.8	710.8	781.2
147.5°	405.0	455.6	566.8	686.4	741.5
150°	418.9	464.0	563.8	664.1	708.8
152.5°	431.8	472.0	558.9	645.2	679.0
155°	443.7	479.0	553.9	627.3	654.2
157.5°	455.6	485.4	548.9	610.5	631.3
160°	466.6	490.8	543.0	593.6	610.5
162.5°	476.5	495.4	537.0	577.2	590.6
165°	483.4	498.3	531.1	562.3	570.8
167.5°	491.4	500.8	525.1	549.4	554.9
170°	496.3	502.8	519.2	536.6	540.0
172.5°	501.3	504.3	513.2	525.1	525.1
175°	504.3	505.3	509.2	516.2	514.2
177.5°	506.3	505.3	506.3	509.7	506.3
180°	505.3	505.3	505.3	505.3	505.3

(END OF REPORT)