

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026449

Luminaire Tested: S124RDIP-B575D365UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026449
REPORT IS A COMBINATION OF REPORTS P999519 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D365UB30-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3615.0 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026449

CATALOG NUMBER: S124RDIP-B575D365UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026449

CATALOG NUMBER: S124RDIP-B575D365UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70
1	101	97	93	90	95	92	88	85	81	78	76	71	69	68	62	61	60
2	93	85	79	74	87	80	75	70	71	67	64	63	60	57	55	53	51
3	85	75	68	62	79	71	65	59	63	58	54	56	52	49	49	46	44
4	78	67	59	53	73	63	56	51	56	51	46	50	46	42	44	41	38
5	72	60	52	46	67	57	49	44	51	45	40	45	40	37	40	36	33
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	31	27	24
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21
10	50	38	30	25	47	36	29	24	32	27	23	29	25	21	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8255	8255	8255
5°	8255	8009	8010
10°	8185	7757	7665
15°	8073	7442	7257
20°	7925	7084	6791
25°	7741	6696	6337
30°	7561	6301	5826
35°	7363	5901	5328
40°	7127	5470	4815
45°	6907	5043	4308
50°	6655	4576	3792
55°	6384	4098	3261
60°	6082	3589	2736
65°	5791	3006	2230
70°	5379	2393	1704
75°	4847	1741	1192
80°	4047	1069	857
85°	3049	615	472

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6907 cd/sqm

TEST NUMBER: P1026449

CATALOG NUMBER: S124RDIP-B575D365UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.2	2.6
10°-20°	265.4	7.3
20°-30°	383.2	10.6
30°-40°	434.3	12.0
40°-50°	419.3	11.6
50°-60°	348.6	9.6
60°-70°	240.6	6.7
70°-80°	121.6	3.4
80°-90°	31.9	0.9
90°-100°	30.0	0.8
100°-110°	89.7	2.5
110°-120°	152.4	4.2
120°-130°	201.0	5.6
130°-140°	225.8	6.2
140°-150°	221.9	6.1
150°-160°	186.6	5.2
160°-170°	124.2	3.4
170°-180°	43.5	1.2
0°-30°	743.8	20.6
0°-40°	1178.0	32.6
0°-60°	1945.9	53.8
0°-90°	2340.0	64.7
90°-120°	272.1	7.5
90°-150°	920.8	25.5
90°-180°	1275.0	35.3
0°-180°	3615.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1012	1012	1012	1012	1012	
5°	1011	1008	998	1006	1004	96
15°	963	956	936	935	929	271
25°	870	856	825	812	804	401
35°	753	728	689	663	649	470
45°	614	585	539	501	487	473
55°	465	434	384	343	329	416
65°	316	283	233	200	191	312
75°	168	140	103	85	81	177
85°	42	26	24	22	22	46
90°	1	5	8	10	11	4
95°	21	24	27	28	28	23
105°	83	83	85	86	87	88
115°	155	155	154	154	154	153
125°	226	226	225	225	224	201
135°	291	293	293	292	291	225
145°	354	355	355	355	354	221
155°	405	405	405	406	405	186
165°	441	440	439	441	440	124
175°	459	457	457	459	457	44
180°	460	460	460	460	460	

TEST NUMBER: P1026449

CATALOG NUMBER: S124RDIP-B575D365UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1012.3	1012.3	1012.3	1012.3	1012.3
2.5°	1015.4	1012.3	1003.8	1012.3	1011.5
5°	1010.7	1007.6	998.3	1006.1	1004.5
7.5°	1003.8	1000.7	989.0	994.5	992.1
10°	992.9	989.0	975.1	978.2	975.1
12.5°	979.0	974.3	957.3	958.8	954.2
15°	962.7	955.7	936.3	934.8	929.4
17.5°	944.1	934.0	911.5	907.6	899.9
20°	921.6	911.5	885.2	879.0	868.9
22.5°	896.8	885.2	856.5	846.4	838.7
25°	870.4	856.5	824.7	811.5	803.8
27.5°	843.3	826.3	792.9	777.4	766.6
30°	814.6	795.3	758.8	739.5	727.0
32.5°	784.4	761.9	723.9	700.7	689.1
35°	752.6	727.8	689.1	662.7	648.8
37.5°	719.3	693.7	651.1	622.4	608.5
40°	683.6	658.1	613.9	581.3	567.4
42.5°	649.5	622.4	575.9	542.6	527.8
45°	613.9	585.2	538.7	500.7	486.8
47.5°	577.5	548.0	499.9	460.4	444.9
50°	540.2	510.0	460.4	421.7	406.9
52.5°	502.3	472.8	421.7	382.1	366.6
55°	465.1	434.1	383.7	343.4	328.6
57.5°	428.6	396.1	346.5	305.4	294.5
60°	389.1	358.1	308.5	268.2	255.8
62.5°	353.4	320.9	269.7	233.3	224.0
65°	316.2	282.9	233.3	200.0	190.7
67.5°	277.5	245.7	199.2	169.7	158.9
70°	241.1	208.5	164.3	138.7	131.0
72.5°	202.3	173.6	132.5	111.6	104.6
75°	168.2	139.5	103.1	85.3	80.6
77.5°	132.5	107.7	76.7	64.3	62.8
80°	98.4	76.0	52.7	50.4	49.6
82.5°	69.0	48.8	38.0	36.4	35.7
85°	41.9	26.4	24.0	22.5	22.5
87.5°	17.8	11.6	10.9	10.1	10.9
90°	1.1	5.0	7.8	10.0	10.7
92.5°	9.2	13.9	15.6	16.7	17.1
95°	21.3	24.5	27.0	28.1	28.1
97.5°	34.1	37.0	39.8	41.2	41.2
100°	49.8	51.2	54.4	55.1	55.1
102.5°	66.1	66.5	69.3	70.4	70.7
105°	82.8	83.2	84.6	85.7	86.7
107.5°	100.2	100.6	100.9	102.4	102.0
110°	118.0	118.7	118.3	117.6	118.7

TEST NUMBER: P1026449

CATALOG NUMBER: S124RDIP-B575D365UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	136.5	136.5	135.8	135.8	135.8
115°	155.0	155.0	154.2	153.9	153.5
117.5°	172.4	172.4	172.0	170.9	169.9
120°	189.8	191.2	190.1	188.4	189.1
122.5°	207.9	208.3	207.9	206.8	205.1
125°	225.7	225.7	225.3	224.6	223.9
127.5°	241.7	242.7	242.0	241.3	241.0
130°	258.7	259.8	259.8	259.1	257.7
132.5°	276.1	276.9	276.5	275.8	275.4
135°	291.1	293.2	293.2	292.5	291.4
137.5°	307.8	308.8	309.5	308.5	308.8
140°	324.5	325.2	325.2	324.8	324.5
142.5°	339.8	340.5	340.1	340.1	340.1
145°	353.6	355.0	355.4	355.0	354.0
147.5°	367.8	369.6	369.3	368.9	368.5
150°	380.6	382.1	382.1	382.1	381.7
152.5°	392.7	393.4	393.8	394.8	393.8
155°	405.2	405.2	404.8	406.2	404.8
157.5°	415.8	415.1	415.1	416.2	415.1
160°	425.1	424.7	424.3	425.4	423.6
162.5°	433.6	432.5	432.2	434.3	432.5
165°	441.0	440.0	439.3	441.4	440.0
167.5°	447.1	445.7	445.7	447.8	445.7
170°	452.1	450.3	450.6	452.8	450.3
172.5°	455.6	454.2	454.2	456.7	454.2
175°	458.8	457.0	456.7	459.2	456.7
177.5°	460.2	458.5	458.5	460.9	458.1
180°	459.5	459.5	459.5	459.5	459.5

(END OF REPORT)