

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026450

Luminaire Tested: S124RDIP-B575D365UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026450
REPORT IS A COMBINATION OF REPORTS P999520 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D365UB30-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3660.6 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026450

CATALOG NUMBER: S124RDIP-B575D365UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026450

CATALOG NUMBER: S124RDIP-B575D365UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59
2	93	85	79	74	87	80	75	70	71	67	63	62	59	57	55	52	50
3	85	75	68	62	79	71	64	59	63	58	54	55	52	48	49	46	43
4	78	67	59	53	73	63	56	50	56	50	46	50	45	42	44	40	37
5	71	60	52	46	67	56	49	44	50	44	40	45	40	36	39	36	33
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	33	29	26
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23
9	53	41	33	28	50	39	32	27	35	29	25	31	27	23	28	24	21
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8255	8255	8255
5°	8255	8009	8010
10°	8185	7757	7665
15°	8073	7442	7257
20°	7925	7084	6791
25°	7741	6696	6337
30°	7561	6301	5826
35°	7363	5901	5328
40°	7127	5470	4815
45°	6907	5043	4308
50°	6655	4576	3792
55°	6384	4098	3261
60°	6082	3589	2736
65°	5791	3006	2230
70°	5379	2393	1704
75°	4847	1741	1192
80°	4047	1069	857
85°	3049	615	472

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6907 cd/sqm

TEST NUMBER: P1026450

CATALOG NUMBER: S124RDIP-B575D365UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.2	2.6
10°-20°	265.4	7.3
20°-30°	383.2	10.5
30°-40°	434.3	11.9
40°-50°	419.3	11.5
50°-60°	348.6	9.5
60°-70°	240.6	6.6
70°-80°	121.6	3.3
80°-90°	31.6	0.9
90°-100°	134.4	3.7
100°-110°	273.5	7.5
110°-120°	243.7	6.7
120°-130°	204.7	5.6
130°-140°	170.9	4.7
140°-150°	130.5	3.6
150°-160°	91.7	2.5
160°-170°	53.9	1.5
170°-180°	17.5	0.5
0°-30°	743.8	20.3
0°-40°	1178.0	32.2
0°-60°	1945.9	53.2
0°-90°	2339.7	63.9
90°-120°	651.6	17.8
90°-150°	1157.7	31.6
90°-180°	1321.0	36.1
0°-180°	3660.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1012	1012	1012	1012	1012	
5°	1011	1008	998	1006	1004	96
15°	963	956	936	935	929	271
25°	870	856	825	812	804	401
35°	753	728	689	663	649	470
45°	614	585	539	501	487	473
55°	465	434	384	343	329	416
65°	316	283	233	200	191	312
75°	168	140	103	85	81	177
85°	42	26	24	22	22	46
90°	0	3	6	7	8	3
95°	12	37	290	143	87	13
105°	42	60	233	502	500	44
115°	73	92	208	400	480	73
125°	102	121	207	340	383	91
135°	121	144	205	302	343	94
145°	140	160	204	255	280	88
155°	159	172	198	225	234	73
165°	173	178	190	201	204	49
175°	181	181	182	185	184	17
180°	181	181	181	181	181	

TEST NUMBER: P1026450

CATALOG NUMBER: S124RDIP-B575D365UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1012.3	1012.3	1012.3	1012.3	1012.3
2.5°	1015.4	1012.3	1003.8	1012.3	1011.5
5°	1010.7	1007.6	998.3	1006.1	1004.5
7.5°	1003.8	1000.7	989.0	994.5	992.1
10°	992.9	989.0	975.1	978.2	975.1
12.5°	979.0	974.3	957.3	958.8	954.2
15°	962.7	955.7	936.3	934.8	929.4
17.5°	944.1	934.0	911.5	907.6	899.9
20°	921.6	911.5	885.2	879.0	868.9
22.5°	896.8	885.2	856.5	846.4	838.7
25°	870.4	856.5	824.7	811.5	803.8
27.5°	843.3	826.3	792.9	777.4	766.6
30°	814.6	795.3	758.8	739.5	727.0
32.5°	784.4	761.9	723.9	700.7	689.1
35°	752.6	727.8	689.1	662.7	648.8
37.5°	719.3	693.7	651.1	622.4	608.5
40°	683.6	658.1	613.9	581.3	567.4
42.5°	649.5	622.4	575.9	542.6	527.8
45°	613.9	585.2	538.7	500.7	486.8
47.5°	577.5	548.0	499.9	460.4	444.9
50°	540.2	510.0	460.4	421.7	406.9
52.5°	502.3	472.8	421.7	382.1	366.6
55°	465.1	434.1	383.7	343.4	328.6
57.5°	428.6	396.1	346.5	305.4	294.5
60°	389.1	358.1	308.5	268.2	255.8
62.5°	353.4	320.9	269.7	233.3	224.0
65°	316.2	282.9	233.3	200.0	190.7
67.5°	277.5	245.7	199.2	169.7	158.9
70°	241.1	208.5	164.3	138.7	131.0
72.5°	202.3	173.6	132.5	111.6	104.6
75°	168.2	139.5	103.1	85.3	80.6
77.5°	132.5	107.7	76.7	64.3	62.8
80°	98.4	76.0	52.7	50.4	49.6
82.5°	69.0	48.8	38.0	36.4	35.7
85°	41.9	26.4	24.0	22.5	22.5
87.5°	17.8	11.6	10.9	10.1	10.9
90°	0.4	2.8	6.4	7.1	7.5
92.5°	5.0	27.4	139.4	46.0	32.4
95°	11.7	37.0	289.8	143.4	86.8
97.5°	19.6	40.9	310.1	293.0	208.4
100°	27.0	46.2	285.9	405.4	326.1
102.5°	34.1	52.6	255.7	475.8	428.5
105°	41.6	60.2	233.3	502.3	500.3
107.5°	49.8	68.1	218.7	494.3	534.5
110°	58.0	75.9	211.9	465.8	535.2



TEST NUMBER: P1026450

CATALOG NUMBER: S124RDIP-B575D365UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.8	83.7	208.7	431.0	514.2
115°	73.3	91.9	208.0	399.7	480.4
117.5°	81.1	99.6	207.7	375.2	447.4
120°	88.9	107.0	207.7	358.6	420.3
122.5°	96.0	114.3	207.3	347.8	399.0
125°	102.1	121.2	207.0	340.2	383.3
127.5°	107.7	127.6	206.3	332.8	373.4
130°	112.4	133.8	205.9	324.2	364.9
132.5°	117.0	139.2	205.5	313.8	355.2
135°	121.3	144.4	205.2	301.9	342.8
137.5°	125.5	148.9	205.2	289.1	328.2
140°	130.2	152.9	204.8	276.6	312.2
142.5°	135.1	156.6	204.8	265.1	295.2
145°	139.8	160.0	204.1	254.6	279.9
147.5°	145.1	163.2	203.1	245.9	265.6
150°	150.1	166.2	202.0	237.9	253.9
152.5°	154.7	169.1	200.2	231.2	243.2
155°	159.0	171.6	198.4	224.8	234.3
157.5°	163.2	173.9	196.6	218.7	226.2
160°	167.1	175.9	194.5	212.6	218.7
162.5°	170.7	177.4	192.4	206.8	211.6
165°	173.2	178.5	190.2	201.4	204.5
167.5°	176.0	179.4	188.1	196.9	198.8
170°	177.8	180.1	186.0	192.2	193.4
172.5°	179.6	180.6	183.8	188.2	188.1
175°	180.6	181.0	182.4	184.9	184.2
177.5°	181.4	181.0	181.4	182.6	181.4
180°	181.0	181.0	181.0	181.0	181.0

(END OF REPORT)