

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026462

Luminaire Tested: S124RDIP-B575D365UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026462
REPORT IS A COMBINATION OF REPORTS P999532 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D365UB40-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3638.6 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026462

CATALOG NUMBER: S124RDIP-B575D365UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026462

CATALOG NUMBER: S124RDIP-B575D365UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59
2	93	85	79	74	87	80	75	70	71	67	63	62	59	57	55	52	50
3	85	75	68	62	79	71	64	59	63	58	54	55	52	48	49	46	43
4	78	67	59	53	73	63	56	50	56	50	46	50	45	42	44	40	37
5	71	60	52	46	67	56	49	44	50	44	40	45	40	36	39	36	33
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	33	29	26
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23
9	53	41	33	28	50	39	32	27	35	29	25	31	27	23	28	24	21
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8205	8205	8205
5°	8206	7962	7962
10°	8137	7710	7618
15°	8025	7397	7213
20°	7878	7041	6750
25°	7695	6656	6299
30°	7517	6264	5792
35°	7319	5865	5296
40°	7086	5437	4787
45°	6865	5013	4283
50°	6615	4549	3770
55°	6346	4073	3242
60°	6046	3567	2720
65°	5758	2988	2216
70°	5345	2378	1694
75°	4818	1731	1184
80°	4022	1063	852
85°	3027	612	467

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6865 cd/sqm

TEST NUMBER: P1026462

CATALOG NUMBER: S124RDIP-B575D365UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	2.6
10°-20°	263.8	7.3
20°-30°	380.9	10.5
30°-40°	431.7	11.9
40°-50°	416.8	11.5
50°-60°	346.5	9.5
60°-70°	239.2	6.6
70°-80°	120.8	3.3
80°-90°	31.4	0.9
90°-100°	133.6	3.7
100°-110°	271.8	7.5
110°-120°	242.3	6.7
120°-130°	203.5	5.6
130°-140°	169.8	4.7
140°-150°	129.7	3.6
150°-160°	91.2	2.5
160°-170°	53.6	1.5
170°-180°	17.4	0.5
0°-30°	739.3	20.3
0°-40°	1171.0	32.2
0°-60°	1934.3	53.2
0°-90°	2325.7	63.9
90°-120°	647.7	17.8
90°-150°	1150.7	31.6
90°-180°	1313.0	36.1
0°-180°	3638.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1005	1002	992	1000	998	95
15°	957	950	931	929	924	270
25°	865	851	820	807	799	399
35°	748	724	685	659	645	468
45°	610	582	536	498	484	471
55°	462	432	381	341	327	414
65°	314	281	232	199	190	310
75°	167	139	102	85	80	176
85°	42	26	24	22	22	46
90°	0	3	6	7	7	3
95°	12	37	288	143	86	13
105°	41	60	232	499	497	44
115°	73	91	207	397	478	72
125°	101	121	206	338	381	90
135°	120	144	204	300	341	93
145°	139	159	203	253	278	87
155°	158	171	197	223	233	73
165°	172	177	189	200	203	49
175°	180	180	181	184	183	17
180°	180	180	180	180	180	

TEST NUMBER: P1026462

CATALOG NUMBER: S124RDIP-B575D365UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1006.2	1006.2	1006.2	1006.2	1006.2
2.5°	1009.3	1006.2	997.8	1006.2	1005.5
5°	1004.7	1001.6	992.4	1000.1	998.5
7.5°	997.8	994.7	983.1	988.5	986.2
10°	987.0	983.1	969.2	972.3	969.2
12.5°	973.1	968.5	951.5	953.1	948.4
15°	956.9	950.0	930.7	929.2	923.8
17.5°	938.4	928.4	906.1	902.2	894.5
20°	916.1	906.1	879.9	873.7	863.7
22.5°	891.4	879.9	851.4	841.3	833.6
25°	865.2	851.4	819.8	806.7	799.0
27.5°	838.3	821.3	788.2	772.8	762.0
30°	809.8	790.5	754.3	735.0	722.7
32.5°	779.7	757.4	719.6	696.5	684.9
35°	748.1	723.5	684.9	658.7	644.9
37.5°	715.0	689.6	647.2	618.7	604.8
40°	679.6	654.1	610.2	577.8	564.0
42.5°	645.7	618.7	572.5	539.3	524.7
45°	610.2	581.7	535.5	497.7	483.9
47.5°	574.0	544.7	497.0	457.7	442.2
50°	537.0	507.0	457.7	419.1	404.5
52.5°	499.3	470.0	419.1	379.8	364.4
55°	462.3	431.5	381.4	341.3	326.7
57.5°	426.1	393.7	344.4	303.6	292.8
60°	386.8	356.0	306.6	266.6	254.3
62.5°	351.3	319.0	268.1	231.9	222.7
65°	314.4	281.2	231.9	198.8	189.5
67.5°	275.8	244.2	198.0	168.7	157.9
70°	239.6	207.3	163.3	137.9	130.2
72.5°	201.1	172.6	131.7	110.9	104.0
75°	167.2	138.7	102.5	84.8	80.1
77.5°	131.7	107.1	76.3	63.9	62.4
80°	97.8	75.5	52.4	50.1	49.3
82.5°	68.6	48.5	37.8	36.2	35.4
85°	41.6	26.2	23.9	22.3	22.3
87.5°	17.7	11.6	10.8	10.0	10.8
90°	0.4	2.8	6.4	7.1	7.4
92.5°	4.9	27.2	138.6	45.8	32.2
95°	11.7	36.8	288.1	142.6	86.2
97.5°	19.4	40.6	308.2	291.2	207.1
100°	26.9	46.0	284.2	403.0	324.1
102.5°	33.9	52.3	254.1	472.9	425.9
105°	41.4	59.9	231.9	499.2	497.3
107.5°	49.5	67.7	217.4	491.2	531.2
110°	57.6	75.4	210.7	463.0	531.9



TEST NUMBER: P1026462

CATALOG NUMBER: S124RDIP-B575D365UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.4	83.2	207.5	428.4	511.1
115°	72.8	91.4	206.8	397.2	477.5
117.5°	80.6	99.0	206.4	372.8	444.6
120°	88.4	106.4	206.4	356.4	417.8
122.5°	95.4	113.6	206.1	345.7	396.6
125°	101.4	120.6	205.7	338.1	381.0
127.5°	107.1	126.8	205.0	330.8	371.1
130°	111.7	133.0	204.6	322.2	362.6
132.5°	116.3	138.4	204.3	312.0	353.1
135°	120.5	143.5	203.9	300.0	340.7
137.5°	124.8	147.9	203.9	287.4	326.2
140°	129.4	152.0	203.6	275.0	310.3
142.5°	134.3	155.7	203.6	263.5	293.4
145°	138.9	159.0	202.9	253.0	278.2
147.5°	144.2	162.2	201.8	244.4	264.0
150°	149.2	165.2	200.8	236.4	252.4
152.5°	153.7	168.1	199.0	229.8	241.8
155°	158.0	170.6	197.2	223.4	232.9
157.5°	162.2	172.8	195.5	217.4	224.8
160°	166.1	174.8	193.3	211.4	217.4
162.5°	169.7	176.4	191.2	205.6	210.3
165°	172.1	177.4	189.1	200.2	203.2
167.5°	175.0	178.3	187.0	195.6	197.6
170°	176.7	179.0	184.9	191.0	192.3
172.5°	178.5	179.6	182.7	187.0	187.0
175°	179.6	179.9	181.3	183.8	183.1
177.5°	180.3	179.9	180.3	181.5	180.3
180°	179.9	179.9	179.9	179.9	179.9

(END OF REPORT)