

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026468

Luminaire Tested: S124RDIP-B575D365UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026468
REPORT IS A COMBINATION OF REPORTS P999538 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D365UB50-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3519.5 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026468

CATALOG NUMBER: S124RDIP-B575D365UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026468

CATALOG NUMBER: S124RDIP-B575D365UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	62	60	59
2	93	85	79	74	87	80	75	70	71	67	63	62	59	57	55	52	50
3	85	75	68	62	79	71	64	59	63	58	54	55	52	48	49	46	43
4	78	67	59	53	73	63	56	50	56	50	46	50	45	42	44	40	37
5	71	60	52	46	67	56	49	44	50	44	40	45	40	36	39	36	33
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	33	29	26
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23
9	53	41	33	28	50	39	32	27	35	29	25	31	27	23	28	24	21
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7937	7937	7937
5°	7937	7701	7702
10°	7870	7459	7370
15°	7762	7156	6977
20°	7620	6811	6530
25°	7444	6439	6093
30°	7271	6059	5603
35°	7080	5674	5123
40°	6853	5260	4630
45°	6641	4849	4142
50°	6400	4400	3647
55°	6139	3940	3136
60°	5848	3451	2630
65°	5569	2890	2144
70°	5171	2301	1639
75°	4660	1674	1146
80°	3895	1028	824
85°	2925	592	453

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6641 cd/sqm

TEST NUMBER: P1026468

CATALOG NUMBER: S124RDIP-B575D365UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	2.6
10°-20°	255.2	7.3
20°-30°	368.4	10.5
30°-40°	417.6	11.9
40°-50°	403.2	11.5
50°-60°	335.2	9.5
60°-70°	231.3	6.6
70°-80°	116.9	3.3
80°-90°	30.3	0.9
90°-100°	129.3	3.7
100°-110°	262.9	7.5
110°-120°	234.3	6.7
120°-130°	196.8	5.6
130°-140°	164.2	4.7
140°-150°	125.4	3.6
150°-160°	88.2	2.5
160°-170°	51.9	1.5
170°-180°	16.9	0.5
0°-30°	715.2	20.3
0°-40°	1132.7	32.2
0°-60°	1871.1	53.2
0°-90°	2249.6	63.9
90°-120°	626.5	17.8
90°-150°	1113.0	31.6
90°-180°	1270.0	36.1
0°-180°	3519.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	973	973	973	973	973	
5°	972	969	960	967	966	92
15°	926	919	900	899	894	261
25°	837	824	793	780	773	386
35°	724	700	663	637	624	452
45°	590	563	518	482	468	455
55°	447	417	369	330	316	400
65°	304	272	224	192	183	300
75°	162	134	99	82	78	171
85°	40	25	23	22	22	44
90°	0	3	6	7	7	3
95°	11	36	279	138	83	12
105°	40	58	224	483	481	43
115°	70	88	200	384	462	70
125°	98	117	199	327	368	87
135°	117	139	197	290	330	90
145°	134	154	196	245	269	84
155°	153	165	191	216	225	70
165°	166	172	183	194	197	47
175°	174	174	175	178	177	16
180°	174	174	174	174	174	

TEST NUMBER: P1026468

CATALOG NUMBER: S124RDIP-B575D365UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	973.3	973.3	973.3	973.3	973.3
2.5°	976.3	973.3	965.1	973.3	972.6
5°	971.8	968.9	959.9	967.4	965.9
7.5°	965.1	962.2	951.0	956.2	954.0
10°	954.7	951.0	937.6	940.5	937.6
12.5°	941.3	936.8	920.4	921.9	917.4
15°	925.6	918.9	900.3	898.8	893.6
17.5°	907.8	898.1	876.5	872.7	865.3
20°	886.1	876.5	851.1	845.1	835.5
22.5°	862.3	851.1	823.5	813.8	806.4
25°	837.0	823.5	793.0	780.3	772.9
27.5°	810.9	794.5	762.4	747.5	737.1
30°	783.3	764.7	729.6	711.0	699.1
32.5°	754.2	732.6	696.1	673.7	662.6
35°	723.7	699.8	662.6	637.2	623.8
37.5°	691.6	667.0	626.0	598.5	585.0
40°	657.3	632.7	590.3	559.0	545.5
42.5°	624.5	598.5	553.7	521.7	507.5
45°	590.3	562.7	518.0	481.5	468.0
47.5°	555.2	526.9	480.7	442.7	427.8
50°	519.5	490.4	442.7	405.4	391.3
52.5°	482.9	454.6	405.4	367.4	352.5
55°	447.2	417.4	368.9	330.2	316.0
57.5°	412.1	380.8	333.1	293.6	283.2
60°	374.1	344.3	296.6	257.9	245.9
62.5°	339.8	308.5	259.4	224.3	215.4
65°	304.1	272.0	224.3	192.3	183.3
67.5°	266.8	236.3	191.5	163.2	152.8
70°	231.8	200.5	158.0	133.4	126.0
72.5°	194.5	166.9	127.4	107.3	100.6
75°	161.7	134.2	99.1	82.0	77.5
77.5°	127.4	103.6	73.8	61.9	60.4
80°	94.7	73.0	50.7	48.4	47.7
82.5°	66.3	47.0	36.5	35.0	34.3
85°	40.2	25.3	23.1	21.6	21.6
87.5°	17.1	11.2	10.4	9.7	10.4
90°	0.3	2.7	6.2	6.8	7.2
92.5°	4.8	26.4	134.0	44.2	31.1
95°	11.3	35.6	278.6	138.0	83.4
97.5°	18.8	39.4	298.1	281.6	200.3
100°	26.0	44.4	274.9	389.8	313.5
102.5°	32.8	50.6	245.8	457.4	411.9
105°	40.0	58.0	224.3	482.9	481.0
107.5°	47.9	65.4	210.2	475.2	513.8
110°	55.7	73.0	203.7	447.8	514.5



TEST NUMBER: P1026468

CATALOG NUMBER: S124RDIP-B575D365UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	63.2	80.5	200.7	414.3	494.3
115°	70.4	88.4	200.0	384.2	461.8
117.5°	77.9	95.7	199.6	360.6	430.1
120°	85.5	102.9	199.6	344.8	404.1
122.5°	92.3	109.9	199.3	334.4	383.6
125°	98.1	116.6	199.0	327.0	368.5
127.5°	103.6	122.7	198.3	320.0	358.9
130°	108.0	128.8	197.9	311.6	350.7
132.5°	112.5	133.8	197.6	301.6	341.5
135°	116.6	138.8	197.3	290.2	329.5
137.5°	120.7	143.0	197.3	278.0	315.5
140°	125.1	147.0	196.9	266.0	300.1
142.5°	129.9	150.6	196.9	254.8	283.7
145°	134.3	153.8	196.2	244.8	269.0
147.5°	139.5	156.9	195.2	236.4	255.4
150°	144.3	159.8	194.2	228.7	244.1
152.5°	148.7	162.6	192.5	222.2	233.8
155°	152.8	165.0	190.8	216.0	225.3
157.5°	156.9	167.1	189.0	210.2	217.4
160°	160.7	169.0	187.0	204.4	210.2
162.5°	164.1	170.6	184.9	198.8	203.4
165°	166.5	171.6	182.9	193.6	196.6
167.5°	169.2	172.4	180.8	189.2	191.1
170°	170.9	173.1	178.8	184.8	186.0
172.5°	172.6	173.6	176.7	180.8	180.8
175°	173.7	174.0	175.4	177.8	177.1
177.5°	174.3	174.0	174.3	175.6	174.3
180°	174.0	174.0	174.0	174.0	174.0

(END OF REPORT)