

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026472

Luminaire Tested: S124RDIP-B575D590UB27-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026472
REPORT IS A COMBINATION OF REPORTS P999542 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D590UB27-4F0-XX-W2A-F
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4664.0 lumens
Efficiency: N/A
Efficacy: 118.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026472

CATALOG NUMBER: S124RDIP-B575D590UB27-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1026472

CATALOG NUMBER: S124RDIP-B575D590UB27-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	50
1	98	94	90	87	90	87	83	80	73	71	69	61	59	58	50	49	48	48	48	42
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	44	42	41	41	41	36
3	82	72	65	60	75	67	61	56	57	52	49	48	44	42	39	37	35	35	35	31
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	33	30	30	30	27
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	26	26	26	23
6	63	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	23	23	21
7	59	47	39	33	54	43	36	31	37	32	28	32	28	24	27	23	21	21	21	18
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	24	21	19	19	19	16
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	23	19	17	17	17	15
10	47	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	15	15	15	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8181	8181	8181
5°	8182	7938	7938
10°	8112	7687	7595
15°	8000	7375	7191
20°	7854	7020	6730
25°	7672	6636	6280
30°	7493	6245	5774
35°	7298	5848	5280
40°	7064	5421	4772
45°	6845	4998	4269
50°	6596	4535	3759
55°	6327	4060	3232
60°	6028	3557	2711
65°	5739	2979	2210
70°	5330	2371	1689
75°	4804	1726	1181
80°	4014	1059	850
85°	3020	610	467

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6845 cd/sqm

TEST NUMBER: P1026472

CATALOG NUMBER: S124RDIP-B575D590UB27-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.3	2.0
10°-20°	263.0	5.6
20°-30°	379.7	8.1
30°-40°	430.4	9.2
40°-50°	415.5	8.9
50°-60°	345.5	7.4
60°-70°	238.4	5.1
70°-80°	120.5	2.6
80°-90°	32.2	0.7
90°-100°	25.2	0.5
100°-110°	165.6	3.6
110°-120°	316.3	6.8
120°-130°	401.5	8.6
130°-140°	429.5	9.2
140°-150°	401.6	8.6
150°-160°	323.9	6.9
160°-170°	208.9	4.5
170°-180°	72.0	1.5
0°-30°	737.1	15.8
0°-40°	1167.5	25.0
0°-60°	1928.5	41.3
0°-90°	2319.6	49.7
90°-120°	507.0	10.9
90°-150°	1739.7	37.3
90°-180°	2344.0	50.3
0°-180°	4664.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1003	1003	1003	1003	1003	
5°	1002	999	989	997	996	95
15°	954	947	928	926	921	269
25°	863	849	817	804	797	397
35°	746	721	683	657	643	466
45°	608	580	534	496	482	469
55°	461	430	380	340	326	412
65°	313	280	231	198	189	309
75°	167	138	102	84	80	176
85°	42	26	24	22	22	46
90°	2	8	12	16	17	4
95°	31	12	12	16	16	38
105°	171	174	177	182	162	179
115°	318	320	320	321	321	313
125°	448	450	449	450	451	400
135°	555	555	557	558	559	428
145°	640	642	642	643	644	400
155°	702	703	701	703	702	324
165°	741	738	738	742	737	209
175°	758	754	755	760	753	72
180°	758	758	758	758	758	

TEST NUMBER: P1026472

CATALOG NUMBER: S124RDIP-B575D590UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1003.2	1003.2	1003.2	1003.2	1003.2
2.5°	1006.3	1003.2	994.8	1003.2	1002.4
5°	1001.7	998.6	989.4	997.1	995.5
7.5°	994.8	991.7	980.2	985.5	983.2
10°	984.0	980.2	966.3	969.4	966.3
12.5°	970.2	965.6	948.7	950.2	945.6
15°	954.0	947.1	927.9	926.4	921.0
17.5°	935.6	925.6	903.3	899.5	891.8
20°	913.3	903.3	877.2	871.1	861.1
22.5°	888.7	877.2	848.8	838.8	831.1
25°	862.6	848.8	817.3	804.2	796.6
27.5°	835.7	818.8	785.8	770.5	759.7
30°	807.3	788.1	752.0	732.8	720.5
32.5°	777.4	755.1	717.4	694.4	682.9
35°	745.9	721.3	682.9	656.8	642.9
37.5°	712.8	687.5	645.2	616.8	603.0
40°	677.5	652.2	608.4	576.1	562.3
42.5°	643.7	616.8	570.7	537.7	523.1
45°	608.4	580.0	533.9	496.2	482.4
47.5°	572.3	543.1	495.5	456.3	440.9
50°	535.4	505.4	456.3	417.9	403.3
52.5°	497.8	468.6	417.9	378.7	363.3
55°	460.9	430.2	380.2	340.3	325.7
57.5°	424.8	392.5	343.4	302.6	291.9
60°	385.6	354.9	305.7	265.8	253.5
62.5°	350.3	318.0	267.3	231.2	222.0
65°	313.4	280.4	231.2	198.2	189.0
67.5°	275.0	243.5	197.4	168.2	157.5
70°	238.9	206.6	162.8	137.5	129.8
72.5°	200.5	172.1	131.4	110.6	103.7
75°	166.7	138.3	102.2	84.5	79.9
77.5°	131.4	106.8	76.0	63.8	62.2
80°	97.6	75.3	52.2	49.9	49.2
82.5°	68.4	48.4	37.6	36.1	35.3
85°	41.5	26.1	23.8	22.3	22.3
87.5°	17.7	11.5	10.8	10.0	10.8
90°	1.7	7.9	12.5	15.9	17.0
92.5°	8.5	7.4	11.9	15.3	15.3
95°	31.2	11.9	12.5	15.9	16.4
97.5°	59.5	72.0	12.5	15.3	15.9
100°	92.9	103.1	24.9	15.3	15.9
102.5°	130.3	137.1	143.9	16.4	16.4
105°	170.6	174.0	176.8	181.9	161.5
107.5°	207.4	209.1	213.1	215.9	218.2
110°	244.8	246.5	249.9	251.0	252.7

TEST NUMBER: P1026472

CATALOG NUMBER: S124RDIP-B575D590UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.1	284.5	285.6	285.0	287.3
115°	318.5	320.2	319.6	320.7	320.7
117.5°	351.9	354.2	355.9	355.3	355.3
120°	385.9	388.2	387.6	388.7	387.6
122.5°	417.6	418.8	419.9	420.5	419.3
125°	447.7	449.9	448.8	450.5	451.1
127.5°	476.6	477.1	480.0	479.4	478.8
130°	504.3	504.9	506.6	507.2	507.2
132.5°	529.8	531.0	533.2	533.8	533.2
135°	555.3	554.8	557.0	558.2	559.3
137.5°	578.0	578.0	580.8	582.0	581.4
140°	600.1	601.2	602.4	604.1	604.6
142.5°	619.9	622.2	622.8	623.9	623.9
145°	640.3	642.0	642.0	642.6	643.7
147.5°	656.2	659.6	659.0	659.6	660.2
150°	673.8	676.0	675.5	675.5	676.0
152.5°	688.5	690.2	689.1	690.2	689.6
155°	702.1	702.7	701.0	703.2	701.5
157.5°	714.0	714.0	711.7	714.6	711.7
160°	724.2	722.5	721.9	725.3	721.9
162.5°	733.3	731.0	730.4	733.8	729.9
165°	740.6	737.8	737.8	742.3	737.2
167.5°	746.9	744.0	743.5	748.6	742.9
170°	752.0	748.6	749.1	753.7	748.0
172.5°	755.4	752.0	752.5	757.1	750.8
175°	757.6	754.2	754.8	759.9	753.1
177.5°	759.3	755.4	756.5	761.0	754.2
180°	757.6	757.6	757.6	757.6	757.6

(END OF REPORT)