

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026492

Luminaire Tested: S124RDIP-B575D590UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026492
REPORT IS A COMBINATION OF REPORTS P999572 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D590UB40-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4437.2 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026492

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026492

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50
2	90	83	77	72	83	77	72	67	66	62	59	56	53	50	46	44	42
3	82	73	66	60	76	68	62	56	58	53	50	49	46	43	41	39	36
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32
5	69	58	50	44	64	54	47	41	47	41	37	40	35	32	33	30	28
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	24
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	28	24	22
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	24	20	18
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8205	8205	8205
5°	8206	7962	7962
10°	8137	7710	7618
15°	8025	7397	7213
20°	7878	7041	6750
25°	7695	6656	6299
30°	7517	6264	5792
35°	7319	5865	5296
40°	7086	5437	4787
45°	6865	5013	4283
50°	6615	4549	3770
55°	6346	4073	3242
60°	6046	3567	2720
65°	5758	2988	2216
70°	5345	2378	1694
75°	4818	1731	1184
80°	4022	1063	852
85°	3027	612	467

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6865 cd/sqm

TEST NUMBER: P1026492

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	2.1
10°-20°	263.8	5.9
20°-30°	380.9	8.6
30°-40°	431.7	9.7
40°-50°	416.8	9.4
50°-60°	346.5	7.8
60°-70°	239.2	5.4
70°-80°	120.8	2.7
80°-90°	31.8	0.7
90°-100°	214.9	4.8
100°-110°	437.0	9.8
110°-120°	389.5	8.8
120°-130°	327.2	7.4
130°-140°	273.1	6.2
140°-150°	208.5	4.7
150°-160°	146.6	3.3
160°-170°	86.2	1.9
170°-180°	28.0	0.6
0°-30°	739.3	16.7
0°-40°	1171.0	26.4
0°-60°	1934.3	43.6
0°-90°	2326.1	52.4
90°-120°	1041.5	23.5
90°-150°	1850.3	41.7
90°-180°	2111.0	47.6
0°-180°	4437.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1005	1002	992	1000	998	95
15°	957	950	931	929	924	270
25°	865	851	820	807	799	399
35°	748	724	685	659	645	468
45°	610	582	536	498	484	471
55°	462	432	381	341	327	414
65°	314	281	232	199	190	310
75°	167	139	102	85	80	176
85°	42	26	24	22	22	46
90°	1	4	10	11	12	4
95°	19	59	463	229	139	21
105°	66	96	373	803	800	71
115°	117	147	332	639	768	116
125°	163	194	331	544	613	145
135°	194	231	328	482	548	150
145°	223	256	326	407	447	140
155°	254	274	317	359	374	117
165°	277	285	304	322	327	78
175°	289	289	292	296	294	27
180°	289	289	289	289	289	

TEST NUMBER: P1026492

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1006.2	1006.2	1006.2	1006.2	1006.2
2.5°	1009.3	1006.2	997.8	1006.2	1005.5
5°	1004.7	1001.6	992.4	1000.1	998.5
7.5°	997.8	994.7	983.1	988.5	986.2
10°	987.0	983.1	969.2	972.3	969.2
12.5°	973.1	968.5	951.5	953.1	948.4
15°	956.9	950.0	930.7	929.2	923.8
17.5°	938.4	928.4	906.1	902.2	894.5
20°	916.1	906.1	879.9	873.7	863.7
22.5°	891.4	879.9	851.4	841.3	833.6
25°	865.2	851.4	819.8	806.7	799.0
27.5°	838.3	821.3	788.2	772.8	762.0
30°	809.8	790.5	754.3	735.0	722.7
32.5°	779.7	757.4	719.6	696.5	684.9
35°	748.1	723.5	684.9	658.7	644.9
37.5°	715.0	689.6	647.2	618.7	604.8
40°	679.6	654.1	610.2	577.8	564.0
42.5°	645.7	618.7	572.5	539.3	524.7
45°	610.2	581.7	535.5	497.7	483.9
47.5°	574.0	544.7	497.0	457.7	442.2
50°	537.0	507.0	457.7	419.1	404.5
52.5°	499.3	470.0	419.1	379.8	364.4
55°	462.3	431.5	381.4	341.3	326.7
57.5°	426.1	393.7	344.4	303.6	292.8
60°	386.8	356.0	306.6	266.6	254.3
62.5°	351.3	319.0	268.1	231.9	222.7
65°	314.4	281.2	231.9	198.8	189.5
67.5°	275.8	244.2	198.0	168.7	157.9
70°	239.6	207.3	163.3	137.9	130.2
72.5°	201.1	172.6	131.7	110.9	104.0
75°	167.2	138.7	102.5	84.8	80.1
77.5°	131.7	107.1	76.3	63.9	62.4
80°	97.8	75.5	52.4	50.1	49.3
82.5°	68.6	48.5	37.8	36.2	35.4
85°	41.6	26.2	23.9	22.3	22.3
87.5°	17.7	11.6	10.8	10.0	10.8
90°	0.6	4.5	10.2	11.4	11.9
92.5°	8.0	43.8	222.8	73.6	51.7
95°	18.8	59.1	463.2	229.4	138.7
97.5°	31.3	65.4	495.6	468.3	333.0
100°	43.2	73.9	456.9	647.9	521.1
102.5°	54.6	84.1	408.6	760.4	684.8
105°	66.5	96.4	372.8	802.8	799.6
107.5°	79.6	108.8	349.5	790.0	854.2
110°	92.6	121.4	338.7	744.5	855.3



TEST NUMBER: P1026492

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	105.1	133.8	333.6	688.8	821.8
115°	117.1	146.9	332.5	638.8	767.8
117.5°	129.6	159.1	331.9	599.6	714.9
120°	142.1	171.0	331.9	573.2	671.8
122.5°	153.4	182.7	331.3	555.8	637.7
125°	163.1	193.8	330.8	543.6	612.6
127.5°	172.2	204.0	329.6	532.0	596.7
130°	179.6	214.0	329.1	518.0	583.1
132.5°	187.0	222.5	328.5	501.6	567.8
135°	193.8	230.7	327.9	482.5	547.9
137.5°	200.6	237.8	327.9	462.0	524.6
140°	208.0	244.4	327.4	442.2	499.0
142.5°	216.0	250.4	327.4	423.6	471.7
145°	223.3	255.8	326.2	407.0	447.3
147.5°	231.9	260.8	324.5	393.0	424.5
150°	239.8	265.7	322.8	380.2	405.8
152.5°	247.2	270.2	320.0	369.4	388.7
155°	254.0	274.2	317.1	359.2	374.5
157.5°	260.9	277.9	314.3	349.5	361.5
160°	267.1	281.0	310.9	339.8	349.5
162.5°	272.8	283.6	307.5	330.5	338.2
165°	276.8	285.3	304.1	322.0	326.8
167.5°	281.3	286.7	300.6	314.5	317.7
170°	284.2	287.8	297.2	307.2	309.2
172.5°	287.0	288.7	293.8	300.6	300.6
175°	288.7	289.3	291.5	295.5	294.4
177.5°	289.8	289.3	289.8	291.8	289.8
180°	289.3	289.3	289.3	289.3	289.3

(END OF REPORT)