

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025973

Luminaire Tested: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025973
REPORT IS A COMBINATION OF REPORTS P998883 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8656.0 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025973

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1025973

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	90	87	91	87	84	81	74	72	69	62	60	59	50	49	48
2	90	83	77	72	83	77	72	67	65	61	58	55	52	50	45	43	41
3	82	73	66	60	76	68	62	57	58	53	49	49	45	42	40	38	36
4	75	65	57	51	69	60	54	48	52	47	42	44	40	37	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27
6	64	52	44	39	59	49	42	36	42	36	32	36	31	28	30	27	24
7	59	47	39	34	55	44	37	32	38	33	29	33	28	25	27	24	22
8	55	43	35	30	51	40	33	29	35	29	26	30	26	22	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13968	13968	13968	13968
5°	13968	15783	13991	12063
10°	13894	18194	13882	10491
15°	13728	20477	13728	8783
20°	13555	22202	13484	7734
25°	13343	22295	13282	6986
30°	13119	18959	13016	6470
35°	12802	14305	12639	6087
40°	12448	10367	12204	5786
45°	11864	7879	11569	5522
50°	11171	6368	10865	5133
55°	10420	5273	10080	4615
60°	9667	4458	9234	3839
65°	8721	3632	8442	3051
70°	7853	2946	7483	2478
75°	6882	2122	6403	1816
80°	5676	1406	5166	1335
85°	4119	723	3413	723

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 17486 cd/sqm

TEST NUMBER: P1025973

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.9	1.9
10°-20°	500.9	5.8
20°-30°	784.6	9.1
30°-40°	871.3	10.1
40°-50°	772.0	8.9
50°-60°	601.7	7.0
60°-70°	393.6	4.5
70°-80°	193.1	2.2
80°-90°	49.4	0.6
90°-100°	430.2	5.0
100°-110°	898.3	10.4
110°-120°	798.5	9.2
120°-130°	672.1	7.8
130°-140°	560.8	6.5
140°-150°	428.1	4.9
150°-160°	301.0	3.5
160°-170°	177.0	2.0
170°-180°	57.6	0.7
0°-30°	1451.3	16.8
0°-40°	2322.6	26.8
0°-60°	3696.3	42.7
0°-90°	4332.3	50.1
90°-120°	2127.0	24.6
90°-150°	3788.0	43.8
90°-180°	4324.0	50.0
0°-180°	8656.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1713	1713	1713	1713	1713	
5°	1710	1979	1713	1513	1710	162
15°	1637	2622	1637	1125	1637	462
25°	1500	2828	1493	886	1500	691
35°	1308	1742	1292	741	1308	818
45°	1054	890	1028	624	1054	813
55°	759	531	734	465	759	679
65°	476	311	461	261	476	475
75°	239	144	222	123	239	253
85°	57	34	47	34	57	64
90°	1	24	1	24	1	6
95°	38	285	38	285	38	42
105°	136	1641	136	1641	136	145
115°	240	1576	240	1576	240	238
125°	335	1257	335	1257	335	298
135°	398	1124	398	1124	398	307
145°	458	918	458	918	458	288
155°	521	769	521	769	521	240
165°	568	671	568	671	568	160
175°	592	604	592	604	592	56
180°	594	594	594	594	594	

TEST NUMBER: P1025973

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1715.7	1730.8	1739.1	1746.0	1759.8	1765.3	1776.4	1779.1	1790.2	1788.8	1784.7
5°	1710.1	1736.4	1755.7	1776.4	1801.2	1815.0	1830.2	1852.3	1863.3	1878.5	1888.2
7.5°	1700.5	1736.4	1768.1	1799.9	1839.9	1862.0	1881.3	1915.8	1944.8	1969.6	1997.2
10°	1685.3	1730.8	1777.8	1820.6	1875.8	1902.0	1931.0	1982.0	2022.1	2056.6	2100.7
12.5°	1661.8	1725.3	1777.8	1835.7	1906.1	1942.0	1980.7	2041.4	2088.3	2144.9	2200.1
15°	1637.0	1707.4	1776.4	1852.3	1932.4	1973.8	2012.4	2093.8	2165.6	2230.5	2291.2
17.5°	1609.4	1686.7	1762.6	1846.8	1943.4	1994.5	2040.0	2138.0	2216.7	2300.9	2361.6
20°	1576.3	1660.4	1747.4	1841.3	1950.3	2006.9	2058.0	2169.8	2256.7	2347.8	2423.7
22.5°	1540.4	1631.5	1726.7	1828.8	1942.0	2004.1	2063.5	2183.6	2284.3	2368.5	2470.7
25°	1500.3	1597.0	1695.0	1802.6	1929.6	1997.2	2058.0	2176.7	2284.3	2394.7	2494.1
27.5°	1458.9	1558.3	1660.4	1773.6	1903.4	1969.6	2038.6	2153.2	2278.8	2398.9	2499.6
30°	1413.4	1510.0	1617.7	1725.3	1863.3	1929.6	2000.0	2124.2	2260.9	2380.9	2490.0
32.5°	1363.7	1463.1	1565.2	1677.0	1812.3	1884.0	1948.9	2089.7	2229.1	2347.8	2450.0
35°	1308.5	1402.3	1499.0	1613.5	1747.4	1812.3	1889.6	2035.9	2176.7	2302.3	2368.5
37.5°	1249.1	1338.8	1428.6	1541.7	1670.1	1748.8	1824.7	1972.4	2121.5	2205.6	2240.2
40°	1193.9	1272.6	1351.3	1460.3	1590.1	1671.5	1748.8	1902.0	2033.1	2098.0	2071.8
42.5°	1123.5	1205.0	1275.4	1376.1	1507.2	1583.2	1661.8	1820.6	1926.8	1953.1	1888.2
45°	1054.5	1122.1	1189.8	1287.8	1425.8	1490.7	1574.9	1722.6	1810.9	1787.4	1692.2
47.5°	986.9	1042.1	1105.6	1200.8	1325.0	1402.3	1481.0	1609.4	1671.5	1638.4	1505.9
50°	906.8	962.0	1028.3	1111.1	1231.2	1305.7	1367.8	1486.5	1533.5	1452.0	1291.9
52.5°	830.9	879.2	935.8	1013.1	1127.7	1195.3	1262.9	1365.1	1380.3	1286.4	1118.0
55°	759.1	797.8	857.1	919.2	1024.1	1095.9	1142.9	1229.8	1225.7	1108.3	963.4
57.5°	684.6	720.5	760.5	825.4	924.8	978.6	1029.7	1105.6	1065.6	966.2	822.6
60°	618.4	639.1	679.1	741.2	825.4	872.3	912.3	953.8	919.2	811.6	701.2
62.5°	545.2	568.7	597.7	647.3	721.9	766.0	795.0	813.0	777.1	694.3	593.5
65°	476.2	496.9	527.3	571.4	628.0	661.1	676.3	688.7	669.4	575.6	495.5
67.5°	414.1	427.9	455.5	484.5	545.2	553.5	574.2	579.7	541.1	469.3	405.8
70°	352.0	365.8	378.2	412.7	440.3	455.5	459.6	459.6	421.0	374.0	321.6
72.5°	294.0	302.3	314.7	338.2	353.3	364.4	369.9	363.0	327.1	288.5	249.8
75°	238.8	242.9	254.0	269.1	281.6	277.4	276.1	267.8	241.5	213.9	191.9
77.5°	183.6	186.3	198.8	202.9	202.9	207.0	201.5	193.2	171.2	150.4	140.8
80°	138.0	142.2	143.5	146.3	143.5	143.5	139.4	125.6	114.6	104.9	98.0
82.5°	95.2	98.0	99.4	95.2	98.0	93.9	87.0	77.3	70.4	69.0	66.3
85°	56.6	58.0	56.6	56.6	52.4	51.1	45.5	44.2	41.4	41.4	40.0
87.5°	27.6	26.2	23.5	20.7	20.7	19.3	20.7	17.9	20.7	19.3	17.9
90°	1.2	3.5	7.0	8.2	9.3	9.3	9.3	16.3	16.3	18.7	21.0
92.5°	16.3	23.3	36.2	53.6	74.6	89.8	105.0	177.3	290.4	400.0	457.2
95°	38.5	42.0	53.6	68.8	96.8	121.3	145.8	247.3	438.5	717.3	950.5
97.5°	64.1	64.1	74.6	88.6	113.1	134.1	155.1	235.6	400.0	686.9	1017.0
100°	88.6	88.6	96.8	110.8	133.0	151.6	170.3	239.1	370.9	608.8	937.7
102.5°	112.0	114.3	121.3	134.1	155.1	172.6	190.1	250.8	362.7	556.3	838.6
105°	136.5	140.0	145.8	159.8	180.8	197.7	214.6	270.6	367.4	530.7	765.1
107.5°	163.3	165.6	171.4	186.6	206.4	223.4	240.3	291.6	381.4	523.7	717.3
110°	190.1	192.4	198.3	212.3	233.3	249.0	264.7	316.1	397.7	526.0	695.1

TEST NUMBER: P1025973

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	215.8	218.1	225.1	237.9	258.9	274.6	290.4	339.4	415.2	533.0	684.6
115°	240.3	243.8	251.9	263.6	285.7	301.4	317.2	363.9	433.9	542.3	682.3
117.5°	265.9	269.4	276.4	289.2	310.2	326.5	342.9	387.2	452.5	551.7	681.1
120°	291.6	293.9	302.1	314.9	334.7	351.0	367.4	411.7	472.3	562.2	681.1
122.5°	314.9	317.2	325.4	337.1	359.2	375.0	390.7	435.0	491.0	572.7	680.0
125°	334.7	339.4	346.4	359.2	381.4	397.7	414.0	456.0	509.7	583.1	678.8
127.5°	353.4	356.9	365.1	379.0	402.4	418.7	435.0	475.8	526.0	591.3	676.5
130°	368.5	373.2	382.5	400.0	422.2	439.1	456.0	495.7	541.2	600.6	675.3
132.5°	383.7	387.2	400.0	416.4	440.9	456.6	472.3	512.0	556.3	608.8	674.1
135°	397.7	402.4	414.0	433.9	458.4	473.6	488.7	527.2	569.2	617.0	673.0
137.5°	411.7	416.4	429.2	447.9	473.5	488.1	502.7	538.8	578.5	621.6	673.0
140°	426.9	430.4	443.2	463.0	487.5	501.5	515.5	550.5	587.8	627.5	671.8
142.5°	443.2	446.7	458.4	477.0	500.3	513.8	527.2	561.0	594.8	632.1	671.8
145°	458.4	461.9	473.5	489.8	512.0	524.8	537.7	568.0	599.5	633.3	669.5
147.5°	475.8	477.0	487.5	505.0	523.7	535.4	547.0	576.2	604.1	634.5	666.0
150°	492.2	493.3	502.7	516.7	534.2	545.2	556.3	582.0	607.6	634.5	662.5
152.5°	507.3	507.3	516.7	529.5	544.7	554.6	564.5	586.6	610.0	632.1	656.6
155°	521.3	522.5	529.5	541.2	554.0	562.8	571.5	591.3	611.1	629.8	650.8
157.5°	535.3	535.3	542.3	551.7	563.3	570.3	577.3	594.8	611.1	627.5	645.0
160°	548.2	548.2	552.8	561.0	570.3	576.7	583.1	597.1	611.1	624.0	638.0
162.5°	559.8	558.7	562.2	569.2	577.3	582.0	586.6	599.5	611.1	620.5	631.0
165°	568.0	568.0	570.3	576.2	582.0	585.5	589.0	599.5	608.8	615.8	624.0
167.5°	577.3	576.2	577.3	582.0	585.5	588.4	591.3	599.5	606.5	611.1	617.0
170°	583.1	582.0	583.1	586.6	589.0	590.8	592.5	598.3	604.1	606.5	610.0
172.5°	589.0	587.8	587.8	590.1	591.3	592.4	593.6	597.1	601.8	601.8	603.0
175°	592.5	591.3	591.3	592.5	593.6	593.6	593.6	596.0	599.5	598.3	598.3
177.5°	594.8	593.6	592.5	593.6	593.6	593.6	593.6	594.8	597.1	594.8	594.8
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1025973

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1795.7	1810.9	1812.3	1826.1	1821.9	1815.0	1827.5	1819.2	1835.7	1830.2	1837.1
5°	1900.6	1921.3	1939.3	1950.3	1969.6	1965.5	1986.2	1979.3	1994.5	1979.3	1998.6
7.5°	2023.5	2058.0	2075.9	2104.9	2113.2	2114.6	2139.4	2144.9	2154.6	2144.9	2156.0
10°	2143.5	2184.9	2226.4	2249.8	2265.0	2285.7	2307.8	2317.4	2324.3	2314.7	2321.6
12.5°	2252.6	2317.4	2363.0	2409.9	2421.0	2438.9	2462.4	2459.6	2487.2	2481.7	2494.1
15°	2353.3	2425.1	2480.3	2517.6	2547.9	2563.1	2607.3	2610.1	2608.7	2622.5	2614.2
17.5°	2443.1	2503.8	2582.5	2630.8	2668.0	2668.0	2692.9	2743.9	2739.8	2738.4	2746.7
20°	2516.2	2585.2	2658.4	2739.8	2770.2	2775.7	2810.2	2836.4	2840.6	2840.6	2840.6
22.5°	2571.4	2652.8	2731.5	2789.5	2813.0	2832.3	2862.6	2879.2	2884.7	2882.0	2884.7
25°	2599.0	2676.3	2756.4	2808.8	2822.6	2833.7	2836.4	2846.1	2844.7	2828.1	2837.8
27.5°	2604.5	2679.1	2731.5	2745.3	2738.4	2731.5	2687.4	2691.5	2679.1	2654.2	2663.9
30°	2579.7	2619.7	2618.3	2575.6	2563.1	2534.1	2494.1	2434.8	2386.5	2365.8	2372.7
32.5°	2490.0	2490.0	2440.3	2343.7	2300.9	2248.4	2176.7	2122.8	2059.3	2045.5	2071.8
35°	2365.8	2295.4	2204.3	2077.3	2012.4	1973.8	1849.5	1810.9	1757.1	1741.9	1754.3
37.5°	2172.5	2055.2	1922.7	1804.0	1748.8	1679.8	1570.7	1515.5	1476.9	1450.6	1463.1
40°	1955.8	1813.7	1675.6	1529.3	1468.6	1412.0	1330.6	1280.9	1218.8	1221.5	1225.7
42.5°	1748.8	1581.8	1427.2	1291.9	1233.9	1187.0	1130.4	1069.7	1047.6	1040.7	1033.8
45°	1529.3	1351.3	1206.3	1105.6	1053.1	1009.0	956.5	922.0	895.8	890.3	897.2
47.5°	1322.3	1171.8	1033.8	940.0	897.2	875.1	833.7	801.9	785.4	771.6	779.8
50°	1134.6	993.8	883.4	804.7	774.3	759.1	720.5	703.9	687.4	683.2	681.8
52.5°	980.0	859.9	764.7	701.2	677.7	669.4	640.4	617.0	603.2	607.3	610.1
55°	839.2	737.1	662.5	611.5	592.1	582.5	561.8	545.2	535.5	531.4	534.2
57.5°	715.0	626.6	572.8	531.4	516.2	512.1	490.0	484.5	477.6	473.4	473.4
60°	601.8	539.7	490.0	466.5	450.0	445.8	429.3	422.4	421.0	416.8	414.1
62.5°	506.6	455.5	421.0	396.1	389.2	387.9	376.8	368.5	364.4	361.6	361.6
65°	423.7	386.5	357.5	339.5	334.0	331.3	318.8	316.1	313.3	310.6	309.2
67.5°	353.3	320.2	299.5	287.1	280.2	281.6	274.7	269.1	269.1	267.8	266.4
70°	285.7	265.0	247.1	240.2	237.4	234.6	231.9	227.7	226.4	226.4	226.4
72.5°	225.0	211.2	201.5	197.4	194.6	191.9	189.1	189.1	189.1	187.7	187.7
75°	172.5	167.0	160.1	156.0	156.0	158.7	154.6	150.4	146.3	143.5	144.9
77.5°	129.7	127.0	122.8	115.9	117.3	114.6	114.6	111.8	113.2	113.2	110.4
80°	95.2	91.1	89.7	85.6	87.0	85.6	84.2	84.2	81.4	81.4	81.4
82.5°	66.3	62.1	62.1	60.7	59.4	59.4	58.0	58.0	59.4	56.6	56.6
85°	40.0	38.6	38.6	35.9	35.9	35.9	35.9	37.3	35.9	34.5	34.5
87.5°	17.9	19.3	17.9	16.6	16.6	16.6	15.2	15.2	13.8	15.2	15.2
90°	19.8	21.0	22.2	23.3	23.3	23.3	24.5	25.7	24.5	24.5	24.5
92.5°	380.2	281.1	209.9	165.6	151.0	136.5	119.0	110.8	106.1	106.1	106.1
95°	977.4	864.2	683.4	527.2	470.6	414.0	356.9	320.7	299.7	284.6	299.7
97.5°	1225.8	1244.4	1154.6	1026.3	961.0	895.7	816.4	746.4	711.4	683.4	711.4
100°	1236.3	1406.6	1429.9	1372.7	1329.6	1286.4	1185.0	1113.8	1078.8	1069.5	1078.8
102.5°	1148.8	1398.4	1537.2	1572.2	1560.5	1548.8	1496.4	1449.7	1412.4	1405.4	1412.4
105°	1039.2	1306.3	1508.0	1623.5	1647.4	1671.3	1673.6	1664.3	1648.0	1641.0	1648.0
107.5°	949.4	1193.1	1411.2	1572.2	1621.2	1670.1	1721.5	1742.4	1751.8	1752.9	1751.8
110°	885.2	1092.8	1294.6	1463.7	1527.8	1592.0	1674.8	1723.8	1744.8	1755.3	1744.8

TEST NUMBER: P1025973

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	849.1	1019.3	1192.0	1349.4	1413.6	1477.7	1574.5	1636.3	1667.8	1686.5	1667.8
115°	829.2	975.0	1118.5	1254.9	1310.9	1366.9	1459.0	1529.0	1566.3	1575.7	1566.3
117.5°	818.7	949.4	1070.7	1181.5	1230.4	1279.4	1361.1	1421.7	1461.4	1467.2	1461.4
120°	810.6	933.0	1041.5	1134.8	1176.2	1217.6	1284.1	1335.4	1365.7	1378.6	1365.7
122.5°	801.2	919.0	1022.8	1105.6	1140.6	1175.6	1229.3	1271.3	1295.8	1308.6	1295.8
125°	790.7	902.7	1003.0	1083.5	1115.6	1147.6	1194.3	1228.1	1250.3	1257.3	1250.3
127.5°	776.8	884.1	980.9	1061.3	1091.6	1122.0	1168.6	1199.0	1217.6	1224.6	1217.6
130°	763.9	860.7	952.9	1032.2	1063.1	1094.0	1141.8	1171.0	1189.6	1196.6	1189.6
132.5°	752.3	836.2	921.4	998.3	1029.2	1060.2	1106.8	1140.6	1158.1	1165.1	1158.1
135°	740.6	814.1	889.9	961.0	990.2	1019.3	1066.0	1098.7	1117.3	1124.3	1117.3
137.5°	730.1	793.1	859.6	921.4	948.2	975.0	1019.3	1053.2	1068.3	1076.5	1068.3
140°	721.9	775.6	830.4	882.9	907.4	931.9	972.7	998.3	1014.7	1024.0	1014.7
142.5°	714.9	759.3	805.9	849.1	869.5	889.9	924.9	948.2	962.2	968.0	962.2
145°	706.8	744.1	783.8	818.7	835.0	851.4	880.6	900.4	912.0	917.9	912.0
147.5°	699.8	731.3	763.9	793.1	806.5	819.9	842.1	859.6	868.9	871.2	868.9
150°	691.6	719.6	746.4	769.8	780.2	790.7	809.4	824.6	831.6	832.7	831.6
152.5°	682.3	706.8	728.9	749.9	758.1	766.3	781.4	793.1	796.6	797.7	796.6
155°	673.0	693.9	712.6	730.1	737.1	744.1	755.8	765.1	768.6	768.6	768.6
157.5°	663.6	680.0	696.3	711.4	717.2	723.1	732.4	739.4	741.8	741.8	741.8
160°	653.1	667.1	680.0	692.8	697.4	702.1	709.1	716.1	717.3	717.3	717.3
162.5°	643.8	654.3	664.8	674.1	678.2	682.3	686.9	693.9	695.1	693.9	695.1
165°	633.3	642.6	649.6	657.8	660.7	663.6	668.3	673.0	671.8	670.6	671.8
167.5°	624.0	631.0	636.8	643.8	645.6	647.3	649.6	653.1	653.1	652.0	653.1
170°	614.6	620.5	624.0	628.6	630.4	632.1	634.5	635.6	634.5	634.5	634.5
172.5°	606.5	611.1	613.5	615.8	617.0	618.1	619.3	620.5	619.3	617.0	619.3
175°	600.6	603.0	604.1	606.5	606.5	606.5	606.5	608.8	606.5	604.1	606.5
177.5°	596.0	597.1	598.3	598.3	598.9	599.5	598.3	599.5	597.1	594.8	597.1
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1025973

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1841.3	1831.6	1830.2	1830.2	1815.0	1823.3	1806.8	1788.8	1780.5	1780.5	1765.3
5°	1994.5	1984.8	1975.1	1960.0	1960.0	1951.7	1925.5	1899.2	1879.9	1863.3	1845.4
7.5°	2151.8	2142.2	2114.6	2099.4	2107.6	2091.1	2056.6	2012.4	1979.3	1953.1	1915.8
10°	2323.0	2296.7	2282.9	2274.7	2245.7	2227.7	2187.7	2122.8	2081.4	2046.9	1998.6
12.5°	2462.4	2470.7	2418.2	2422.3	2393.4	2368.5	2306.4	2244.3	2182.2	2133.9	2062.1
15°	2612.8	2588.0	2556.2	2531.4	2521.7	2491.4	2438.9	2356.1	2288.5	2212.5	2131.1
17.5°	2731.5	2712.2	2681.8	2658.4	2637.7	2564.5	2520.3	2447.2	2354.7	2280.2	2180.8
20°	2832.3	2814.3	2771.6	2756.4	2719.1	2666.7	2603.2	2490.0	2407.2	2325.7	2229.1
22.5°	2875.1	2857.1	2819.9	2800.5	2777.1	2726.0	2665.3	2557.6	2455.5	2353.3	2251.2
25°	2839.2	2839.2	2821.2	2814.3	2793.6	2748.1	2686.0	2594.9	2485.8	2375.4	2254.0
27.5°	2665.3	2699.8	2712.2	2719.1	2719.1	2720.5	2677.7	2589.4	2483.1	2375.4	2248.4
30°	2414.1	2472.0	2523.1	2538.3	2564.5	2593.5	2611.4	2568.7	2473.4	2360.2	2233.3
32.5°	2098.0	2172.5	2267.8	2291.2	2327.1	2414.1	2462.4	2480.3	2427.9	2328.5	2193.2
35°	1783.3	1877.1	1935.1	2006.9	2040.0	2168.4	2276.0	2340.9	2328.5	2269.1	2146.3
37.5°	1508.6	1562.4	1632.8	1708.8	1775.0	1897.9	2031.7	2157.3	2208.4	2179.4	2086.9
40°	1245.0	1308.5	1392.7	1454.8	1500.3	1623.2	1788.8	1925.5	2037.3	2055.2	1998.6
42.5°	1058.7	1122.1	1173.2	1240.8	1276.7	1395.4	1541.7	1712.9	1845.4	1915.8	1890.9
45°	915.1	953.8	995.2	1033.8	1078.0	1182.9	1318.1	1505.9	1654.9	1754.3	1764.0
47.5°	789.5	824.0	859.9	895.8	920.6	1002.1	1126.3	1279.5	1442.4	1579.0	1632.8
50°	701.2	717.7	744.0	764.7	793.6	864.0	963.4	1095.9	1268.5	1416.1	1486.5
52.5°	614.2	634.9	655.6	673.6	692.9	742.6	833.7	948.2	1097.3	1249.1	1336.1
55°	541.1	557.6	576.9	589.4	600.4	644.6	713.6	801.9	930.3	1073.8	1181.5
57.5°	481.7	488.6	505.2	512.1	524.5	560.4	610.1	688.7	792.3	931.7	1020.0
60°	416.8	430.6	443.1	448.6	458.2	483.1	517.6	590.7	680.5	782.6	883.4
62.5°	364.4	369.9	379.6	386.5	393.4	419.6	448.6	503.8	571.4	657.0	749.5
65°	316.1	318.8	324.4	334.0	338.2	357.5	374.0	414.1	477.6	542.4	634.9
67.5°	266.4	269.1	276.1	281.6	285.7	298.1	316.1	345.1	379.6	451.3	502.4
70°	227.7	227.7	231.9	234.6	238.8	244.3	254.0	276.1	307.8	353.3	400.3
72.5°	190.5	190.5	190.5	194.6	194.6	198.8	204.3	219.5	241.5	277.4	307.8
75°	147.7	149.1	151.8	151.8	153.2	158.7	162.9	167.0	178.1	201.5	229.1
77.5°	111.8	114.6	115.9	113.2	115.9	115.9	121.5	127.0	132.5	139.4	160.1
80°	82.8	84.2	81.4	82.8	82.8	85.6	88.3	87.0	89.7	98.0	103.5
82.5°	55.2	56.6	56.6	56.6	56.6	60.7	60.7	59.4	60.7	62.1	63.5
85°	34.5	33.1	33.1	34.5	33.1	33.1	34.5	35.9	34.5	35.9	37.3
87.5°	15.2	15.2	15.2	15.2	13.8	13.8	15.2	13.8	15.2	13.8	12.4
90°	25.7	24.5	23.3	23.3	23.3	22.2	21.0	19.8	21.0	18.7	16.3
92.5°	110.8	119.0	136.5	151.0	165.6	209.9	281.1	380.2	457.2	400.0	290.4
95°	320.7	356.9	414.0	470.6	527.2	683.4	864.2	977.4	950.5	717.3	438.5
97.5°	746.4	816.4	895.7	961.0	1026.3	1154.6	1244.4	1225.8	1017.0	686.9	400.0
100°	1113.8	1185.0	1286.4	1329.6	1372.7	1429.9	1406.6	1236.3	937.7	608.8	370.9
102.5°	1449.7	1496.4	1548.8	1560.5	1572.2	1537.2	1398.4	1148.8	838.6	556.3	362.7
105°	1664.3	1673.6	1671.3	1647.4	1623.5	1508.0	1306.3	1039.2	765.1	530.7	367.4
107.5°	1742.4	1721.5	1670.1	1621.2	1572.2	1411.2	1193.1	949.4	717.3	523.7	381.4
110°	1723.8	1674.8	1592.0	1527.8	1463.7	1294.6	1092.8	885.2	695.1	526.0	397.7

TEST NUMBER: P1025973

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1636.3	1574.5	1477.7	1413.6	1349.4	1192.0	1019.3	849.1	684.6	533.0	415.2
115°	1529.0	1459.0	1366.9	1310.9	1254.9	1118.5	975.0	829.2	682.3	542.3	433.9
117.5°	1421.7	1361.1	1279.4	1230.4	1181.5	1070.7	949.4	818.7	681.1	551.7	452.5
120°	1335.4	1284.1	1217.6	1176.2	1134.8	1041.5	933.0	810.6	681.1	562.2	472.3
122.5°	1271.3	1229.3	1175.6	1140.6	1105.6	1022.8	919.0	801.2	680.0	572.7	491.0
125°	1228.1	1194.3	1147.6	1115.6	1083.5	1003.0	902.7	790.7	678.8	583.1	509.7
127.5°	1199.0	1168.6	1122.0	1091.6	1061.3	980.9	884.1	776.8	676.5	591.3	526.0
130°	1171.0	1141.8	1094.0	1063.1	1032.2	952.9	860.7	763.9	675.3	600.6	541.2
132.5°	1140.6	1106.8	1060.2	1029.2	998.3	921.4	836.2	752.3	674.1	608.8	556.3
135°	1098.7	1066.0	1019.3	990.2	961.0	889.9	814.1	740.6	673.0	617.0	569.2
137.5°	1053.2	1019.3	975.0	948.2	921.4	859.6	793.1	730.1	673.0	621.6	578.5
140°	998.3	972.7	931.9	907.4	882.9	830.4	775.6	721.9	671.8	627.5	587.8
142.5°	948.2	924.9	889.9	869.5	849.1	805.9	759.3	714.9	671.8	632.1	594.8
145°	900.4	880.6	851.4	835.0	818.7	783.8	744.1	706.8	669.5	633.3	599.5
147.5°	859.6	842.1	819.9	806.5	793.1	763.9	731.3	699.8	666.0	634.5	604.1
150°	824.6	809.4	790.7	780.2	769.8	746.4	719.6	691.6	662.5	634.5	607.6
152.5°	793.1	781.4	766.3	758.1	749.9	728.9	706.8	682.3	656.6	632.1	610.0
155°	765.1	755.8	744.1	737.1	730.1	712.6	693.9	673.0	650.8	629.8	611.1
157.5°	739.4	732.4	723.1	717.2	711.4	696.3	680.0	663.6	645.0	627.5	611.1
160°	716.1	709.1	702.1	697.4	692.8	680.0	667.1	653.1	638.0	624.0	611.1
162.5°	693.9	686.9	682.3	678.2	674.1	664.8	654.3	643.8	631.0	620.5	611.1
165°	673.0	668.3	663.6	660.7	657.8	649.6	642.6	633.3	624.0	615.8	608.8
167.5°	653.1	649.6	647.3	645.6	643.8	636.8	631.0	624.0	617.0	611.1	606.5
170°	635.6	634.5	632.1	630.4	628.6	624.0	620.5	614.6	610.0	606.5	604.1
172.5°	620.5	619.3	618.1	617.0	615.8	613.5	611.1	606.5	603.0	601.8	601.8
175°	608.8	606.5	606.5	606.5	606.5	604.1	603.0	600.6	598.3	598.3	599.5
177.5°	599.5	598.3	599.5	598.9	598.3	598.3	597.1	596.0	594.8	594.8	597.1
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1025973

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1757.1	1750.2	1746.0	1744.6	1732.2	1725.3	1721.2	1718.4	1714.3	1703.2	1693.6
5°	1823.3	1804.0	1794.3	1783.3	1764.0	1741.9	1723.9	1712.9	1699.1	1677.0	1656.3
7.5°	1885.4	1856.4	1837.1	1821.9	1788.8	1752.9	1723.9	1700.5	1674.2	1643.9	1614.9
10°	1950.3	1903.4	1878.5	1855.1	1806.8	1759.8	1718.4	1683.9	1646.6	1606.6	1574.9
12.5°	2001.4	1939.3	1911.7	1878.5	1819.2	1764.0	1711.5	1664.6	1616.3	1573.5	1527.9
15°	2060.7	1983.4	1951.7	1908.9	1827.5	1755.7	1688.1	1637.0	1587.3	1523.8	1475.5
17.5°	2095.2	2005.5	1960.0	1922.7	1834.4	1747.4	1668.7	1605.2	1547.3	1483.8	1432.7
20°	2129.7	2027.6	1976.5	1924.1	1819.2	1726.7	1643.9	1568.0	1507.2	1438.2	1385.8
22.5°	2140.8	2022.1	1968.2	1919.9	1809.5	1706.0	1610.8	1533.5	1463.1	1394.1	1334.7
25°	2140.8	2020.7	1957.2	1895.1	1779.1	1672.9	1577.6	1493.4	1414.8	1345.7	1286.4
27.5°	2118.7	1993.1	1926.8	1870.2	1750.2	1635.6	1537.6	1445.1	1369.2	1300.2	1232.6
30°	2091.1	1953.1	1886.8	1819.2	1703.2	1594.2	1487.9	1402.3	1322.3	1243.6	1182.9
32.5°	2056.6	1910.3	1837.1	1768.1	1645.3	1532.1	1434.1	1349.9	1274.0	1192.5	1124.9
35°	2006.9	1846.8	1765.3	1704.6	1585.9	1468.6	1374.7	1291.9	1218.8	1134.6	1061.4
37.5°	1943.4	1788.8	1706.0	1631.5	1508.6	1401.0	1312.6	1232.6	1160.8	1083.5	1002.1
40°	1868.9	1707.4	1635.6	1556.9	1427.2	1325.0	1242.2	1170.5	1098.7	1025.5	946.9
42.5°	1784.7	1624.6	1544.5	1468.6	1344.4	1243.6	1166.3	1101.4	1035.2	967.6	883.4
45°	1683.9	1533.5	1456.2	1384.4	1264.3	1160.8	1090.4	1028.3	971.7	902.7	828.2
47.5°	1570.7	1439.6	1360.9	1283.6	1166.3	1076.6	1007.6	955.1	906.8	837.8	770.2
50°	1460.3	1330.6	1267.1	1188.4	1080.7	996.5	926.2	882.0	844.7	777.1	716.4
52.5°	1320.9	1222.9	1162.2	1094.5	991.0	905.4	850.2	811.6	767.4	715.0	661.1
55°	1198.1	1107.0	1058.7	995.2	893.0	817.1	770.2	734.3	699.8	652.9	610.1
57.5°	1058.7	1002.1	953.8	898.5	797.8	732.9	691.5	661.1	629.4	590.7	556.2
60°	912.3	886.1	839.2	795.0	709.5	652.9	618.4	590.7	560.4	528.6	499.7
62.5°	782.6	767.4	739.8	705.3	625.3	576.9	542.4	521.7	499.7	470.7	443.1
65°	659.8	652.9	626.6	601.8	546.6	503.8	473.4	461.0	436.2	414.1	389.2
67.5°	550.7	542.4	527.3	516.2	469.3	429.3	414.1	397.5	376.8	360.2	339.5
70°	440.3	438.9	429.3	415.5	390.6	361.6	346.4	335.4	314.7	302.3	287.1
72.5°	342.3	349.2	340.9	335.4	318.8	298.1	284.3	277.4	260.9	251.2	240.2
75°	255.3	260.9	265.0	255.3	251.2	241.5	229.1	222.2	213.9	200.1	196.0
77.5°	173.9	186.3	186.3	189.1	190.5	185.0	175.3	169.8	160.1	157.3	151.8
80°	114.6	125.6	127.0	129.7	133.9	133.9	127.0	125.6	115.9	114.6	110.4
82.5°	66.3	75.9	81.4	85.6	84.2	89.7	84.2	82.8	77.3	77.3	74.5
85°	35.9	37.3	40.0	42.8	45.5	48.3	48.3	46.9	45.5	44.2	41.4
87.5°	13.8	13.8	15.2	13.8	15.2	17.9	19.3	19.3	17.9	16.6	13.8
90°	16.3	9.3	9.3	9.3	8.2	7.0	3.5	1.2	3.5	7.0	8.2
92.5°	177.3	105.0	89.8	74.6	53.6	36.2	23.3	16.3	23.3	36.2	53.6
95°	247.3	145.8	121.3	96.8	68.8	53.6	42.0	38.5	42.0	53.6	68.8
97.5°	235.6	155.1	134.1	113.1	88.6	74.6	64.1	64.1	64.1	74.6	88.6
100°	239.1	170.3	151.6	133.0	110.8	96.8	88.6	88.6	88.6	96.8	110.8
102.5°	250.8	190.1	172.6	155.1	134.1	121.3	114.3	112.0	114.3	121.3	134.1
105°	270.6	214.6	197.7	180.8	159.8	145.8	140.0	136.5	140.0	145.8	159.8
107.5°	291.6	240.3	223.4	206.4	186.6	171.4	165.6	163.3	165.6	171.4	186.6
110°	316.1	264.7	249.0	233.3	212.3	198.3	192.4	190.1	192.4	198.3	212.3

TEST NUMBER: P1025973

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	339.4	290.4	274.6	258.9	237.9	225.1	218.1	215.8	218.1	225.1	237.9
115°	363.9	317.2	301.4	285.7	263.6	251.9	243.8	240.3	243.8	251.9	263.6
117.5°	387.2	342.9	326.5	310.2	289.2	276.4	269.4	265.9	269.4	276.4	289.2
120°	411.7	367.4	351.0	334.7	314.9	302.1	293.9	291.6	293.9	302.1	314.9
122.5°	435.0	390.7	375.0	359.2	337.1	325.4	317.2	314.9	317.2	325.4	337.1
125°	456.0	414.0	397.7	381.4	359.2	346.4	339.4	334.7	339.4	346.4	359.2
127.5°	475.8	435.0	418.7	402.4	379.0	365.1	356.9	353.4	356.9	365.1	379.0
130°	495.7	456.0	439.1	422.2	400.0	382.5	373.2	368.5	373.2	382.5	400.0
132.5°	512.0	472.3	456.6	440.9	416.4	400.0	387.2	383.7	387.2	400.0	416.4
135°	527.2	488.7	473.6	458.4	433.9	414.0	402.4	397.7	402.4	414.0	433.9
137.5°	538.8	502.7	488.1	473.5	447.9	429.2	416.4	411.7	416.4	429.2	447.9
140°	550.5	515.5	501.5	487.5	463.0	443.2	430.4	426.9	430.4	443.2	463.0
142.5°	561.0	527.2	513.8	500.3	477.0	458.4	446.7	443.2	446.7	458.4	477.0
145°	568.0	537.7	524.8	512.0	489.8	473.5	461.9	458.4	461.9	473.5	489.8
147.5°	576.2	547.0	535.4	523.7	505.0	487.5	477.0	475.8	477.0	487.5	505.0
150°	582.0	556.3	545.2	534.2	516.7	502.7	493.3	492.2	493.3	502.7	516.7
152.5°	586.6	564.5	554.6	544.7	529.5	516.7	507.3	507.3	507.3	516.7	529.5
155°	591.3	571.5	562.8	554.0	541.2	529.5	522.5	521.3	522.5	529.5	541.2
157.5°	594.8	577.3	570.3	563.3	551.7	542.3	535.3	535.3	535.3	542.3	551.7
160°	597.1	583.1	576.7	570.3	561.0	552.8	548.2	548.2	548.2	552.8	561.0
162.5°	599.5	586.6	582.0	577.3	569.2	562.2	558.7	559.8	558.7	562.2	569.2
165°	599.5	589.0	585.5	582.0	576.2	570.3	568.0	568.0	568.0	570.3	576.2
167.5°	599.5	591.3	588.4	585.5	582.0	577.3	576.2	577.3	576.2	577.3	582.0
170°	598.3	592.5	590.8	589.0	586.6	583.1	582.0	583.1	582.0	583.1	586.6
172.5°	597.1	593.6	592.4	591.3	590.1	587.8	587.8	589.0	587.8	587.8	590.1
175°	596.0	593.6	593.6	593.6	592.5	591.3	591.3	592.5	591.3	591.3	592.5
177.5°	594.8	593.6	593.6	593.6	593.6	592.5	593.6	594.8	593.6	592.5	593.6
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1025973

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1685.3	1682.5	1679.8	1668.7	1659.1	1642.5	1628.7	1623.2	1621.8	1623.2	1619.0
5°	1637.0	1635.6	1625.9	1606.6	1588.7	1569.3	1555.5	1541.7	1533.5	1533.5	1523.8
7.5°	1591.4	1581.8	1573.5	1548.6	1527.9	1501.7	1481.0	1468.6	1461.7	1446.5	1446.5
10°	1543.1	1529.3	1518.3	1494.8	1464.5	1438.2	1412.0	1396.8	1384.4	1373.4	1369.2
12.5°	1494.8	1483.8	1463.1	1438.2	1407.9	1374.7	1347.1	1336.1	1307.1	1283.6	1285.0
15°	1449.3	1424.4	1414.8	1378.9	1343.0	1311.2	1271.2	1239.5	1216.0	1200.8	1181.5
17.5°	1398.2	1373.4	1355.4	1325.0	1278.1	1228.4	1189.8	1147.0	1123.5	1097.3	1084.9
20°	1341.6	1320.9	1307.1	1258.8	1202.2	1142.9	1100.1	1073.8	1047.6	1028.3	1017.2
22.5°	1293.3	1267.1	1250.5	1185.6	1123.5	1064.2	1031.1	1009.0	986.9	970.3	964.8
25°	1231.2	1216.0	1176.0	1119.4	1043.5	1003.4	974.5	945.5	933.1	922.0	909.6
27.5°	1180.1	1142.9	1115.2	1040.7	993.8	948.2	919.2	897.2	882.0	870.9	861.3
30°	1116.6	1082.1	1043.5	981.4	938.6	895.8	869.6	851.6	835.1	828.2	819.9
32.5°	1050.4	1018.6	981.4	931.7	879.2	846.1	825.4	806.1	795.0	788.1	778.5
35°	991.0	951.0	926.2	879.2	836.4	799.2	779.8	763.3	750.9	748.1	746.7
37.5°	927.5	897.2	873.7	825.4	789.5	757.8	739.8	721.9	715.0	713.6	708.1
40°	872.3	846.1	824.0	778.5	739.8	710.8	697.0	686.0	679.1	679.1	677.7
42.5°	824.0	796.4	774.3	732.9	698.4	672.2	657.0	646.0	643.2	644.6	643.2
45°	770.2	746.7	724.6	681.8	652.9	633.5	617.0	611.5	607.3	608.7	610.1
47.5°	719.1	699.8	677.7	643.2	610.1	589.4	579.7	574.2	574.2	574.2	576.9
50°	673.6	651.5	632.2	596.3	565.9	549.3	541.1	534.2	535.5	536.9	538.3
52.5°	619.7	600.4	586.6	550.7	528.6	507.9	498.3	499.7	498.3	498.3	501.0
55°	572.8	553.5	539.7	506.6	484.5	470.7	462.4	458.2	459.6	456.9	462.4
57.5°	520.4	503.8	494.1	462.4	443.1	430.6	423.7	416.8	419.6	418.2	416.8
60°	474.8	455.5	440.3	418.2	401.7	386.5	382.3	375.4	378.2	375.4	374.0
62.5°	422.4	407.2	396.1	374.0	360.2	347.8	338.2	334.0	332.6	328.5	324.4
65°	369.9	361.6	350.6	328.5	314.7	305.0	299.5	295.4	294.0	283.0	270.5
67.5°	321.6	316.1	305.0	288.5	276.1	266.4	258.1	251.2	242.9	234.6	227.7
70°	276.1	267.8	260.9	245.7	234.6	225.0	216.7	208.4	204.3	196.0	193.2
72.5°	231.9	223.6	216.7	202.9	193.2	183.6	180.8	171.2	167.0	165.6	165.6
75°	186.3	179.4	175.3	162.9	154.6	147.7	143.5	140.8	138.0	135.3	131.1
77.5°	142.2	138.0	135.3	127.0	120.1	115.9	114.6	104.9	102.1	99.4	96.6
80°	103.5	102.1	99.4	92.5	89.7	80.1	80.1	77.3	75.9	75.9	75.9
82.5°	70.4	67.6	66.3	59.4	58.0	56.6	55.2	53.8	55.2	53.8	55.2
85°	37.3	35.9	34.5	34.5	34.5	34.5	34.5	34.5	34.5	33.1	34.5
87.5°	13.8	13.8	13.8	13.8	12.4	13.8	13.8	12.4	13.8	13.8	13.8
90°	9.3	9.3	9.3	16.3	16.3	18.7	21.0	19.8	21.0	22.2	23.3
92.5°	74.6	89.8	105.0	177.3	290.4	400.0	457.2	380.2	281.1	209.9	165.6
95°	96.8	121.3	145.8	247.3	438.5	717.3	950.5	977.4	864.2	683.4	527.2
97.5°	113.1	134.1	155.1	235.6	400.0	686.9	1017.0	1225.8	1244.4	1154.6	1026.3
100°	133.0	151.6	170.3	239.1	370.9	608.8	937.7	1236.3	1406.6	1429.9	1372.7
102.5°	155.1	172.6	190.1	250.8	362.7	556.3	838.6	1148.8	1398.4	1537.2	1572.2
105°	180.8	197.7	214.6	270.6	367.4	530.7	765.1	1039.2	1306.3	1508.0	1623.5
107.5°	206.4	223.4	240.3	291.6	381.4	523.7	717.3	949.4	1193.1	1411.2	1572.2
110°	233.3	249.0	264.7	316.1	397.7	526.0	695.1	885.2	1092.8	1294.6	1463.7

TEST NUMBER: P1025973

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	258.9	274.6	290.4	339.4	415.2	533.0	684.6	849.1	1019.3	1192.0	1349.4
115°	285.7	301.4	317.2	363.9	433.9	542.3	682.3	829.2	975.0	1118.5	1254.9
117.5°	310.2	326.5	342.9	387.2	452.5	551.7	681.1	818.7	949.4	1070.7	1181.5
120°	334.7	351.0	367.4	411.7	472.3	562.2	681.1	810.6	933.0	1041.5	1134.8
122.5°	359.2	375.0	390.7	435.0	491.0	572.7	680.0	801.2	919.0	1022.8	1105.6
125°	381.4	397.7	414.0	456.0	509.7	583.1	678.8	790.7	902.7	1003.0	1083.5
127.5°	402.4	418.7	435.0	475.8	526.0	591.3	676.5	776.8	884.1	980.9	1061.3
130°	422.2	439.1	456.0	495.7	541.2	600.6	675.3	763.9	860.7	952.9	1032.2
132.5°	440.9	456.6	472.3	512.0	556.3	608.8	674.1	752.3	836.2	921.4	998.3
135°	458.4	473.6	488.7	527.2	569.2	617.0	673.0	740.6	814.1	889.9	961.0
137.5°	473.5	488.1	502.7	538.8	578.5	621.6	673.0	730.1	793.1	859.6	921.4
140°	487.5	501.5	515.5	550.5	587.8	627.5	671.8	721.9	775.6	830.4	882.9
142.5°	500.3	513.8	527.2	561.0	594.8	632.1	671.8	714.9	759.3	805.9	849.1
145°	512.0	524.8	537.7	568.0	599.5	633.3	669.5	706.8	744.1	783.8	818.7
147.5°	523.7	535.4	547.0	576.2	604.1	634.5	666.0	699.8	731.3	763.9	793.1
150°	534.2	545.2	556.3	582.0	607.6	634.5	662.5	691.6	719.6	746.4	769.8
152.5°	544.7	554.6	564.5	586.6	610.0	632.1	656.6	682.3	706.8	728.9	749.9
155°	554.0	562.8	571.5	591.3	611.1	629.8	650.8	673.0	693.9	712.6	730.1
157.5°	563.3	570.3	577.3	594.8	611.1	627.5	645.0	663.6	680.0	696.3	711.4
160°	570.3	576.7	583.1	597.1	611.1	624.0	638.0	653.1	667.1	680.0	692.8
162.5°	577.3	582.0	586.6	599.5	611.1	620.5	631.0	643.8	654.3	664.8	674.1
165°	582.0	585.5	589.0	599.5	608.8	615.8	624.0	633.3	642.6	649.6	657.8
167.5°	585.5	588.4	591.3	599.5	606.5	611.1	617.0	624.0	631.0	636.8	643.8
170°	589.0	590.8	592.5	598.3	604.1	606.5	610.0	614.6	620.5	624.0	628.6
172.5°	591.3	592.4	593.6	597.1	601.8	601.8	603.0	606.5	611.1	613.5	615.8
175°	593.6	593.6	593.6	596.0	599.5	598.3	598.3	600.6	603.0	604.1	606.5
177.5°	593.6	593.6	593.6	594.8	597.1	594.8	594.8	596.0	597.1	598.3	598.3
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1025973

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1619.0	1624.6	1617.7	1621.8	1612.1	1610.8	1612.1	1612.1	1613.5	1614.9	1616.3
5°	1527.9	1526.6	1518.3	1512.8	1508.6	1512.8	1515.5	1518.3	1515.5	1518.3	1519.7
7.5°	1442.4	1438.2	1434.1	1424.4	1427.2	1424.4	1432.7	1428.6	1428.6	1435.5	1441.0
10°	1366.5	1358.2	1355.4	1344.4	1336.1	1334.7	1344.4	1348.5	1352.6	1355.4	1366.5
12.5°	1268.5	1256.0	1246.4	1250.5	1227.0	1236.7	1239.5	1233.9	1250.5	1269.8	1258.8
15°	1163.6	1164.9	1145.6	1138.7	1119.4	1124.9	1126.3	1140.1	1153.9	1152.5	1169.1
17.5°	1086.3	1078.0	1061.4	1060.0	1051.8	1055.9	1054.5	1065.6	1061.4	1068.3	1082.1
20°	1014.5	1009.0	995.2	989.6	992.4	989.6	991.0	992.4	996.5	1011.7	1009.0
22.5°	957.9	951.0	951.0	944.1	935.8	933.1	940.0	944.1	949.6	952.4	959.3
25°	908.2	902.7	895.8	891.6	884.7	886.1	890.3	895.8	899.9	905.4	911.0
27.5°	857.1	857.1	850.2	848.9	846.1	844.7	850.2	853.0	853.0	857.1	862.7
30°	817.1	817.1	810.2	808.8	807.4	807.4	811.6	813.0	814.4	818.5	821.3
32.5°	778.5	777.1	774.3	775.7	774.3	775.7	775.7	777.1	779.8	781.2	786.7
35°	742.6	744.0	741.2	741.2	739.8	741.2	744.0	745.3	746.7	749.5	749.5
37.5°	708.1	710.8	709.5	713.6	713.6	713.6	713.6	716.4	716.4	716.4	715.0
40°	677.7	677.7	676.3	679.1	681.8	681.8	683.2	683.2	684.6	684.6	683.2
42.5°	643.2	646.0	650.1	651.5	654.2	652.9	657.0	655.6	657.0	654.2	651.5
45°	611.5	611.5	617.0	622.5	623.9	623.9	623.9	626.6	623.9	619.7	618.4
47.5°	576.9	579.7	582.5	589.4	590.7	590.7	590.7	590.7	588.0	588.0	588.0
50°	542.4	543.8	545.2	548.0	552.1	550.7	550.7	550.7	556.2	550.7	552.1
52.5°	501.0	502.4	503.8	509.3	507.9	507.9	509.3	509.3	513.5	512.1	509.3
55°	459.6	459.6	462.4	462.4	462.4	465.1	466.5	469.3	467.9	469.3	470.7
57.5°	418.2	415.5	414.1	414.1	418.2	416.8	418.2	418.2	423.7	426.5	427.9
60°	369.9	369.9	368.5	360.2	360.2	358.9	363.0	365.8	368.5	381.0	379.6
62.5°	320.2	314.7	309.2	310.6	302.3	306.4	303.7	306.4	314.7	324.4	325.7
65°	270.5	266.4	260.9	259.5	256.7	260.9	259.5	260.9	265.0	270.5	277.4
67.5°	226.4	225.0	222.2	220.8	220.8	220.8	223.6	223.6	225.0	229.1	233.3
70°	193.2	191.9	193.2	190.5	191.9	190.5	191.9	193.2	194.6	196.0	200.1
72.5°	162.9	162.9	162.9	160.1	162.9	161.5	161.5	162.9	164.3	165.6	168.4
75°	129.7	127.0	124.2	121.5	120.1	122.8	124.2	122.8	127.0	132.5	132.5
77.5°	98.0	96.6	96.6	96.6	98.0	96.6	99.4	98.0	99.4	99.4	102.1
80°	75.9	74.5	75.9	75.9	74.5	77.3	75.9	75.9	77.3	78.7	77.3
82.5°	55.2	56.6	55.2	55.2	55.2	58.0	55.2	55.2	55.2	56.6	56.6
85°	34.5	34.5	34.5	34.5	35.9	34.5	35.9	34.5	37.3	35.9	35.9
87.5°	12.4	13.8	15.2	15.2	15.2	15.2	13.8	15.2	16.6	15.2	16.6
90°	23.3	23.3	24.5	25.7	24.5	24.5	24.5	25.7	24.5	23.3	23.3
92.5°	151.0	136.5	119.0	110.8	106.1	106.1	106.1	110.8	119.0	136.5	151.0
95°	470.6	414.0	356.9	320.7	299.7	284.6	299.7	320.7	356.9	414.0	470.6
97.5°	961.0	895.7	816.4	746.4	711.4	683.4	711.4	746.4	816.4	895.7	961.0
100°	1329.6	1286.4	1185.0	1113.8	1078.8	1069.5	1078.8	1113.8	1185.0	1286.4	1329.6
102.5°	1560.5	1548.8	1496.4	1449.7	1412.4	1405.4	1412.4	1449.7	1496.4	1548.8	1560.5
105°	1647.4	1671.3	1673.6	1664.3	1648.0	1641.0	1648.0	1664.3	1673.6	1671.3	1647.4
107.5°	1621.2	1670.1	1721.5	1742.4	1751.8	1752.9	1751.8	1742.4	1721.5	1670.1	1621.2
110°	1527.8	1592.0	1674.8	1723.8	1744.8	1755.3	1744.8	1723.8	1674.8	1592.0	1527.8

TEST NUMBER: P1025973

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1413.6	1477.7	1574.5	1636.3	1667.8	1686.5	1667.8	1636.3	1574.5	1477.7	1413.6
115°	1310.9	1366.9	1459.0	1529.0	1566.3	1575.7	1566.3	1529.0	1459.0	1366.9	1310.9
117.5°	1230.4	1279.4	1361.1	1421.7	1461.4	1467.2	1461.4	1421.7	1361.1	1279.4	1230.4
120°	1176.2	1217.6	1284.1	1335.4	1365.7	1378.6	1365.7	1335.4	1284.1	1217.6	1176.2
122.5°	1140.6	1175.6	1229.3	1271.3	1295.8	1308.6	1295.8	1271.3	1229.3	1175.6	1140.6
125°	1115.6	1147.6	1194.3	1228.1	1250.3	1257.3	1250.3	1228.1	1194.3	1147.6	1115.6
127.5°	1091.6	1122.0	1168.6	1199.0	1217.6	1224.6	1217.6	1199.0	1168.6	1122.0	1091.6
130°	1063.1	1094.0	1141.8	1171.0	1189.6	1196.6	1189.6	1171.0	1141.8	1094.0	1063.1
132.5°	1029.2	1060.2	1106.8	1140.6	1158.1	1165.1	1158.1	1140.6	1106.8	1060.2	1029.2
135°	990.2	1019.3	1066.0	1098.7	1117.3	1124.3	1117.3	1098.7	1066.0	1019.3	990.2
137.5°	948.2	975.0	1019.3	1053.2	1068.3	1076.5	1068.3	1053.2	1019.3	975.0	948.2
140°	907.4	931.9	972.7	998.3	1014.7	1024.0	1014.7	998.3	972.7	931.9	907.4
142.5°	869.5	889.9	924.9	948.2	962.2	968.0	962.2	948.2	924.9	889.9	869.5
145°	835.0	851.4	880.6	900.4	912.0	917.9	912.0	900.4	880.6	851.4	835.0
147.5°	806.5	819.9	842.1	859.6	868.9	871.2	868.9	859.6	842.1	819.9	806.5
150°	780.2	790.7	809.4	824.6	831.6	832.7	831.6	824.6	809.4	790.7	780.2
152.5°	758.1	766.3	781.4	793.1	796.6	797.7	796.6	793.1	781.4	766.3	758.1
155°	737.1	744.1	755.8	765.1	768.6	768.6	768.6	765.1	755.8	744.1	737.1
157.5°	717.2	723.1	732.4	739.4	741.8	741.8	741.8	739.4	732.4	723.1	717.2
160°	697.4	702.1	709.1	716.1	717.3	717.3	717.3	716.1	709.1	702.1	697.4
162.5°	678.2	682.3	686.9	693.9	695.1	693.9	695.1	693.9	686.9	682.3	678.2
165°	660.7	663.6	668.3	673.0	671.8	670.6	671.8	673.0	668.3	663.6	660.7
167.5°	645.6	647.3	649.6	653.1	653.1	652.0	653.1	653.1	649.6	647.3	645.6
170°	630.4	632.1	634.5	635.6	634.5	634.5	634.5	635.6	634.5	632.1	630.4
172.5°	617.0	618.1	619.3	620.5	619.3	617.0	619.3	620.5	619.3	618.1	617.0
175°	606.5	606.5	606.5	608.8	606.5	604.1	606.5	608.8	606.5	606.5	606.5
177.5°	598.9	599.5	598.3	599.5	597.1	594.8	597.1	599.5	598.3	599.5	598.9
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1025973

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1621.8	1628.7	1625.9	1616.3	1620.4	1628.7	1637.0	1648.0	1654.9	1660.4	1663.2
5°	1526.6	1539.0	1536.2	1536.2	1541.7	1555.5	1569.3	1592.8	1601.1	1610.8	1624.6
7.5°	1442.4	1452.0	1460.3	1463.1	1471.4	1489.3	1507.2	1533.5	1554.2	1565.2	1573.5
10°	1367.8	1374.7	1387.2	1394.1	1402.3	1424.4	1450.6	1478.3	1499.0	1518.3	1529.3
12.5°	1272.6	1300.2	1316.8	1327.8	1338.8	1372.0	1392.7	1423.0	1447.9	1465.8	1482.4
15°	1166.3	1199.4	1209.1	1251.9	1279.5	1305.7	1337.5	1373.4	1396.8	1417.5	1439.6
17.5°	1076.6	1100.1	1111.1	1156.7	1180.1	1221.5	1267.1	1312.6	1348.5	1363.7	1385.8
20°	1020.0	1032.4	1054.5	1069.7	1094.5	1142.9	1192.5	1247.8	1301.6	1316.8	1338.8
22.5°	962.0	978.6	993.8	1014.5	1033.8	1066.9	1116.6	1177.4	1235.3	1262.9	1289.2
25°	909.6	926.2	935.8	957.9	975.8	1009.0	1043.5	1105.6	1174.6	1198.1	1239.5
27.5°	868.2	877.8	894.4	904.1	924.8	955.1	986.9	1033.8	1101.4	1141.5	1181.5
30°	826.8	833.7	847.5	861.3	876.5	897.2	933.1	978.6	1040.7	1075.2	1115.2
32.5°	785.4	796.4	804.7	814.4	830.9	855.8	880.6	924.8	974.5	1013.1	1053.1
35°	750.9	755.0	766.0	777.1	788.1	810.2	836.4	879.2	923.4	953.8	989.6
37.5°	713.6	720.5	728.8	732.9	750.9	764.7	792.3	825.4	877.8	897.2	933.1
40°	684.6	683.2	691.5	698.4	706.7	728.8	745.3	781.2	822.6	853.0	875.1
42.5°	648.7	648.7	651.5	659.8	670.8	684.6	703.9	734.3	777.1	799.2	825.4
45°	619.7	615.6	617.0	622.5	629.4	643.2	662.5	688.7	731.5	749.5	777.1
47.5°	585.2	581.1	581.1	586.6	592.1	601.8	617.0	647.3	681.8	705.3	726.0
50°	546.6	548.0	546.6	550.7	553.5	563.1	579.7	604.6	636.3	655.6	679.1
52.5°	510.7	507.9	506.6	509.3	514.8	521.7	539.7	561.8	592.1	611.5	632.2
55°	466.5	469.3	469.3	469.3	477.6	480.3	494.1	516.2	546.6	561.8	581.1
57.5°	426.5	425.1	427.9	426.5	433.4	443.1	454.1	470.7	501.0	516.2	534.2
60°	382.3	383.7	385.1	385.1	390.6	400.3	412.7	427.9	452.7	467.9	484.5
62.5°	328.5	335.4	342.3	345.1	353.3	360.2	368.5	385.1	407.2	418.2	433.4
65°	277.4	287.1	296.8	303.7	309.2	316.1	327.1	342.3	360.2	371.3	386.5
67.5°	233.3	240.2	252.6	259.5	270.5	278.8	285.7	298.1	320.2	324.4	336.8
70°	201.5	204.3	209.8	215.3	227.7	234.6	242.9	255.3	271.9	281.6	288.5
72.5°	169.8	171.2	173.9	179.4	185.0	193.2	202.9	213.9	229.1	233.3	242.9
75°	135.3	143.5	143.5	147.7	151.8	156.0	164.3	175.3	185.0	191.9	197.4
77.5°	100.8	104.9	107.7	114.6	120.1	124.2	129.7	138.0	143.5	149.1	153.2
80°	78.7	80.1	81.4	81.4	84.2	89.7	95.2	100.8	107.7	110.4	114.6
82.5°	58.0	58.0	58.0	60.7	62.1	63.5	63.5	66.3	73.2	75.9	80.1
85°	37.3	37.3	37.3	37.3	38.6	40.0	41.4	42.8	42.8	42.8	45.5
87.5°	15.2	17.9	16.6	17.9	17.9	17.9	17.9	19.3	19.3	20.7	20.7
90°	23.3	22.2	21.0	19.8	21.0	18.7	16.3	16.3	9.3	9.3	9.3
92.5°	165.6	209.9	281.1	380.2	457.2	400.0	290.4	177.3	105.0	89.8	74.6
95°	527.2	683.4	864.2	977.4	950.5	717.3	438.5	247.3	145.8	121.3	96.8
97.5°	1026.3	1154.6	1244.4	1225.8	1017.0	686.9	400.0	235.6	155.1	134.1	113.1
100°	1372.7	1429.9	1406.6	1236.3	937.7	608.8	370.9	239.1	170.3	151.6	133.0
102.5°	1572.2	1537.2	1398.4	1148.8	838.6	556.3	362.7	250.8	190.1	172.6	155.1
105°	1623.5	1508.0	1306.3	1039.2	765.1	530.7	367.4	270.6	214.6	197.7	180.8
107.5°	1572.2	1411.2	1193.1	949.4	717.3	523.7	381.4	291.6	240.3	223.4	206.4
110°	1463.7	1294.6	1092.8	885.2	695.1	526.0	397.7	316.1	264.7	249.0	233.3

TEST NUMBER: P1025973

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1349.4	1192.0	1019.3	849.1	684.6	533.0	415.2	339.4	290.4	274.6	258.9
115°	1254.9	1118.5	975.0	829.2	682.3	542.3	433.9	363.9	317.2	301.4	285.7
117.5°	1181.5	1070.7	949.4	818.7	681.1	551.7	452.5	387.2	342.9	326.5	310.2
120°	1134.8	1041.5	933.0	810.6	681.1	562.2	472.3	411.7	367.4	351.0	334.7
122.5°	1105.6	1022.8	919.0	801.2	680.0	572.7	491.0	435.0	390.7	375.0	359.2
125°	1083.5	1003.0	902.7	790.7	678.8	583.1	509.7	456.0	414.0	397.7	381.4
127.5°	1061.3	980.9	884.1	776.8	676.5	591.3	526.0	475.8	435.0	418.7	402.4
130°	1032.2	952.9	860.7	763.9	675.3	600.6	541.2	495.7	456.0	439.1	422.2
132.5°	998.3	921.4	836.2	752.3	674.1	608.8	556.3	512.0	472.3	456.6	440.9
135°	961.0	889.9	814.1	740.6	673.0	617.0	569.2	527.2	488.7	473.6	458.4
137.5°	921.4	859.6	793.1	730.1	673.0	621.6	578.5	538.8	502.7	488.1	473.5
140°	882.9	830.4	775.6	721.9	671.8	627.5	587.8	550.5	515.5	501.5	487.5
142.5°	849.1	805.9	759.3	714.9	671.8	632.1	594.8	561.0	527.2	513.8	500.3
145°	818.7	783.8	744.1	706.8	669.5	633.3	599.5	568.0	537.7	524.8	512.0
147.5°	793.1	763.9	731.3	699.8	666.0	634.5	604.1	576.2	547.0	535.4	523.7
150°	769.8	746.4	719.6	691.6	662.5	634.5	607.6	582.0	556.3	545.2	534.2
152.5°	749.9	728.9	706.8	682.3	656.6	632.1	610.0	586.6	564.5	554.6	544.7
155°	730.1	712.6	693.9	673.0	650.8	629.8	611.1	591.3	571.5	562.8	554.0
157.5°	711.4	696.3	680.0	663.6	645.0	627.5	611.1	594.8	577.3	570.3	563.3
160°	692.8	680.0	667.1	653.1	638.0	624.0	611.1	597.1	583.1	576.7	570.3
162.5°	674.1	664.8	654.3	643.8	631.0	620.5	611.1	599.5	586.6	582.0	577.3
165°	657.8	649.6	642.6	633.3	624.0	615.8	608.8	599.5	589.0	585.5	582.0
167.5°	643.8	636.8	631.0	624.0	617.0	611.1	606.5	599.5	591.3	588.4	585.5
170°	628.6	624.0	620.5	614.6	610.0	606.5	604.1	598.3	592.5	590.8	589.0
172.5°	615.8	613.5	611.1	606.5	603.0	601.8	601.8	597.1	593.6	592.4	591.3
175°	606.5	604.1	603.0	600.6	598.3	598.3	599.5	596.0	593.6	593.6	593.6
177.5°	598.3	598.3	597.1	596.0	594.8	594.8	597.1	594.8	593.6	593.6	593.6
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1025973

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1712.9	1712.9	1712.9	1712.9
2.5°	1674.2	1682.5	1696.3	1715.7
5°	1635.6	1659.1	1681.2	1710.1
7.5°	1601.1	1628.7	1659.1	1700.5
10°	1561.1	1595.6	1634.2	1685.3
12.5°	1514.1	1562.4	1606.6	1661.8
15°	1479.6	1515.5	1572.1	1637.0
17.5°	1431.3	1479.6	1536.2	1609.4
20°	1385.8	1436.8	1500.3	1576.3
22.5°	1337.5	1395.4	1458.9	1540.4
25°	1287.8	1349.9	1413.4	1500.3
27.5°	1242.2	1298.8	1370.6	1458.9
30°	1187.0	1251.9	1320.9	1413.4
32.5°	1133.2	1200.8	1271.2	1363.7
35°	1075.2	1142.9	1220.1	1308.5
37.5°	1018.6	1093.2	1163.6	1249.1
40°	956.5	1033.8	1107.0	1193.9
42.5°	895.8	975.8	1049.0	1123.5
45°	839.2	917.9	984.1	1054.5
47.5°	785.4	855.8	923.4	986.9
50°	732.9	792.3	854.4	906.8
52.5°	677.7	734.3	784.0	830.9
55°	628.0	672.2	716.4	759.1
57.5°	568.7	612.8	651.5	684.6
60°	519.0	546.6	583.8	618.4
62.5°	462.4	494.1	523.1	545.2
65°	407.2	434.8	456.9	476.2
67.5°	360.2	376.8	393.4	414.1
70°	303.7	317.5	336.8	352.0
72.5°	255.3	266.4	276.1	294.0
75°	207.0	216.7	222.2	238.8
77.5°	160.1	169.8	173.9	183.6
80°	122.8	124.2	129.7	138.0
82.5°	84.2	87.0	88.3	95.2
85°	48.3	55.2	53.8	56.6
87.5°	20.7	22.1	24.8	27.6
90°	8.2	7.0	3.5	1.2
92.5°	53.6	36.2	23.3	16.3
95°	68.8	53.6	42.0	38.5
97.5°	88.6	74.6	64.1	64.1
100°	110.8	96.8	88.6	88.6
102.5°	134.1	121.3	114.3	112.0
105°	159.8	145.8	140.0	136.5
107.5°	186.6	171.4	165.6	163.3
110°	212.3	198.3	192.4	190.1

TEST NUMBER: P1025973

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	237.9	225.1	218.1	215.8
115°	263.6	251.9	243.8	240.3
117.5°	289.2	276.4	269.4	265.9
120°	314.9	302.1	293.9	291.6
122.5°	337.1	325.4	317.2	314.9
125°	359.2	346.4	339.4	334.7
127.5°	379.0	365.1	356.9	353.4
130°	400.0	382.5	373.2	368.5
132.5°	416.4	400.0	387.2	383.7
135°	433.9	414.0	402.4	397.7
137.5°	447.9	429.2	416.4	411.7
140°	463.0	443.2	430.4	426.9
142.5°	477.0	458.4	446.7	443.2
145°	489.8	473.5	461.9	458.4
147.5°	505.0	487.5	477.0	475.8
150°	516.7	502.7	493.3	492.2
152.5°	529.5	516.7	507.3	507.3
155°	541.2	529.5	522.5	521.3
157.5°	551.7	542.3	535.3	535.3
160°	561.0	552.8	548.2	548.2
162.5°	569.2	562.2	558.7	559.8
165°	576.2	570.3	568.0	568.0
167.5°	582.0	577.3	576.2	577.3
170°	586.6	583.1	582.0	583.1
172.5°	590.1	587.8	587.8	589.0
175°	592.5	591.3	591.3	592.5
177.5°	593.6	592.5	593.6	594.8
180°	593.6	593.6	593.6	593.6

(END OF REPORT)