

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025975

Luminaire Tested: S124RDIP-B1020D1205UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025975
REPORT IS A COMBINATION OF REPORTS P998885 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1020D1205UB35-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8352.0 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025975

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1025975

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	90	87	90	87	83	81	73	71	69	61	60	58	50	49	48
2	89	82	76	71	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	72	65	60	75	67	61	56	57	53	49	48	45	42	39	37	35
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	33	30
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	27
6	63	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23
7	59	47	39	33	54	43	36	31	37	32	28	32	28	24	27	23	21
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	23	19	17
10	48	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14699	14699	14699
5°	14700	14262	14264
10°	14576	13812	13648
15°	14375	13252	12922
20°	14113	12613	12093
25°	13785	11923	11284
30°	13464	11220	10375
35°	13112	10508	9487
40°	12692	9740	8574
45°	12298	8979	7671
50°	11851	8148	6753
55°	11367	7296	5807
60°	10831	6391	4872
65°	10312	5353	3970
70°	9575	4261	3035
75°	8631	3101	2122
80°	7210	1904	1525
85°	5421	1097	838

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12298 cd/sqm

TEST NUMBER: P1025975

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.5	2.0
10°-20°	472.6	5.7
20°-30°	682.3	8.2
30°-40°	773.3	9.3
40°-50°	746.6	8.9
50°-60°	620.7	7.4
60°-70°	428.4	5.1
70°-80°	216.5	2.6
80°-90°	58.2	0.7
90°-100°	98.3	1.2
100°-110°	294.4	3.5
110°-120°	500.1	6.0
120°-130°	659.6	7.9
130°-140°	740.8	8.9
140°-150°	728.1	8.7
150°-160°	612.4	7.3
160°-170°	407.5	4.9
170°-180°	142.7	1.7
0°-30°	1324.4	15.9
0°-40°	2097.7	25.1
0°-60°	3465.1	41.5
0°-90°	4168.2	49.9
90°-120°	892.8	10.7
90°-150°	3021.3	36.2
90°-180°	4184.0	50.1
0°-180°	8352.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1803	1803	1803	1803	1803	
5°	1800	1794	1778	1792	1789	171
15°	1714	1702	1667	1664	1655	483
25°	1550	1525	1468	1445	1431	714
35°	1340	1296	1227	1180	1155	838
45°	1093	1042	959	892	867	843
55°	828	773	683	611	585	741
65°	563	504	415	356	340	556
75°	300	248	184	152	144	316
85°	74	47	43	40	40	82
90°	4	16	26	33	35	9
95°	70	80	89	92	92	76
105°	272	273	278	281	284	288
115°	508	508	506	505	504	501
125°	740	740	739	737	735	660
135°	955	962	962	960	956	739
145°	1160	1165	1166	1165	1162	726
155°	1329	1329	1328	1333	1328	612
165°	1447	1444	1441	1448	1444	408
175°	1506	1500	1498	1507	1498	143
180°	1508	1508	1508	1508	1508	

TEST NUMBER: P1025975

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1802.6	1802.6	1802.6	1802.6	1802.6
2.5°	1808.1	1802.6	1787.4	1802.6	1801.2
5°	1799.8	1794.3	1777.7	1791.5	1788.8
7.5°	1787.4	1781.9	1761.2	1770.8	1766.7
10°	1768.1	1761.2	1736.3	1741.8	1736.3
12.5°	1743.2	1734.9	1704.6	1707.3	1699.0
15°	1714.2	1701.8	1667.3	1664.5	1654.9
17.5°	1681.1	1663.2	1623.1	1616.2	1602.4
20°	1641.1	1623.1	1576.2	1565.2	1547.2
22.5°	1596.9	1576.2	1525.1	1507.2	1493.4
25°	1550.0	1525.1	1468.5	1445.1	1431.3
27.5°	1501.7	1471.3	1412.0	1384.4	1365.0
30°	1450.6	1416.1	1351.2	1316.7	1294.6
32.5°	1396.8	1356.7	1289.1	1247.7	1227.0
35°	1340.2	1296.0	1227.0	1180.1	1155.2
37.5°	1280.8	1235.3	1159.4	1108.3	1083.5
40°	1217.3	1171.8	1093.1	1035.2	1010.3
42.5°	1156.6	1108.3	1025.5	966.1	939.9
45°	1093.1	1042.1	959.2	891.6	866.8
47.5°	1028.3	975.8	890.2	819.8	792.2
50°	962.0	908.2	819.8	750.8	724.6
52.5°	894.4	841.9	750.8	680.4	652.8
55°	828.1	772.9	683.2	611.4	585.2
57.5°	763.3	705.3	617.0	543.8	524.5
60°	692.9	637.7	549.3	477.6	455.5
62.5°	629.4	571.4	480.3	415.4	398.9
65°	563.1	503.8	415.4	356.1	339.5
67.5°	494.1	437.5	354.7	302.3	282.9
70°	429.2	371.3	292.6	247.1	233.3
72.5°	360.2	309.2	236.0	198.8	186.3
75°	299.5	248.4	183.6	151.8	143.5
77.5°	236.0	191.8	136.6	114.6	111.8
80°	175.3	135.3	93.9	89.7	88.3
82.5°	122.8	87.0	67.6	64.9	63.5
85°	74.5	46.9	42.8	40.0	40.0
87.5°	31.7	20.7	19.3	17.9	19.3
90°	3.5	16.3	25.7	32.7	35.0
92.5°	30.3	45.5	51.3	54.8	56.0
95°	70.0	80.5	88.6	92.1	92.1
97.5°	112.0	121.3	130.6	135.3	135.3
100°	163.3	167.9	178.4	180.8	180.8
102.5°	216.9	218.1	227.4	230.9	232.1
105°	271.7	272.9	277.6	281.0	284.5
107.5°	328.9	330.0	331.2	335.9	334.7
110°	387.2	389.5	388.3	386.0	389.5

TEST NUMBER: P1025975

CATALOG NUMBER: S124RDIP-B1020D1205UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	447.8	447.8	445.5	445.5	445.5
115°	508.5	508.5	506.1	505.0	503.8
117.5°	565.6	565.6	564.4	560.9	557.4
120°	622.7	627.4	623.9	618.1	620.4
122.5°	682.2	683.4	682.2	678.7	672.9
125°	740.5	740.5	739.4	737.0	734.7
127.5°	793.0	796.5	794.2	791.8	790.7
130°	849.0	852.5	852.5	850.1	845.5
132.5°	906.1	908.5	907.3	905.0	903.8
135°	955.1	962.1	962.1	959.8	956.3
137.5°	1009.9	1013.4	1015.7	1012.2	1013.4
140°	1064.7	1067.1	1067.1	1065.9	1064.7
142.5°	1114.9	1117.2	1116.0	1116.0	1116.0
145°	1160.3	1165.0	1166.2	1165.0	1161.5
147.5°	1207.0	1212.8	1211.7	1210.5	1209.3
150°	1249.0	1253.6	1253.6	1253.6	1252.5
152.5°	1288.6	1291.0	1292.1	1295.6	1292.1
155°	1329.4	1329.4	1328.3	1332.9	1328.3
157.5°	1364.4	1362.1	1362.1	1365.6	1362.1
160°	1394.7	1393.6	1392.4	1395.9	1390.1
162.5°	1422.7	1419.2	1418.1	1425.1	1419.2
165°	1447.2	1443.7	1441.4	1448.4	1443.7
167.5°	1467.1	1462.4	1462.4	1469.4	1462.4
170°	1483.4	1477.5	1478.7	1485.7	1477.5
172.5°	1495.0	1490.4	1490.4	1498.5	1490.4
175°	1505.5	1499.7	1498.5	1506.7	1498.5
177.5°	1510.2	1504.4	1504.4	1512.5	1503.2
180°	1507.9	1507.9	1507.9	1507.9	1507.9

(END OF REPORT)