

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026503

Luminaire Tested: S124RDIP-B575D810UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026503
REPORT IS A COMBINATION OF REPORTS P999583 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D810UB27-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5036.0 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026503

CATALOG NUMBER: S124RDIP-B575D810UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026503

CATALOG NUMBER: S124RDIP-B575D810UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53
1	97	93	89	86	89	85	82	79	71	69	67	59	57	56	47	46	45
2	89	81	75	70	81	75	70	66	63	59	56	52	49	47	41	40	38
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33
4	74	64	56	50	68	59	52	47	50	44	40	41	37	34	33	31	28
5	68	57	49	43	62	53	46	40	44	39	35	37	33	30	30	27	25
6	63	51	43	37	58	47	40	35	40	35	31	33	29	26	27	24	22
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	20
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	31	26	46	36	29	24	30	25	22	26	22	19	21	18	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8181	8181	8181
5°	8182	7938	7938
10°	8112	7687	7595
15°	8000	7375	7191
20°	7854	7020	6730
25°	7672	6636	6280
30°	7493	6245	5774
35°	7298	5848	5280
40°	7064	5421	4772
45°	6845	4998	4269
50°	6596	4535	3759
55°	6327	4060	3232
60°	6028	3557	2711
65°	5739	2979	2210
70°	5330	2371	1689
75°	4804	1726	1181
80°	4014	1059	850
85°	3020	610	467

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6845 cd/sqm

TEST NUMBER: P1026503

CATALOG NUMBER: S124RDIP-B575D810UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.3	1.9
10°-20°	263.0	5.2
20°-30°	379.7	7.5
30°-40°	430.4	8.5
40°-50°	415.5	8.3
50°-60°	345.5	6.9
60°-70°	238.4	4.7
70°-80°	120.5	2.4
80°-90°	32.7	0.6
90°-100°	63.8	1.3
100°-110°	191.1	3.8
110°-120°	324.7	6.4
120°-130°	428.2	8.5
130°-140°	480.9	9.5
140°-150°	472.7	9.4
150°-160°	397.5	7.9
160°-170°	264.5	5.3
170°-180°	92.6	1.8
0°-30°	737.1	14.6
0°-40°	1167.5	23.2
0°-60°	1928.5	38.3
0°-90°	2320.1	46.1
90°-120°	579.5	11.5
90°-150°	1961.2	38.9
90°-180°	2716.0	53.9
0°-180°	5036.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1003	1003	1003	1003	1003	
5°	1002	999	989	997	996	95
15°	954	947	928	926	921	269
25°	863	849	817	804	797	397
35°	746	721	683	657	643	466
45°	608	580	534	496	482	469
55°	461	430	380	340	326	412
65°	313	280	231	198	189	309
75°	167	138	102	84	80	176
85°	42	26	24	22	22	46
90°	2	11	17	21	23	6
95°	45	52	58	60	60	49
105°	176	177	180	182	185	187
115°	330	330	328	328	327	326
125°	481	481	480	478	477	429
135°	620	624	624	623	621	480
145°	753	756	757	756	754	471
155°	863	863	862	865	862	397
165°	940	937	936	940	937	265
175°	977	974	973	978	973	93
180°	979	979	979	979	979	

TEST NUMBER: P1026503

CATALOG NUMBER: S124RDIP-B575D810UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1003.2	1003.2	1003.2	1003.2	1003.2
2.5°	1006.3	1003.2	994.8	1003.2	1002.4
5°	1001.7	998.6	989.4	997.1	995.5
7.5°	994.8	991.7	980.2	985.5	983.2
10°	984.0	980.2	966.3	969.4	966.3
12.5°	970.2	965.6	948.7	950.2	945.6
15°	954.0	947.1	927.9	926.4	921.0
17.5°	935.6	925.6	903.3	899.5	891.8
20°	913.3	903.3	877.2	871.1	861.1
22.5°	888.7	877.2	848.8	838.8	831.1
25°	862.6	848.8	817.3	804.2	796.6
27.5°	835.7	818.8	785.8	770.5	759.7
30°	807.3	788.1	752.0	732.8	720.5
32.5°	777.4	755.1	717.4	694.4	682.9
35°	745.9	721.3	682.9	656.8	642.9
37.5°	712.8	687.5	645.2	616.8	603.0
40°	677.5	652.2	608.4	576.1	562.3
42.5°	643.7	616.8	570.7	537.7	523.1
45°	608.4	580.0	533.9	496.2	482.4
47.5°	572.3	543.1	495.5	456.3	440.9
50°	535.4	505.4	456.3	417.9	403.3
52.5°	497.8	468.6	417.9	378.7	363.3
55°	460.9	430.2	380.2	340.3	325.7
57.5°	424.8	392.5	343.4	302.6	291.9
60°	385.6	354.9	305.7	265.8	253.5
62.5°	350.3	318.0	267.3	231.2	222.0
65°	313.4	280.4	231.2	198.2	189.0
67.5°	275.0	243.5	197.4	168.2	157.5
70°	238.9	206.6	162.8	137.5	129.8
72.5°	200.5	172.1	131.4	110.6	103.7
75°	166.7	138.3	102.2	84.5	79.9
77.5°	131.4	106.8	76.0	63.8	62.2
80°	97.6	75.3	52.2	49.9	49.2
82.5°	68.4	48.4	37.6	36.1	35.3
85°	41.5	26.1	23.8	22.3	22.3
87.5°	17.7	11.5	10.8	10.0	10.8
90°	2.3	10.6	16.7	21.2	22.7
92.5°	19.7	29.5	33.3	35.6	36.3
95°	45.4	52.2	57.5	59.8	59.8
97.5°	72.7	78.7	84.8	87.8	87.8
100°	106.0	109.0	115.8	117.3	117.3
102.5°	140.8	141.6	147.6	149.9	150.6
105°	176.4	177.1	180.2	182.4	184.7
107.5°	213.5	214.2	215.0	218.0	217.3
110°	251.3	252.8	252.1	250.6	252.8



TEST NUMBER: P1026503

CATALOG NUMBER: S124RDIP-B575D810UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	290.7	290.7	289.2	289.2	289.2
115°	330.1	330.1	328.5	327.8	327.0
117.5°	367.2	367.2	366.4	364.1	361.9
120°	404.3	407.3	405.0	401.2	402.7
122.5°	442.9	443.6	442.9	440.6	436.8
125°	480.7	480.7	480.0	478.4	476.9
127.5°	514.8	517.0	515.5	514.0	513.3
130°	551.1	553.4	553.4	551.9	548.8
132.5°	588.2	589.7	589.0	587.5	586.7
135°	620.0	624.5	624.5	623.0	620.8
137.5°	655.6	657.9	659.4	657.1	657.9
140°	691.2	692.7	692.7	691.9	691.2
142.5°	723.7	725.2	724.5	724.5	724.5
145°	753.2	756.3	757.0	756.3	754.0
147.5°	783.5	787.3	786.6	785.8	785.0
150°	810.8	813.8	813.8	813.8	813.0
152.5°	836.5	838.0	838.8	841.1	838.8
155°	863.0	863.0	862.3	865.3	862.3
157.5°	885.7	884.2	884.2	886.5	884.2
160°	905.4	904.6	903.9	906.2	902.4
162.5°	923.6	921.3	920.5	925.1	921.3
165°	939.5	937.2	935.7	940.2	937.2
167.5°	952.3	949.3	949.3	953.9	949.3
170°	962.9	959.2	959.9	964.5	959.2
172.5°	970.5	967.5	967.5	972.8	967.5
175°	977.3	973.5	972.8	978.1	972.8
177.5°	980.3	976.6	976.6	981.9	975.8
180°	978.8	978.8	978.8	978.8	978.8

(END OF REPORT)